

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035804

Luminaire Tested: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035804
REPORT IS A COMBINATION OF REPORTS P1006215 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10243.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035804
CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	49	48	47	41	41	41	41
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35	35	35	35
3	82	73	65	60	75	67	61	56	57	52	48	47	44	41	39	36	34	30	30	30	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26	26	26	26
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23
6	63	52	44	38	58	48	41	36	41	36	31	35	30	27	28	25	23	20	20	20	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18	18	18	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16	16	16	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15	15	15	15
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15	13	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12125	12125	12125	12125
5°	12115	13665	12115	10504
10°	12047	15357	12006	9080
15°	11917	16247	11834	7906
20°	11758	17539	11653	7146
25°	11553	19852	11422	6486
30°	11343	21101	11173	6013
35°	11072	17354	10916	5573
40°	10590	11785	10501	5177
45°	9958	8471	9944	4787
50°	9310	6514	9354	4427
55°	8580	5297	8564	4080
60°	7901	4342	7862	3623
65°	7110	3618	7154	2916
70°	6454	2904	6428	2428
75°	5452	2199	5452	1996
80°	4417	1342	4369	1342
85°	3110	705	3019	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°
 Vertical Angle: 45°
 Luminance: 17260 cd/sqm



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.5	1.8
10°-20°	532.1	5.2
20°-30°	843.6	8.2
30°-40°	1019.4	10.0
40°-50°	907.6	8.9
50°-60°	696.0	6.8
60°-70°	452.0	4.4
70°-80°	219.4	2.1
80°-90°	54.2	0.5
90°-100°	59.0	0.6
100°-110°	392.1	3.8
110°-120°	706.2	6.9
120°-130°	906.4	8.8
130°-140°	974.9	9.5
140°-150°	915.0	8.9
150°-160°	740.1	7.2
160°-170°	478.7	4.7
170°-180°	165.1	1.6
0°-30°	1557.1	15.2
0°-40°	2576.5	25.2
0°-60°	4180.0	40.8
0°-90°	4905.6	47.9
90°-120°	1157.3	11.3
90°-150°	3953.6	38.6
90°-180°	5337.0	52.1
0°-180°	10243.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1892	1892	1892	1892	1892	
5°	1888	2169	1888	1667	1888	179
15°	1809	2606	1796	1268	1809	510
25°	1653	3120	1634	1019	1653	762
35°	1440	2589	1420	831	1440	897
45°	1126	1158	1125	654	1126	869
55°	796	636	794	489	796	713
65°	494	360	497	291	494	494
75°	241	168	241	152	241	258
85°	54	36	53	40	54	62
90°	1	31	1	31	1	7
95°	73	27	73	27	73	90
105°	379	382	379	382	379	401
115°	711	706	711	706	711	705
125°	1011	1011	1011	1011	1011	903
135°	1261	1256	1261	1256	1261	972
145°	1462	1458	1462	1458	1462	914
155°	1610	1598	1610	1598	1610	742
165°	1699	1690	1699	1690	1699	480
175°	1738	1730	1738	1730	1738	165
180°	1738	1738	1738	1738	1738	



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1894.0	1909.6	1914.2	1926.7	1940.6	1943.7	1951.5	1962.4	1968.6	1967.1	1967.1
5°	1887.8	1914.2	1932.9	1954.6	1981.0	1991.9	2001.2	2024.5	2043.2	2054.1	2072.7
7.5°	1876.9	1915.8	1946.9	1979.5	2019.9	2038.5	2058.7	2091.4	2125.5	2147.3	2167.5
10°	1859.8	1909.6	1953.1	2001.2	2055.6	2083.6	2108.4	2158.2	2200.1	2228.1	2274.7
12.5°	1835.0	1897.1	1957.7	2021.4	2089.8	2119.3	2153.5	2207.9	2266.9	2307.3	2346.2
15°	1808.6	1883.1	1948.4	2024.5	2106.9	2151.9	2195.5	2252.9	2305.8	2350.8	2395.9
17.5°	1777.5	1856.7	1937.5	2024.5	2117.8	2162.8	2200.1	2268.5	2324.4	2369.5	2409.9
20°	1740.2	1828.8	1920.4	2016.8	2111.5	2153.5	2189.2	2263.8	2313.5	2361.7	2419.2
22.5°	1699.8	1796.1	1894.0	1988.8	2082.0	2127.1	2169.0	2234.3	2288.7	2353.9	2428.5
25°	1653.2	1758.8	1858.3	1953.1	2041.6	2083.6	2120.9	2192.3	2268.5	2350.8	2434.7
27.5°	1606.6	1709.1	1805.5	1892.5	1988.8	2027.6	2064.9	2155.1	2245.2	2332.2	2447.2
30°	1555.3	1659.4	1743.3	1824.1	1917.3	1957.7	2004.3	2106.9	2209.4	2327.5	2467.4
32.5°	1497.8	1592.6	1670.3	1754.2	1838.1	1887.8	1946.9	2058.7	2176.8	2318.2	2496.9
35°	1440.3	1516.5	1587.9	1667.2	1768.2	1821.0	1878.5	1996.6	2144.2	2313.5	2521.7
37.5°	1367.3	1440.3	1496.3	1577.1	1681.2	1743.3	1800.8	1937.5	2105.3	2302.7	2520.2
40°	1292.7	1354.9	1407.7	1491.6	1605.0	1662.5	1724.7	1873.8	2064.9	2271.6	2482.9
42.5°	1211.9	1264.8	1322.2	1403.0	1513.4	1569.3	1640.8	1814.8	2009.0	2228.1	2386.6
45°	1126.5	1177.7	1225.9	1309.8	1420.1	1480.7	1558.4	1737.1	1940.6	2136.4	2231.2
47.5°	1042.6	1087.6	1138.9	1211.9	1323.8	1390.6	1469.8	1661.0	1849.0	2013.7	2021.4
50°	961.8	997.5	1041.0	1115.6	1232.1	1295.8	1378.2	1556.9	1740.2	1853.6	1777.5
52.5°	877.9	910.5	955.6	1020.8	1129.6	1204.2	1275.6	1454.3	1608.1	1684.3	1544.4
55°	795.5	823.5	870.1	943.1	1037.9	1095.4	1168.4	1334.7	1469.8	1471.4	1319.1
57.5°	714.7	739.6	778.4	843.7	932.3	999.1	1065.9	1210.4	1302.0	1275.6	1106.3
60°	643.3	658.8	694.5	758.2	840.6	888.7	960.2	1081.4	1142.0	1093.8	912.1
62.5°	568.7	584.2	612.2	663.5	741.1	792.4	837.5	936.9	978.9	905.8	756.7
65°	494.1	512.7	532.9	573.3	646.4	680.5	720.9	794.0	834.4	748.9	619.9
67.5°	428.8	438.2	458.4	500.3	551.6	582.7	610.6	660.3	668.1	599.7	494.1
70°	368.2	371.3	390.0	414.9	453.7	472.3	495.6	525.2	525.2	469.2	385.3
72.5°	299.9	304.5	318.5	344.9	368.2	377.6	385.3	404.0	400.9	349.6	292.1
75°	240.8	243.9	254.8	267.2	276.6	293.7	299.9	296.8	295.2	251.7	219.1
77.5°	186.5	188.0	195.8	206.6	208.2	214.4	209.8	209.8	195.8	170.9	153.8
80°	136.7	138.3	141.4	144.5	144.5	144.5	144.5	136.7	127.4	111.9	107.2
82.5°	91.7	91.7	93.2	96.3	94.8	91.7	88.6	80.8	74.6	69.9	66.8
85°	54.4	54.4	55.9	54.4	48.2	46.6	43.5	42.0	40.4	38.8	38.8
87.5°	26.4	24.9	21.8	18.6	18.6	18.6	18.6	18.6	18.6	17.1	17.1
90°	1.3	3.6	5.9	8.2	10.5	11.6	12.6	14.6	16.6	18.6	20.6
92.5°	24.5	21.9	19.3	16.8	14.2	12.9	13.8	15.5	17.2	18.9	20.6
95°	73.4	72.6	71.7	70.9	70.0	69.6	64.2	53.3	42.4	31.5	20.6
97.5°	137.8	139.5	141.2	142.9	144.6	145.5	131.9	104.7	77.6	50.4	23.2
100°	215.1	216.0	216.8	217.7	218.6	219.0	219.6	220.7	221.8	223.0	224.1
102.5°	293.7	294.8	296.0	297.1	298.2	298.8	299.1	299.7	300.2	300.8	301.4
105°	378.7	379.8	381.0	382.1	383.2	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	466.3	466.3	466.3	466.3	466.3	466.3	466.6	467.1	467.7	468.2	468.8
110°	551.3	551.3	551.3	551.3	551.3	551.3	551.6	552.2	552.7	553.3	553.9



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	631.1	632.0	632.8	633.7	634.6	635.0	635.1	635.4	635.7	636.0	636.3
115°	711.0	712.4	713.8	715.3	716.7	717.4	717.5	717.8	718.1	718.4	718.7
117.5°	794.7	794.7	794.7	794.7	794.7	794.7	795.3	796.4	797.6	798.7	799.9
120°	872.0	871.7	871.4	871.1	870.8	870.7	871.1	872.0	872.9	873.7	874.6
122.5°	940.3	941.7	943.1	944.6	946.0	946.7	946.8	947.1	947.4	947.7	948.0
125°	1011.1	1013.1	1015.1	1017.1	1019.1	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1
127.5°	1079.4	1080.8	1082.2	1083.7	1085.1	1085.8	1085.7	1085.4	1085.1	1084.8	1084.5
130°	1141.2	1142.6	1144.0	1145.5	1146.9	1147.6	1147.7	1148.0	1148.3	1148.6	1148.9
132.5°	1203.0	1204.7	1206.5	1208.2	1209.9	1210.8	1210.4	1209.5	1208.6	1207.8	1206.9
135°	1261.0	1262.7	1264.4	1266.1	1267.8	1268.7	1268.4	1267.8	1267.3	1266.7	1266.1
137.5°	1315.1	1316.8	1318.5	1320.2	1321.9	1322.8	1322.5	1321.9	1321.4	1320.8	1320.2
140°	1367.9	1368.5	1369.1	1369.6	1370.2	1370.5	1370.4	1370.1	1369.8	1369.5	1369.2
142.5°	1415.6	1415.9	1416.1	1416.4	1416.7	1416.8	1417.1	1417.7	1418.2	1418.8	1419.4
145°	1461.9	1462.5	1463.1	1463.6	1464.2	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5
147.5°	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.2	1503.5	1503.8	1504.1	1504.4
150°	1541.8	1541.2	1540.6	1540.1	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8
152.5°	1579.1	1577.7	1576.3	1574.8	1573.4	1572.7	1573.0	1573.6	1574.1	1574.7	1575.3
155°	1610.0	1608.3	1606.6	1604.9	1603.2	1602.3	1602.6	1603.2	1603.7	1604.3	1604.9
157.5°	1634.5	1633.7	1632.8	1632.0	1631.1	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7
160°	1660.3	1658.6	1656.9	1655.2	1653.5	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8
162.5°	1680.9	1679.2	1677.5	1675.8	1674.1	1673.2	1673.3	1673.6	1673.9	1674.1	1674.4
165°	1698.9	1697.2	1695.5	1693.8	1692.1	1691.2	1691.3	1691.6	1691.9	1692.2	1692.5
167.5°	1713.1	1711.4	1709.7	1708.0	1706.3	1705.4	1705.5	1705.8	1706.1	1706.3	1706.6
170°	1724.7	1722.7	1720.7	1718.7	1716.7	1715.7	1715.8	1716.1	1716.4	1716.7	1717.0
172.5°	1732.4	1730.4	1728.4	1726.4	1724.4	1723.4	1723.7	1724.3	1724.8	1725.4	1726.0
175°	1737.6	1735.9	1734.1	1732.4	1730.7	1729.8	1729.9	1730.2	1730.5	1730.8	1731.1
177.5°	1741.4	1739.7	1738.0	1736.3	1734.6	1733.7	1733.8	1734.1	1734.4	1734.7	1735.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1974.8	1985.7	1995.0	1990.4	2009.0	2007.4	2010.6	2016.8	2018.3	2015.2	2009.0
5°	2082.0	2097.6	2124.0	2138.0	2134.9	2147.3	2153.5	2162.8	2172.1	2169.0	2169.0
7.5°	2201.7	2223.4	2249.8	2285.6	2290.2	2301.1	2319.8	2319.8	2330.6	2326.0	2324.4
10°	2305.8	2332.2	2374.1	2402.1	2414.5	2420.7	2439.4	2445.6	2458.0	2459.6	2459.6
12.5°	2391.2	2437.8	2465.8	2493.8	2500.0	2509.3	2523.3	2532.6	2537.3	2537.3	2532.6
15°	2436.3	2473.6	2506.2	2535.7	2552.8	2560.6	2574.6	2585.4	2591.7	2605.6	2608.7
17.5°	2454.9	2500.0	2552.8	2594.8	2624.3	2632.1	2660.0	2669.3	2681.8	2688.0	2695.8
20°	2481.3	2546.6	2610.3	2661.6	2689.5	2709.7	2739.3	2782.8	2795.2	2795.2	2790.5
22.5°	2504.6	2588.6	2675.6	2757.9	2781.2	2821.6	2876.0	2922.6	2941.3	2949.0	2942.8
25°	2532.6	2647.6	2761.0	2863.6	2927.3	2956.8	3029.8	3085.8	3107.5	3119.9	3123.0
27.5°	2580.8	2725.3	2869.8	3000.3	3065.6	3099.7	3175.9	3224.0	3250.4	3261.3	3253.6
30°	2635.2	2812.3	2980.1	3096.6	3140.1	3182.1	3231.8	3250.4	3244.2	3244.2	3267.5
32.5°	2691.1	2874.4	3023.6	3099.7	3115.3	3109.1	3088.9	3032.9	3000.3	3000.3	3020.5
35°	2722.2	2880.7	2956.8	2931.9	2871.3	2835.6	2725.3	2663.1	2593.2	2588.6	2611.9
37.5°	2705.1	2773.4	2742.4	2579.2	2496.9	2428.5	2256.0	2187.7	2136.4	2064.9	2175.3
40°	2585.4	2562.1	2400.5	2165.9	2074.3	1977.9	1841.2	1772.8	1701.4	1690.5	1716.9
42.5°	2383.5	2245.2	2009.0	1782.2	1688.9	1620.6	1516.5	1449.7	1404.6	1385.9	1417.0
45°	2131.7	1914.2	1678.1	1497.8	1395.3	1359.5	1264.8	1205.7	1171.5	1157.5	1179.3
47.5°	1824.1	1605.0	1381.3	1229.0	1168.4	1132.7	1069.0	1017.7	988.2	978.9	988.2
50°	1549.1	1323.8	1135.8	1037.9	983.5	954.0	901.2	868.5	845.2	839.0	854.6
52.5°	1311.4	1106.3	963.3	876.3	840.6	815.7	778.4	750.5	736.5	730.3	741.1
55°	1098.5	932.3	817.3	742.7	716.3	700.7	668.1	652.6	637.0	635.5	646.4
57.5°	910.5	795.5	689.9	637.0	629.3	606.0	578.0	564.0	556.2	554.7	559.4
60°	758.2	655.7	592.0	545.4	534.5	515.8	500.3	491.0	481.7	478.6	481.7
62.5°	630.8	550.0	498.8	467.7	452.1	447.5	430.4	419.5	418.0	418.0	421.1
65°	520.5	452.1	419.5	394.7	383.8	379.1	366.7	358.9	360.5	360.5	362.0
67.5°	424.2	374.5	344.9	332.5	323.2	321.6	309.2	306.1	303.0	303.0	306.1
70°	337.2	306.1	284.3	278.1	276.6	265.7	261.0	259.5	254.8	256.4	256.4
72.5°	264.1	243.9	231.5	222.2	223.7	217.5	211.3	211.3	208.2	212.9	212.9
75°	195.8	186.5	177.1	174.0	177.1	174.0	169.4	167.8	169.4	167.8	167.8
77.5°	144.5	139.8	136.7	135.2	135.2	129.0	125.9	129.0	122.7	125.9	125.9
80°	101.0	94.8	93.2	90.1	91.7	87.0	88.6	85.5	85.5	85.5	85.5
82.5°	63.7	62.2	62.2	62.2	60.6	60.6	60.6	60.6	60.6	60.6	59.0
85°	38.8	37.3	37.3	37.3	35.7	35.7	35.7	35.7	35.7	35.7	35.7
87.5°	15.5	17.1	17.1	18.6	17.1	15.5	15.5	15.5	17.1	17.1	15.5
90°	22.0	23.4	24.9	26.3	27.0	27.4	28.3	29.2	30.0	30.9	30.0
92.5°	22.0	23.4	24.9	26.3	27.0	27.1	27.4	27.7	28.0	28.3	28.0
95°	22.0	23.4	24.9	26.3	27.0	27.0	27.0	27.0	27.0	27.0	27.0
97.5°	23.8	24.4	24.9	25.5	25.8	25.9	26.2	26.5	26.7	27.0	26.7
100°	181.5	138.8	96.2	53.5	32.2	31.6	30.5	29.3	28.2	27.0	28.2
102.5°	302.0	302.6	303.1	303.7	304.0	292.0	267.9	243.9	219.8	195.8	219.8
105°	383.8	383.8	383.8	383.8	383.8	383.7	383.4	383.1	382.8	382.5	382.8
107.5°	469.1	469.4	469.7	470.0	470.1	469.5	468.4	467.3	466.1	465.0	466.1
110°	553.0	552.2	551.3	550.4	550.0	550.1	550.4	550.7	551.0	551.3	551.0



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	635.1	634.0	632.8	631.7	631.1	630.8	630.3	629.7	629.2	628.6	629.2
115°	717.6	716.4	715.3	714.2	713.6	712.7	711.0	709.3	707.5	705.8	707.5
117.5°	798.2	796.4	794.7	793.0	792.1	791.8	791.3	790.7	790.2	789.6	790.2
120°	874.0	873.4	872.9	872.3	872.0	871.3	869.9	868.4	867.0	865.6	867.0
122.5°	947.4	946.8	946.3	945.7	945.4	944.5	942.8	941.1	939.4	937.7	939.4
125°	1019.0	1017.8	1016.7	1015.6	1015.0	1014.6	1013.7	1012.8	1012.0	1011.1	1012.0
127.5°	1083.9	1083.4	1082.8	1082.3	1082.0	1080.8	1078.5	1076.2	1073.9	1071.6	1073.9
130°	1148.1	1147.2	1146.4	1145.5	1145.1	1144.4	1142.9	1141.5	1140.0	1138.6	1140.0
132.5°	1206.9	1206.9	1206.9	1206.9	1206.9	1206.2	1204.8	1203.3	1201.9	1200.5	1201.9
135°	1265.5	1265.0	1264.4	1263.9	1263.6	1262.7	1261.0	1259.3	1257.5	1255.8	1257.5
137.5°	1320.2	1320.2	1320.2	1320.2	1320.2	1319.5	1318.1	1316.6	1315.2	1313.8	1315.2
140°	1369.8	1370.4	1370.9	1371.5	1371.8	1370.9	1369.2	1367.5	1365.7	1364.0	1365.7
142.5°	1419.4	1419.4	1419.4	1419.4	1419.4	1418.5	1416.8	1415.1	1413.4	1411.7	1413.4
145°	1464.8	1465.1	1465.4	1465.7	1465.8	1464.9	1463.2	1461.5	1459.8	1458.1	1459.8
147.5°	1504.7	1505.0	1505.3	1505.6	1505.7	1504.7	1502.7	1500.7	1498.7	1496.7	1498.7
150°	1542.4	1543.0	1543.5	1544.1	1544.4	1543.3	1541.0	1538.7	1536.4	1534.1	1536.4
152.5°	1575.9	1576.4	1577.0	1577.5	1577.8	1576.8	1574.8	1572.8	1570.8	1568.8	1570.8
155°	1605.8	1606.6	1607.5	1608.4	1608.8	1607.7	1605.4	1603.1	1600.8	1598.5	1600.8
157.5°	1631.5	1632.4	1633.2	1634.1	1634.5	1633.4	1631.1	1628.8	1626.5	1624.2	1626.5
160°	1655.0	1656.1	1657.3	1658.4	1659.0	1657.9	1655.6	1653.3	1651.0	1648.7	1651.0
162.5°	1676.1	1677.9	1679.6	1681.3	1682.2	1680.9	1678.3	1675.8	1673.2	1670.6	1673.2
165°	1694.2	1695.9	1697.6	1699.3	1700.2	1699.1	1696.8	1694.5	1692.2	1689.9	1692.2
167.5°	1708.6	1710.6	1712.7	1714.7	1715.7	1714.4	1711.8	1709.3	1706.7	1704.1	1706.7
170°	1719.3	1721.6	1723.9	1726.2	1727.3	1726.0	1723.4	1720.9	1718.3	1715.7	1718.3
172.5°	1728.0	1730.0	1732.0	1734.0	1735.0	1733.7	1731.1	1728.6	1726.0	1723.4	1726.0
175°	1733.4	1735.7	1738.0	1740.3	1741.4	1740.1	1737.5	1735.0	1732.4	1729.8	1732.4
177.5°	1737.0	1739.0	1741.0	1743.0	1744.0	1742.9	1740.6	1738.3	1736.0	1733.7	1736.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	2016.8	2005.9	2010.6	2005.9	2001.2	1996.6	1985.7	1970.2	1957.7	1948.4	1946.9
5°	2172.1	2158.2	2148.8	2144.2	2134.9	2122.4	2102.2	2078.9	2051.0	2040.1	2018.3
7.5°	2315.1	2310.4	2288.7	2285.6	2279.4	2256.0	2221.9	2190.8	2155.1	2125.5	2097.6
10°	2450.3	2439.4	2423.9	2402.1	2399.0	2369.5	2336.8	2293.3	2246.7	2218.8	2169.0
12.5°	2534.2	2521.7	2504.6	2490.7	2482.9	2464.3	2419.2	2375.7	2333.7	2282.5	2239.0
15°	2594.8	2579.2	2548.2	2537.3	2528.0	2503.1	2470.5	2425.4	2369.5	2333.7	2271.6
17.5°	2677.1	2658.5	2627.4	2607.2	2590.1	2551.3	2504.6	2444.1	2391.2	2350.8	2294.9
20°	2771.9	2743.9	2703.5	2677.1	2652.3	2607.2	2541.9	2470.5	2394.3	2344.6	2287.1
22.5°	2928.8	2876.0	2812.3	2775.0	2740.8	2663.1	2585.4	2496.9	2411.4	2336.8	2266.9
25°	3081.1	3028.3	2949.0	2897.7	2844.9	2754.8	2652.3	2529.5	2420.7	2333.7	2242.1
27.5°	3222.5	3168.1	3095.1	3032.9	2981.7	2846.5	2711.3	2573.0	2434.7	2315.1	2221.9
30°	3255.1	3231.8	3175.9	3121.5	3074.9	2950.6	2793.6	2618.1	2451.8	2298.0	2193.9
32.5°	3057.8	3115.3	3129.3	3121.5	3092.0	3003.4	2858.9	2674.0	2476.7	2290.2	2147.3
35°	2647.6	2751.7	2858.9	2916.4	2944.4	2956.8	2871.3	2702.0	2493.8	2277.8	2116.2
37.5°	2195.5	2296.4	2465.8	2551.3	2646.0	2770.3	2804.5	2695.8	2486.0	2268.5	2066.5
40°	1803.9	1932.9	2072.7	2150.4	2232.7	2456.5	2625.8	2613.4	2461.1	2234.3	2027.6
42.5°	1468.3	1549.1	1671.8	1757.3	1858.3	2108.4	2335.3	2447.2	2386.6	2192.3	1977.9
45°	1224.4	1286.5	1373.5	1460.5	1522.7	1749.5	2018.3	2201.7	2259.2	2117.8	1901.8
47.5°	1031.7	1078.3	1154.4	1208.8	1275.6	1454.3	1687.4	1945.3	2066.5	2012.1	1821.0
50°	884.1	921.4	982.0	1016.2	1075.2	1229.0	1406.1	1676.5	1859.8	1866.1	1713.8
52.5°	755.1	792.4	843.7	873.2	908.9	1013.0	1191.7	1420.1	1631.4	1709.1	1591.0
55°	657.2	679.0	720.9	744.2	776.9	877.9	991.3	1185.5	1406.1	1533.6	1459.0
57.5°	567.1	590.4	616.8	635.5	658.8	739.6	842.1	988.2	1207.3	1345.5	1320.7
60°	494.1	508.1	532.9	546.9	568.7	621.5	693.0	839.0	1013.0	1143.6	1157.5
62.5°	425.7	438.2	455.2	467.7	481.7	523.6	576.4	680.5	832.8	974.2	992.8
65°	366.7	377.6	386.9	397.8	408.6	435.1	480.1	560.9	679.0	811.1	851.5
67.5°	313.9	317.0	330.9	332.5	338.7	358.9	391.5	456.8	542.3	647.9	700.7
70°	262.6	268.8	271.9	276.6	282.8	296.8	323.2	357.4	421.1	506.5	556.2
72.5°	212.9	214.4	219.1	222.2	228.4	239.3	251.7	278.1	318.5	380.7	425.7
75°	169.4	170.9	174.0	175.6	180.2	183.3	189.6	208.2	236.2	273.5	306.1
77.5°	127.4	130.5	133.6	133.6	135.2	138.3	141.4	147.6	161.6	186.5	214.4
80°	87.0	88.6	88.6	90.1	88.6	93.2	97.9	105.7	111.9	119.6	133.6
82.5°	60.6	60.6	60.6	62.2	62.2	63.7	63.7	65.3	66.8	71.5	77.7
85°	37.3	37.3	38.8	35.7	37.3	38.8	38.8	37.3	38.8	40.4	42.0
87.5°	15.5	15.5	17.1	17.1	17.1	17.1	15.5	17.1	15.5	17.1	17.1
90°	29.2	28.3	27.4	27.0	26.3	24.9	23.4	22.0	20.6	18.6	16.6
92.5°	27.7	27.4	27.1	27.0	26.3	24.9	23.4	22.0	20.6	18.9	17.2
95°	27.0	27.0	27.0	27.0	26.3	24.9	23.4	22.0	20.6	31.5	42.4
97.5°	26.5	26.2	25.9	25.8	25.5	24.9	24.4	23.8	23.2	50.4	77.6
100°	29.3	30.5	31.6	32.2	53.5	96.2	138.8	181.5	224.1	223.0	221.8
102.5°	243.9	267.9	292.0	304.0	303.7	303.1	302.6	302.0	301.4	300.8	300.2
105°	383.1	383.4	383.7	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	467.3	468.4	469.5	470.1	470.0	469.7	469.4	469.1	468.8	468.2	467.7
110°	550.7	550.4	550.1	550.0	550.4	551.3	552.2	553.0	553.9	553.3	552.7



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	629.7	630.3	630.8	631.1	631.7	632.8	634.0	635.1	636.3	636.0	635.7
115°	709.3	711.0	712.7	713.6	714.2	715.3	716.4	717.6	718.7	718.4	718.1
117.5°	790.7	791.3	791.8	792.1	793.0	794.7	796.4	798.2	799.9	798.7	797.6
120°	868.4	869.9	871.3	872.0	872.3	872.9	873.4	874.0	874.6	873.7	872.9
122.5°	941.1	942.8	944.5	945.4	945.7	946.3	946.8	947.4	948.0	947.7	947.4
125°	1012.8	1013.7	1014.6	1015.0	1015.6	1016.7	1017.8	1019.0	1020.1	1020.1	1020.1
127.5°	1076.2	1078.5	1080.8	1082.0	1082.3	1082.8	1083.4	1083.9	1084.5	1084.8	1085.1
130°	1141.5	1142.9	1144.4	1145.1	1145.5	1146.4	1147.2	1148.1	1148.9	1148.6	1148.3
132.5°	1203.3	1204.8	1206.2	1206.9	1206.9	1206.9	1206.9	1206.9	1206.9	1207.8	1208.6
135°	1259.3	1261.0	1262.7	1263.6	1263.9	1264.4	1265.0	1265.5	1266.1	1266.7	1267.3
137.5°	1316.6	1318.1	1319.5	1320.2	1320.2	1320.2	1320.2	1320.2	1320.2	1320.8	1321.4
140°	1367.5	1369.2	1370.9	1371.8	1371.5	1370.9	1370.4	1369.8	1369.2	1369.5	1369.8
142.5°	1415.1	1416.8	1418.5	1419.4	1419.4	1419.4	1419.4	1419.4	1419.4	1418.8	1418.2
145°	1461.5	1463.2	1464.9	1465.8	1465.7	1465.4	1465.1	1464.8	1464.5	1464.5	1464.5
147.5°	1500.7	1502.7	1504.7	1505.7	1505.6	1505.3	1505.0	1504.7	1504.4	1504.1	1503.8
150°	1538.7	1541.0	1543.3	1544.4	1544.1	1543.5	1543.0	1542.4	1541.8	1541.2	1540.6
152.5°	1572.8	1574.8	1576.8	1577.8	1577.5	1577.0	1576.4	1575.9	1575.3	1574.7	1574.1
155°	1603.1	1605.4	1607.7	1608.8	1608.4	1607.5	1606.6	1605.8	1604.9	1604.3	1603.7
157.5°	1628.8	1631.1	1633.4	1634.5	1634.1	1633.2	1632.4	1631.5	1630.7	1630.7	1630.7
160°	1653.3	1655.6	1657.9	1659.0	1658.4	1657.3	1656.1	1655.0	1653.8	1653.5	1653.3
162.5°	1675.8	1678.3	1680.9	1682.2	1681.3	1679.6	1677.9	1676.1	1674.4	1674.1	1673.9
165°	1694.5	1696.8	1699.1	1700.2	1699.3	1697.6	1695.9	1694.2	1692.5	1692.2	1691.9
167.5°	1709.3	1711.8	1714.4	1715.7	1714.7	1712.7	1710.6	1708.6	1706.6	1706.3	1706.1
170°	1720.9	1723.4	1726.0	1727.3	1726.2	1723.9	1721.6	1719.3	1717.0	1716.7	1716.4
172.5°	1728.6	1731.1	1733.7	1735.0	1734.0	1732.0	1730.0	1728.0	1726.0	1725.4	1724.8
175°	1735.0	1737.5	1740.1	1741.4	1740.3	1738.0	1735.7	1733.4	1731.1	1730.8	1730.5
177.5°	1738.3	1740.6	1742.9	1744.0	1743.0	1741.0	1739.0	1737.0	1735.0	1734.7	1734.4
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1942.2	1932.9	1926.7	1925.1	1915.8	1908.0	1898.7	1897.1	1892.5	1880.0	1872.3
5°	2002.8	1981.0	1976.4	1962.4	1939.1	1922.0	1900.2	1887.8	1873.8	1850.5	1831.9
7.5°	2064.9	2035.4	2013.7	1993.5	1960.8	1929.8	1898.7	1873.8	1849.0	1814.8	1786.8
10°	2125.5	2080.5	2054.1	2024.5	1979.5	1932.9	1889.4	1853.6	1813.2	1772.8	1732.4
12.5°	2181.5	2124.0	2085.1	2043.2	1987.2	1929.8	1873.8	1824.1	1782.2	1727.8	1682.7
15°	2215.7	2151.9	2113.1	2072.7	1988.8	1925.1	1859.8	1796.1	1740.2	1682.7	1640.8
17.5°	2235.8	2164.4	2120.9	2083.6	1998.1	1911.1	1827.2	1758.8	1698.3	1629.9	1574.0
20°	2226.5	2156.6	2116.2	2080.5	1981.0	1894.0	1803.9	1724.7	1648.5	1578.6	1519.6
22.5°	2206.3	2133.3	2088.2	2055.6	1967.1	1864.5	1765.1	1679.6	1600.4	1530.4	1463.6
25°	2162.8	2091.4	2052.5	2012.1	1925.1	1827.2	1726.2	1634.5	1550.6	1476.1	1401.5
27.5°	2124.0	2037.0	1996.6	1960.8	1869.2	1782.2	1682.7	1581.7	1496.3	1418.6	1344.0
30°	2078.9	1981.0	1937.5	1889.4	1807.0	1724.7	1625.2	1532.0	1443.4	1361.1	1289.6
32.5°	2030.8	1917.3	1867.6	1813.2	1729.3	1651.6	1567.7	1476.1	1387.5	1306.7	1232.1
35°	1968.6	1847.4	1789.9	1738.6	1651.6	1574.0	1496.3	1420.1	1331.6	1246.1	1174.6
37.5°	1909.6	1775.9	1715.3	1656.3	1564.6	1490.0	1426.3	1354.9	1269.4	1187.1	1118.7
40°	1842.7	1688.9	1626.8	1572.4	1477.6	1395.3	1337.8	1281.8	1207.3	1128.0	1053.4
42.5°	1782.2	1608.1	1542.9	1486.9	1387.5	1309.8	1255.4	1208.8	1143.6	1070.5	994.4
45°	1698.3	1521.1	1454.3	1395.3	1294.3	1221.2	1165.3	1124.9	1073.6	1005.3	936.9
47.5°	1620.6	1437.2	1364.2	1292.7	1201.1	1126.5	1075.2	1044.1	1009.9	949.3	879.4
50°	1525.8	1340.9	1266.3	1207.3	1103.2	1039.5	988.2	966.4	935.4	877.9	821.9
52.5°	1423.2	1247.7	1177.7	1106.3	1009.9	947.8	902.7	877.9	853.0	811.1	758.2
55°	1303.6	1143.6	1078.3	1014.6	918.3	860.8	820.4	794.0	780.0	741.1	702.3
57.5°	1188.6	1037.9	977.3	918.3	834.4	769.1	742.7	719.4	699.2	671.2	638.6
60°	1072.1	935.4	870.1	817.3	744.2	685.2	663.5	640.1	624.6	602.9	579.5
62.5°	938.5	821.9	772.2	722.5	660.3	613.7	588.9	570.2	550.0	536.0	515.8
65°	797.1	714.7	666.6	629.3	570.2	528.3	509.6	497.2	480.1	466.1	450.6
67.5°	665.0	599.7	579.5	539.2	494.1	456.8	442.8	427.3	413.3	405.5	391.5
70°	537.6	491.0	470.8	459.9	410.2	385.3	372.9	366.7	349.6	341.8	332.5
72.5°	416.4	399.3	385.3	371.3	338.7	323.2	309.2	303.0	290.6	284.3	281.2
75°	307.6	296.8	289.0	287.4	273.5	257.9	243.9	240.8	231.5	225.3	222.2
77.5°	216.0	212.9	211.3	212.9	203.5	194.2	191.1	188.0	177.1	175.6	175.6
80°	141.4	149.2	149.2	147.6	144.5	142.9	138.3	135.2	129.0	127.4	129.0
82.5°	87.0	91.7	93.2	96.3	94.8	93.2	90.1	88.6	90.1	87.0	88.6
85°	43.5	46.6	52.8	52.8	54.4	54.4	54.4	52.8	49.7	51.3	49.7
87.5°	17.1	18.6	18.6	18.6	17.1	21.8	23.3	23.3	23.3	20.2	20.2
90°	14.6	12.6	11.6	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	15.5	13.8	12.9	14.2	16.8	19.3	21.9	24.5	21.9	19.3	16.8
95°	53.3	64.2	69.6	70.0	70.9	71.7	72.6	73.4	72.6	71.7	70.9
97.5°	104.7	131.9	145.5	144.6	142.9	141.2	139.5	137.8	139.5	141.2	142.9
100°	220.7	219.6	219.0	218.6	217.7	216.8	216.0	215.1	216.0	216.8	217.7
102.5°	299.7	299.1	298.8	298.2	297.1	296.0	294.8	293.7	294.8	296.0	297.1
105°	383.8	383.8	383.8	383.2	382.1	381.0	379.8	378.7	379.8	381.0	382.1
107.5°	467.1	466.6	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3	466.3
110°	552.2	551.6	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	635.4	635.1	635.0	634.6	633.7	632.8	632.0	631.1	632.0	632.8	633.7
115°	717.8	717.5	717.4	716.7	715.3	713.8	712.4	711.0	712.4	713.8	715.3
117.5°	796.4	795.3	794.7	794.7	794.7	794.7	794.7	794.7	794.7	794.7	794.7
120°	872.0	871.1	870.7	870.8	871.1	871.4	871.7	872.0	871.7	871.4	871.1
122.5°	947.1	946.8	946.7	946.0	944.6	943.1	941.7	940.3	941.7	943.1	944.6
125°	1020.1	1020.1	1020.1	1019.1	1017.1	1015.1	1013.1	1011.1	1013.1	1015.1	1017.1
127.5°	1085.4	1085.7	1085.8	1085.1	1083.7	1082.2	1080.8	1079.4	1080.8	1082.2	1083.7
130°	1148.0	1147.7	1147.6	1146.9	1145.5	1144.0	1142.6	1141.2	1142.6	1144.0	1145.5
132.5°	1209.5	1210.4	1210.8	1209.9	1208.2	1206.5	1204.7	1203.0	1204.7	1206.5	1208.2
135°	1267.8	1268.4	1268.7	1267.8	1266.1	1264.4	1262.7	1261.0	1262.7	1264.4	1266.1
137.5°	1321.9	1322.5	1322.8	1321.9	1320.2	1318.5	1316.8	1315.1	1316.8	1318.5	1320.2
140°	1370.1	1370.4	1370.5	1370.2	1369.6	1369.1	1368.5	1367.9	1368.5	1369.1	1369.6
142.5°	1417.7	1417.1	1416.8	1416.7	1416.4	1416.1	1415.9	1415.6	1415.9	1416.1	1416.4
145°	1464.5	1464.5	1464.5	1464.2	1463.6	1463.1	1462.5	1461.9	1462.5	1463.1	1463.6
147.5°	1503.5	1503.2	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1	1503.1
150°	1540.1	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8	1541.2	1540.6	1540.1
152.5°	1573.6	1573.0	1572.7	1573.4	1574.8	1576.3	1577.7	1579.1	1577.7	1576.3	1574.8
155°	1603.2	1602.6	1602.3	1603.2	1604.9	1606.6	1608.3	1610.0	1608.3	1606.6	1604.9
157.5°	1630.7	1630.7	1630.7	1631.1	1632.0	1632.8	1633.7	1634.5	1633.7	1632.8	1632.0
160°	1653.0	1652.7	1652.6	1653.5	1655.2	1656.9	1658.6	1660.3	1658.6	1656.9	1655.2
162.5°	1673.6	1673.3	1673.2	1674.1	1675.8	1677.5	1679.2	1680.9	1679.2	1677.5	1675.8
165°	1691.6	1691.3	1691.2	1692.1	1693.8	1695.5	1697.2	1698.9	1697.2	1695.5	1693.8
167.5°	1705.8	1705.5	1705.4	1706.3	1708.0	1709.7	1711.4	1713.1	1711.4	1709.7	1708.0
170°	1716.1	1715.8	1715.7	1716.7	1718.7	1720.7	1722.7	1724.7	1722.7	1720.7	1718.7
172.5°	1724.3	1723.7	1723.4	1724.4	1726.4	1728.4	1730.4	1732.4	1730.4	1728.4	1726.4
175°	1730.2	1729.9	1729.8	1730.7	1732.4	1734.1	1735.9	1737.6	1735.9	1734.1	1732.4
177.5°	1734.1	1733.8	1733.7	1734.6	1736.3	1738.0	1739.7	1741.4	1739.7	1738.0	1736.3
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1867.6	1861.4	1856.7	1852.1	1831.9	1810.1	1807.0	1802.4	1793.0	1803.9	1799.2
5°	1819.4	1805.5	1797.7	1777.5	1752.6	1734.0	1718.4	1699.8	1692.0	1685.8	1684.3
7.5°	1760.4	1748.0	1734.0	1713.8	1682.7	1651.6	1628.3	1609.7	1594.1	1586.4	1586.4
10°	1702.9	1687.4	1668.7	1634.5	1605.0	1566.2	1541.3	1522.7	1500.9	1488.5	1477.6
12.5°	1643.9	1626.8	1609.7	1566.2	1532.0	1491.6	1455.9	1432.6	1421.7	1407.7	1389.1
15°	1584.8	1558.4	1541.3	1497.8	1454.3	1413.9	1390.6	1365.7	1340.9	1326.9	1320.7
17.5°	1522.7	1504.0	1476.1	1429.5	1381.3	1345.5	1311.4	1288.1	1258.5	1244.6	1230.6
20°	1466.7	1438.8	1410.8	1364.2	1317.6	1269.4	1235.2	1207.3	1188.6	1177.7	1165.3
22.5°	1399.9	1373.5	1350.2	1300.5	1249.2	1204.2	1166.9	1149.8	1131.1	1114.0	1101.6
25°	1342.4	1316.0	1292.7	1238.3	1182.4	1140.5	1112.5	1090.7	1070.5	1062.8	1050.3
27.5°	1281.8	1257.0	1225.9	1171.5	1121.8	1086.1	1056.6	1036.4	1020.8	1005.3	996.0
30°	1224.4	1196.4	1168.4	1109.4	1069.0	1033.2	1005.3	980.4	968.0	960.2	944.7
32.5°	1168.4	1132.7	1109.4	1055.0	1016.2	982.0	958.7	936.9	921.4	907.4	895.0
35°	1107.8	1069.0	1045.7	1000.6	960.2	926.0	905.8	890.3	871.7	859.2	853.0
37.5°	1050.3	1017.7	994.4	947.8	907.4	879.4	857.7	837.5	829.7	812.6	809.5
40°	988.2	960.2	938.5	893.4	856.1	834.4	811.1	792.4	778.4	770.7	759.8
42.5°	932.3	908.9	885.6	843.7	808.0	781.5	764.4	747.4	734.9	722.5	714.7
45°	881.0	856.1	834.4	794.0	758.2	734.9	717.8	697.6	694.5	677.4	669.7
47.5°	826.6	804.8	786.2	744.2	711.6	688.3	668.1	654.1	640.1	633.9	623.1
50°	773.8	752.0	730.3	693.0	663.5	640.1	619.9	604.4	596.6	587.3	578.0
52.5°	716.3	699.2	682.1	643.3	613.7	593.5	576.4	556.2	548.5	540.7	534.5
55°	668.1	643.3	624.6	592.0	565.6	543.8	525.2	509.6	501.9	495.6	487.9
57.5°	602.9	587.3	571.8	542.3	517.4	495.6	477.0	464.6	455.2	450.6	452.1
60°	546.9	529.8	520.5	489.4	464.6	447.5	430.4	418.0	408.6	404.0	402.4
62.5°	487.9	475.4	458.4	436.6	411.7	396.2	383.8	374.5	358.9	357.4	352.7
65°	430.4	421.1	405.5	385.3	365.1	351.1	337.2	324.7	318.5	310.8	306.1
67.5°	374.5	365.1	351.1	334.1	320.1	306.1	293.7	281.2	270.4	264.1	261.0
70°	320.1	312.3	303.0	282.8	265.7	254.8	245.5	237.7	226.8	223.7	222.2
72.5°	267.2	259.5	254.8	237.7	222.2	212.9	203.5	195.8	191.1	189.6	184.9
75°	219.1	211.3	205.1	189.6	180.2	174.0	164.7	161.6	156.9	155.4	153.8
77.5°	170.9	163.1	161.6	150.7	139.8	136.7	133.6	127.4	127.4	127.4	124.3
80°	122.7	121.2	119.6	108.8	104.1	101.0	99.4	94.8	91.7	88.6	87.0
82.5°	82.3	80.8	79.2	74.6	69.9	68.4	66.8	63.7	63.7	65.3	62.2
85°	49.7	46.6	45.1	43.5	40.4	40.4	42.0	40.4	40.4	40.4	38.8
87.5°	18.6	18.6	18.6	18.6	20.2	17.1	18.6	18.6	17.1	17.1	15.5
90°	10.5	11.6	12.6	14.6	16.6	18.6	20.6	22.0	23.4	24.9	26.3
92.5°	14.2	12.9	13.8	15.5	17.2	18.9	20.6	22.0	23.4	24.9	26.3
95°	70.0	69.6	64.2	53.3	42.4	31.5	20.6	22.0	23.4	24.9	26.3
97.5°	144.6	145.5	131.9	104.7	77.6	50.4	23.2	23.8	24.4	24.9	25.5
100°	218.6	219.0	219.6	220.7	221.8	223.0	224.1	181.5	138.8	96.2	53.5
102.5°	298.2	298.8	299.1	299.7	300.2	300.8	301.4	302.0	302.6	303.1	303.7
105°	383.2	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
107.5°	466.3	466.3	466.6	467.1	467.7	468.2	468.8	469.1	469.4	469.7	470.0
110°	551.3	551.3	551.6	552.2	552.7	553.3	553.9	553.0	552.2	551.3	550.4



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	634.6	635.0	635.1	635.4	635.7	636.0	636.3	635.1	634.0	632.8	631.7
115°	716.7	717.4	717.5	717.8	718.1	718.4	718.7	717.6	716.4	715.3	714.2
117.5°	794.7	794.7	795.3	796.4	797.6	798.7	799.9	798.2	796.4	794.7	793.0
120°	870.8	870.7	871.1	872.0	872.9	873.7	874.6	874.0	873.4	872.9	872.3
122.5°	946.0	946.7	946.8	947.1	947.4	947.7	948.0	947.4	946.8	946.3	945.7
125°	1019.1	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1	1019.0	1017.8	1016.7	1015.6
127.5°	1085.1	1085.8	1085.7	1085.4	1085.1	1084.8	1084.5	1083.9	1083.4	1082.8	1082.3
130°	1146.9	1147.6	1147.7	1148.0	1148.3	1148.6	1148.9	1148.1	1147.2	1146.4	1145.5
132.5°	1209.9	1210.8	1210.4	1209.5	1208.6	1207.8	1206.9	1206.9	1206.9	1206.9	1206.9
135°	1267.8	1268.7	1268.4	1267.8	1267.3	1266.7	1266.1	1265.5	1265.0	1264.4	1263.9
137.5°	1321.9	1322.8	1322.5	1321.9	1321.4	1320.8	1320.2	1320.2	1320.2	1320.2	1320.2
140°	1370.2	1370.5	1370.4	1370.1	1369.8	1369.5	1369.2	1369.8	1370.4	1370.9	1371.5
142.5°	1416.7	1416.8	1417.1	1417.7	1418.2	1418.8	1419.4	1419.4	1419.4	1419.4	1419.4
145°	1464.2	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5	1464.8	1465.1	1465.4	1465.7
147.5°	1503.1	1503.1	1503.2	1503.5	1503.8	1504.1	1504.4	1504.7	1505.0	1505.3	1505.6
150°	1539.5	1539.2	1539.5	1540.1	1540.6	1541.2	1541.8	1542.4	1543.0	1543.5	1544.1
152.5°	1573.4	1572.7	1573.0	1573.6	1574.1	1574.7	1575.3	1575.9	1576.4	1577.0	1577.5
155°	1603.2	1602.3	1602.6	1603.2	1603.7	1604.3	1604.9	1605.8	1606.6	1607.5	1608.4
157.5°	1631.1	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7	1631.5	1632.4	1633.2	1634.1
160°	1653.5	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8	1655.0	1656.1	1657.3	1658.4
162.5°	1674.1	1673.2	1673.3	1673.6	1673.9	1674.1	1674.4	1676.1	1677.9	1679.6	1681.3
165°	1692.1	1691.2	1691.3	1691.6	1691.9	1692.2	1692.5	1694.2	1695.9	1697.6	1699.3
167.5°	1706.3	1705.4	1705.5	1705.8	1706.1	1706.3	1706.6	1708.6	1710.6	1712.7	1714.7
170°	1716.7	1715.7	1715.8	1716.1	1716.4	1716.7	1717.0	1719.3	1721.6	1723.9	1726.2
172.5°	1724.4	1723.4	1723.7	1724.3	1724.8	1725.4	1726.0	1728.0	1730.0	1732.0	1734.0
175°	1730.7	1729.8	1729.9	1730.2	1730.5	1730.8	1731.1	1733.4	1735.7	1738.0	1740.3
177.5°	1734.6	1733.7	1733.8	1734.1	1734.4	1734.7	1735.0	1737.0	1739.0	1741.0	1743.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1791.5	1794.6	1786.8	1783.7	1777.5	1785.3	1786.8	1785.3	1799.2	1793.0	1796.1
5°	1687.4	1681.2	1676.5	1665.6	1665.6	1667.2	1671.8	1664.1	1668.7	1679.6	1678.1
7.5°	1572.4	1569.3	1570.8	1558.4	1549.1	1552.2	1549.1	1563.1	1570.8	1567.7	1574.0
10°	1468.3	1474.5	1460.5	1454.3	1448.1	1454.3	1452.8	1455.9	1465.2	1471.4	1482.3
12.5°	1384.4	1382.8	1375.1	1368.9	1358.0	1361.1	1370.4	1367.3	1368.9	1382.8	1381.3
15°	1305.2	1295.8	1289.6	1275.6	1278.7	1267.9	1277.2	1288.1	1292.7	1305.2	1312.9
17.5°	1225.9	1224.4	1216.6	1215.0	1197.9	1193.3	1202.6	1205.7	1210.4	1216.6	1227.5
20°	1159.1	1157.5	1146.7	1143.6	1129.6	1138.9	1135.8	1142.0	1145.1	1157.5	1162.2
22.5°	1098.5	1090.7	1087.6	1083.0	1078.3	1076.8	1083.0	1081.4	1092.3	1096.9	1098.5
25°	1042.6	1036.4	1034.8	1027.0	1023.9	1019.3	1023.9	1028.6	1041.0	1045.7	1051.9
27.5°	991.3	986.6	983.5	977.3	972.6	972.6	975.8	982.0	986.6	989.7	992.8
30°	944.7	941.6	932.3	929.1	924.5	924.5	924.5	927.6	935.4	944.7	949.3
32.5°	896.5	890.3	884.1	884.1	879.4	879.4	881.0	884.1	891.9	893.4	901.2
35°	849.9	843.7	839.0	835.9	837.5	831.3	834.4	839.0	848.3	851.5	856.1
37.5°	804.8	803.3	794.0	789.3	792.4	792.4	790.9	794.0	800.2	806.4	809.5
40°	755.1	752.0	752.0	747.4	748.9	742.7	747.4	750.5	753.6	759.8	764.4
42.5°	711.6	708.5	702.3	703.8	699.2	699.2	702.3	703.8	708.5	716.3	719.4
45°	665.0	665.0	661.9	657.2	658.8	654.1	657.2	658.8	665.0	672.8	669.7
47.5°	619.9	618.4	618.4	612.2	615.3	610.6	615.3	616.8	619.9	624.6	623.1
50°	576.4	571.8	573.3	571.8	570.2	570.2	573.3	573.3	576.4	576.4	581.1
52.5°	531.4	531.4	528.3	529.8	532.9	529.8	534.5	529.8	532.9	534.5	537.6
55°	491.0	487.9	489.4	487.9	494.1	489.4	494.1	491.0	494.1	492.5	495.6
57.5°	447.5	442.8	444.4	442.8	447.5	445.9	450.6	445.9	447.5	449.0	453.7
60°	397.8	397.8	397.8	394.7	399.3	399.3	397.8	397.8	404.0	407.1	405.5
62.5°	351.1	349.6	344.9	343.4	344.9	341.8	348.0	346.5	349.6	352.7	355.8
65°	299.9	296.8	295.2	292.1	292.1	290.6	292.1	298.3	299.9	301.4	309.2
67.5°	257.9	256.4	254.8	250.2	250.2	253.3	253.3	253.3	262.6	257.9	264.1
70°	220.6	217.5	214.4	212.9	212.9	214.4	216.0	217.5	216.0	222.2	223.7
72.5°	184.9	186.5	183.3	183.3	183.3	181.8	181.8	184.9	186.5	184.9	186.5
75°	153.8	153.8	152.3	153.8	153.8	152.3	152.3	155.4	155.4	153.8	158.5
77.5°	124.3	122.7	119.6	116.5	118.1	116.5	118.1	116.5	121.2	125.9	122.7
80°	87.0	85.5	85.5	85.5	87.0	85.5	88.6	85.5	87.0	87.0	88.6
82.5°	62.2	63.7	63.7	62.2	63.7	62.2	63.7	63.7	63.7	62.2	63.7
85°	40.4	40.4	40.4	40.4	38.8	40.4	40.4	40.4	42.0	40.4	42.0
87.5°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	18.6	17.1	18.6
90°	27.0	27.4	28.3	29.2	30.0	30.9	30.0	29.2	28.3	27.4	27.0
92.5°	27.0	27.1	27.4	27.7	28.0	28.3	28.0	27.7	27.4	27.1	27.0
95°	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0	27.0
97.5°	25.8	25.9	26.2	26.5	26.7	27.0	26.7	26.5	26.2	25.9	25.8
100°	32.2	31.6	30.5	29.3	28.2	27.0	28.2	29.3	30.5	31.6	32.2
102.5°	304.0	292.0	267.9	243.9	219.8	195.8	219.8	243.9	267.9	292.0	304.0
105°	383.8	383.7	383.4	383.1	382.8	382.5	382.8	383.1	383.4	383.7	383.8
107.5°	470.1	469.5	468.4	467.3	466.1	465.0	466.1	467.3	468.4	469.5	470.1
110°	550.0	550.1	550.4	550.7	551.0	551.3	551.0	550.7	550.4	550.1	550.0



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	631.1	630.8	630.3	629.7	629.2	628.6	629.2	629.7	630.3	630.8	631.1
115°	713.6	712.7	711.0	709.3	707.5	705.8	707.5	709.3	711.0	712.7	713.6
117.5°	792.1	791.8	791.3	790.7	790.2	789.6	790.2	790.7	791.3	791.8	792.1
120°	872.0	871.3	869.9	868.4	867.0	865.6	867.0	868.4	869.9	871.3	872.0
122.5°	945.4	944.5	942.8	941.1	939.4	937.7	939.4	941.1	942.8	944.5	945.4
125°	1015.0	1014.6	1013.7	1012.8	1012.0	1011.1	1012.0	1012.8	1013.7	1014.6	1015.0
127.5°	1082.0	1080.8	1078.5	1076.2	1073.9	1071.6	1073.9	1076.2	1078.5	1080.8	1082.0
130°	1145.1	1144.4	1142.9	1141.5	1140.0	1138.6	1140.0	1141.5	1142.9	1144.4	1145.1
132.5°	1206.9	1206.2	1204.8	1203.3	1201.9	1200.5	1201.9	1203.3	1204.8	1206.2	1206.9
135°	1263.6	1262.7	1261.0	1259.3	1257.5	1255.8	1257.5	1259.3	1261.0	1262.7	1263.6
137.5°	1320.2	1319.5	1318.1	1316.6	1315.2	1313.8	1315.2	1316.6	1318.1	1319.5	1320.2
140°	1371.8	1370.9	1369.2	1367.5	1365.7	1364.0	1365.7	1367.5	1369.2	1370.9	1371.8
142.5°	1419.4	1418.5	1416.8	1415.1	1413.4	1411.7	1413.4	1415.1	1416.8	1418.5	1419.4
145°	1465.8	1464.9	1463.2	1461.5	1459.8	1458.1	1459.8	1461.5	1463.2	1464.9	1465.8
147.5°	1505.7	1504.7	1502.7	1500.7	1498.7	1496.7	1498.7	1500.7	1502.7	1504.7	1505.7
150°	1544.4	1543.3	1541.0	1538.7	1536.4	1534.1	1536.4	1538.7	1541.0	1543.3	1544.4
152.5°	1577.8	1576.8	1574.8	1572.8	1570.8	1568.8	1570.8	1572.8	1574.8	1576.8	1577.8
155°	1608.8	1607.7	1605.4	1603.1	1600.8	1598.5	1600.8	1603.1	1605.4	1607.7	1608.8
157.5°	1634.5	1633.4	1631.1	1628.8	1626.5	1624.2	1626.5	1628.8	1631.1	1633.4	1634.5
160°	1659.0	1657.9	1655.6	1653.3	1651.0	1648.7	1651.0	1653.3	1655.6	1657.9	1659.0
162.5°	1682.2	1680.9	1678.3	1675.8	1673.2	1670.6	1673.2	1675.8	1678.3	1680.9	1682.2
165°	1700.2	1699.1	1696.8	1694.5	1692.2	1689.9	1692.2	1694.5	1696.8	1699.1	1700.2
167.5°	1715.7	1714.4	1711.8	1709.3	1706.7	1704.1	1706.7	1709.3	1711.8	1714.4	1715.7
170°	1727.3	1726.0	1723.4	1720.9	1718.3	1715.7	1718.3	1720.9	1723.4	1726.0	1727.3
172.5°	1735.0	1733.7	1731.1	1728.6	1726.0	1723.4	1726.0	1728.6	1731.1	1733.7	1735.0
175°	1741.4	1740.1	1737.5	1735.0	1732.4	1729.8	1732.4	1735.0	1737.5	1740.1	1741.4
177.5°	1744.0	1742.9	1740.6	1738.3	1736.0	1733.7	1736.0	1738.3	1740.6	1742.9	1744.0
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5	1892.5
2.5°	1789.9	1797.7	1791.5	1786.8	1799.2	1805.5	1805.5	1816.3	1827.2	1836.5	1838.1
5°	1679.6	1692.0	1695.1	1693.6	1712.2	1721.6	1741.8	1752.6	1768.2	1779.0	1791.5
7.5°	1578.6	1595.7	1597.3	1600.4	1628.3	1643.9	1661.0	1688.9	1710.7	1726.2	1740.2
10°	1477.6	1488.5	1499.4	1513.4	1541.3	1567.7	1592.6	1622.1	1650.1	1665.6	1685.8
12.5°	1401.5	1409.3	1421.7	1431.0	1460.5	1483.8	1516.5	1556.9	1597.3	1609.7	1634.5
15°	1322.2	1326.9	1351.8	1361.1	1385.9	1424.8	1445.0	1483.8	1527.3	1550.6	1578.6
17.5°	1230.6	1258.5	1274.1	1285.0	1316.0	1347.1	1379.7	1420.1	1476.1	1497.8	1518.0
20°	1165.3	1185.5	1202.6	1216.6	1244.6	1291.2	1320.7	1353.3	1406.1	1431.0	1460.5
22.5°	1107.8	1124.9	1140.5	1156.0	1174.6	1216.6	1250.8	1295.8	1348.7	1372.0	1406.1
25°	1053.4	1070.5	1079.9	1098.5	1123.4	1152.9	1193.3	1233.7	1286.5	1312.9	1345.5
27.5°	1000.6	1017.7	1034.8	1050.3	1067.4	1095.4	1123.4	1174.6	1229.0	1260.1	1288.1
30°	955.6	963.3	978.9	996.0	1013.0	1039.5	1072.1	1107.8	1170.0	1197.9	1232.1
32.5°	905.8	919.8	930.7	943.1	964.9	986.6	1016.2	1061.2	1110.9	1137.3	1174.6
35°	859.2	871.7	879.4	901.2	915.2	938.5	968.0	1008.4	1050.3	1079.9	1112.5
37.5°	814.2	826.6	835.9	848.3	867.0	887.2	918.3	947.8	997.5	1022.4	1059.7
40°	767.6	778.4	789.3	803.3	820.4	845.2	863.9	901.2	941.6	969.5	997.5
42.5°	722.5	728.7	741.1	756.7	773.8	795.5	821.9	851.5	891.9	916.7	941.6
45°	674.3	685.2	699.2	710.1	725.6	747.4	770.7	797.1	837.5	862.3	888.7
47.5°	629.3	637.0	646.4	663.5	683.7	699.2	724.0	748.9	786.2	809.5	834.4
50°	582.7	590.4	604.4	615.3	630.8	651.0	674.3	700.7	736.5	752.0	776.9
52.5°	539.2	542.3	556.2	567.1	582.7	606.0	624.6	647.9	682.1	699.2	724.0
55°	495.6	498.8	506.5	517.4	534.5	553.1	573.3	599.7	629.3	644.8	668.1
57.5°	450.6	453.7	461.5	469.2	486.3	503.4	526.7	548.5	578.0	592.0	613.7
60°	405.5	405.5	413.3	424.2	436.6	452.1	472.3	498.8	520.5	537.6	553.1
62.5°	357.4	362.0	366.7	374.5	388.4	407.1	424.2	442.8	469.2	481.7	495.6
65°	309.2	313.9	323.2	330.9	341.8	354.3	376.0	391.5	411.7	425.7	438.2
67.5°	267.2	271.9	278.1	287.4	295.2	309.2	324.7	340.3	362.0	371.3	380.7
70°	223.7	228.4	233.1	245.5	253.3	264.1	275.0	290.6	309.2	315.4	323.2
72.5°	189.6	191.1	197.3	200.4	211.3	220.6	233.1	242.4	256.4	264.1	270.4
75°	160.0	160.0	161.6	164.7	170.9	177.1	186.5	195.8	208.2	212.9	220.6
77.5°	125.9	130.5	129.0	132.1	135.2	138.3	146.1	152.3	164.7	167.8	170.9
80°	90.1	91.7	96.3	101.0	101.0	105.7	110.3	111.9	119.6	124.3	124.3
82.5°	65.3	66.8	65.3	66.8	68.4	69.9	74.6	80.8	80.8	82.3	85.5
85°	40.4	40.4	42.0	43.5	43.5	42.0	45.1	43.5	45.1	48.2	48.2
87.5°	20.2	18.6	18.6	18.6	18.6	18.6	20.2	18.6	20.2	20.2	20.2
90°	26.3	24.9	23.4	22.0	20.6	18.6	16.6	14.6	12.6	11.6	10.5
92.5°	26.3	24.9	23.4	22.0	20.6	18.9	17.2	15.5	13.8	12.9	14.2
95°	26.3	24.9	23.4	22.0	20.6	31.5	42.4	53.3	64.2	69.6	70.0
97.5°	25.5	24.9	24.4	23.8	23.2	50.4	77.6	104.7	131.9	145.5	144.6
100°	53.5	96.2	138.8	181.5	224.1	223.0	221.8	220.7	219.6	219.0	218.6
102.5°	303.7	303.1	302.6	302.0	301.4	300.8	300.2	299.7	299.1	298.8	298.2
105°	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.2
107.5°	470.0	469.7	469.4	469.1	468.8	468.2	467.7	467.1	466.6	466.3	466.3
110°	550.4	551.3	552.2	553.0	553.9	553.3	552.7	552.2	551.6	551.3	551.3



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	631.7	632.8	634.0	635.1	636.3	636.0	635.7	635.4	635.1	635.0	634.6
115°	714.2	715.3	716.4	717.6	718.7	718.4	718.1	717.8	717.5	717.4	716.7
117.5°	793.0	794.7	796.4	798.2	799.9	798.7	797.6	796.4	795.3	794.7	794.7
120°	872.3	872.9	873.4	874.0	874.6	873.7	872.9	872.0	871.1	870.7	870.8
122.5°	945.7	946.3	946.8	947.4	948.0	947.7	947.4	947.1	946.8	946.7	946.0
125°	1015.6	1016.7	1017.8	1019.0	1020.1	1020.1	1020.1	1020.1	1020.1	1020.1	1019.1
127.5°	1082.3	1082.8	1083.4	1083.9	1084.5	1084.8	1085.1	1085.4	1085.7	1085.8	1085.1
130°	1145.5	1146.4	1147.2	1148.1	1148.9	1148.6	1148.3	1148.0	1147.7	1147.6	1146.9
132.5°	1206.9	1206.9	1206.9	1206.9	1206.9	1207.8	1208.6	1209.5	1210.4	1210.8	1209.9
135°	1263.9	1264.4	1265.0	1265.5	1266.1	1266.7	1267.3	1267.8	1268.4	1268.7	1267.8
137.5°	1320.2	1320.2	1320.2	1320.2	1320.2	1320.8	1321.4	1321.9	1322.5	1322.8	1321.9
140°	1371.5	1370.9	1370.4	1369.8	1369.2	1369.5	1369.8	1370.1	1370.4	1370.5	1370.2
142.5°	1419.4	1419.4	1419.4	1419.4	1419.4	1418.8	1418.2	1417.7	1417.1	1416.8	1416.7
145°	1465.7	1465.4	1465.1	1464.8	1464.5	1464.5	1464.5	1464.5	1464.5	1464.5	1464.2
147.5°	1505.6	1505.3	1505.0	1504.7	1504.4	1504.1	1503.8	1503.5	1503.2	1503.1	1503.1
150°	1544.1	1543.5	1543.0	1542.4	1541.8	1541.2	1540.6	1540.1	1539.5	1539.2	1539.5
152.5°	1577.5	1577.0	1576.4	1575.9	1575.3	1574.7	1574.1	1573.6	1573.0	1572.7	1573.4
155°	1608.4	1607.5	1606.6	1605.8	1604.9	1604.3	1603.7	1603.2	1602.6	1602.3	1603.2
157.5°	1634.1	1633.2	1632.4	1631.5	1630.7	1630.7	1630.7	1630.7	1630.7	1630.7	1631.1
160°	1658.4	1657.3	1656.1	1655.0	1653.8	1653.5	1653.3	1653.0	1652.7	1652.6	1653.5
162.5°	1681.3	1679.6	1677.9	1676.1	1674.4	1674.1	1673.9	1673.6	1673.3	1673.2	1674.1
165°	1699.3	1697.6	1695.9	1694.2	1692.5	1692.2	1691.9	1691.6	1691.3	1691.2	1692.1
167.5°	1714.7	1712.7	1710.6	1708.6	1706.6	1706.3	1706.1	1705.8	1705.5	1705.4	1706.3
170°	1726.2	1723.9	1721.6	1719.3	1717.0	1716.7	1716.4	1716.1	1715.8	1715.7	1716.7
172.5°	1734.0	1732.0	1730.0	1728.0	1726.0	1725.4	1724.8	1724.3	1723.7	1723.4	1724.4
175°	1740.3	1738.0	1735.7	1733.4	1731.1	1730.8	1730.5	1730.2	1729.9	1729.8	1730.7
177.5°	1743.0	1741.0	1739.0	1737.0	1735.0	1734.7	1734.4	1734.1	1733.8	1733.7	1734.6
180°	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6	1737.6



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1892.5	1892.5	1892.5	1892.5
2.5°	1849.0	1862.9	1876.9	1894.0
5°	1811.7	1836.5	1862.9	1887.8
7.5°	1771.3	1807.0	1841.2	1876.9
10°	1726.2	1771.3	1810.1	1859.8
12.5°	1676.5	1724.7	1779.0	1835.0
15°	1626.8	1687.4	1744.9	1808.6
17.5°	1580.2	1637.7	1701.4	1777.5
20°	1524.2	1587.9	1659.4	1740.2
22.5°	1465.2	1535.1	1612.8	1699.8
25°	1415.5	1486.9	1561.5	1653.2
27.5°	1361.1	1435.7	1508.7	1606.6
30°	1298.9	1379.7	1454.3	1555.3
32.5°	1239.9	1320.7	1403.0	1497.8
35°	1182.4	1261.6	1344.0	1440.3
37.5°	1128.0	1199.5	1280.3	1367.3
40°	1076.8	1142.0	1213.5	1292.7
42.5°	1011.5	1087.6	1154.4	1211.9
45°	955.6	1017.7	1079.9	1126.5
47.5°	890.3	952.4	1005.3	1042.6
50°	835.9	885.6	929.1	961.8
52.5°	770.7	817.3	853.0	877.9
55°	707.0	747.4	778.4	795.5
57.5°	649.5	675.9	699.2	714.7
60°	585.8	606.0	626.2	643.3
62.5°	517.4	539.2	550.0	568.7
65°	456.8	470.8	487.9	494.1
67.5°	397.8	405.5	416.4	428.8
70°	335.6	340.3	351.1	368.2
72.5°	281.2	285.9	293.7	299.9
75°	223.7	228.4	234.6	240.8
77.5°	175.6	177.1	180.2	186.5
80°	127.4	132.1	135.2	136.7
82.5°	88.6	90.1	90.1	91.7
85°	55.9	52.8	52.8	54.4
87.5°	20.2	23.3	23.3	26.4
90°	8.2	5.9	3.6	1.3
92.5°	16.8	19.3	21.9	24.5
95°	70.9	71.7	72.6	73.4
97.5°	142.9	141.2	139.5	137.8
100°	217.7	216.8	216.0	215.1
102.5°	297.1	296.0	294.8	293.7
105°	382.1	381.0	379.8	378.7
107.5°	466.3	466.3	466.3	466.3
110°	551.3	551.3	551.3	551.3



TEST NUMBER: P1035804

CATALOG NUMBER: S125RDIW-B1270D1340UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	633.7	632.8	632.0	631.1
115°	715.3	713.8	712.4	711.0
117.5°	794.7	794.7	794.7	794.7
120°	871.1	871.4	871.7	872.0
122.5°	944.6	943.1	941.7	940.3
125°	1017.1	1015.1	1013.1	1011.1
127.5°	1083.7	1082.2	1080.8	1079.4
130°	1145.5	1144.0	1142.6	1141.2
132.5°	1208.2	1206.5	1204.7	1203.0
135°	1266.1	1264.4	1262.7	1261.0
137.5°	1320.2	1318.5	1316.8	1315.1
140°	1369.6	1369.1	1368.5	1367.9
142.5°	1416.4	1416.1	1415.9	1415.6
145°	1463.6	1463.1	1462.5	1461.9
147.5°	1503.1	1503.1	1503.1	1503.1
150°	1540.1	1540.6	1541.2	1541.8
152.5°	1574.8	1576.3	1577.7	1579.1
155°	1604.9	1606.6	1608.3	1610.0
157.5°	1632.0	1632.8	1633.7	1634.5
160°	1655.2	1656.9	1658.6	1660.3
162.5°	1675.8	1677.5	1679.2	1680.9
165°	1693.8	1695.5	1697.2	1698.9
167.5°	1708.0	1709.7	1711.4	1713.1
170°	1718.7	1720.7	1722.7	1724.7
172.5°	1726.4	1728.4	1730.4	1732.4
175°	1732.4	1734.1	1735.9	1737.6
177.5°	1736.3	1738.0	1739.7	1741.4
180°	1737.6	1737.6	1737.6	1737.6

(END OF REPORT)