

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035819

Luminaire Tested: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035819
REPORT IS A COMBINATION OF REPORTS P1006254 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10467.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	57	51	69	59	53	48	50	45	41	42	38	35	34	32	29
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	35	29	50	39	33	28	34	28	25	29	24	21	24	21	18
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17
10	47	35	28	24	44	33	27	22	29	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12247	12247	12247	12247
5°	12236	13802	12236	10608
10°	12167	15511	12127	9171
15°	12035	16409	11953	7984
20°	11876	17714	11770	7218
25°	11668	20050	11536	6550
30°	11456	21312	11284	6073
35°	11182	17527	11026	5629
40°	10695	11903	10606	5229
45°	10057	8556	10044	4835
50°	9402	6580	9448	4472
55°	8666	5350	8649	4120
60°	7980	4385	7941	3659
65°	7180	3654	7226	2946
70°	6519	2932	6493	2453
75°	5507	2222	5507	2016
80°	4463	1355	4411	1355
85°	3139	713	3053	806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17432 cd/sqm

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	1.8
10°-20°	537.4	5.1
20°-30°	852.0	8.1
30°-40°	1029.6	9.8
40°-50°	916.7	8.8
50°-60°	702.9	6.7
60°-70°	456.5	4.4
70°-80°	221.6	2.1
80°-90°	55.2	0.5
90°-100°	131.3	1.3
100°-110°	390.1	3.7
110°-120°	661.7	6.3
120°-130°	871.1	8.3
130°-140°	976.1	9.3
140°-150°	956.8	9.1
150°-160°	803.6	7.7
160°-170°	534.2	5.1
170°-180°	186.9	1.8
0°-30°	1572.7	15.0
0°-40°	2602.3	24.9
0°-60°	4221.8	40.3
0°-90°	4955.1	47.3
90°-120°	1183.1	11.3
90°-150°	3987.1	38.1
90°-180°	5512.0	52.7
0°-180°	10467.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1911	1911	1911	1911	1911	
5°	1907	2191	1907	1684	1907	181
15°	1827	2632	1814	1280	1827	515
25°	1670	3151	1651	1029	1670	770
35°	1455	2614	1434	840	1455	906
45°	1138	1169	1136	661	1138	878
55°	804	642	802	494	804	720
65°	499	364	502	294	499	499
75°	243	170	243	154	243	261
85°	55	36	53	41	55	63
90°	2	37	2	37	2	10
95°	100	132	100	132	100	104
105°	350	381	350	381	350	374
115°	662	669	662	669	662	655
125°	967	973	967	973	967	866
135°	1257	1262	1257	1262	1257	969
145°	1523	1529	1523	1529	1523	952
155°	1743	1743	1743	1743	1743	803
165°	1895	1890	1895	1890	1895	535
175°	1970	1963	1970	1963	1970	187
180°	1975	1975	1975	1975	1975	

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1913.0	1928.6	1933.4	1945.9	1960.0	1963.2	1971.0	1982.0	1988.3	1986.7	1986.7
5°	1906.7	1933.4	1952.2	1974.2	2000.8	2011.8	2021.2	2044.8	2063.6	2074.6	2093.4
7.5°	1895.7	1934.9	1966.3	1999.3	2040.1	2058.9	2079.3	2112.3	2146.8	2168.7	2189.1
10°	1878.4	1928.6	1972.6	2021.2	2076.2	2104.4	2129.5	2179.7	2222.1	2250.3	2297.4
12.5°	1853.3	1916.1	1977.3	2041.6	2110.7	2140.5	2175.0	2229.9	2289.6	2330.4	2369.6
15°	1826.6	1902.0	1967.9	2044.8	2127.9	2173.5	2217.4	2275.5	2328.8	2374.3	2419.8
17.5°	1795.3	1875.3	1956.9	2044.8	2138.9	2184.4	2222.1	2291.1	2347.6	2393.2	2434.0
20°	1757.6	1847.0	1939.6	2036.9	2132.7	2175.0	2211.1	2286.4	2336.7	2385.3	2443.4
22.5°	1716.8	1814.1	1913.0	2008.7	2102.8	2148.3	2190.7	2256.6	2311.5	2377.5	2452.8
25°	1669.7	1776.4	1876.9	1972.6	2062.0	2104.4	2142.1	2214.3	2291.1	2374.3	2459.1
27.5°	1622.6	1726.2	1823.5	1911.4	2008.7	2047.9	2085.6	2176.6	2267.6	2355.5	2471.6
30°	1570.8	1676.0	1760.7	1842.3	1936.5	1977.3	2024.4	2127.9	2231.5	2350.8	2492.0
32.5°	1512.8	1608.5	1687.0	1771.7	1856.5	1906.7	1966.3	2079.3	2198.6	2341.4	2521.8
35°	1454.7	1531.6	1603.8	1683.8	1785.8	1839.2	1897.3	2016.5	2165.6	2336.7	2546.9
37.5°	1381.0	1454.7	1511.2	1592.8	1698.0	1760.7	1818.8	1956.9	2126.4	2325.7	2545.4
40°	1305.6	1368.4	1421.8	1506.5	1621.1	1679.1	1741.9	1892.6	2085.6	2294.3	2507.7
42.5°	1224.0	1277.4	1335.5	1417.1	1528.5	1585.0	1657.2	1832.9	2029.1	2250.3	2410.4
45°	1137.7	1189.5	1238.2	1322.9	1434.3	1495.5	1574.0	1754.5	1960.0	2157.8	2253.5
47.5°	1053.0	1098.5	1150.3	1224.0	1337.0	1404.5	1484.5	1677.6	1867.4	2033.8	2041.6
50°	971.4	1007.5	1051.4	1126.7	1244.4	1308.8	1392.0	1572.4	1757.6	1872.2	1795.3
52.5°	886.6	919.6	965.1	1031.0	1140.9	1216.2	1288.4	1468.8	1624.2	1701.1	1559.9
55°	803.5	831.7	878.8	952.6	1048.3	1106.3	1180.1	1348.0	1484.5	1486.1	1332.3
57.5°	721.9	747.0	786.2	852.1	941.6	1009.0	1076.5	1222.5	1315.1	1288.4	1117.3
60°	649.7	665.4	701.5	765.8	849.0	897.6	969.8	1092.2	1153.4	1104.8	921.2
62.5°	574.4	590.0	618.3	670.1	748.5	800.3	845.8	946.3	988.6	914.9	764.2
65°	499.0	517.9	538.3	579.1	652.8	687.3	728.1	801.9	842.7	756.4	626.1
67.5°	433.1	442.5	462.9	505.3	557.1	588.5	616.7	666.9	674.8	605.7	499.0
70°	371.9	375.1	393.9	419.0	458.2	477.1	500.6	530.4	530.4	473.9	389.2
72.5°	302.9	307.6	321.7	348.4	371.9	381.3	389.2	408.0	404.9	353.1	295.0
75°	243.2	246.4	257.4	269.9	279.3	296.6	302.9	299.7	298.2	254.2	221.3
77.5°	188.3	189.9	197.7	208.7	210.3	216.6	211.9	211.9	197.7	172.6	155.4
80°	138.1	139.7	142.8	145.9	145.9	145.9	145.9	138.1	128.7	113.0	108.3
82.5°	92.6	92.6	94.2	97.3	95.7	92.6	89.4	81.6	75.3	70.6	67.5
85°	54.9	54.9	56.5	54.9	48.6	47.1	43.9	42.4	40.8	39.2	39.2
87.5°	26.7	25.1	22.0	18.8	18.8	18.8	18.8	18.8	18.8	17.3	17.3
90°	1.5	4.2	7.0	9.7	12.4	13.8	15.0	17.4	19.8	22.2	24.6
92.5°	46.1	47.8	49.5	51.2	52.9	53.8	55.3	58.4	61.5	64.5	67.6
95°	99.9	100.6	101.3	102.0	102.7	103.0	104.7	108.1	111.5	114.9	118.3
97.5°	153.7	154.0	154.4	154.7	155.0	155.2	157.6	162.4	167.1	171.9	176.7
100°	215.2	215.2	215.2	215.2	215.2	215.2	217.4	221.8	226.3	230.7	235.1
102.5°	281.3	283.0	284.7	286.4	288.1	288.9	289.8	291.5	293.2	294.9	296.6
105°	350.4	352.1	353.8	355.5	357.2	358.1	359.1	361.2	363.2	365.3	367.3
107.5°	425.7	427.4	429.1	430.8	432.5	433.4	434.3	436.0	437.7	439.4	441.1
110°	504.1	505.8	507.5	509.2	510.9	511.8	512.3	513.3	514.4	515.4	516.4

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	584.0	584.7	585.4	586.1	586.8	587.1	587.8	589.2	590.5	591.9	593.3
115°	662.4	663.8	665.2	666.5	667.9	668.6	668.9	669.6	670.3	670.9	671.6
117.5°	742.3	742.7	743.0	743.4	743.7	743.9	744.2	744.9	745.6	746.2	746.9
120°	816.1	817.8	819.5	821.2	822.9	823.8	824.0	824.3	824.6	825.0	825.3
122.5°	896.0	896.4	896.7	897.1	897.4	897.6	898.1	899.1	900.2	901.2	902.2
125°	966.7	968.7	970.8	972.8	974.9	975.9	976.1	976.4	976.8	977.1	977.5
127.5°	1045.1	1046.1	1047.1	1048.2	1049.2	1049.7	1049.9	1050.2	1050.6	1050.9	1051.3
130°	1114.3	1116.0	1117.7	1119.4	1121.1	1122.0	1122.3	1123.0	1123.7	1124.3	1125.0
132.5°	1183.4	1186.5	1189.6	1192.7	1195.8	1197.3	1197.1	1196.8	1196.4	1196.1	1195.7
135°	1257.2	1259.2	1261.3	1263.3	1265.4	1266.4	1266.6	1266.9	1267.3	1267.6	1268.0
137.5°	1326.4	1328.4	1330.5	1332.5	1334.6	1335.6	1335.9	1336.6	1337.3	1338.0	1338.7
140°	1392.5	1394.2	1395.9	1397.6	1399.3	1400.1	1400.6	1401.7	1402.7	1403.8	1404.8
142.5°	1458.5	1459.9	1461.3	1462.6	1464.0	1464.7	1465.4	1466.7	1468.1	1469.4	1470.8
145°	1523.1	1524.5	1525.8	1527.2	1528.5	1529.2	1529.7	1530.8	1531.8	1532.9	1533.9
147.5°	1583.0	1584.0	1585.0	1586.1	1587.1	1587.6	1587.9	1588.6	1589.3	1590.0	1590.7
150°	1643.0	1642.6	1642.3	1641.9	1641.6	1641.4	1642.1	1643.5	1644.8	1646.2	1647.6
152.5°	1692.2	1692.9	1693.5	1694.2	1694.9	1695.2	1695.4	1695.7	1696.1	1696.4	1696.8
155°	1742.9	1742.9	1742.9	1742.9	1742.9	1742.9	1743.1	1743.4	1743.7	1744.1	1744.4
157.5°	1789.0	1788.3	1787.6	1786.9	1786.2	1785.9	1786.1	1786.4	1786.7	1787.1	1787.4
160°	1828.9	1827.9	1826.9	1825.8	1824.8	1824.3	1824.5	1824.8	1825.2	1825.5	1825.9
162.5°	1864.3	1863.6	1862.9	1862.2	1861.5	1861.2	1861.2	1861.2	1861.2	1861.2	1861.2
165°	1895.0	1894.3	1893.7	1893.0	1892.3	1892.0	1892.2	1892.5	1892.8	1893.2	1893.5
167.5°	1922.7	1921.3	1919.9	1918.6	1917.2	1916.5	1916.5	1916.5	1916.5	1916.5	1916.5
170°	1944.2	1942.8	1941.5	1940.1	1938.8	1938.1	1938.1	1938.1	1938.1	1938.1	1938.1
172.5°	1959.6	1958.2	1956.8	1955.5	1954.1	1953.4	1953.4	1953.4	1953.4	1953.4	1953.4
175°	1970.3	1968.9	1967.6	1966.2	1964.9	1964.2	1964.2	1964.2	1964.2	1964.2	1964.2
177.5°	1978.0	1976.6	1975.3	1973.9	1972.6	1971.9	1971.7	1971.4	1971.0	1970.7	1970.3
180°	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1994.6	2005.5	2015.0	2010.2	2029.1	2027.5	2030.6	2036.9	2038.5	2035.4	2029.1
5°	2102.8	2118.5	2145.2	2159.3	2156.2	2168.7	2175.0	2184.4	2193.9	2190.7	2190.7
7.5°	2223.7	2245.6	2272.3	2308.4	2313.1	2324.1	2342.9	2342.9	2353.9	2349.2	2347.6
10°	2328.8	2355.5	2397.9	2426.1	2438.7	2444.9	2463.8	2470.0	2482.6	2484.2	2484.2
12.5°	2415.1	2462.2	2490.4	2518.7	2525.0	2534.4	2548.5	2557.9	2562.6	2562.6	2557.9
15°	2460.6	2498.3	2531.2	2561.1	2578.3	2586.2	2600.3	2611.3	2617.6	2631.7	2634.8
17.5°	2479.5	2525.0	2578.3	2620.7	2650.5	2658.4	2686.6	2696.0	2708.6	2714.9	2722.7
20°	2506.1	2572.0	2636.4	2688.2	2716.4	2736.8	2766.6	2810.6	2823.1	2823.1	2818.4
22.5°	2529.7	2614.4	2702.3	2785.5	2809.0	2849.8	2904.7	2951.8	2970.6	2978.5	2972.2
25°	2557.9	2674.1	2788.6	2892.2	2956.5	2986.3	3060.1	3116.6	3138.6	3151.1	3154.3
27.5°	2606.6	2752.5	2898.5	3030.3	3096.2	3130.7	3207.6	3256.3	3282.9	3293.9	3286.1
30°	2661.5	2840.4	3009.9	3127.6	3171.5	3213.9	3264.1	3282.9	3276.7	3276.7	3300.2
32.5°	2718.0	2903.2	3053.8	3130.7	3146.4	3140.1	3119.7	3063.2	3030.3	3030.3	3050.7
35°	2749.4	2909.4	2986.3	2961.2	2900.0	2863.9	2752.5	2689.7	2619.1	2614.4	2638.0
37.5°	2732.1	2801.2	2769.8	2605.0	2521.8	2452.8	2278.6	2209.5	2157.8	2085.6	2197.0
40°	2611.3	2587.7	2424.5	2187.6	2095.0	1997.7	1859.6	1790.5	1718.4	1707.4	1734.1
42.5°	2407.3	2267.6	2029.1	1800.0	1705.8	1636.8	1531.6	1464.1	1418.6	1399.8	1431.2
45°	2153.1	1933.4	1694.8	1512.8	1409.2	1373.1	1277.4	1217.8	1183.2	1169.1	1191.1
47.5°	1842.3	1621.1	1395.1	1241.3	1180.1	1144.0	1079.7	1027.9	998.1	988.6	998.1
50°	1564.6	1337.0	1147.1	1048.3	993.4	963.5	910.2	877.2	853.7	847.4	863.1
52.5°	1324.5	1117.3	973.0	885.1	849.0	823.9	786.2	758.0	743.8	737.6	748.5
55°	1109.5	941.6	825.4	750.1	723.4	707.7	674.8	659.1	643.4	641.8	652.8
57.5°	919.6	803.5	696.8	643.4	635.6	612.0	583.8	569.6	561.8	560.2	564.9
60°	765.8	662.2	597.9	550.8	539.8	521.0	505.3	495.9	486.5	483.3	486.5
62.5°	637.1	555.5	503.7	472.4	456.7	452.0	434.7	423.7	422.1	422.1	425.3
65°	525.7	456.7	423.7	398.6	387.6	382.9	370.4	362.5	364.1	364.1	365.6
67.5°	428.4	378.2	348.4	335.8	326.4	324.8	312.3	309.1	306.0	306.0	309.1
70°	340.5	309.1	287.2	280.9	279.3	268.3	263.6	262.1	257.4	258.9	258.9
72.5°	266.8	246.4	233.8	224.4	226.0	219.7	213.4	213.4	210.3	215.0	215.0
75°	197.7	188.3	178.9	175.8	178.9	175.8	171.1	169.5	171.1	169.5	169.5
77.5°	145.9	141.2	138.1	136.5	136.5	130.3	127.1	130.3	124.0	127.1	127.1
80°	102.0	95.7	94.2	91.0	92.6	87.9	89.4	86.3	86.3	86.3	86.3
82.5°	64.3	62.8	62.8	62.8	61.2	61.2	61.2	61.2	61.2	61.2	59.6
85°	39.2	37.7	37.7	37.7	36.1	36.1	36.1	36.1	36.1	36.1	36.1
87.5°	15.7	17.3	17.3	18.8	17.3	15.7	15.7	15.7	17.3	17.3	15.7
90°	26.3	28.0	29.7	31.4	32.3	32.8	33.8	34.9	35.9	36.9	35.9
92.5°	70.0	72.4	74.8	77.2	78.4	78.7	79.4	80.1	80.8	81.5	80.8
95°	120.7	123.1	125.5	127.9	129.1	129.4	130.1	130.8	131.5	132.2	131.5
97.5°	178.8	180.8	182.9	185.0	186.0	186.2	186.5	186.8	187.2	187.5	187.2
100°	238.2	241.3	244.4	247.5	249.0	249.3	250.0	250.7	251.4	252.1	251.4
102.5°	300.0	303.4	306.9	310.3	312.0	312.5	313.5	314.6	315.6	316.6	315.6
105°	369.3	371.4	373.4	375.5	376.5	377.0	378.1	379.1	380.2	381.2	380.2
107.5°	442.1	443.1	444.2	445.2	445.7	445.7	445.7	445.7	445.7	445.7	445.7
110°	517.4	518.4	519.5	520.5	521.0	520.8	520.5	520.2	519.8	519.5	519.8

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	593.6	594.0	594.3	594.6	594.8	594.5	593.8	593.1	592.4	591.7	592.4
115°	671.3	670.9	670.6	670.3	670.1	669.9	669.6	669.3	668.9	668.6	668.9
117.5°	747.3	747.6	748.0	748.3	748.5	747.8	746.4	745.1	743.7	742.3	743.7
120°	825.3	825.3	825.3	825.3	825.3	824.6	823.3	821.9	820.6	819.2	820.6
122.5°	901.8	901.5	901.1	900.8	900.6	900.1	899.1	898.0	897.0	896.0	897.0
125°	976.8	976.1	975.4	974.7	974.4	974.2	973.9	973.6	973.2	972.9	973.2
127.5°	1050.9	1050.6	1050.2	1049.9	1049.7	1049.4	1048.7	1048.0	1047.3	1046.6	1047.3
130°	1124.7	1124.3	1124.0	1123.7	1123.5	1123.2	1122.5	1121.8	1121.1	1120.4	1121.1
132.5°	1195.4	1195.0	1194.7	1194.4	1194.2	1193.7	1192.7	1191.6	1190.6	1189.6	1190.6
135°	1268.0	1268.0	1268.0	1268.0	1268.0	1267.3	1265.9	1264.6	1263.2	1261.8	1263.2
137.5°	1339.0	1339.4	1339.7	1340.0	1340.2	1339.3	1337.6	1335.9	1334.2	1332.5	1334.2
140°	1405.5	1406.1	1406.8	1407.5	1407.8	1406.9	1405.2	1403.5	1401.8	1400.1	1401.8
142.5°	1471.2	1471.5	1471.9	1472.2	1472.4	1471.5	1469.8	1468.1	1466.4	1464.7	1466.4
145°	1533.9	1533.9	1533.9	1533.9	1533.9	1533.4	1532.3	1531.3	1530.2	1529.2	1530.2
147.5°	1591.7	1592.7	1593.8	1594.8	1595.3	1593.9	1591.2	1588.5	1585.7	1583.0	1585.7
150°	1647.6	1647.6	1647.6	1647.6	1647.6	1647.3	1646.6	1645.9	1645.2	1644.5	1645.2
152.5°	1697.8	1698.8	1699.9	1700.9	1701.4	1700.7	1699.3	1698.0	1696.6	1695.2	1696.6
155°	1745.8	1747.2	1748.5	1749.9	1750.6	1749.7	1748.0	1746.3	1744.6	1742.9	1744.6
157.5°	1788.8	1790.2	1791.5	1792.9	1793.6	1792.4	1790.0	1787.6	1785.2	1782.8	1785.2
160°	1827.3	1828.6	1830.0	1831.3	1832.0	1831.1	1829.4	1827.7	1826.0	1824.3	1826.0
162.5°	1862.9	1864.6	1866.3	1868.0	1868.9	1867.9	1865.8	1863.8	1861.7	1859.7	1861.7
165°	1894.9	1896.2	1897.6	1898.9	1899.6	1898.6	1896.5	1894.5	1892.4	1890.4	1892.4
167.5°	1918.6	1920.6	1922.7	1924.8	1925.8	1924.8	1922.7	1920.6	1918.6	1916.5	1918.6
170°	1940.1	1942.2	1944.2	1946.3	1947.3	1946.1	1943.7	1941.3	1938.9	1936.5	1938.9
172.5°	1955.5	1957.5	1959.6	1961.7	1962.7	1961.7	1959.6	1957.5	1955.5	1953.4	1955.5
175°	1966.2	1968.3	1970.3	1972.4	1973.4	1972.2	1969.8	1967.5	1965.1	1962.7	1965.1
177.5°	1972.4	1974.4	1976.5	1978.6	1979.6	1978.4	1976.0	1973.6	1971.2	1968.8	1971.2
180°	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	2036.9	2025.9	2030.6	2025.9	2021.2	2016.5	2005.5	1989.8	1977.3	1967.9	1966.3
5°	2193.9	2179.7	2170.3	2165.6	2156.2	2143.6	2123.2	2099.7	2071.4	2060.5	2038.5
7.5°	2338.2	2333.5	2311.5	2308.4	2302.1	2278.6	2244.1	2212.7	2176.6	2146.8	2118.5
10°	2474.8	2463.8	2448.1	2426.1	2423.0	2393.2	2360.2	2316.3	2269.2	2240.9	2190.7
12.5°	2559.5	2546.9	2529.7	2515.6	2507.7	2488.9	2443.4	2399.4	2357.1	2305.3	2261.3
15°	2620.7	2605.0	2573.6	2562.6	2553.2	2528.1	2495.2	2449.6	2393.2	2357.1	2294.3
17.5°	2703.9	2685.0	2653.7	2633.3	2616.0	2576.8	2529.7	2468.5	2415.1	2374.3	2317.8
20°	2799.6	2771.3	2730.5	2703.9	2678.8	2633.3	2567.3	2495.2	2418.3	2368.0	2310.0
22.5°	2958.1	2904.7	2840.4	2802.7	2768.2	2689.7	2611.3	2521.8	2435.5	2360.2	2289.6
25°	3111.9	3058.5	2978.5	2926.7	2873.4	2782.3	2678.8	2554.8	2444.9	2357.1	2264.5
27.5°	3254.7	3199.8	3126.0	3063.2	3011.4	2874.9	2738.4	2598.7	2459.1	2338.2	2244.1
30°	3287.6	3264.1	3207.6	3152.7	3105.6	2980.1	2821.6	2644.2	2476.3	2321.0	2215.8
32.5°	3088.3	3146.4	3160.5	3152.7	3122.9	3033.4	2887.5	2700.7	2501.4	2313.1	2168.7
35°	2674.1	2779.2	2887.5	2945.5	2973.8	2986.3	2900.0	2729.0	2518.7	2300.6	2137.4
37.5°	2217.4	2319.4	2490.4	2576.8	2672.5	2798.0	2832.6	2722.7	2510.8	2291.1	2087.1
40°	1821.9	1952.2	2093.4	2171.9	2255.1	2481.0	2652.1	2639.5	2485.7	2256.6	2047.9
42.5°	1483.0	1564.6	1688.5	1774.9	1876.9	2129.5	2358.6	2471.6	2410.4	2214.3	1997.7
45°	1236.6	1299.4	1387.2	1475.1	1537.9	1767.0	2038.5	2223.7	2281.7	2138.9	1920.8
47.5°	1042.0	1089.1	1166.0	1220.9	1288.4	1468.8	1704.2	1964.7	2087.1	2032.2	1839.2
50°	892.9	930.6	991.8	1026.3	1085.9	1241.3	1420.2	1693.3	1878.4	1884.7	1730.9
52.5°	762.7	800.3	852.1	881.9	918.0	1023.2	1203.6	1434.3	1647.7	1726.2	1606.9
55°	663.8	685.8	728.1	751.7	784.6	886.6	1001.2	1197.4	1420.2	1548.9	1473.6
57.5°	572.8	596.3	623.0	641.8	665.4	747.0	850.5	998.1	1219.3	1359.0	1333.9
60°	499.0	513.2	538.3	552.4	574.4	627.7	699.9	847.4	1023.2	1155.0	1169.1
62.5°	430.0	442.5	459.8	472.4	486.5	528.8	582.2	687.3	841.1	983.9	1002.8
65°	370.4	381.3	390.8	401.7	412.7	439.4	484.9	566.5	685.8	819.2	860.0
67.5°	317.0	320.1	334.3	335.8	342.1	362.5	395.5	461.4	547.7	654.4	707.7
70°	265.2	271.5	274.6	279.3	285.6	299.7	326.4	360.9	425.3	511.6	561.8
72.5°	215.0	216.6	221.3	224.4	230.7	241.7	254.2	280.9	321.7	384.5	430.0
75°	171.1	172.6	175.8	177.3	182.0	185.2	191.5	210.3	238.5	276.2	309.1
77.5°	128.7	131.8	135.0	135.0	136.5	139.7	142.8	149.1	163.2	188.3	216.6
80°	87.9	89.4	89.4	91.0	89.4	94.2	98.9	106.7	113.0	120.8	135.0
82.5°	61.2	61.2	61.2	62.8	62.8	64.3	64.3	65.9	67.5	72.2	78.5
85°	37.7	37.7	39.2	36.1	37.7	39.2	39.2	37.7	39.2	40.8	42.4
87.5°	15.7	15.7	17.3	17.3	17.3	17.3	15.7	17.3	15.7	17.3	17.3
90°	34.9	33.8	32.8	32.3	31.4	29.7	28.0	26.3	24.6	22.2	19.8
92.5°	80.1	79.4	78.7	78.4	77.2	74.8	72.4	70.0	67.6	64.5	61.5
95°	130.8	130.1	129.4	129.1	127.9	125.5	123.1	120.7	118.3	114.9	111.5
97.5°	186.8	186.5	186.2	186.0	185.0	182.9	180.8	178.8	176.7	171.9	167.1
100°	250.7	250.0	249.3	249.0	247.5	244.4	241.3	238.2	235.1	230.7	226.3
102.5°	314.6	313.5	312.5	312.0	310.3	306.9	303.4	300.0	296.6	294.9	293.2
105°	379.1	378.1	377.0	376.5	375.5	373.4	371.4	369.3	367.3	365.3	363.2
107.5°	445.7	445.7	445.7	445.7	445.2	444.2	443.1	442.1	441.1	439.4	437.7
110°	520.2	520.5	520.8	521.0	520.5	519.5	518.4	517.4	516.4	515.4	514.4

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	593.1	593.8	594.5	594.8	594.6	594.3	594.0	593.6	593.3	591.9	590.5
115°	669.3	669.6	669.9	670.1	670.3	670.6	670.9	671.3	671.6	670.9	670.3
117.5°	745.1	746.4	747.8	748.5	748.3	748.0	747.6	747.3	746.9	746.2	745.6
120°	821.9	823.3	824.6	825.3	825.3	825.3	825.3	825.3	825.3	825.0	824.6
122.5°	898.0	899.1	900.1	900.6	900.8	901.1	901.5	901.8	902.2	901.2	900.2
125°	973.6	973.9	974.2	974.4	974.7	975.4	976.1	976.8	977.5	977.1	976.8
127.5°	1048.0	1048.7	1049.4	1049.7	1049.9	1050.2	1050.6	1050.9	1051.3	1050.9	1050.6
130°	1121.8	1122.5	1123.2	1123.5	1123.7	1124.0	1124.3	1124.7	1125.0	1124.3	1123.7
132.5°	1191.6	1192.7	1193.7	1194.2	1194.4	1194.7	1195.0	1195.4	1195.7	1196.1	1196.4
135°	1264.6	1265.9	1267.3	1268.0	1268.0	1268.0	1268.0	1268.0	1268.0	1267.6	1267.3
137.5°	1335.9	1337.6	1339.3	1340.2	1340.0	1339.7	1339.4	1339.0	1338.7	1338.0	1337.3
140°	1403.5	1405.2	1406.9	1407.8	1407.5	1406.8	1406.1	1405.5	1404.8	1403.8	1402.7
142.5°	1468.1	1469.8	1471.5	1472.4	1472.2	1471.9	1471.5	1471.2	1470.8	1469.4	1468.1
145°	1531.3	1532.3	1533.4	1533.9	1533.9	1533.9	1533.9	1533.9	1533.9	1532.9	1531.8
147.5°	1588.5	1591.2	1593.9	1595.3	1594.8	1593.8	1592.7	1591.7	1590.7	1590.0	1589.3
150°	1645.9	1646.6	1647.3	1647.6	1647.6	1647.6	1647.6	1647.6	1647.6	1646.2	1644.8
152.5°	1698.0	1699.3	1700.7	1701.4	1700.9	1699.9	1698.8	1697.8	1696.8	1696.4	1696.1
155°	1746.3	1748.0	1749.7	1750.6	1749.9	1748.5	1747.2	1745.8	1744.4	1744.1	1743.7
157.5°	1787.6	1790.0	1792.4	1793.6	1792.9	1791.5	1790.2	1788.8	1787.4	1787.1	1786.7
160°	1827.7	1829.4	1831.1	1832.0	1831.3	1830.0	1828.6	1827.3	1825.9	1825.5	1825.2
162.5°	1863.8	1865.8	1867.9	1868.9	1868.0	1866.3	1864.6	1862.9	1861.2	1861.2	1861.2
165°	1894.5	1896.5	1898.6	1899.6	1898.9	1897.6	1896.2	1894.9	1893.5	1893.2	1892.8
167.5°	1920.6	1922.7	1924.8	1925.8	1924.8	1922.7	1920.6	1918.6	1916.5	1916.5	1916.5
170°	1941.3	1943.7	1946.1	1947.3	1946.3	1944.2	1942.2	1940.1	1938.1	1938.1	1938.1
172.5°	1957.5	1959.6	1961.7	1962.7	1961.7	1959.6	1957.5	1955.5	1953.4	1953.4	1953.4
175°	1967.5	1969.8	1972.2	1973.4	1972.4	1970.3	1968.3	1966.2	1964.2	1964.2	1964.2
177.5°	1973.6	1976.0	1978.4	1979.6	1978.6	1976.5	1974.4	1972.4	1970.3	1970.7	1971.0
180°	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1961.6	1952.2	1945.9	1944.3	1934.9	1927.1	1917.7	1916.1	1911.4	1898.8	1891.0
5°	2022.8	2000.8	1996.1	1982.0	1958.5	1941.2	1919.2	1906.7	1892.6	1869.0	1850.2
7.5°	2085.6	2055.8	2033.8	2013.4	1980.4	1949.0	1917.7	1892.6	1867.4	1832.9	1804.7
10°	2146.8	2101.3	2074.6	2044.8	1999.3	1952.2	1908.2	1872.2	1831.3	1790.5	1749.7
12.5°	2203.3	2145.2	2106.0	2063.6	2007.1	1949.0	1892.6	1842.3	1800.0	1745.0	1699.5
15°	2237.8	2173.5	2134.2	2093.4	2008.7	1944.3	1878.4	1814.1	1757.6	1699.5	1657.2
17.5°	2258.2	2186.0	2142.1	2104.4	2018.1	1930.2	1845.5	1776.4	1715.2	1646.2	1589.7
20°	2248.8	2178.2	2137.4	2101.3	2000.8	1913.0	1821.9	1741.9	1665.0	1594.4	1534.8
22.5°	2228.4	2154.6	2109.1	2076.2	1986.7	1883.1	1782.7	1696.4	1616.4	1545.7	1478.3
25°	2184.4	2112.3	2073.0	2032.2	1944.3	1845.5	1743.5	1650.9	1566.1	1490.8	1415.5
27.5°	2145.2	2057.3	2016.5	1980.4	1887.8	1800.0	1699.5	1597.5	1511.2	1432.8	1357.4
30°	2099.7	2000.8	1956.9	1908.2	1825.1	1741.9	1641.5	1547.3	1457.9	1374.7	1302.5
32.5°	2051.0	1936.5	1886.3	1831.3	1746.6	1668.1	1583.4	1490.8	1401.4	1319.8	1244.4
35°	1988.3	1865.9	1807.8	1756.0	1668.1	1589.7	1511.2	1434.3	1344.9	1258.6	1186.4
37.5°	1928.6	1793.7	1732.5	1672.9	1580.3	1504.9	1440.6	1368.4	1282.1	1198.9	1129.9
40°	1861.2	1705.8	1643.0	1588.1	1492.4	1409.2	1351.2	1294.7	1219.3	1139.3	1064.0
42.5°	1800.0	1624.2	1558.3	1501.8	1401.4	1322.9	1268.0	1220.9	1155.0	1081.2	1004.3
45°	1715.2	1536.3	1468.8	1409.2	1307.2	1233.5	1177.0	1136.2	1084.4	1015.3	946.3
47.5°	1636.8	1451.6	1377.8	1305.6	1213.1	1137.7	1085.9	1054.6	1020.0	958.8	888.2
50°	1541.0	1354.3	1279.0	1219.3	1114.2	1049.8	998.1	976.1	944.7	886.6	830.1
52.5°	1437.5	1260.1	1189.5	1117.3	1020.0	957.3	911.8	886.6	861.5	819.2	765.8
55°	1316.6	1155.0	1089.1	1024.7	927.4	869.4	828.6	801.9	787.8	748.5	709.3
57.5°	1200.5	1048.3	987.1	927.4	842.7	776.8	750.1	726.6	706.2	677.9	645.0
60°	1082.8	944.7	878.8	825.4	751.7	692.1	670.1	646.5	630.9	608.9	585.3
62.5°	947.8	830.1	779.9	729.7	666.9	619.9	594.8	575.9	555.5	541.4	521.0
65°	805.0	721.9	673.2	635.6	575.9	533.6	514.7	502.2	484.9	470.8	455.1
67.5°	671.7	605.7	585.3	544.5	499.0	461.4	447.2	431.6	417.4	409.6	395.5
70°	543.0	495.9	475.5	464.5	414.3	389.2	376.6	370.4	353.1	345.2	335.8
72.5°	420.6	403.3	389.2	375.1	342.1	326.4	312.3	306.0	293.5	287.2	284.0
75°	310.7	299.7	291.9	290.3	276.2	260.5	246.4	243.2	233.8	227.5	224.4
77.5°	218.1	215.0	213.4	215.0	205.6	196.2	193.0	189.9	178.9	177.3	177.3
80°	142.8	150.7	150.7	149.1	145.9	144.4	139.7	136.5	130.3	128.7	130.3
82.5°	87.9	92.6	94.2	97.3	95.7	94.2	91.0	89.4	91.0	87.9	89.4
85°	43.9	47.1	53.4	53.4	54.9	54.9	54.9	53.4	50.2	51.8	50.2
87.5°	17.3	18.8	18.8	18.8	17.3	22.0	23.5	23.5	23.5	20.4	20.4
90°	17.4	15.0	13.8	12.4	9.7	7.0	4.2	1.5	4.2	7.0	9.7
92.5°	58.4	55.3	53.8	52.9	51.2	49.5	47.8	46.1	47.8	49.5	51.2
95°	108.1	104.7	103.0	102.7	102.0	101.3	100.6	99.9	100.6	101.3	102.0
97.5°	162.4	157.6	155.2	155.0	154.7	154.4	154.0	153.7	154.0	154.4	154.7
100°	221.8	217.4	215.2	215.2	215.2	215.2	215.2	215.2	215.2	215.2	215.2
102.5°	291.5	289.8	288.9	288.1	286.4	284.7	283.0	281.3	283.0	284.7	286.4
105°	361.2	359.1	358.1	357.2	355.5	353.8	352.1	350.4	352.1	353.8	355.5
107.5°	436.0	434.3	433.4	432.5	430.8	429.1	427.4	425.7	427.4	429.1	430.8
110°	513.3	512.3	511.8	510.9	509.2	507.5	505.8	504.1	505.8	507.5	509.2

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	589.2	587.8	587.1	586.8	586.1	585.4	584.7	584.0	584.7	585.4	586.1
115°	669.6	668.9	668.6	667.9	666.5	665.2	663.8	662.4	663.8	665.2	666.5
117.5°	744.9	744.2	743.9	743.7	743.4	743.0	742.7	742.3	742.7	743.0	743.4
120°	824.3	824.0	823.8	822.9	821.2	819.5	817.8	816.1	817.8	819.5	821.2
122.5°	899.1	898.1	897.6	897.4	897.1	896.7	896.4	896.0	896.4	896.7	897.1
125°	976.4	976.1	975.9	974.9	972.8	970.8	968.7	966.7	968.7	970.8	972.8
127.5°	1050.2	1049.9	1049.7	1049.2	1048.2	1047.1	1046.1	1045.1	1046.1	1047.1	1048.2
130°	1123.0	1122.3	1122.0	1121.1	1119.4	1117.7	1116.0	1114.3	1116.0	1117.7	1119.4
132.5°	1196.8	1197.1	1197.3	1195.8	1192.7	1189.6	1186.5	1183.4	1186.5	1189.6	1192.7
135°	1266.9	1266.6	1266.4	1265.4	1263.3	1261.3	1259.2	1257.2	1259.2	1261.3	1263.3
137.5°	1336.6	1335.9	1335.6	1334.6	1332.5	1330.5	1328.4	1326.4	1328.4	1330.5	1332.5
140°	1401.7	1400.6	1400.1	1399.3	1397.6	1395.9	1394.2	1392.5	1394.2	1395.9	1397.6
142.5°	1466.7	1465.4	1464.7	1464.0	1462.6	1461.3	1459.9	1458.5	1459.9	1461.3	1462.6
145°	1530.8	1529.7	1529.2	1528.5	1527.2	1525.8	1524.5	1523.1	1524.5	1525.8	1527.2
147.5°	1588.6	1587.9	1587.6	1587.1	1586.1	1585.0	1584.0	1583.0	1584.0	1585.0	1586.1
150°	1643.5	1642.1	1641.4	1641.6	1641.9	1642.3	1642.6	1643.0	1642.6	1642.3	1641.9
152.5°	1695.7	1695.4	1695.2	1694.9	1694.2	1693.5	1692.9	1692.2	1692.9	1693.5	1694.2
155°	1743.4	1743.1	1742.9	1742.9	1742.9	1742.9	1742.9	1742.9	1742.9	1742.9	1742.9
157.5°	1786.4	1786.1	1785.9	1786.2	1786.9	1787.6	1788.3	1789.0	1788.3	1787.6	1786.9
160°	1824.8	1824.5	1824.3	1824.8	1825.8	1826.9	1827.9	1828.9	1827.9	1826.9	1825.8
162.5°	1861.2	1861.2	1861.2	1861.5	1862.2	1862.9	1863.6	1864.3	1863.6	1862.9	1862.2
165°	1892.5	1892.2	1892.0	1892.3	1893.0	1893.7	1894.3	1895.0	1894.3	1893.7	1893.0
167.5°	1916.5	1916.5	1916.5	1917.2	1918.6	1919.9	1921.3	1922.7	1921.3	1919.9	1918.6
170°	1938.1	1938.1	1938.1	1938.8	1940.1	1941.5	1942.8	1944.2	1942.8	1941.5	1940.1
172.5°	1953.4	1953.4	1953.4	1954.1	1955.5	1956.8	1958.2	1959.6	1958.2	1956.8	1955.5
175°	1964.2	1964.2	1964.2	1964.9	1966.2	1967.6	1968.9	1970.3	1968.9	1967.6	1966.2
177.5°	1971.4	1971.7	1971.9	1972.6	1973.9	1975.3	1976.6	1978.0	1976.6	1975.3	1973.9
180°	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1886.3	1880.0	1875.3	1870.6	1850.2	1828.2	1825.1	1820.4	1810.9	1821.9	1817.2
5°	1837.6	1823.5	1815.7	1795.3	1770.1	1751.3	1735.6	1716.8	1708.9	1702.7	1701.1
7.5°	1778.0	1765.4	1751.3	1730.9	1699.5	1668.1	1644.6	1625.8	1610.1	1602.2	1602.2
10°	1719.9	1704.2	1685.4	1650.9	1621.1	1581.8	1556.7	1537.9	1515.9	1503.4	1492.4
12.5°	1660.3	1643.0	1625.8	1581.8	1547.3	1506.5	1470.4	1446.9	1435.9	1421.8	1402.9
15°	1600.7	1574.0	1556.7	1512.8	1468.8	1428.0	1404.5	1379.4	1354.3	1340.2	1333.9
17.5°	1537.9	1519.1	1490.8	1443.7	1395.1	1359.0	1324.5	1300.9	1271.1	1257.0	1242.9
20°	1481.4	1453.2	1424.9	1377.8	1330.7	1282.1	1247.6	1219.3	1200.5	1189.5	1177.0
22.5°	1413.9	1387.2	1363.7	1313.5	1261.7	1216.2	1178.5	1161.3	1142.4	1125.2	1112.6
25°	1355.9	1329.2	1305.6	1250.7	1194.2	1151.9	1123.6	1101.6	1081.2	1073.4	1060.8
27.5°	1294.7	1269.5	1238.2	1183.2	1133.0	1096.9	1067.1	1046.7	1031.0	1015.3	1005.9
30°	1236.6	1208.3	1180.1	1120.5	1079.7	1043.6	1015.3	990.2	977.7	969.8	954.1
32.5°	1180.1	1144.0	1120.5	1065.5	1026.3	991.8	968.2	946.3	930.6	916.5	903.9
35°	1118.9	1079.7	1056.1	1010.6	969.8	935.3	914.9	899.2	880.4	867.8	861.5
37.5°	1060.8	1027.9	1004.3	957.3	916.5	888.2	866.2	845.8	838.0	820.7	817.6
40°	998.1	969.8	947.8	902.3	864.7	842.7	819.2	800.3	786.2	778.4	767.4
42.5°	941.6	918.0	894.5	852.1	816.0	789.3	772.1	754.8	742.3	729.7	721.9
45°	889.8	864.7	842.7	801.9	765.8	742.3	725.0	704.6	701.5	684.2	676.4
47.5°	834.9	812.9	794.1	751.7	718.7	695.2	674.8	660.7	646.5	640.3	629.3
50°	781.5	759.5	737.6	699.9	670.1	646.5	626.1	610.4	602.6	593.2	583.8
52.5°	723.4	706.2	688.9	649.7	619.9	599.5	582.2	561.8	554.0	546.1	539.8
55°	674.8	649.7	630.9	597.9	571.2	549.2	530.4	514.7	506.9	500.6	492.8
57.5°	608.9	593.2	577.5	547.7	522.6	500.6	481.8	469.2	459.8	455.1	456.7
60°	552.4	535.1	525.7	494.3	469.2	452.0	434.7	422.1	412.7	408.0	406.4
62.5°	492.8	480.2	462.9	441.0	415.9	400.2	387.6	378.2	362.5	360.9	356.2
65°	434.7	425.3	409.6	389.2	368.8	354.7	340.5	328.0	321.7	313.9	309.1
67.5°	378.2	368.8	354.7	337.4	323.3	309.1	296.6	284.0	273.1	266.8	263.6
70°	323.3	315.4	306.0	285.6	268.3	257.4	247.9	240.1	229.1	226.0	224.4
72.5°	269.9	262.1	257.4	240.1	224.4	215.0	205.6	197.7	193.0	191.5	186.7
75°	221.3	213.4	207.1	191.5	182.0	175.8	166.3	163.2	158.5	156.9	155.4
77.5°	172.6	164.8	163.2	152.2	141.2	138.1	135.0	128.7	128.7	128.7	125.5
80°	124.0	122.4	120.8	109.8	105.1	102.0	100.4	95.7	92.6	89.4	87.9
82.5°	83.2	81.6	80.0	75.3	70.6	69.0	67.5	64.3	64.3	65.9	62.8
85°	50.2	47.1	45.5	43.9	40.8	40.8	42.4	40.8	40.8	40.8	39.2
87.5°	18.8	18.8	18.8	18.8	20.4	17.3	18.8	18.8	17.3	17.3	15.7
90°	12.4	13.8	15.0	17.4	19.8	22.2	24.6	26.3	28.0	29.7	31.4
92.5°	52.9	53.8	55.3	58.4	61.5	64.5	67.6	70.0	72.4	74.8	77.2
95°	102.7	103.0	104.7	108.1	111.5	114.9	118.3	120.7	123.1	125.5	127.9
97.5°	155.0	155.2	157.6	162.4	167.1	171.9	176.7	178.8	180.8	182.9	185.0
100°	215.2	215.2	217.4	221.8	226.3	230.7	235.1	238.2	241.3	244.4	247.5
102.5°	288.1	288.9	289.8	291.5	293.2	294.9	296.6	300.0	303.4	306.9	310.3
105°	357.2	358.1	359.1	361.2	363.2	365.3	367.3	369.3	371.4	373.4	375.5
107.5°	432.5	433.4	434.3	436.0	437.7	439.4	441.1	442.1	443.1	444.2	445.2
110°	510.9	511.8	512.3	513.3	514.4	515.4	516.4	517.4	518.4	519.5	520.5

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	586.8	587.1	587.8	589.2	590.5	591.9	593.3	593.6	594.0	594.3	594.6
115°	667.9	668.6	668.9	669.6	670.3	670.9	671.6	671.3	670.9	670.6	670.3
117.5°	743.7	743.9	744.2	744.9	745.6	746.2	746.9	747.3	747.6	748.0	748.3
120°	822.9	823.8	824.0	824.3	824.6	825.0	825.3	825.3	825.3	825.3	825.3
122.5°	897.4	897.6	898.1	899.1	900.2	901.2	902.2	901.8	901.5	901.1	900.8
125°	974.9	975.9	976.1	976.4	976.8	977.1	977.5	976.8	976.1	975.4	974.7
127.5°	1049.2	1049.7	1049.9	1050.2	1050.6	1050.9	1051.3	1050.9	1050.6	1050.2	1049.9
130°	1121.1	1122.0	1122.3	1123.0	1123.7	1124.3	1125.0	1124.7	1124.3	1124.0	1123.7
132.5°	1195.8	1197.3	1197.1	1196.8	1196.4	1196.1	1195.7	1195.4	1195.0	1194.7	1194.4
135°	1265.4	1266.4	1266.6	1266.9	1267.3	1267.6	1268.0	1268.0	1268.0	1268.0	1268.0
137.5°	1334.6	1335.6	1335.9	1336.6	1337.3	1338.0	1338.7	1339.0	1339.4	1339.7	1340.0
140°	1399.3	1400.1	1400.6	1401.7	1402.7	1403.8	1404.8	1405.5	1406.1	1406.8	1407.5
142.5°	1464.0	1464.7	1465.4	1466.7	1468.1	1469.4	1470.8	1471.2	1471.5	1471.9	1472.2
145°	1528.5	1529.2	1529.7	1530.8	1531.8	1532.9	1533.9	1533.9	1533.9	1533.9	1533.9
147.5°	1587.1	1587.6	1587.9	1588.6	1589.3	1590.0	1590.7	1591.7	1592.7	1593.8	1594.8
150°	1641.6	1641.4	1642.1	1643.5	1644.8	1646.2	1647.6	1647.6	1647.6	1647.6	1647.6
152.5°	1694.9	1695.2	1695.4	1695.7	1696.1	1696.4	1696.8	1697.8	1698.8	1699.9	1700.9
155°	1742.9	1742.9	1743.1	1743.4	1743.7	1744.1	1744.4	1745.8	1747.2	1748.5	1749.9
157.5°	1786.2	1785.9	1786.1	1786.4	1786.7	1787.1	1787.4	1788.8	1790.2	1791.5	1792.9
160°	1824.8	1824.3	1824.5	1824.8	1825.2	1825.5	1825.9	1827.3	1828.6	1830.0	1831.3
162.5°	1861.5	1861.2	1861.2	1861.2	1861.2	1861.2	1861.2	1862.9	1864.6	1866.3	1868.0
165°	1892.3	1892.0	1892.2	1892.5	1892.8	1893.2	1893.5	1894.9	1896.2	1897.6	1898.9
167.5°	1917.2	1916.5	1916.5	1916.5	1916.5	1916.5	1916.5	1918.6	1920.6	1922.7	1924.8
170°	1938.8	1938.1	1938.1	1938.1	1938.1	1938.1	1938.1	1940.1	1942.2	1944.2	1946.3
172.5°	1954.1	1953.4	1953.4	1953.4	1953.4	1953.4	1953.4	1955.5	1957.5	1959.6	1961.7
175°	1964.9	1964.2	1964.2	1964.2	1964.2	1964.2	1964.2	1966.2	1968.3	1970.3	1972.4
177.5°	1972.6	1971.9	1971.7	1971.4	1971.0	1970.7	1970.3	1972.4	1974.4	1976.5	1978.6
180°	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1809.4	1812.5	1804.7	1801.5	1795.3	1803.1	1804.7	1803.1	1817.2	1810.9	1814.1
5°	1704.2	1698.0	1693.3	1682.3	1682.3	1683.8	1688.5	1680.7	1685.4	1696.4	1694.8
7.5°	1588.1	1585.0	1586.5	1574.0	1564.6	1567.7	1564.6	1578.7	1586.5	1583.4	1589.7
10°	1483.0	1489.2	1475.1	1468.8	1462.6	1468.8	1467.3	1470.4	1479.8	1486.1	1497.1
12.5°	1398.2	1396.7	1388.8	1382.5	1371.6	1374.7	1384.1	1381.0	1382.5	1396.7	1395.1
15°	1318.2	1308.8	1302.5	1288.4	1291.5	1280.5	1289.9	1300.9	1305.6	1318.2	1326.0
17.5°	1238.2	1236.6	1228.7	1227.2	1209.9	1205.2	1214.6	1217.8	1222.5	1228.7	1239.7
20°	1170.7	1169.1	1158.1	1155.0	1140.9	1150.3	1147.1	1153.4	1156.6	1169.1	1173.8
22.5°	1109.5	1101.6	1098.5	1093.8	1089.1	1087.5	1093.8	1092.2	1103.2	1107.9	1109.5
25°	1053.0	1046.7	1045.1	1037.3	1034.2	1029.4	1034.2	1038.9	1051.4	1056.1	1062.4
27.5°	1001.2	996.5	993.4	987.1	982.4	982.4	985.5	991.8	996.5	999.6	1002.8
30°	954.1	951.0	941.6	938.4	933.7	933.7	933.7	936.9	944.7	954.1	958.8
32.5°	905.5	899.2	892.9	892.9	888.2	888.2	889.8	892.9	900.8	902.3	910.2
35°	858.4	852.1	847.4	844.3	845.8	839.6	842.7	847.4	856.8	860.0	864.7
37.5°	812.9	811.3	801.9	797.2	800.3	800.3	798.8	801.9	808.2	814.5	817.6
40°	762.7	759.5	759.5	754.8	756.4	750.1	754.8	758.0	761.1	767.4	772.1
42.5°	718.7	715.6	709.3	710.9	706.2	706.2	709.3	710.9	715.6	723.4	726.6
45°	671.7	671.7	668.5	663.8	665.4	660.7	663.8	665.4	671.7	679.5	676.4
47.5°	626.1	624.6	624.6	618.3	621.4	616.7	621.4	623.0	626.1	630.9	629.3
50°	582.2	577.5	579.1	577.5	575.9	575.9	579.1	579.1	582.2	582.2	586.9
52.5°	536.7	536.7	533.6	535.1	538.3	535.1	539.8	535.1	538.3	539.8	543.0
55°	495.9	492.8	494.3	492.8	499.0	494.3	499.0	495.9	499.0	497.5	500.6
57.5°	452.0	447.2	448.8	447.2	452.0	450.4	455.1	450.4	452.0	453.5	458.2
60°	401.7	401.7	401.7	398.6	403.3	403.3	401.7	401.7	408.0	411.2	409.6
62.5°	354.7	353.1	348.4	346.8	348.4	345.2	351.5	349.9	353.1	356.2	359.4
65°	302.9	299.7	298.2	295.0	295.0	293.5	295.0	301.3	302.9	304.4	312.3
67.5°	260.5	258.9	257.4	252.7	252.7	255.8	255.8	255.8	265.2	260.5	266.8
70°	222.8	219.7	216.6	215.0	215.0	216.6	218.1	219.7	218.1	224.4	226.0
72.5°	186.7	188.3	185.2	185.2	185.2	183.6	183.6	186.7	188.3	186.7	188.3
75°	155.4	155.4	153.8	155.4	155.4	153.8	153.8	156.9	156.9	155.4	160.1
77.5°	125.5	124.0	120.8	117.7	119.3	117.7	119.3	117.7	122.4	127.1	124.0
80°	87.9	86.3	86.3	86.3	87.9	86.3	89.4	86.3	87.9	87.9	89.4
82.5°	62.8	64.3	64.3	62.8	64.3	62.8	64.3	64.3	64.3	62.8	64.3
85°	40.8	40.8	40.8	40.8	39.2	40.8	40.8	40.8	42.4	40.8	42.4
87.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	18.8	17.3	18.8
90°	32.3	32.8	33.8	34.9	35.9	36.9	35.9	34.9	33.8	32.8	32.3
92.5°	78.4	78.7	79.4	80.1	80.8	81.5	80.8	80.1	79.4	78.7	78.4
95°	129.1	129.4	130.1	130.8	131.5	132.2	131.5	130.8	130.1	129.4	129.1
97.5°	186.0	186.2	186.5	186.8	187.2	187.5	187.2	186.8	186.5	186.2	186.0
100°	249.0	249.3	250.0	250.7	251.4	252.1	251.4	250.7	250.0	249.3	249.0
102.5°	312.0	312.5	313.5	314.6	315.6	316.6	315.6	314.6	313.5	312.5	312.0
105°	376.5	377.0	378.1	379.1	380.2	381.2	380.2	379.1	378.1	377.0	376.5
107.5°	445.7	445.7	445.7	445.7	445.7	445.7	445.7	445.7	445.7	445.7	445.7
110°	521.0	520.8	520.5	520.2	519.8	519.5	519.8	520.2	520.5	520.8	521.0

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	594.8	594.5	593.8	593.1	592.4	591.7	592.4	593.1	593.8	594.5	594.8
115°	670.1	669.9	669.6	669.3	668.9	668.6	668.9	669.3	669.6	669.9	670.1
117.5°	748.5	747.8	746.4	745.1	743.7	742.3	743.7	745.1	746.4	747.8	748.5
120°	825.3	824.6	823.3	821.9	820.6	819.2	820.6	821.9	823.3	824.6	825.3
122.5°	900.6	900.1	899.1	898.0	897.0	896.0	897.0	898.0	899.1	900.1	900.6
125°	974.4	974.2	973.9	973.6	973.2	972.9	973.2	973.6	973.9	974.2	974.4
127.5°	1049.7	1049.4	1048.7	1048.0	1047.3	1046.6	1047.3	1048.0	1048.7	1049.4	1049.7
130°	1123.5	1123.2	1122.5	1121.8	1121.1	1120.4	1121.1	1121.8	1122.5	1123.2	1123.5
132.5°	1194.2	1193.7	1192.7	1191.6	1190.6	1189.6	1190.6	1191.6	1192.7	1193.7	1194.2
135°	1268.0	1267.3	1265.9	1264.6	1263.2	1261.8	1263.2	1264.6	1265.9	1267.3	1268.0
137.5°	1340.2	1339.3	1337.6	1335.9	1334.2	1332.5	1334.2	1335.9	1337.6	1339.3	1340.2
140°	1407.8	1406.9	1405.2	1403.5	1401.8	1400.1	1401.8	1403.5	1405.2	1406.9	1407.8
142.5°	1472.4	1471.5	1469.8	1468.1	1466.4	1464.7	1466.4	1468.1	1469.8	1471.5	1472.4
145°	1533.9	1533.4	1532.3	1531.3	1530.2	1529.2	1530.2	1531.3	1532.3	1533.4	1533.9
147.5°	1595.3	1593.9	1591.2	1588.5	1585.7	1583.0	1585.7	1588.5	1591.2	1593.9	1595.3
150°	1647.6	1647.3	1646.6	1645.9	1645.2	1644.5	1645.2	1645.9	1646.6	1647.3	1647.6
152.5°	1701.4	1700.7	1699.3	1698.0	1696.6	1695.2	1696.6	1698.0	1699.3	1700.7	1701.4
155°	1750.6	1749.7	1748.0	1746.3	1744.6	1742.9	1744.6	1746.3	1748.0	1749.7	1750.6
157.5°	1793.6	1792.4	1790.0	1787.6	1785.2	1782.8	1785.2	1787.6	1790.0	1792.4	1793.6
160°	1832.0	1831.1	1829.4	1827.7	1826.0	1824.3	1826.0	1827.7	1829.4	1831.1	1832.0
162.5°	1868.9	1867.9	1865.8	1863.8	1861.7	1859.7	1861.7	1863.8	1865.8	1867.9	1868.9
165°	1899.6	1898.6	1896.5	1894.5	1892.4	1890.4	1892.4	1894.5	1896.5	1898.6	1899.6
167.5°	1925.8	1924.8	1922.7	1920.6	1918.6	1916.5	1918.6	1920.6	1922.7	1924.8	1925.8
170°	1947.3	1946.1	1943.7	1941.3	1938.9	1936.5	1938.9	1941.3	1943.7	1946.1	1947.3
172.5°	1962.7	1961.7	1959.6	1957.5	1955.5	1953.4	1955.5	1957.5	1959.6	1961.7	1962.7
175°	1973.4	1972.2	1969.8	1967.5	1965.1	1962.7	1965.1	1967.5	1969.8	1972.2	1973.4
177.5°	1979.6	1978.4	1976.0	1973.6	1971.2	1968.8	1971.2	1973.6	1976.0	1978.4	1979.6
180°	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1807.8	1815.7	1809.4	1804.7	1817.2	1823.5	1823.5	1834.5	1845.5	1854.9	1856.5
5°	1696.4	1708.9	1712.1	1710.5	1729.3	1738.8	1759.2	1770.1	1785.8	1796.8	1809.4
7.5°	1594.4	1611.7	1613.2	1616.4	1644.6	1660.3	1677.6	1705.8	1727.8	1743.5	1757.6
10°	1492.4	1503.4	1514.4	1528.5	1556.7	1583.4	1608.5	1638.3	1666.6	1682.3	1702.7
12.5°	1415.5	1423.3	1435.9	1445.3	1475.1	1498.7	1531.6	1572.4	1613.2	1625.8	1650.9
15°	1335.5	1340.2	1365.3	1374.7	1399.8	1439.0	1459.4	1498.7	1542.6	1566.1	1594.4
17.5°	1242.9	1271.1	1286.8	1297.8	1329.2	1360.6	1393.5	1434.3	1490.8	1512.8	1533.2
20°	1177.0	1197.4	1214.6	1228.7	1257.0	1304.1	1333.9	1366.8	1420.2	1445.3	1475.1
22.5°	1118.9	1136.2	1151.9	1167.5	1186.4	1228.7	1263.3	1308.8	1362.1	1385.7	1420.2
25°	1064.0	1081.2	1090.6	1109.5	1134.6	1164.4	1205.2	1246.0	1299.4	1326.0	1359.0
27.5°	1010.6	1027.9	1045.1	1060.8	1078.1	1106.3	1134.6	1186.4	1241.3	1272.7	1300.9
30°	965.1	973.0	988.6	1005.9	1023.2	1049.8	1082.8	1118.9	1181.7	1209.9	1244.4
32.5°	914.9	929.0	940.0	952.6	974.5	996.5	1026.3	1071.8	1122.0	1148.7	1186.4
35°	867.8	880.4	888.2	910.2	924.3	947.8	977.7	1018.5	1060.8	1090.6	1123.6
37.5°	822.3	834.9	844.3	856.8	875.7	896.1	927.4	957.3	1007.5	1032.6	1070.2
40°	775.2	786.2	797.2	811.3	828.6	853.7	872.5	910.2	951.0	979.2	1007.5
42.5°	729.7	736.0	748.5	764.2	781.5	803.5	830.1	860.0	900.8	925.9	951.0
45°	681.1	692.1	706.2	717.2	732.9	754.8	778.4	805.0	845.8	871.0	897.6
47.5°	635.6	643.4	652.8	670.1	690.5	706.2	731.3	756.4	794.1	817.6	842.7
50°	588.5	596.3	610.4	621.4	637.1	657.5	681.1	707.7	743.8	759.5	784.6
52.5°	544.5	547.7	561.8	572.8	588.5	612.0	630.9	654.4	688.9	706.2	731.3
55°	500.6	503.7	511.6	522.6	539.8	558.7	579.1	605.7	635.6	651.3	674.8
57.5°	455.1	458.2	466.1	473.9	491.2	508.4	532.0	554.0	583.8	597.9	619.9
60°	409.6	409.6	417.4	428.4	441.0	456.7	477.1	503.7	525.7	543.0	558.7
62.5°	360.9	365.6	370.4	378.2	392.3	411.2	428.4	447.2	473.9	486.5	500.6
65°	312.3	317.0	326.4	334.3	345.2	357.8	379.8	395.5	415.9	430.0	442.5
67.5°	269.9	274.6	280.9	290.3	298.2	312.3	328.0	343.7	365.6	375.1	384.5
70°	226.0	230.7	235.4	247.9	255.8	266.8	277.8	293.5	312.3	318.6	326.4
72.5°	191.5	193.0	199.3	202.4	213.4	222.8	235.4	244.8	258.9	266.8	273.1
75°	161.6	161.6	163.2	166.3	172.6	178.9	188.3	197.7	210.3	215.0	222.8
77.5°	127.1	131.8	130.3	133.4	136.5	139.7	147.5	153.8	166.3	169.5	172.6
80°	91.0	92.6	97.3	102.0	102.0	106.7	111.4	113.0	120.8	125.5	125.5
82.5°	65.9	67.5	65.9	67.5	69.0	70.6	75.3	81.6	81.6	83.2	86.3
85°	40.8	40.8	42.4	43.9	43.9	42.4	45.5	43.9	45.5	48.6	48.6
87.5°	20.4	18.8	18.8	18.8	18.8	18.8	20.4	18.8	20.4	20.4	20.4
90°	31.4	29.7	28.0	26.3	24.6	22.2	19.8	17.4	15.0	13.8	12.4
92.5°	77.2	74.8	72.4	70.0	67.6	64.5	61.5	58.4	55.3	53.8	52.9
95°	127.9	125.5	123.1	120.7	118.3	114.9	111.5	108.1	104.7	103.0	102.7
97.5°	185.0	182.9	180.8	178.8	176.7	171.9	167.1	162.4	157.6	155.2	155.0
100°	247.5	244.4	241.3	238.2	235.1	230.7	226.3	221.8	217.4	215.2	215.2
102.5°	310.3	306.9	303.4	300.0	296.6	294.9	293.2	291.5	289.8	288.9	288.1
105°	375.5	373.4	371.4	369.3	367.3	365.3	363.2	361.2	359.1	358.1	357.2
107.5°	445.2	444.2	443.1	442.1	441.1	439.4	437.7	436.0	434.3	433.4	432.5
110°	520.5	519.5	518.4	517.4	516.4	515.4	514.4	513.3	512.3	511.8	510.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	594.6	594.3	594.0	593.6	593.3	591.9	590.5	589.2	587.8	587.1	586.8
115°	670.3	670.6	670.9	671.3	671.6	670.9	670.3	669.6	668.9	668.6	667.9
117.5°	748.3	748.0	747.6	747.3	746.9	746.2	745.6	744.9	744.2	743.9	743.7
120°	825.3	825.3	825.3	825.3	825.3	825.0	824.6	824.3	824.0	823.8	822.9
122.5°	900.8	901.1	901.5	901.8	902.2	901.2	900.2	899.1	898.1	897.6	897.4
125°	974.7	975.4	976.1	976.8	977.5	977.1	976.8	976.4	976.1	975.9	974.9
127.5°	1049.9	1050.2	1050.6	1050.9	1051.3	1050.9	1050.6	1050.2	1049.9	1049.7	1049.2
130°	1123.7	1124.0	1124.3	1124.7	1125.0	1124.3	1123.7	1123.0	1122.3	1122.0	1121.1
132.5°	1194.4	1194.7	1195.0	1195.4	1195.7	1196.1	1196.4	1196.8	1197.1	1197.3	1195.8
135°	1268.0	1268.0	1268.0	1268.0	1268.0	1267.6	1267.3	1266.9	1266.6	1266.4	1265.4
137.5°	1340.0	1339.7	1339.4	1339.0	1338.7	1338.0	1337.3	1336.6	1335.9	1335.6	1334.6
140°	1407.5	1406.8	1406.1	1405.5	1404.8	1403.8	1402.7	1401.7	1400.6	1400.1	1399.3
142.5°	1472.2	1471.9	1471.5	1471.2	1470.8	1469.4	1468.1	1466.7	1465.4	1464.7	1464.0
145°	1533.9	1533.9	1533.9	1533.9	1533.9	1532.9	1531.8	1530.8	1529.7	1529.2	1528.5
147.5°	1594.8	1593.8	1592.7	1591.7	1590.7	1590.0	1589.3	1588.6	1587.9	1587.6	1587.1
150°	1647.6	1647.6	1647.6	1647.6	1647.6	1646.2	1644.8	1643.5	1642.1	1641.4	1641.6
152.5°	1700.9	1699.9	1698.8	1697.8	1696.8	1696.4	1696.1	1695.7	1695.4	1695.2	1694.9
155°	1749.9	1748.5	1747.2	1745.8	1744.4	1744.1	1743.7	1743.4	1743.1	1742.9	1742.9
157.5°	1792.9	1791.5	1790.2	1788.8	1787.4	1787.1	1786.7	1786.4	1786.1	1785.9	1786.2
160°	1831.3	1830.0	1828.6	1827.3	1825.9	1825.5	1825.2	1824.8	1824.5	1824.3	1824.8
162.5°	1868.0	1866.3	1864.6	1862.9	1861.2	1861.2	1861.2	1861.2	1861.2	1861.2	1861.5
165°	1898.9	1897.6	1896.2	1894.9	1893.5	1893.2	1892.8	1892.5	1892.2	1892.0	1892.3
167.5°	1924.8	1922.7	1920.6	1918.6	1916.5	1916.5	1916.5	1916.5	1916.5	1916.5	1917.2
170°	1946.3	1944.2	1942.2	1940.1	1938.1	1938.1	1938.1	1938.1	1938.1	1938.1	1938.8
172.5°	1961.7	1959.6	1957.5	1955.5	1953.4	1953.4	1953.4	1953.4	1953.4	1953.4	1954.1
175°	1972.4	1970.3	1968.3	1966.2	1964.2	1964.2	1964.2	1964.2	1964.2	1964.2	1964.9
177.5°	1978.6	1976.5	1974.4	1972.4	1970.3	1970.7	1971.0	1971.4	1971.7	1971.9	1972.6
180°	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9	1974.9

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1911.4	1911.4	1911.4	1911.4
2.5°	1867.4	1881.6	1895.7	1913.0
5°	1829.8	1854.9	1881.6	1906.7
7.5°	1789.0	1825.1	1859.6	1895.7
10°	1743.5	1789.0	1828.2	1878.4
12.5°	1693.3	1741.9	1796.8	1853.3
15°	1643.0	1704.2	1762.3	1826.6
17.5°	1596.0	1654.0	1718.4	1795.3
20°	1539.5	1603.8	1676.0	1757.6
22.5°	1479.8	1550.4	1628.9	1716.8
25°	1429.6	1501.8	1577.1	1669.7
27.5°	1374.7	1450.0	1523.8	1622.6
30°	1311.9	1393.5	1468.8	1570.8
32.5°	1252.3	1333.9	1417.1	1512.8
35°	1194.2	1274.3	1357.4	1454.7
37.5°	1139.3	1211.5	1293.1	1381.0
40°	1087.5	1153.4	1225.6	1305.6
42.5°	1021.6	1098.5	1166.0	1224.0
45°	965.1	1027.9	1090.6	1137.7
47.5°	899.2	962.0	1015.3	1053.0
50°	844.3	894.5	938.4	971.4
52.5°	778.4	825.4	861.5	886.6
55°	714.0	754.8	786.2	803.5
57.5°	656.0	682.6	706.2	721.9
60°	591.6	612.0	632.4	649.7
62.5°	522.6	544.5	555.5	574.4
65°	461.4	475.5	492.8	499.0
67.5°	401.7	409.6	420.6	433.1
70°	339.0	343.7	354.7	371.9
72.5°	284.0	288.7	296.6	302.9
75°	226.0	230.7	237.0	243.2
77.5°	177.3	178.9	182.0	188.3
80°	128.7	133.4	136.5	138.1
82.5°	89.4	91.0	91.0	92.6
85°	56.5	53.4	53.4	54.9
87.5°	20.4	23.5	23.5	26.7
90°	9.7	7.0	4.2	1.5
92.5°	51.2	49.5	47.8	46.1
95°	102.0	101.3	100.6	99.9
97.5°	154.7	154.4	154.0	153.7
100°	215.2	215.2	215.2	215.2
102.5°	286.4	284.7	283.0	281.3
105°	355.5	353.8	352.1	350.4
107.5°	430.8	429.1	427.4	425.7
110°	509.2	507.5	505.8	504.1

TEST NUMBER: P1035819

CATALOG NUMBER: S125RDIW-B1270D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	586.1	585.4	584.7	584.0
115°	666.5	665.2	663.8	662.4
117.5°	743.4	743.0	742.7	742.3
120°	821.2	819.5	817.8	816.1
122.5°	897.1	896.7	896.4	896.0
125°	972.8	970.8	968.7	966.7
127.5°	1048.2	1047.1	1046.1	1045.1
130°	1119.4	1117.7	1116.0	1114.3
132.5°	1192.7	1189.6	1186.5	1183.4
135°	1263.3	1261.3	1259.2	1257.2
137.5°	1332.5	1330.5	1328.4	1326.4
140°	1397.6	1395.9	1394.2	1392.5
142.5°	1462.6	1461.3	1459.9	1458.5
145°	1527.2	1525.8	1524.5	1523.1
147.5°	1586.1	1585.0	1584.0	1583.0
150°	1641.9	1642.3	1642.6	1643.0
152.5°	1694.2	1693.5	1692.9	1692.2
155°	1742.9	1742.9	1742.9	1742.9
157.5°	1786.9	1787.6	1788.3	1789.0
160°	1825.8	1826.9	1827.9	1828.9
162.5°	1862.2	1862.9	1863.6	1864.3
165°	1893.0	1893.7	1894.3	1895.0
167.5°	1918.6	1919.9	1921.3	1922.7
170°	1940.1	1941.5	1942.8	1944.2
172.5°	1955.5	1956.8	1958.2	1959.6
175°	1966.2	1967.6	1968.9	1970.3
177.5°	1973.9	1975.3	1976.6	1978.0
180°	1974.9	1974.9	1974.9	1974.9

(END OF REPORT)