

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224629

Luminaire Tested: **LSRWM2B10FL409027D010 2LBDLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224629  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSRWM2B10FL409027D010 2LBDLC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 732.5 lumens  
Efficiency: N/A  
Efficacy: 71.1 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224629

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P224629

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 0   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 100 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  |  | 102 | 101 | 100 |  |  | 95  |
| 2   | 110 | 106 | 102 | 100 |  | 108 | 104 | 101 | 99  |  | 101 | 99  | 96  |  |  | 98  | 96  | 94  |  |  | 91  |
| 3   | 106 | 100 | 96  | 93  |  | 104 | 99  | 95  | 92  |  | 97  | 93  | 91  |  |  | 94  | 92  | 89  |  |  | 87  |
| 4   | 102 | 95  | 91  | 87  |  | 100 | 94  | 90  | 87  |  | 92  | 89  | 86  |  |  | 90  | 87  | 85  |  |  | 83  |
| 5   | 98  | 91  | 86  | 83  |  | 96  | 90  | 86  | 82  |  | 88  | 85  | 82  |  |  | 87  | 83  | 81  |  |  | 79  |
| 6   | 94  | 87  | 82  | 78  |  | 93  | 86  | 82  | 78  |  | 85  | 81  | 78  |  |  | 83  | 80  | 77  |  |  | 76  |
| 7   | 91  | 83  | 78  | 75  |  | 89  | 82  | 78  | 75  |  | 81  | 77  | 74  |  |  | 80  | 77  | 74  |  |  | 72  |
| 8   | 87  | 80  | 75  | 71  |  | 86  | 79  | 75  | 71  |  | 78  | 74  | 71  |  |  | 77  | 73  | 71  |  |  | 69  |
| 9   | 84  | 76  | 72  | 68  |  | 83  | 76  | 71  | 68  |  | 75  | 71  | 68  |  |  | 74  | 71  | 68  |  |  | 67  |
| 10  | 81  | 74  | 69  | 66  |  | 81  | 73  | 69  | 66  |  | 72  | 68  | 65  |  |  | 72  | 68  | 65  |  |  | 64  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 666777 |
| 5°  | 653966 |
| 10° | 580896 |
| 15° | 458435 |
| 20° | 305774 |
| 25° | 175999 |
| 30° | 89141  |
| 35° | 41801  |
| 40° | 17091  |
| 45° | 7724   |
| 50° | 3977   |
| 55° | 2566   |
| 60° | 1472   |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P224629

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC\*MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 153.9  | 21.0      |
| 10°-20°   | 308.9  | 42.2      |
| 20°-30°   | 193.5  | 26.4      |
| 30°-40°   | 59.9   | 8.2       |
| 40°-50°   | 12.4   | 1.7       |
| 50°-60°   | 3.5    | 0.5       |
| 60°-70°   | 0.4    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 656.4  | 89.6      |
| 0°-40°    | 716.2  | 97.8      |
| 0°-60°    | 732.1  | 99.9      |
| 0°-90°    | 732.5  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 732.5  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1721 |      |
| 5°  | 1682 | 154  |
| 15° | 1143 | 309  |
| 25° | 412  | 194  |
| 35° | 88   | 60   |
| 45° | 14   | 12   |
| 55° | 4    | 3    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P224629

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1721.4 |
| 2.5°  | 1712.9 |
| 5°    | 1681.9 |
| 7.5°  | 1602.9 |
| 10°   | 1476.9 |
| 12.5° | 1321.8 |
| 15°   | 1143.2 |
| 17.5° | 937.3  |
| 20°   | 741.8  |
| 22.5° | 564.1  |
| 25°   | 411.8  |
| 27.5° | 289.6  |
| 30°   | 199.3  |
| 32.5° | 133.5  |
| 35°   | 88.4   |
| 37.5° | 55.5   |
| 40°   | 33.8   |
| 42.5° | 21.6   |
| 45°   | 14.1   |
| 47.5° | 9.4    |
| 50°   | 6.6    |
| 52.5° | 4.7    |
| 55°   | 3.8    |
| 57.5° | 2.8    |
| 60°   | 1.9    |
| 62.5° | 0.9    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)