

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224659

Luminaire Tested: **LSRWM2B10FL409027D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224659
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409027D010 2LBDLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 733.8 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224659

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224659

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99	108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93	104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87	100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82	96	90	85	82		88	84	81			86	83	80			79
6	94	87	82	78	93	86	81	78		84	80	77			83	80	77			75
7	90	83	78	74	89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71	86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68	83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65	80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	664298
5°	652216
10°	579795
15°	455989
20°	303424
25°	174204
30°	87978
35°	41375
40°	16636
45°	8272
50°	4520
55°	3174
60°	2944
65°	1741
70°	2152
75°	1347
80°	2008
85°	0



TEST NUMBER: P224659

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.6	20.9
10°-20°	308.0	42.0
20°-30°	191.6	26.1
30°-40°	58.9	8.0
40°-50°	13.0	1.8
50°-60°	4.6	0.6
60°-70°	2.3	0.3
70°-80°	1.3	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.3	89.0
0°-40°	712.2	97.1
0°-60°	729.7	99.4
0°-90°	733.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	733.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1715	
5°	1677	154
15°	1137	308
25°	408	192
35°	88	59
45°	15	13
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224659

CATALOG NUMBER: LSRWM2B10FL409027D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1715.0
2.5°	1707.5
5°	1677.4
7.5°	1601.2
10°	1474.1
12.5°	1321.6
15°	1137.1
17.5°	935.7
20°	736.1
22.5°	558.2
25°	407.6
27.5°	287.1
30°	196.7
32.5°	132.7
35°	87.5
37.5°	52.7
40°	32.9
42.5°	22.6
45°	15.1
47.5°	10.4
50°	7.5
52.5°	6.6
55°	4.7
57.5°	3.8
60°	3.8
62.5°	2.8
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)