

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035903

Luminaire Tested: S125RDIW-B375D1340UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035903
REPORT IS A COMBINATION OF REPORTS P1006438 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D1340UB40-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6739.0 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035903

CATALOG NUMBER: S125RDIW-B375D1340UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035903

CATALOG NUMBER: S125RDIW-B375D1340UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	41	39	26	25	25
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	18	17	16
5	64	53	45	39	56	47	40	35	36	31	28	26	23	21	16	15	14
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12
7	54	42	35	29	47	38	31	27	29	25	21	21	18	16	14	12	11
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3794	3794	3794
5°	3794	3699	3705
10°	3758	3606	3575
15°	3704	3476	3402
20°	3639	3319	3221
25°	3562	3165	3028
30°	3471	2997	2825
35°	3376	2826	2609
40°	3287	2650	2397
45°	3179	2460	2177
50°	3069	2258	1951
55°	2942	2061	1719
60°	2813	1834	1477
65°	2658	1580	1216
70°	2477	1287	957
75°	2228	967	697
80°	1878	627	471
85°	1407	336	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3179 cd/sqm

TEST NUMBER: P1035903

CATALOG NUMBER: S125RDIW-B375D1340UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.7	0.8
10°-20°	155.7	2.3
20°-30°	225.8	3.4
30°-40°	257.3	3.8
40°-50°	250.8	3.7
50°-60°	211.0	3.1
60°-70°	147.9	2.2
70°-80°	75.8	1.1
80°-90°	21.5	0.3
90°-100°	59.0	0.9
100°-110°	392.1	5.8
110°-120°	706.2	10.5
120°-130°	906.4	13.5
130°-140°	974.9	14.5
140°-150°	915.0	13.6
150°-160°	740.1	11.0
160°-170°	478.7	7.1
170°-180°	165.1	2.4
0°-30°	437.3	6.5
0°-40°	694.6	10.3
0°-60°	1156.4	17.2
0°-90°	1401.6	20.8
90°-120°	1157.3	17.2
90°-150°	3953.6	58.7
90°-180°	5337.0	79.2
0°-180°	6739.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	592	592	592	592	592	
5°	591	589	584	589	588	56
15°	562	560	550	550	546	159
25°	510	503	487	481	476	235
35°	439	428	408	395	389	275
45°	360	347	322	304	297	277
55°	273	258	234	213	206	244
65°	185	170	146	128	121	183
75°	98	85	66	56	53	104
85°	25	16	14	14	13	27
90°	1	12	21	27	31	5
95°	73	70	21	27	27	90
105°	379	384	384	384	382	401
115°	711	717	719	714	706	705
125°	1011	1020	1020	1015	1011	903
135°	1261	1269	1266	1264	1256	972
145°	1462	1464	1464	1466	1458	914
155°	1610	1602	1605	1609	1598	742
165°	1699	1691	1692	1700	1690	480
175°	1738	1730	1731	1741	1730	165
180°	1738	1738	1738	1738	1738	

TEST NUMBER: P1035903

CATALOG NUMBER: S125RDIW-B375D1340UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	592.1	592.1	592.1	592.1	592.1
2.5°	593.5	592.1	587.7	592.1	591.7
5°	591.2	589.4	584.5	589.0	588.1
7.5°	586.8	585.0	579.2	582.7	581.8
10°	580.1	578.7	572.5	573.8	572.5
12.5°	572.5	570.7	561.7	562.6	560.4
15°	562.2	559.5	550.1	549.6	545.6
17.5°	551.4	547.4	536.2	534.0	530.9
20°	538.5	534.0	519.7	517.4	513.4
22.5°	524.2	519.7	504.5	499.6	496.4
25°	509.8	503.1	486.6	480.8	475.9
27.5°	493.7	485.7	468.3	460.6	455.7
30°	475.9	467.4	448.6	438.3	434.3
32.5°	458.4	448.1	428.9	417.3	411.9
35°	439.2	428.4	408.3	395.4	389.1
37.5°	420.8	407.9	387.3	372.1	365.8
40°	401.2	387.7	366.3	349.3	343.9
42.5°	380.6	366.7	344.4	328.3	319.8
45°	359.6	346.6	322.0	304.1	297.4
47.5°	337.7	324.2	299.6	281.3	273.7
50°	317.1	302.3	276.8	258.1	251.3
52.5°	294.7	279.5	255.8	235.2	228.5
55°	272.8	258.5	233.5	213.3	206.2
57.5°	250.4	235.2	211.1	191.4	185.2
60°	229.0	213.3	189.2	169.5	162.8
62.5°	206.2	191.4	166.8	148.9	142.2
65°	184.7	169.5	145.8	127.9	121.2
67.5°	163.2	148.0	125.2	108.2	102.9
70°	141.3	126.1	103.8	89.9	84.5
72.5°	119.9	105.1	84.5	72.0	68.9
75°	98.4	85.0	66.2	56.4	53.2
77.5°	76.5	65.7	50.1	42.5	39.8
80°	58.1	47.4	34.9	30.9	30.0
82.5°	40.3	30.9	23.3	21.9	21.5
85°	24.6	16.5	14.3	13.9	13.4
87.5°	10.3	7.2	6.7	6.7	6.3
90°	1.3	11.6	20.6	27.0	30.9
92.5°	24.5	12.9	20.6	27.0	28.3
95°	73.4	69.6	20.6	27.0	27.0
97.5°	137.8	145.5	23.2	25.8	27.0
100°	215.1	219.0	224.1	32.2	27.0
102.5°	293.7	298.8	301.4	304.0	195.8
105°	378.7	383.8	383.8	383.8	382.5
107.5°	466.3	466.3	468.8	470.1	465.0
110°	551.3	551.3	553.9	550.0	551.3

TEST NUMBER: P1035903

CATALOG NUMBER: S125RDIW-B375D1340UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	631.1	635.0	636.3	631.1	628.6
115°	711.0	717.4	718.7	713.6	705.8
117.5°	794.7	794.7	799.9	792.1	789.6
120°	872.0	870.7	874.6	872.0	865.6
122.5°	940.3	946.7	948.0	945.4	937.7
125°	1011.1	1020.1	1020.1	1015.0	1011.1
127.5°	1079.4	1085.8	1084.5	1082.0	1071.6
130°	1141.2	1147.6	1148.9	1145.1	1138.6
132.5°	1203.0	1210.8	1206.9	1206.9	1200.5
135°	1261.0	1268.7	1266.1	1263.6	1255.8
137.5°	1315.1	1322.8	1320.2	1320.2	1313.8
140°	1367.9	1370.5	1369.2	1371.8	1364.0
142.5°	1415.6	1416.8	1419.4	1419.4	1411.7
145°	1461.9	1464.5	1464.5	1465.8	1458.1
147.5°	1503.1	1503.1	1504.4	1505.7	1496.7
150°	1541.8	1539.2	1541.8	1544.4	1534.1
152.5°	1579.1	1572.7	1575.3	1577.8	1568.8
155°	1610.0	1602.3	1604.9	1608.8	1598.5
157.5°	1634.5	1630.7	1630.7	1634.5	1624.2
160°	1660.3	1652.6	1653.8	1659.0	1648.7
162.5°	1680.9	1673.2	1674.4	1682.2	1670.6
165°	1698.9	1691.2	1692.5	1700.2	1689.9
167.5°	1713.1	1705.4	1706.6	1715.7	1704.1
170°	1724.7	1715.7	1717.0	1727.3	1715.7
172.5°	1732.4	1723.4	1726.0	1735.0	1723.4
175°	1737.6	1729.8	1731.1	1741.4	1729.8
177.5°	1741.4	1733.7	1735.0	1744.0	1733.7
180°	1737.6	1737.6	1737.6	1737.6	1737.6

(END OF REPORT)