

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224455

Luminaire Tested: **LSSQ2B10FL409727D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL409727D010 2LBDL*WH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 684.6 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224455

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224455

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		87	83	81		85
6	94	87	82	78	93	86	81	78	85	80	77		83	80	77		82
7	91	83	78	75	89	82	78	74	81	77	74		80	76	74		79
8	87	79	75	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	631684
5°	607773
10°	534996
15°	420218
20°	285699
25°	166810
30°	84981
35°	40193
40°	17546
45°	7614
50°	3676
55°	2364
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224455

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.8	20.9
10°-20°	284.9	41.6
20°-30°	182.9	26.7
30°-40°	58.0	8.5
40°-50°	12.4	1.8
50°-60°	3.2	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.6	89.2
0°-40°	668.6	97.7
0°-60°	684.2	99.9
0°-90°	684.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	684.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1631	
5°	1563	143
15°	1048	285
25°	390	183
35°	85	58
45°	14	12
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224455

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1630.8
2.5°	1615.2
5°	1563.1
7.5°	1478.1
10°	1360.2
12.5°	1216.2
15°	1047.9
17.5°	868.3
20°	693.1
22.5°	529.1
25°	390.3
27.5°	278.4
30°	190.0
32.5°	127.5
35°	85.0
37.5°	56.4
40°	34.7
42.5°	21.7
45°	13.9
47.5°	9.5
50°	6.1
52.5°	4.3
55°	3.5
57.5°	2.6
60°	1.7
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)