

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224664

Luminaire Tested: **LSSQ2B10FL409727D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL409727D010 2LBDLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 660.4 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224664

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224664

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	87	82	78		93	86	81	78		84	80	77		83	80	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	597869
5°	586971
10°	521780
15°	410394
20°	273086
25°	156766
30°	79211
35°	37262
40°	15018
45°	7450
50°	4098
55°	2836
60°	2634
65°	1558
70°	1925
75°	1197
80°	1785
85°	0



TEST NUMBER: P224664

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.3	20.9
10°-20°	277.2	42.0
20°-30°	172.5	26.1
30°-40°	53.0	8.0
40°-50°	11.7	1.8
50°-60°	4.1	0.6
60°-70°	2.1	0.3
70°-80°	1.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	587.9	89.0
0°-40°	641.0	97.1
0°-60°	656.7	99.5
0°-90°	660.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	660.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1544	
5°	1510	138
15°	1023	277
25°	367	172
35°	79	53
45°	14	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224664

CATALOG NUMBER: LSSQ2B10FL409727D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1543.5
2.5°	1536.7
5°	1509.6
7.5°	1441.0
10°	1326.6
12.5°	1189.4
15°	1023.4
17.5°	842.1
20°	662.5
22.5°	502.4
25°	366.8
27.5°	258.4
30°	177.1
32.5°	119.4
35°	78.8
37.5°	47.4
40°	29.7
42.5°	20.3
45°	13.6
47.5°	9.3
50°	6.8
52.5°	5.9
55°	4.2
57.5°	3.4
60°	3.4
62.5°	2.5
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)