

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035920

Luminaire Tested: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035920
REPORT IS A COMBINATION OF REPORTS P1006479 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D1560UB40-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7708.0 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	18		
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16		
2	83	76	70	65	73	67	62	58	51	48	45	35	34	32	21	20	20	13		
3	76	67	60	54	66	59	53	49	45	41	38	31	29	27	19	18	17	12		
4	69	59	52	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10		
5	63	52	45	39	56	46	40	35	35	31	28	25	22	20	15	14	13	9		
6	58	47	39	34	51	42	35	30	32	27	24	23	20	17	14	12	11	8		
7	54	42	35	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7		
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	10	9	6		
9	46	34	27	23	40	31	25	21	24	19	16	17	14	12	11	9	8	6		
10	43	31	25	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3492	3492	3492	3492
5°	3489	3936	3489	3025
10°	3469	4422	3458	2615
15°	3432	4679	3408	2277
20°	3387	5051	3356	2058
25°	3327	5717	3289	1868
30°	3267	6077	3218	1731
35°	3189	4998	3144	1605
40°	3050	3394	3024	1491
45°	2868	2440	2864	1379
50°	2681	1876	2694	1275
55°	2471	1525	2467	1175
60°	2275	1250	2265	1043
65°	2048	1042	2061	840
70°	1858	836	1851	699
75°	1571	633	1571	575
80°	1273	386	1257	386
85°	898	203	869	229

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 4970 cd/sqm

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	0.7
10°-20°	153.2	2.0
20°-30°	242.9	3.2
30°-40°	293.6	3.8
40°-50°	261.4	3.4
50°-60°	200.4	2.6
60°-70°	130.2	1.7
70°-80°	63.2	0.8
80°-90°	17.9	0.2
90°-100°	69.5	0.9
100°-110°	462.4	6.0
110°-120°	832.6	10.8
120°-130°	1068.7	13.9
130°-140°	1149.4	14.9
140°-150°	1078.8	14.0
150°-160°	872.6	11.3
160°-170°	564.3	7.3
170°-180°	194.6	2.5
0°-30°	448.4	5.8
0°-40°	742.0	9.6
0°-60°	1203.8	15.6
0°-90°	1415.0	18.4
90°-120°	1364.5	17.7
90°-150°	4661.4	60.5
90°-180°	6293.0	81.6
0°-180°	7708.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	545	545	545	545	545	
5°	544	625	544	480	544	52
15°	521	750	517	365	521	147
25°	476	898	471	294	476	219
35°	415	746	409	239	415	258
45°	324	333	324	188	324	250
55°	229	183	229	141	229	205
65°	142	104	143	84	142	142
75°	69	48	69	44	69	74
85°	16	10	15	12	16	18
90°	2	36	2	36	2	5
95°	87	32	87	32	87	106
105°	446	451	446	451	446	473
115°	838	832	838	832	838	831
125°	1192	1192	1192	1192	1192	1065
135°	1487	1481	1487	1481	1487	1146
145°	1724	1719	1724	1719	1724	1078
155°	1898	1885	1898	1885	1898	875
165°	2003	1992	2003	1992	2003	566
175°	2049	2040	2049	2040	2049	195
180°	2049	2049	2049	2049	2049	

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	545.5	549.9	551.3	554.9	558.9	559.8	562.0	565.1	566.9	566.5	566.5
5°	543.7	551.3	556.6	562.9	570.5	573.6	576.3	583.0	588.4	591.5	596.9
7.5°	540.5	551.7	560.7	570.1	581.7	587.1	592.9	602.3	612.1	618.4	624.2
10°	535.6	549.9	562.5	576.3	592.0	600.0	607.2	621.5	633.6	641.7	655.1
12.5°	528.5	546.3	563.8	582.1	601.8	610.3	620.2	635.8	652.8	664.5	675.7
15°	520.8	542.3	561.1	583.0	606.8	619.7	632.3	648.8	664.0	677.0	690.0
17.5°	511.9	534.7	558.0	583.0	609.9	622.9	633.6	653.3	669.4	682.4	694.0
20°	501.2	526.7	553.1	580.8	608.1	620.2	630.5	651.9	666.3	680.1	696.7
22.5°	489.5	517.3	545.5	572.7	599.6	612.6	624.7	643.4	659.1	677.9	699.4
25°	476.1	506.5	535.2	562.5	588.0	600.0	610.8	631.4	653.3	677.0	701.2
27.5°	462.7	492.2	519.9	545.0	572.7	583.9	594.7	620.6	646.6	671.6	704.7
30°	447.9	477.9	502.1	525.3	552.2	563.8	577.2	606.8	636.3	670.3	710.6
32.5°	431.4	458.6	481.0	505.2	529.3	543.7	560.7	592.9	626.9	667.6	719.1
35°	414.8	436.7	457.3	480.1	509.2	524.4	541.0	575.0	617.5	666.3	726.2
37.5°	393.8	414.8	430.9	454.2	484.2	502.1	518.6	558.0	606.3	663.1	725.8
40°	372.3	390.2	405.4	429.6	462.2	478.8	496.7	539.6	594.7	654.2	715.0
42.5°	349.0	364.2	380.8	404.1	435.8	451.9	472.5	522.6	578.6	641.7	687.3
45°	324.4	339.2	353.0	377.2	409.0	426.4	448.8	500.3	558.9	615.3	642.6
47.5°	300.2	313.2	328.0	349.0	381.2	400.5	423.3	478.3	532.5	579.9	582.1
50°	277.0	287.3	299.8	321.3	354.8	373.2	396.9	448.4	501.2	533.8	511.9
52.5°	252.8	262.2	275.2	294.0	325.3	346.8	367.4	418.8	463.1	485.0	444.8
55°	229.1	237.2	250.6	271.6	298.9	315.5	336.5	384.4	423.3	423.7	379.9
57.5°	205.8	213.0	224.2	243.0	268.5	287.7	307.0	348.6	375.0	367.4	318.6
60°	185.2	189.7	200.0	218.4	242.1	255.9	276.5	311.4	328.9	315.0	262.7
62.5°	163.8	168.2	176.3	191.1	213.4	228.2	241.2	269.8	281.9	260.9	217.9
65°	142.3	147.7	153.5	165.1	186.1	196.0	207.6	228.7	240.3	215.7	178.5
67.5°	123.5	126.2	132.0	144.1	158.8	167.8	175.9	190.2	192.4	172.7	142.3
70°	106.0	106.9	112.3	119.5	130.7	136.0	142.7	151.2	151.2	135.1	111.0
72.5°	86.4	87.7	91.7	99.3	106.0	108.7	111.0	116.3	115.4	100.7	84.1
75°	69.4	70.3	73.4	77.0	79.6	84.6	86.4	85.5	85.0	72.5	63.1
77.5°	53.7	54.1	56.4	59.5	60.0	61.7	60.4	60.4	56.4	49.2	44.3
80°	39.4	39.8	40.7	41.6	41.6	41.6	41.6	39.4	36.7	32.2	30.9
82.5°	26.4	26.4	26.8	27.7	27.3	26.4	25.5	23.3	21.5	20.1	19.2
85°	15.7	15.7	16.1	15.7	13.9	13.4	12.5	12.1	11.6	11.2	11.2
87.5°	7.6	7.2	6.3	5.4	5.4	5.4	5.4	5.4	5.4	4.9	4.9
90°	1.5	4.2	6.9	9.6	12.3	13.7	14.9	17.2	19.6	21.9	24.3
92.5°	28.9	25.9	22.8	19.8	16.7	15.2	16.2	18.2	20.3	22.3	24.3
95°	86.6	85.6	84.6	83.5	82.5	82.0	75.6	62.8	49.9	37.1	24.3
97.5°	162.5	164.5	166.5	168.6	170.6	171.6	155.6	123.5	91.4	59.4	27.3
100°	253.6	254.6	255.6	256.7	257.7	258.2	258.9	260.2	261.5	262.9	264.2
102.5°	346.2	347.6	348.9	350.3	351.6	352.3	352.6	353.3	354.0	354.7	355.4
105°	446.5	447.9	449.2	450.6	451.9	452.6	452.6	452.6	452.6	452.6	452.6
107.5°	549.7	549.7	549.7	549.7	549.7	549.7	550.0	550.7	551.4	552.1	552.8
110°	650.0	650.0	650.0	650.0	650.0	650.0	650.3	651.0	651.7	652.3	653.0

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	744.1	745.1	746.1	747.2	748.2	748.7	748.9	749.2	749.5	749.9	750.2
115°	838.3	840.0	841.7	843.4	845.1	845.9	846.1	846.4	846.7	847.1	847.4
117.5°	937.0	937.0	937.0	937.0	937.0	937.0	937.7	939.0	940.4	941.7	943.1
120°	1028.1	1027.8	1027.4	1027.1	1026.8	1026.6	1027.1	1028.1	1029.1	1030.1	1031.1
122.5°	1108.6	1110.3	1112.0	1113.7	1115.4	1116.2	1116.4	1116.7	1117.0	1117.4	1117.7
125°	1192.1	1194.5	1196.9	1199.2	1201.6	1202.8	1202.8	1202.8	1202.8	1202.8	1202.8
127.5°	1272.6	1274.3	1276.0	1277.7	1279.4	1280.2	1280.0	1279.7	1279.4	1279.0	1278.7
130°	1345.5	1347.2	1348.9	1350.6	1352.3	1353.1	1353.3	1353.6	1353.9	1354.3	1354.6
132.5°	1418.4	1420.4	1422.4	1424.5	1426.5	1427.5	1427.0	1426.0	1425.0	1424.0	1423.0
135°	1486.7	1488.7	1490.7	1492.8	1494.8	1495.8	1495.5	1494.8	1494.1	1493.5	1492.8
137.5°	1550.5	1552.5	1554.5	1556.6	1558.6	1559.6	1559.3	1558.6	1557.9	1557.3	1556.6
140°	1612.8	1613.5	1614.1	1614.8	1615.5	1615.8	1615.6	1615.3	1615.0	1614.6	1614.3
142.5°	1669.0	1669.3	1669.7	1670.0	1670.3	1670.5	1670.8	1671.5	1672.2	1672.8	1673.5
145°	1723.6	1724.3	1725.0	1725.7	1726.4	1726.7	1726.7	1726.7	1726.7	1726.7	1726.7
147.5°	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.4	1772.7	1773.1	1773.4	1773.8
150°	1817.8	1817.1	1816.5	1815.8	1815.1	1814.8	1815.1	1815.8	1816.5	1817.1	1817.8
152.5°	1861.8	1860.1	1858.4	1856.7	1855.0	1854.2	1854.5	1855.2	1855.9	1856.6	1857.3
155°	1898.3	1896.3	1894.3	1892.2	1890.2	1889.2	1889.5	1890.2	1890.9	1891.5	1892.2
157.5°	1927.1	1926.1	1925.1	1924.1	1923.1	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6
160°	1957.5	1955.5	1953.5	1951.4	1949.4	1948.4	1948.6	1948.9	1949.2	1949.6	1949.9
162.5°	1981.8	1979.8	1977.8	1975.7	1973.7	1972.7	1972.9	1973.2	1973.5	1973.9	1974.2
165°	2003.1	2001.1	1999.1	1997.0	1995.0	1994.0	1994.2	1994.5	1994.8	1995.2	1995.5
167.5°	2019.8	2017.8	2015.8	2013.7	2011.7	2010.7	2010.9	2011.2	2011.5	2011.9	2012.2
170°	2033.4	2031.0	2028.7	2026.3	2024.0	2022.8	2023.0	2023.3	2023.6	2024.0	2024.3
172.5°	2042.6	2040.2	2037.8	2035.5	2033.1	2031.9	2032.2	2032.9	2033.6	2034.3	2035.0
175°	2048.6	2046.6	2044.6	2042.5	2040.5	2039.5	2039.7	2040.0	2040.3	2040.7	2041.0
177.5°	2053.2	2051.2	2049.2	2047.1	2045.1	2044.1	2044.3	2044.6	2044.9	2045.3	2045.6
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	568.7	571.9	574.5	573.2	578.6	578.1	579.0	580.8	581.3	580.4	578.6
5°	599.6	604.1	611.7	615.7	614.8	618.4	620.2	622.9	625.5	624.7	624.7
7.5°	634.1	640.3	647.9	658.2	659.6	662.7	668.1	668.1	671.2	669.8	669.4
10°	664.0	671.6	683.7	691.8	695.4	697.1	702.5	704.3	707.9	708.3	708.3
12.5°	688.6	702.1	710.1	718.2	720.0	722.6	726.7	729.4	730.7	730.7	729.4
15°	701.6	712.4	721.8	730.3	735.2	737.4	741.4	744.6	746.4	750.4	751.3
17.5°	707.0	720.0	735.2	747.3	755.8	758.0	766.1	768.7	772.3	774.1	776.3
20°	714.6	733.4	751.7	766.5	774.6	780.4	788.9	801.4	805.0	805.0	803.6
22.5°	721.3	745.5	770.5	794.2	801.0	812.6	828.2	841.7	847.0	849.3	847.5
25°	729.4	762.5	795.1	824.7	843.0	851.5	872.5	888.7	894.9	898.5	899.4
27.5°	743.2	784.8	826.5	864.0	882.8	892.7	914.6	928.5	936.1	939.2	937.0
30°	758.9	809.9	858.2	891.8	904.3	916.4	930.7	936.1	934.3	934.3	941.0
32.5°	775.0	827.8	870.8	892.7	897.2	895.4	889.6	873.4	864.0	864.0	869.9
35°	784.0	829.6	851.5	844.4	826.9	816.6	784.8	766.9	746.8	745.5	752.2
37.5°	779.0	798.7	789.8	742.8	719.1	699.4	649.7	630.0	615.3	594.7	626.4
40°	744.6	737.9	691.3	623.8	597.4	569.6	530.2	510.6	490.0	486.8	494.4
42.5°	686.4	646.6	578.6	513.2	486.4	466.7	436.7	417.5	404.5	399.1	408.1
45°	613.9	551.3	483.3	431.4	401.8	391.5	364.2	347.2	337.4	333.4	339.6
47.5°	525.3	462.2	397.8	353.9	336.5	326.2	307.9	293.1	284.6	281.9	284.6
50°	446.1	381.2	327.1	298.9	283.2	274.7	259.5	250.1	243.4	241.6	246.1
52.5°	377.7	318.6	277.4	252.4	242.1	234.9	224.2	216.1	212.1	210.3	213.4
55°	316.4	268.5	235.4	213.9	206.3	201.8	192.4	187.9	183.5	183.0	186.1
57.5°	262.2	229.1	198.7	183.5	181.2	174.5	166.5	162.4	160.2	159.7	161.1
60°	218.4	188.8	170.5	157.1	153.9	148.6	144.1	141.4	138.7	137.8	138.7
62.5°	181.7	158.4	143.6	134.7	130.2	128.9	123.9	120.8	120.4	120.4	121.3
65°	149.9	130.2	120.8	113.7	110.5	109.2	105.6	103.4	103.8	103.8	104.3
67.5°	122.2	107.8	99.3	95.8	93.1	92.6	89.0	88.1	87.3	87.3	88.1
70°	97.1	88.1	81.9	80.1	79.6	76.5	75.2	74.7	73.4	73.8	73.8
72.5°	76.1	70.3	66.7	64.0	64.4	62.6	60.9	60.9	60.0	61.3	61.3
75°	56.4	53.7	51.0	50.1	51.0	50.1	48.8	48.3	48.8	48.3	48.3
77.5°	41.6	40.3	39.4	38.9	38.9	37.1	36.2	37.1	35.3	36.2	36.2
80°	29.1	27.3	26.8	26.0	26.4	25.1	25.5	24.6	24.6	24.6	24.6
82.5°	18.3	17.9	17.9	17.9	17.5	17.5	17.5	17.5	17.5	17.5	17.0
85°	11.2	10.7	10.7	10.7	10.3	10.3	10.3	10.3	10.3	10.3	10.3
87.5°	4.5	4.9	4.9	5.4	4.9	4.5	4.5	4.5	4.9	4.9	4.5
90°	26.0	27.7	29.4	31.1	31.9	32.4	33.4	34.4	35.4	36.4	35.4
92.5°	26.0	27.7	29.4	31.1	31.9	32.1	32.4	32.7	33.1	33.4	33.1
95°	26.0	27.7	29.4	31.1	31.9	31.9	31.9	31.9	31.9	31.9	31.9
97.5°	28.0	28.7	29.4	30.1	30.4	30.6	30.9	31.2	31.6	31.9	31.6
100°	213.9	163.7	113.4	63.1	38.0	37.3	36.0	34.6	33.3	31.9	33.3
102.5°	356.1	356.7	357.4	358.1	358.4	344.2	315.9	287.5	259.2	230.8	259.2
105°	452.6	452.6	452.6	452.6	452.6	452.4	452.1	451.7	451.4	451.0	451.4
107.5°	553.1	553.5	553.8	554.1	554.3	553.6	552.3	550.9	549.6	548.2	549.6
110°	652.0	651.0	650.0	649.0	648.5	648.7	649.0	649.3	649.7	650.0	649.7

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	748.8	747.5	746.1	744.8	744.1	743.8	743.1	742.4	741.8	741.1	741.8
115°	846.0	844.7	843.3	842.0	841.3	840.3	838.3	836.2	834.2	832.2	834.2
117.5°	941.1	939.1	937.0	935.0	934.0	933.7	933.0	932.3	931.6	930.9	931.6
120°	1030.4	1029.8	1029.1	1028.4	1028.1	1027.3	1025.6	1023.9	1022.2	1020.5	1022.2
122.5°	1117.0	1116.4	1115.7	1115.0	1114.7	1113.7	1111.7	1109.6	1107.6	1105.6	1107.6
125°	1201.4	1200.1	1198.7	1197.4	1196.7	1196.2	1195.2	1194.1	1193.1	1192.1	1193.1
127.5°	1278.0	1277.3	1276.6	1275.9	1275.6	1274.3	1271.6	1268.9	1266.2	1263.5	1266.2
130°	1353.6	1352.6	1351.6	1350.6	1350.1	1349.3	1347.6	1345.9	1344.2	1342.5	1344.2
132.5°	1423.0	1423.0	1423.0	1423.0	1423.0	1422.2	1420.5	1418.8	1417.1	1415.4	1417.1
135°	1492.1	1491.5	1490.8	1490.1	1489.8	1488.8	1486.8	1484.7	1482.7	1480.7	1482.7
137.5°	1556.6	1556.6	1556.6	1556.6	1556.6	1555.8	1554.1	1552.4	1550.7	1549.0	1550.7
140°	1615.0	1615.6	1616.3	1617.0	1617.3	1616.3	1614.3	1612.2	1610.2	1608.2	1610.2
142.5°	1673.5	1673.5	1673.5	1673.5	1673.5	1672.5	1670.5	1668.4	1666.4	1664.4	1666.4
145°	1727.0	1727.4	1727.7	1728.0	1728.2	1727.2	1725.2	1723.1	1721.1	1719.1	1721.1
147.5°	1774.1	1774.5	1774.8	1775.1	1775.3	1774.1	1771.7	1769.4	1767.0	1764.6	1767.0
150°	1818.5	1819.1	1819.8	1820.5	1820.8	1819.5	1816.8	1814.1	1811.4	1808.7	1811.4
152.5°	1858.0	1858.6	1859.3	1860.0	1860.3	1859.1	1856.8	1854.4	1852.1	1849.7	1852.1
155°	1893.2	1894.2	1895.3	1896.3	1896.8	1895.4	1892.7	1890.0	1887.3	1884.6	1887.3
157.5°	1923.6	1924.6	1925.6	1926.6	1927.1	1925.8	1923.1	1920.4	1917.7	1915.0	1917.7
160°	1951.3	1952.6	1954.0	1955.3	1956.0	1954.6	1951.9	1949.2	1946.5	1943.8	1946.5
162.5°	1976.2	1978.2	1980.3	1982.3	1983.3	1981.8	1978.8	1975.7	1972.7	1969.7	1972.7
165°	1997.5	1999.5	2001.6	2003.6	2004.6	2003.2	2000.5	1997.8	1995.1	1992.4	1995.1
167.5°	2014.6	2016.9	2019.3	2021.6	2022.8	2021.3	2018.2	2015.2	2012.1	2009.1	2012.1
170°	2027.0	2029.7	2032.4	2035.1	2036.5	2035.0	2031.9	2028.9	2025.8	2022.8	2025.8
172.5°	2037.4	2039.7	2042.1	2044.4	2045.6	2044.1	2041.0	2038.0	2034.9	2031.9	2034.9
175°	2043.7	2046.4	2049.1	2051.8	2053.2	2051.7	2048.6	2045.6	2042.5	2039.5	2042.5
177.5°	2048.0	2050.3	2052.7	2055.0	2056.2	2054.9	2052.2	2049.5	2046.8	2044.1	2046.8
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	580.8	577.7	579.0	577.7	576.3	575.0	571.9	567.4	563.8	561.1	560.7
5°	625.5	621.5	618.8	617.5	614.8	611.2	605.4	598.7	590.6	587.5	581.3
7.5°	666.7	665.4	659.1	658.2	656.4	649.7	639.9	630.9	620.6	612.1	604.1
10°	705.6	702.5	698.0	691.8	690.9	682.4	673.0	660.5	647.0	639.0	624.7
12.5°	729.8	726.2	721.3	717.3	715.0	709.7	696.7	684.2	672.1	657.3	644.8
15°	747.3	742.8	733.8	730.7	728.0	720.9	711.5	698.5	682.4	672.1	654.2
17.5°	771.0	765.6	756.7	750.8	745.9	734.7	721.3	703.9	688.6	677.0	660.9
20°	798.3	790.2	778.6	771.0	763.8	750.8	732.0	711.5	689.5	675.2	658.7
22.5°	843.5	828.2	809.9	799.2	789.3	766.9	744.6	719.1	694.5	673.0	652.8
25°	887.3	872.1	849.3	834.5	819.3	793.3	763.8	728.5	697.1	672.1	645.7
27.5°	928.0	912.4	891.3	873.4	858.7	819.7	780.8	741.0	701.2	666.7	639.9
30°	937.4	930.7	914.6	898.9	885.5	849.7	804.5	754.0	706.1	661.8	631.8
32.5°	880.6	897.2	901.2	898.9	890.4	864.9	823.3	770.1	713.3	659.6	618.4
35°	762.5	792.5	823.3	839.9	847.9	851.5	826.9	778.1	718.2	656.0	609.4
37.5°	632.3	661.3	710.1	734.7	762.0	797.8	807.7	776.3	715.9	653.3	595.1
40°	519.5	556.6	596.9	619.3	643.0	707.4	756.2	752.6	708.8	643.4	583.9
42.5°	422.8	446.1	481.5	506.1	535.2	607.2	672.5	704.7	687.3	631.4	569.6
45°	352.6	370.5	395.6	420.6	438.5	503.8	581.3	634.1	650.6	609.9	547.7
47.5°	297.1	310.5	332.5	348.1	367.4	418.8	485.9	560.2	595.1	579.5	524.4
50°	254.6	265.3	282.8	292.6	309.6	353.9	405.0	482.8	535.6	537.4	493.5
52.5°	217.5	228.2	243.0	251.5	261.8	291.7	343.2	409.0	469.8	492.2	458.2
55°	189.3	195.5	207.6	214.3	223.7	252.8	285.5	341.4	405.0	441.6	420.2
57.5°	163.3	170.0	177.6	183.0	189.7	213.0	242.5	284.6	347.7	387.5	380.3
60°	142.3	146.3	153.5	157.5	163.8	179.0	199.6	241.6	291.7	329.3	333.4
62.5°	122.6	126.2	131.1	134.7	138.7	150.8	166.0	196.0	239.8	280.6	285.9
65°	105.6	108.7	111.4	114.5	117.7	125.3	138.3	161.5	195.5	233.6	245.2
67.5°	90.4	91.3	95.3	95.8	97.5	103.4	112.8	131.6	156.2	186.6	201.8
70°	75.6	77.4	78.3	79.6	81.4	85.5	93.1	102.9	121.3	145.9	160.2
72.5°	61.3	61.7	63.1	64.0	65.8	68.9	72.5	80.1	91.7	109.6	122.6
75°	48.8	49.2	50.1	50.6	51.9	52.8	54.6	60.0	68.0	78.8	88.1
77.5°	36.7	37.6	38.5	38.5	38.9	39.8	40.7	42.5	46.5	53.7	61.7
80°	25.1	25.5	25.5	26.0	25.5	26.8	28.2	30.4	32.2	34.5	38.5
82.5°	17.5	17.5	17.5	17.9	17.9	18.3	18.3	18.8	19.2	20.6	22.4
85°	10.7	10.7	11.2	10.3	10.7	11.2	11.2	10.7	11.2	11.6	12.1
87.5°	4.5	4.5	4.9	4.9	4.9	4.9	4.5	4.9	4.5	4.9	4.9
90°	34.4	33.4	32.4	31.9	31.1	29.4	27.7	26.0	24.3	21.9	19.6
92.5°	32.7	32.4	32.1	31.9	31.1	29.4	27.7	26.0	24.3	22.3	20.3
95°	31.9	31.9	31.9	31.9	31.1	29.4	27.7	26.0	24.3	37.1	49.9
97.5°	31.2	30.9	30.6	30.4	30.1	29.4	28.7	28.0	27.3	59.4	91.4
100°	34.6	36.0	37.3	38.0	63.1	113.4	163.7	213.9	264.2	262.9	261.5
102.5°	287.5	315.9	344.2	358.4	358.1	357.4	356.7	356.1	355.4	354.7	354.0
105°	451.7	452.1	452.4	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
107.5°	550.9	552.3	553.6	554.3	554.1	553.8	553.5	553.1	552.8	552.1	551.4
110°	649.3	649.0	648.7	648.5	649.0	650.0	651.0	652.0	653.0	652.3	651.7

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	742.4	743.1	743.8	744.1	744.8	746.1	747.5	748.8	750.2	749.9	749.5
115°	836.2	838.3	840.3	841.3	842.0	843.3	844.7	846.0	847.4	847.1	846.7
117.5°	932.3	933.0	933.7	934.0	935.0	937.0	939.1	941.1	943.1	941.7	940.4
120°	1023.9	1025.6	1027.3	1028.1	1028.4	1029.1	1029.8	1030.4	1031.1	1030.1	1029.1
122.5°	1109.6	1111.7	1113.7	1114.7	1115.0	1115.7	1116.4	1117.0	1117.7	1117.4	1117.0
125°	1194.1	1195.2	1196.2	1196.7	1197.4	1198.7	1200.1	1201.4	1202.8	1202.8	1202.8
127.5°	1268.9	1271.6	1274.3	1275.6	1275.9	1276.6	1277.3	1278.0	1278.7	1279.0	1279.4
130°	1345.9	1347.6	1349.3	1350.1	1350.6	1351.6	1352.6	1353.6	1354.6	1354.3	1353.9
132.5°	1418.8	1420.5	1422.2	1423.0	1423.0	1423.0	1423.0	1423.0	1423.0	1424.0	1425.0
135°	1484.7	1486.8	1488.8	1489.8	1490.1	1490.8	1491.5	1492.1	1492.8	1493.5	1494.1
137.5°	1552.4	1554.1	1555.8	1556.6	1556.6	1556.6	1556.6	1556.6	1556.6	1557.3	1557.9
140°	1612.2	1614.3	1616.3	1617.3	1617.0	1616.3	1615.6	1615.0	1614.3	1614.6	1615.0
142.5°	1668.4	1670.5	1672.5	1673.5	1673.5	1673.5	1673.5	1673.5	1673.5	1672.8	1672.2
145°	1723.1	1725.2	1727.2	1728.2	1728.0	1727.7	1727.4	1727.0	1726.7	1726.7	1726.7
147.5°	1769.4	1771.7	1774.1	1775.3	1775.1	1774.8	1774.5	1774.1	1773.8	1773.4	1773.1
150°	1814.1	1816.8	1819.5	1820.8	1820.5	1819.8	1819.1	1818.5	1817.8	1817.1	1816.5
152.5°	1854.4	1856.8	1859.1	1860.3	1860.0	1859.3	1858.6	1858.0	1857.3	1856.6	1855.9
155°	1890.0	1892.7	1895.4	1896.8	1896.3	1895.3	1894.2	1893.2	1892.2	1891.5	1890.9
157.5°	1920.4	1923.1	1925.8	1927.1	1926.6	1925.6	1924.6	1923.6	1922.6	1922.6	1922.6
160°	1949.2	1951.9	1954.6	1956.0	1955.3	1954.0	1952.6	1951.3	1949.9	1949.6	1949.2
162.5°	1975.7	1978.8	1981.8	1983.3	1982.3	1980.3	1978.2	1976.2	1974.2	1973.9	1973.5
165°	1997.8	2000.5	2003.2	2004.6	2003.6	2001.6	1999.5	1997.5	1995.5	1995.2	1994.8
167.5°	2015.2	2018.2	2021.3	2022.8	2021.6	2019.3	2016.9	2014.6	2012.2	2011.9	2011.5
170°	2028.9	2031.9	2035.0	2036.5	2035.1	2032.4	2029.7	2027.0	2024.3	2024.0	2023.6
172.5°	2038.0	2041.0	2044.1	2045.6	2044.4	2042.1	2039.7	2037.4	2035.0	2034.3	2033.6
175°	2045.6	2048.6	2051.7	2053.2	2051.8	2049.1	2046.4	2043.7	2041.0	2040.7	2040.3
177.5°	2049.5	2052.2	2054.9	2056.2	2055.0	2052.7	2050.3	2048.0	2045.6	2045.3	2044.9
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	559.3	556.6	554.9	554.4	551.7	549.5	546.8	546.3	545.0	541.4	539.2
5°	576.8	570.5	569.2	565.1	558.4	553.5	547.2	543.7	539.6	532.9	527.6
7.5°	594.7	586.2	579.9	574.1	564.7	555.7	546.8	539.6	532.5	522.6	514.6
10°	612.1	599.1	591.5	583.0	570.1	556.6	544.1	533.8	522.2	510.6	498.9
12.5°	628.2	611.7	600.5	588.4	572.3	555.7	539.6	525.3	513.2	497.6	484.6
15°	638.1	619.7	608.5	596.9	572.7	554.4	535.6	517.3	501.2	484.6	472.5
17.5°	643.9	623.3	610.8	600.0	575.4	550.4	526.2	506.5	489.1	469.4	453.3
20°	641.2	621.1	609.4	599.1	570.5	545.5	519.5	496.7	474.8	454.6	437.6
22.5°	635.4	614.4	601.4	592.0	566.5	537.0	508.3	483.7	460.9	440.7	421.5
25°	622.9	602.3	591.1	579.5	554.4	526.2	497.1	470.7	446.6	425.1	403.6
27.5°	611.7	586.6	575.0	564.7	538.3	513.2	484.6	455.5	430.9	408.5	387.1
30°	598.7	570.5	558.0	544.1	520.4	496.7	468.0	441.2	415.7	392.0	371.4
32.5°	584.8	552.2	537.8	522.2	498.0	475.7	451.5	425.1	399.6	376.3	354.8
35°	566.9	532.0	515.5	500.7	475.7	453.3	430.9	409.0	383.5	358.9	338.3
37.5°	549.9	511.4	494.0	477.0	450.6	429.1	410.8	390.2	365.6	341.9	322.2
40°	530.7	486.4	468.5	452.8	425.5	401.8	385.3	369.2	347.7	324.9	303.4
42.5°	513.2	463.1	444.3	428.2	399.6	377.2	361.5	348.1	329.3	308.3	286.4
45°	489.1	438.1	418.8	401.8	372.7	351.7	335.6	324.0	309.2	289.5	269.8
47.5°	466.7	413.9	392.9	372.3	345.9	324.4	309.6	300.7	290.8	273.4	253.3
50°	439.4	386.2	364.7	347.7	317.7	299.4	284.6	278.3	269.4	252.8	236.7
52.5°	409.9	359.3	339.2	318.6	290.8	273.0	260.0	252.8	245.7	233.6	218.4
55°	375.4	329.3	310.5	292.2	264.4	247.9	236.3	228.7	224.6	213.4	202.3
57.5°	342.3	298.9	281.5	264.4	240.3	221.5	213.9	207.2	201.4	193.3	183.9
60°	308.7	269.4	250.6	235.4	214.3	197.3	191.1	184.4	179.9	173.6	166.9
62.5°	270.3	236.7	222.4	208.1	190.2	176.7	169.6	164.2	158.4	154.4	148.6
65°	229.5	205.8	192.0	181.2	164.2	152.1	146.8	143.2	138.3	134.2	129.8
67.5°	191.5	172.7	166.9	155.3	142.3	131.6	127.5	123.1	119.0	116.8	112.8
70°	154.8	141.4	135.6	132.4	118.1	111.0	107.4	105.6	100.7	98.4	95.8
72.5°	119.9	115.0	111.0	106.9	97.5	93.1	89.0	87.3	83.7	81.9	81.0
75°	88.6	85.5	83.2	82.8	78.8	74.3	70.3	69.4	66.7	64.9	64.0
77.5°	62.2	61.3	60.9	61.3	58.6	55.9	55.0	54.1	51.0	50.6	50.6
80°	40.7	43.0	43.0	42.5	41.6	41.2	39.8	38.9	37.1	36.7	37.1
82.5°	25.1	26.4	26.8	27.7	27.3	26.8	26.0	25.5	26.0	25.1	25.5
85°	12.5	13.4	15.2	15.2	15.7	15.7	15.7	15.2	14.3	14.8	14.3
87.5°	4.9	5.4	5.4	5.4	4.9	6.3	6.7	6.7	6.7	5.8	5.8
90°	17.2	14.9	13.7	12.3	9.6	6.9	4.2	1.5	4.2	6.9	9.6
92.5°	18.2	16.2	15.2	16.7	19.8	22.8	25.9	28.9	25.9	22.8	19.8
95°	62.8	75.6	82.0	82.5	83.5	84.6	85.6	86.6	85.6	84.6	83.5
97.5°	123.5	155.6	171.6	170.6	168.6	166.5	164.5	162.5	164.5	166.5	168.6
100°	260.2	258.9	258.2	257.7	256.7	255.6	254.6	253.6	254.6	255.6	256.7
102.5°	353.3	352.6	352.3	351.6	350.3	348.9	347.6	346.2	347.6	348.9	350.3
105°	452.6	452.6	452.6	451.9	450.6	449.2	447.9	446.5	447.9	449.2	450.6
107.5°	550.7	550.0	549.7	549.7	549.7	549.7	549.7	549.7	549.7	549.7	549.7
110°	651.0	650.3	650.0	650.0	650.0	650.0	650.0	650.0	650.0	650.0	650.0

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	749.2	748.9	748.7	748.2	747.2	746.1	745.1	744.1	745.1	746.1	747.2
115°	846.4	846.1	845.9	845.1	843.4	841.7	840.0	838.3	840.0	841.7	843.4
117.5°	939.0	937.7	937.0	937.0	937.0	937.0	937.0	937.0	937.0	937.0	937.0
120°	1028.1	1027.1	1026.6	1026.8	1027.1	1027.4	1027.8	1028.1	1027.8	1027.4	1027.1
122.5°	1116.7	1116.4	1116.2	1115.4	1113.7	1112.0	1110.3	1108.6	1110.3	1112.0	1113.7
125°	1202.8	1202.8	1202.8	1201.6	1199.2	1196.9	1194.5	1192.1	1194.5	1196.9	1199.2
127.5°	1279.7	1280.0	1280.2	1279.4	1277.7	1276.0	1274.3	1272.6	1274.3	1276.0	1277.7
130°	1353.6	1353.3	1353.1	1352.3	1350.6	1348.9	1347.2	1345.5	1347.2	1348.9	1350.6
132.5°	1426.0	1427.0	1427.5	1426.5	1424.5	1422.4	1420.4	1418.4	1420.4	1422.4	1424.5
135°	1494.8	1495.5	1495.8	1494.8	1492.8	1490.7	1488.7	1486.7	1488.7	1490.7	1492.8
137.5°	1558.6	1559.3	1559.6	1558.6	1556.6	1554.5	1552.5	1550.5	1552.5	1554.5	1556.6
140°	1615.3	1615.6	1615.8	1615.5	1614.8	1614.1	1613.5	1612.8	1613.5	1614.1	1614.8
142.5°	1671.5	1670.8	1670.5	1670.3	1670.0	1669.7	1669.3	1669.0	1669.3	1669.7	1670.0
145°	1726.7	1726.7	1726.7	1726.4	1725.7	1725.0	1724.3	1723.6	1724.3	1725.0	1725.7
147.5°	1772.7	1772.4	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2	1772.2
150°	1815.8	1815.1	1814.8	1815.1	1815.8	1816.5	1817.1	1817.8	1817.1	1816.5	1815.8
152.5°	1855.2	1854.5	1854.2	1855.0	1856.7	1858.4	1860.1	1861.8	1860.1	1858.4	1856.7
155°	1890.2	1889.5	1889.2	1890.2	1892.2	1894.3	1896.3	1898.3	1896.3	1894.3	1892.2
157.5°	1922.6	1922.6	1922.6	1923.1	1924.1	1925.1	1926.1	1927.1	1926.1	1925.1	1924.1
160°	1948.9	1948.6	1948.4	1949.4	1951.4	1953.5	1955.5	1957.5	1955.5	1953.5	1951.4
162.5°	1973.2	1972.9	1972.7	1973.7	1975.7	1977.8	1979.8	1981.8	1979.8	1977.8	1975.7
165°	1994.5	1994.2	1994.0	1995.0	1997.0	1999.1	2001.1	2003.1	2001.1	1999.1	1997.0
167.5°	2011.2	2010.9	2010.7	2011.7	2013.7	2015.8	2017.8	2019.8	2017.8	2015.8	2013.7
170°	2023.3	2023.0	2022.8	2024.0	2026.3	2028.7	2031.0	2033.4	2031.0	2028.7	2026.3
172.5°	2032.9	2032.2	2031.9	2033.1	2035.5	2037.8	2040.2	2042.6	2040.2	2037.8	2035.5
175°	2040.0	2039.7	2039.5	2040.5	2042.5	2044.6	2046.6	2048.6	2046.6	2044.6	2042.5
177.5°	2044.6	2044.3	2044.1	2045.1	2047.1	2049.2	2051.2	2053.2	2051.2	2049.2	2047.1
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	537.8	536.1	534.7	533.4	527.6	521.3	520.4	519.1	516.4	519.5	518.2
5°	524.0	519.9	517.7	511.9	504.7	499.4	494.9	489.5	487.3	485.5	485.0
7.5°	507.0	503.4	499.4	493.5	484.6	475.7	468.9	463.6	459.1	456.9	456.9
10°	490.4	485.9	480.6	470.7	462.2	451.0	443.9	438.5	432.2	428.7	425.5
12.5°	473.4	468.5	463.6	451.0	441.2	429.6	419.3	412.6	409.4	405.4	400.0
15°	456.4	448.8	443.9	431.4	418.8	407.2	400.5	393.3	386.2	382.1	380.3
17.5°	438.5	433.1	425.1	411.7	397.8	387.5	377.7	370.9	362.4	358.4	354.4
20°	422.4	414.3	406.3	392.9	379.4	365.6	355.7	347.7	342.3	339.2	335.6
22.5°	403.2	395.6	388.8	374.5	359.8	346.8	336.0	331.1	325.8	320.8	317.2
25°	386.6	379.0	372.3	356.6	340.5	328.4	320.4	314.1	308.3	306.1	302.5
27.5°	369.2	362.0	353.0	337.4	323.1	312.8	304.3	298.5	294.0	289.5	286.8
30°	352.6	344.5	336.5	319.5	307.9	297.6	289.5	282.3	278.8	276.5	272.1
32.5°	336.5	326.2	319.5	303.8	292.6	282.8	276.1	269.8	265.3	261.3	257.7
35°	319.0	307.9	301.1	288.2	276.5	266.7	260.9	256.4	251.0	247.4	245.7
37.5°	302.5	293.1	286.4	273.0	261.3	253.3	247.0	241.2	238.9	234.0	233.1
40°	284.6	276.5	270.3	257.3	246.6	240.3	233.6	228.2	224.2	221.9	218.8
42.5°	268.5	261.8	255.1	243.0	232.7	225.1	220.2	215.2	211.6	208.1	205.8
45°	253.7	246.6	240.3	228.7	218.4	211.6	206.7	200.9	200.0	195.1	192.9
47.5°	238.0	231.8	226.4	214.3	204.9	198.2	192.4	188.4	184.4	182.6	179.4
50°	222.8	216.6	210.3	199.6	191.1	184.4	178.5	174.1	171.8	169.1	166.5
52.5°	206.3	201.4	196.4	185.2	176.7	170.9	166.0	160.2	158.0	155.7	153.9
55°	192.4	185.2	179.9	170.5	162.9	156.6	151.2	146.8	144.5	142.7	140.5
57.5°	173.6	169.1	164.7	156.2	149.0	142.7	137.4	133.8	131.1	129.8	130.2
60°	157.5	152.6	149.9	140.9	133.8	128.9	123.9	120.4	117.7	116.3	115.9
62.5°	140.5	136.9	132.0	125.7	118.6	114.1	110.5	107.8	103.4	102.9	101.6
65°	123.9	121.3	116.8	111.0	105.2	101.1	97.1	93.5	91.7	89.5	88.1
67.5°	107.8	105.2	101.1	96.2	92.2	88.1	84.6	81.0	77.9	76.1	75.2
70°	92.2	89.9	87.3	81.4	76.5	73.4	70.7	68.5	65.3	64.4	64.0
72.5°	77.0	74.7	73.4	68.5	64.0	61.3	58.6	56.4	55.0	54.6	53.2
75°	63.1	60.9	59.1	54.6	51.9	50.1	47.4	46.5	45.2	44.7	44.3
77.5°	49.2	47.0	46.5	43.4	40.3	39.4	38.5	36.7	36.7	36.7	35.8
80°	35.3	34.9	34.5	31.3	30.0	29.1	28.6	27.3	26.4	25.5	25.1
82.5°	23.7	23.3	22.8	21.5	20.1	19.7	19.2	18.3	18.3	18.8	17.9
85°	14.3	13.4	13.0	12.5	11.6	11.6	12.1	11.6	11.6	11.6	11.2
87.5°	5.4	5.4	5.4	5.4	5.8	4.9	5.4	5.4	4.9	4.9	4.5
90°	12.3	13.7	14.9	17.2	19.6	21.9	24.3	26.0	27.7	29.4	31.1
92.5°	16.7	15.2	16.2	18.2	20.3	22.3	24.3	26.0	27.7	29.4	31.1
95°	82.5	82.0	75.6	62.8	49.9	37.1	24.3	26.0	27.7	29.4	31.1
97.5°	170.6	171.6	155.6	123.5	91.4	59.4	27.3	28.0	28.7	29.4	30.1
100°	257.7	258.2	258.9	260.2	261.5	262.9	264.2	213.9	163.7	113.4	63.1
102.5°	351.6	352.3	352.6	353.3	354.0	354.7	355.4	356.1	356.7	357.4	358.1
105°	451.9	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6
107.5°	549.7	549.7	550.0	550.7	551.4	552.1	552.8	553.1	553.5	553.8	554.1
110°	650.0	650.0	650.3	651.0	651.7	652.3	653.0	652.0	651.0	650.0	649.0

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	748.2	748.7	748.9	749.2	749.5	749.9	750.2	748.8	747.5	746.1	744.8
115°	845.1	845.9	846.1	846.4	846.7	847.1	847.4	846.0	844.7	843.3	842.0
117.5°	937.0	937.0	937.7	939.0	940.4	941.7	943.1	941.1	939.1	937.0	935.0
120°	1026.8	1026.6	1027.1	1028.1	1029.1	1030.1	1031.1	1030.4	1029.8	1029.1	1028.4
122.5°	1115.4	1116.2	1116.4	1116.7	1117.0	1117.4	1117.7	1117.0	1116.4	1115.7	1115.0
125°	1201.6	1202.8	1202.8	1202.8	1202.8	1202.8	1202.8	1201.4	1200.1	1198.7	1197.4
127.5°	1279.4	1280.2	1280.0	1279.7	1279.4	1279.0	1278.7	1278.0	1277.3	1276.6	1275.9
130°	1352.3	1353.1	1353.3	1353.6	1353.9	1354.3	1354.6	1353.6	1352.6	1351.6	1350.6
132.5°	1426.5	1427.5	1427.0	1426.0	1425.0	1424.0	1423.0	1423.0	1423.0	1423.0	1423.0
135°	1494.8	1495.8	1495.5	1494.8	1494.1	1493.5	1492.8	1492.1	1491.5	1490.8	1490.1
137.5°	1558.6	1559.6	1559.3	1558.6	1557.9	1557.3	1556.6	1556.6	1556.6	1556.6	1556.6
140°	1615.5	1615.8	1615.6	1615.3	1615.0	1614.6	1614.3	1615.0	1615.6	1616.3	1617.0
142.5°	1670.3	1670.5	1670.8	1671.5	1672.2	1672.8	1673.5	1673.5	1673.5	1673.5	1673.5
145°	1726.4	1726.7	1726.7	1726.7	1726.7	1726.7	1726.7	1727.0	1727.4	1727.7	1728.0
147.5°	1772.2	1772.2	1772.4	1772.7	1773.1	1773.4	1773.8	1774.1	1774.5	1774.8	1775.1
150°	1815.1	1814.8	1815.1	1815.8	1816.5	1817.1	1817.8	1818.5	1819.1	1819.8	1820.5
152.5°	1855.0	1854.2	1854.5	1855.2	1855.9	1856.6	1857.3	1858.0	1858.6	1859.3	1860.0
155°	1890.2	1889.2	1889.5	1890.2	1890.9	1891.5	1892.2	1893.2	1894.2	1895.3	1896.3
157.5°	1923.1	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1923.6	1924.6	1925.6	1926.6
160°	1949.4	1948.4	1948.6	1948.9	1949.2	1949.6	1949.9	1951.3	1952.6	1954.0	1955.3
162.5°	1973.7	1972.7	1972.9	1973.2	1973.5	1973.9	1974.2	1976.2	1978.2	1980.3	1982.3
165°	1995.0	1994.0	1994.2	1994.5	1994.8	1995.2	1995.5	1997.5	1999.5	2001.6	2003.6
167.5°	2011.7	2010.7	2010.9	2011.2	2011.5	2011.9	2012.2	2014.6	2016.9	2019.3	2021.6
170°	2024.0	2022.8	2023.0	2023.3	2023.6	2024.0	2024.3	2027.0	2029.7	2032.4	2035.1
172.5°	2033.1	2031.9	2032.2	2032.9	2033.6	2034.3	2035.0	2037.4	2039.7	2042.1	2044.4
175°	2040.5	2039.5	2039.7	2040.0	2040.3	2040.7	2041.0	2043.7	2046.4	2049.1	2051.8
177.5°	2045.1	2044.1	2044.3	2044.6	2044.9	2045.3	2045.6	2048.0	2050.3	2052.7	2055.0
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	515.9	516.8	514.6	513.7	511.9	514.1	514.6	514.1	518.2	516.4	517.3
5°	485.9	484.2	482.8	479.7	479.7	480.1	481.5	479.2	480.6	483.7	483.3
7.5°	452.8	451.9	452.4	448.8	446.1	447.0	446.1	450.1	452.4	451.5	453.3
10°	422.8	424.6	420.6	418.8	417.0	418.8	418.4	419.3	422.0	423.7	426.9
12.5°	398.7	398.2	396.0	394.2	391.1	392.0	394.7	393.8	394.2	398.2	397.8
15°	375.9	373.2	371.4	367.4	368.3	365.1	367.8	370.9	372.3	375.9	378.1
17.5°	353.0	352.6	350.4	349.9	345.0	343.6	346.3	347.2	348.6	350.4	353.5
20°	333.8	333.4	330.2	329.3	325.3	328.0	327.1	328.9	329.8	333.4	334.7
22.5°	316.4	314.1	313.2	311.9	310.5	310.1	311.9	311.4	314.6	315.9	316.4
25°	300.2	298.5	298.0	295.8	294.9	293.5	294.9	296.2	299.8	301.1	302.9
27.5°	285.5	284.1	283.2	281.5	280.1	280.1	281.0	282.8	284.1	285.0	285.9
30°	272.1	271.2	268.5	267.6	266.2	266.2	266.2	267.1	269.4	272.1	273.4
32.5°	258.2	256.4	254.6	254.6	253.3	253.3	253.7	254.6	256.8	257.3	259.5
35°	244.8	243.0	241.6	240.7	241.2	239.4	240.3	241.6	244.3	245.2	246.6
37.5°	231.8	231.3	228.7	227.3	228.2	228.2	227.8	228.7	230.4	232.2	233.1
40°	217.5	216.6	216.6	215.2	215.7	213.9	215.2	216.1	217.0	218.8	220.2
42.5°	204.9	204.0	202.3	202.7	201.4	201.4	202.3	202.7	204.0	206.3	207.2
45°	191.5	191.5	190.6	189.3	189.7	188.4	189.3	189.7	191.5	193.8	192.9
47.5°	178.5	178.1	178.1	176.3	177.2	175.9	177.2	177.6	178.5	179.9	179.4
50°	166.0	164.7	165.1	164.7	164.2	164.2	165.1	165.1	166.0	166.0	167.4
52.5°	153.0	153.0	152.1	152.6	153.5	152.6	153.9	152.6	153.5	153.9	154.8
55°	141.4	140.5	140.9	140.5	142.3	140.9	142.3	141.4	142.3	141.8	142.7
57.5°	128.9	127.5	128.0	127.5	128.9	128.4	129.8	128.4	128.9	129.3	130.7
60°	114.5	114.5	114.5	113.7	115.0	115.0	114.5	114.5	116.3	117.2	116.8
62.5°	101.1	100.7	99.3	98.9	99.3	98.4	100.2	99.8	100.7	101.6	102.5
65°	86.4	85.5	85.0	84.1	84.1	83.7	84.1	85.9	86.4	86.8	89.0
67.5°	74.3	73.8	73.4	72.0	72.0	72.9	72.9	72.9	75.6	74.3	76.1
70°	63.5	62.6	61.7	61.3	61.3	61.7	62.2	62.6	62.2	64.0	64.4
72.5°	53.2	53.7	52.8	52.8	52.8	52.4	52.4	53.2	53.7	53.2	53.7
75°	44.3	44.3	43.9	44.3	44.3	43.9	43.9	44.7	44.7	44.3	45.6
77.5°	35.8	35.3	34.5	33.6	34.0	33.6	34.0	33.6	34.9	36.2	35.3
80°	25.1	24.6	24.6	24.6	25.1	24.6	25.5	24.6	25.1	25.1	25.5
82.5°	17.9	18.3	18.3	17.9	18.3	17.9	18.3	18.3	18.3	17.9	18.3
85°	11.6	11.6	11.6	11.6	11.2	11.6	11.6	11.6	12.1	11.6	12.1
87.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	5.4	4.9	5.4
90°	31.9	32.4	33.4	34.4	35.4	36.4	35.4	34.4	33.4	32.4	31.9
92.5°	31.9	32.1	32.4	32.7	33.1	33.4	33.1	32.7	32.4	32.1	31.9
95°	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9	31.9
97.5°	30.4	30.6	30.9	31.2	31.6	31.9	31.6	31.2	30.9	30.6	30.4
100°	38.0	37.3	36.0	34.6	33.3	31.9	33.3	34.6	36.0	37.3	38.0
102.5°	358.4	344.2	315.9	287.5	259.2	230.8	259.2	287.5	315.9	344.2	358.4
105°	452.6	452.4	452.1	451.7	451.4	451.0	451.4	451.7	452.1	452.4	452.6
107.5°	554.3	553.6	552.3	550.9	549.6	548.2	549.6	550.9	552.3	553.6	554.3
110°	648.5	648.7	649.0	649.3	649.7	650.0	649.7	649.3	649.0	648.7	648.5

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	744.1	743.8	743.1	742.4	741.8	741.1	741.8	742.4	743.1	743.8	744.1
115°	841.3	840.3	838.3	836.2	834.2	832.2	834.2	836.2	838.3	840.3	841.3
117.5°	934.0	933.7	933.0	932.3	931.6	930.9	931.6	932.3	933.0	933.7	934.0
120°	1028.1	1027.3	1025.6	1023.9	1022.2	1020.5	1022.2	1023.9	1025.6	1027.3	1028.1
122.5°	1114.7	1113.7	1111.7	1109.6	1107.6	1105.6	1107.6	1109.6	1111.7	1113.7	1114.7
125°	1196.7	1196.2	1195.2	1194.1	1193.1	1192.1	1193.1	1194.1	1195.2	1196.2	1196.7
127.5°	1275.6	1274.3	1271.6	1268.9	1266.2	1263.5	1266.2	1268.9	1271.6	1274.3	1275.6
130°	1350.1	1349.3	1347.6	1345.9	1344.2	1342.5	1344.2	1345.9	1347.6	1349.3	1350.1
132.5°	1423.0	1422.2	1420.5	1418.8	1417.1	1415.4	1417.1	1418.8	1420.5	1422.2	1423.0
135°	1489.8	1488.8	1486.8	1484.7	1482.7	1480.7	1482.7	1484.7	1486.8	1488.8	1489.8
137.5°	1556.6	1555.8	1554.1	1552.4	1550.7	1549.0	1550.7	1552.4	1554.1	1555.8	1556.6
140°	1617.3	1616.3	1614.3	1612.2	1610.2	1608.2	1610.2	1612.2	1614.3	1616.3	1617.3
142.5°	1673.5	1672.5	1670.5	1668.4	1666.4	1664.4	1666.4	1668.4	1670.5	1672.5	1673.5
145°	1728.2	1727.2	1725.2	1723.1	1721.1	1719.1	1721.1	1723.1	1725.2	1727.2	1728.2
147.5°	1775.3	1774.1	1771.7	1769.4	1767.0	1764.6	1767.0	1769.4	1771.7	1774.1	1775.3
150°	1820.8	1819.5	1816.8	1814.1	1811.4	1808.7	1811.4	1814.1	1816.8	1819.5	1820.8
152.5°	1860.3	1859.1	1856.8	1854.4	1852.1	1849.7	1852.1	1854.4	1856.8	1859.1	1860.3
155°	1896.8	1895.4	1892.7	1890.0	1887.3	1884.6	1887.3	1890.0	1892.7	1895.4	1896.8
157.5°	1927.1	1925.8	1923.1	1920.4	1917.7	1915.0	1917.7	1920.4	1923.1	1925.8	1927.1
160°	1956.0	1954.6	1951.9	1949.2	1946.5	1943.8	1946.5	1949.2	1951.9	1954.6	1956.0
162.5°	1983.3	1981.8	1978.8	1975.7	1972.7	1969.7	1972.7	1975.7	1978.8	1981.8	1983.3
165°	2004.6	2003.2	2000.5	1997.8	1995.1	1992.4	1995.1	1997.8	2000.5	2003.2	2004.6
167.5°	2022.8	2021.3	2018.2	2015.2	2012.1	2009.1	2012.1	2015.2	2018.2	2021.3	2022.8
170°	2036.5	2035.0	2031.9	2028.9	2025.8	2022.8	2025.8	2028.9	2031.9	2035.0	2036.5
172.5°	2045.6	2044.1	2041.0	2038.0	2034.9	2031.9	2034.9	2038.0	2041.0	2044.1	2045.6
175°	2053.2	2051.7	2048.6	2045.6	2042.5	2039.5	2042.5	2045.6	2048.6	2051.7	2053.2
177.5°	2056.2	2054.9	2052.2	2049.5	2046.8	2044.1	2046.8	2049.5	2052.2	2054.9	2056.2
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0	545.0
2.5°	515.5	517.7	515.9	514.6	518.2	519.9	519.9	523.1	526.2	528.9	529.3
5°	483.7	487.3	488.2	487.7	493.1	495.8	501.6	504.7	509.2	512.3	515.9
7.5°	454.6	459.5	460.0	460.9	468.9	473.4	478.3	486.4	492.7	497.1	501.2
10°	425.5	428.7	431.8	435.8	443.9	451.5	458.6	467.1	475.2	479.7	485.5
12.5°	403.6	405.8	409.4	412.1	420.6	427.3	436.7	448.4	460.0	463.6	470.7
15°	380.8	382.1	389.3	392.0	399.1	410.3	416.1	427.3	439.9	446.6	454.6
17.5°	354.4	362.4	366.9	370.0	379.0	387.9	397.3	409.0	425.1	431.4	437.2
20°	335.6	341.4	346.3	350.4	358.4	371.8	380.3	389.7	405.0	412.1	420.6
22.5°	319.0	324.0	328.4	332.9	338.3	350.4	360.2	373.2	388.4	395.1	405.0
25°	303.4	308.3	311.0	316.4	323.5	332.0	343.6	355.3	370.5	378.1	387.5
27.5°	288.2	293.1	298.0	302.5	307.4	315.5	323.5	338.3	353.9	362.9	370.9
30°	275.2	277.4	281.9	286.8	291.7	299.4	308.7	319.0	336.9	345.0	354.8
32.5°	260.9	264.9	268.0	271.6	277.9	284.1	292.6	305.6	319.9	327.5	338.3
35°	247.4	251.0	253.3	259.5	263.6	270.3	278.8	290.4	302.5	311.0	320.4
37.5°	234.5	238.0	240.7	244.3	249.7	255.5	264.4	273.0	287.3	294.4	305.2
40°	221.0	224.2	227.3	231.3	236.3	243.4	248.8	259.5	271.2	279.2	287.3
42.5°	208.1	209.9	213.4	217.9	222.8	229.1	236.7	245.2	256.8	264.0	271.2
45°	194.2	197.3	201.4	204.5	209.0	215.2	221.9	229.5	241.2	248.3	255.9
47.5°	181.2	183.5	186.1	191.1	196.9	201.4	208.5	215.7	226.4	233.1	240.3
50°	167.8	170.0	174.1	177.2	181.7	187.5	194.2	201.8	212.1	216.6	223.7
52.5°	155.3	156.2	160.2	163.3	167.8	174.5	179.9	186.6	196.4	201.4	208.5
55°	142.7	143.6	145.9	149.0	153.9	159.3	165.1	172.7	181.2	185.7	192.4
57.5°	129.8	130.7	132.9	135.1	140.1	145.0	151.7	158.0	166.5	170.5	176.7
60°	116.8	116.8	119.0	122.2	125.7	130.2	136.0	143.6	149.9	154.8	159.3
62.5°	102.9	104.3	105.6	107.8	111.9	117.2	122.2	127.5	135.1	138.7	142.7
65°	89.0	90.4	93.1	95.3	98.4	102.0	108.3	112.8	118.6	122.6	126.2
67.5°	77.0	78.3	80.1	82.8	85.0	89.0	93.5	98.0	104.3	106.9	109.6
70°	64.4	65.8	67.1	70.7	72.9	76.1	79.2	83.7	89.0	90.8	93.1
72.5°	54.6	55.0	56.8	57.7	60.9	63.5	67.1	69.8	73.8	76.1	77.9
75°	46.1	46.1	46.5	47.4	49.2	51.0	53.7	56.4	60.0	61.3	63.5
77.5°	36.2	37.6	37.1	38.0	38.9	39.8	42.1	43.9	47.4	48.3	49.2
80°	26.0	26.4	27.7	29.1	29.1	30.4	31.8	32.2	34.5	35.8	35.8
82.5°	18.8	19.2	18.8	19.2	19.7	20.1	21.5	23.3	23.3	23.7	24.6
85°	11.6	11.6	12.1	12.5	12.5	12.1	13.0	12.5	13.0	13.9	13.9
87.5°	5.8	5.4	5.4	5.4	5.4	5.4	5.8	5.4	5.8	5.8	5.8
90°	31.1	29.4	27.7	26.0	24.3	21.9	19.6	17.2	14.9	13.7	12.3
92.5°	31.1	29.4	27.7	26.0	24.3	22.3	20.3	18.2	16.2	15.2	16.7
95°	31.1	29.4	27.7	26.0	24.3	37.1	49.9	62.8	75.6	82.0	82.5
97.5°	30.1	29.4	28.7	28.0	27.3	59.4	91.4	123.5	155.6	171.6	170.6
100°	63.1	113.4	163.7	213.9	264.2	262.9	261.5	260.2	258.9	258.2	257.7
102.5°	358.1	357.4	356.7	356.1	355.4	354.7	354.0	353.3	352.6	352.3	351.6
105°	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	452.6	451.9
107.5°	554.1	553.8	553.5	553.1	552.8	552.1	551.4	550.7	550.0	549.7	549.7
110°	649.0	650.0	651.0	652.0	653.0	652.3	651.7	651.0	650.3	650.0	650.0

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	744.8	746.1	747.5	748.8	750.2	749.9	749.5	749.2	748.9	748.7	748.2
115°	842.0	843.3	844.7	846.0	847.4	847.1	846.7	846.4	846.1	845.9	845.1
117.5°	935.0	937.0	939.1	941.1	943.1	941.7	940.4	939.0	937.7	937.0	937.0
120°	1028.4	1029.1	1029.8	1030.4	1031.1	1030.1	1029.1	1028.1	1027.1	1026.6	1026.8
122.5°	1115.0	1115.7	1116.4	1117.0	1117.7	1117.4	1117.0	1116.7	1116.4	1116.2	1115.4
125°	1197.4	1198.7	1200.1	1201.4	1202.8	1202.8	1202.8	1202.8	1202.8	1202.8	1201.6
127.5°	1275.9	1276.6	1277.3	1278.0	1278.7	1279.0	1279.4	1279.7	1280.0	1280.2	1279.4
130°	1350.6	1351.6	1352.6	1353.6	1354.6	1354.3	1353.9	1353.6	1353.3	1353.1	1352.3
132.5°	1423.0	1423.0	1423.0	1423.0	1423.0	1424.0	1425.0	1426.0	1427.0	1427.5	1426.5
135°	1490.1	1490.8	1491.5	1492.1	1492.8	1493.5	1494.1	1494.8	1495.5	1495.8	1494.8
137.5°	1556.6	1556.6	1556.6	1556.6	1556.6	1557.3	1557.9	1558.6	1559.3	1559.6	1558.6
140°	1617.0	1616.3	1615.6	1615.0	1614.3	1614.6	1615.0	1615.3	1615.6	1615.8	1615.5
142.5°	1673.5	1673.5	1673.5	1673.5	1673.5	1672.8	1672.2	1671.5	1670.8	1670.5	1670.3
145°	1728.0	1727.7	1727.4	1727.0	1726.7	1726.7	1726.7	1726.7	1726.7	1726.7	1726.4
147.5°	1775.1	1774.8	1774.5	1774.1	1773.8	1773.4	1773.1	1772.7	1772.4	1772.2	1772.2
150°	1820.5	1819.8	1819.1	1818.5	1817.8	1817.1	1816.5	1815.8	1815.1	1814.8	1815.1
152.5°	1860.0	1859.3	1858.6	1858.0	1857.3	1856.6	1855.9	1855.2	1854.5	1854.2	1855.0
155°	1896.3	1895.3	1894.2	1893.2	1892.2	1891.5	1890.9	1890.2	1889.5	1889.2	1890.2
157.5°	1926.6	1925.6	1924.6	1923.6	1922.6	1922.6	1922.6	1922.6	1922.6	1922.6	1923.1
160°	1955.3	1954.0	1952.6	1951.3	1949.9	1949.6	1949.2	1948.9	1948.6	1948.4	1949.4
162.5°	1982.3	1980.3	1978.2	1976.2	1974.2	1973.9	1973.5	1973.2	1972.9	1972.7	1973.7
165°	2003.6	2001.6	1999.5	1997.5	1995.5	1995.2	1994.8	1994.5	1994.2	1994.0	1995.0
167.5°	2021.6	2019.3	2016.9	2014.6	2012.2	2011.9	2011.5	2011.2	2010.9	2010.7	2011.7
170°	2035.1	2032.4	2029.7	2027.0	2024.3	2024.0	2023.6	2023.3	2023.0	2022.8	2024.0
172.5°	2044.4	2042.1	2039.7	2037.4	2035.0	2034.3	2033.6	2032.9	2032.2	2031.9	2033.1
175°	2051.8	2049.1	2046.4	2043.7	2041.0	2040.7	2040.3	2040.0	2039.7	2039.5	2040.5
177.5°	2055.0	2052.7	2050.3	2048.0	2045.6	2045.3	2044.9	2044.6	2044.3	2044.1	2045.1
180°	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6	2048.6

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	545.0	545.0	545.0	545.0
2.5°	532.5	536.5	540.5	545.5
5°	521.7	528.9	536.5	543.7
7.5°	510.1	520.4	530.2	540.5
10°	497.1	510.1	521.3	535.6
12.5°	482.8	496.7	512.3	528.5
15°	468.5	485.9	502.5	520.8
17.5°	455.1	471.6	490.0	511.9
20°	439.0	457.3	477.9	501.2
22.5°	422.0	442.1	464.5	489.5
25°	407.6	428.2	449.7	476.1
27.5°	392.0	413.5	434.5	462.7
30°	374.1	397.3	418.8	447.9
32.5°	357.1	380.3	404.1	431.4
35°	340.5	363.3	387.1	414.8
37.5°	324.9	345.4	368.7	393.8
40°	310.1	328.9	349.5	372.3
42.5°	291.3	313.2	332.5	349.0
45°	275.2	293.1	311.0	324.4
47.5°	256.4	274.3	289.5	300.2
50°	240.7	255.1	267.6	277.0
52.5°	221.9	235.4	245.7	252.8
55°	203.6	215.2	224.2	229.1
57.5°	187.0	194.6	201.4	205.8
60°	168.7	174.5	180.3	185.2
62.5°	149.0	155.3	158.4	163.8
65°	131.6	135.6	140.5	142.3
67.5°	114.5	116.8	119.9	123.5
70°	96.7	98.0	101.1	106.0
72.5°	81.0	82.3	84.6	86.4
75°	64.4	65.8	67.6	69.4
77.5°	50.6	51.0	51.9	53.7
80°	36.7	38.0	38.9	39.4
82.5°	25.5	26.0	26.0	26.4
85°	16.1	15.2	15.2	15.7
87.5°	5.8	6.7	6.7	7.6
90°	9.6	6.9	4.2	1.5
92.5°	19.8	22.8	25.9	28.9
95°	83.5	84.6	85.6	86.6
97.5°	168.6	166.5	164.5	162.5
100°	256.7	255.6	254.6	253.6
102.5°	350.3	348.9	347.6	346.2
105°	450.6	449.2	447.9	446.5
107.5°	549.7	549.7	549.7	549.7
110°	650.0	650.0	650.0	650.0

TEST NUMBER: P1035920

CATALOG NUMBER: S125RDIW-B375D1560UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	747.2	746.1	745.1	744.1
115°	843.4	841.7	840.0	838.3
117.5°	937.0	937.0	937.0	937.0
120°	1027.1	1027.4	1027.8	1028.1
122.5°	1113.7	1112.0	1110.3	1108.6
125°	1199.2	1196.9	1194.5	1192.1
127.5°	1277.7	1276.0	1274.3	1272.6
130°	1350.6	1348.9	1347.2	1345.5
132.5°	1424.5	1422.4	1420.4	1418.4
135°	1492.8	1490.7	1488.7	1486.7
137.5°	1556.6	1554.5	1552.5	1550.5
140°	1614.8	1614.1	1613.5	1612.8
142.5°	1670.0	1669.7	1669.3	1669.0
145°	1725.7	1725.0	1724.3	1723.6
147.5°	1772.2	1772.2	1772.2	1772.2
150°	1815.8	1816.5	1817.1	1817.8
152.5°	1856.7	1858.4	1860.1	1861.8
155°	1892.2	1894.3	1896.3	1898.3
157.5°	1924.1	1925.1	1926.1	1927.1
160°	1951.4	1953.5	1955.5	1957.5
162.5°	1975.7	1977.8	1979.8	1981.8
165°	1997.0	1999.1	2001.1	2003.1
167.5°	2013.7	2015.8	2017.8	2019.8
170°	2026.3	2028.7	2031.0	2033.4
172.5°	2035.5	2037.8	2040.2	2042.6
175°	2042.5	2044.6	2046.6	2048.6
177.5°	2047.1	2049.2	2051.2	2053.2
180°	2048.6	2048.6	2048.6	2048.6

(END OF REPORT)