

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B10WFL559727D010 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14805)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10WFL559727D010 2LBDL*WMH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 617.7 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559727D010 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559727D010 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	111	108	106		111	108	106	104		104	103	101			101	99	98			93
2	108	103	99	95		105	101	97	94		98	95	92			95	92	90			86
3	102	95	90	86		100	94	89	86		91	87	84			89	86	83			80
4	97	89	83	79		95	88	83	79		86	81	78			84	80	77			74
5	92	83	77	73		90	82	77	72		80	75	72			79	74	71			69
6	87	78	72	67		85	77	71	67		75	70	67			74	70	66			64
7	82	73	67	63		81	72	67	62		71	66	62			70	65	62			60
8	78	69	63	58		77	68	62	58		67	62	58			66	61	58			56
9	75	65	59	55		73	64	59	55		63	58	54			62	58	54			53
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	294189
5°	290686
10°	268678
15°	235473
20°	203217
25°	173007
30°	136998
35°	95093
40°	61790
45°	37195
50°	21453
55°	12021
60°	5268
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559727D010 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	11.2
10°-20°	163.6	26.5
20°-30°	184.2	29.8
30°-40°	127.2	20.6
40°-50°	55.1	8.9
50°-60°	17.1	2.8
60°-70°	1.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	417.1	67.5
0°-40°	544.3	88.1
0°-60°	616.5	99.8
0°-90°	617.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	617.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	760	
5°	748	69
15°	587	164
25°	405	184
35°	201	127
45°	68	55
55°	18	17
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559727D010 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	759.5
2.5°	757.8
5°	747.6
7.5°	723.8
10°	683.1
12.5°	636.4
15°	587.2
17.5°	536.3
20°	493.0
22.5°	449.7
25°	404.8
27.5°	358.9
30°	306.3
32.5°	251.2
35°	201.1
37.5°	157.8
40°	122.2
42.5°	92.5
45°	67.9
47.5°	50.1
50°	35.6
52.5°	25.5
55°	17.8
57.5°	12.7
60°	6.8
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)