

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B10WFL558030D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10WFL558030D010 2LBDL*H
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 895.2 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL558030D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL558030D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	102	101		101	99	98		97
2	108	102	98	95	105	101	97	94	98	94	92		95	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	96	89	83	79	95	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	66	62	81	72	66	62	71	65	62		69	65	61		68
8	78	68	62	58	77	68	62	58	67	61	57		66	61	57		65
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61
10	71	61	55	51	70	60	55	51	60	54	51		59	54	51		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419961
5°	411805
10°	382820
15°	338934
20°	293408
25°	246646
30°	193131
35°	137981
40°	92128
45°	57134
50°	34228
55°	20530
60°	9219
65°	1192
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL558030D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.3	11.0
10°-20°	235.4	26.3
20°-30°	262.6	29.3
30°-40°	183.9	20.5
40°-50°	84.0	9.4
50°-60°	28.1	3.1
60°-70°	3.1	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.2	66.6
0°-40°	780.1	87.1
0°-60°	892.1	99.7
0°-90°	895.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	895.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1084	
5°	1059	98
15°	845	235
25°	577	263
35°	292	184
45°	104	84
55°	30	28
65°	1	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B10WFL558030D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1084.2
2.5°	1078.9
5°	1059.1
7.5°	1022.1
10°	973.3
12.5°	911.2
15°	845.2
17.5°	776.5
20°	711.8
22.5°	647.1
25°	577.1
27.5°	505.8
30°	431.8
32.5°	359.2
35°	291.8
37.5°	232.4
40°	182.2
42.5°	138.7
45°	104.3
47.5°	77.9
50°	56.8
52.5°	40.9
55°	30.4
57.5°	21.1
60°	11.9
62.5°	4.0
65°	1.3
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)