

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035955

Luminaire Tested: S125RDIW-B375D770UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035955
REPORT IS A COMBINATION OF REPORTS P1006559 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D770UB30-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4117.0 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035955

CATALOG NUMBER: S125RDIW-B375D770UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035955

CATALOG NUMBER: S125RDIW-B375D770UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	87	83	85	82	78	76	65	63	61	51	49	48	37	36	35
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	31	30
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17
7	56	44	36	31	50	40	34	29	33	28	24	26	22	20	20	17	15
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3815	3815	3815
5°	3816	3721	3727
10°	3779	3627	3595
15°	3725	3495	3421
20°	3659	3338	3240
25°	3583	3184	3045
30°	3490	3014	2840
35°	3395	2842	2623
40°	3305	2665	2411
45°	3197	2474	2189
50°	3087	2271	1963
55°	2959	2072	1729
60°	2829	1844	1485
65°	2673	1589	1223
70°	2491	1294	963
75°	2242	973	701
80°	1890	630	473
85°	1412	339	267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3197 cd/sqm

TEST NUMBER: P1035955

CATALOG NUMBER: S125RDIW-B375D770UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	1.4
10°-20°	156.6	3.8
20°-30°	227.1	5.5
30°-40°	258.7	6.3
40°-50°	252.2	6.1
50°-60°	212.2	5.2
60°-70°	148.7	3.6
70°-80°	76.3	1.9
80°-90°	20.5	0.5
90°-100°	64.5	1.6
100°-110°	191.7	4.7
110°-120°	325.1	7.9
120°-130°	428.0	10.4
130°-140°	479.7	11.7
140°-150°	470.1	11.4
150°-160°	394.9	9.6
160°-170°	262.5	6.4
170°-180°	91.9	2.2
0°-30°	439.8	10.7
0°-40°	698.5	17.0
0°-60°	1163.0	28.2
0°-90°	1408.5	34.2
90°-120°	581.4	14.1
90°-150°	1959.2	47.6
90°-180°	2708.0	65.8
0°-180°	4117.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	595	593	588	592	592	56
15°	565	563	553	553	549	159
25°	513	506	489	484	479	236
35°	442	431	411	398	391	277
45°	362	349	324	306	299	279
55°	274	260	235	214	207	245
65°	186	170	147	129	122	184
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	1	7	12	16	18	5
95°	49	51	58	63	65	51
105°	172	176	180	185	187	184
115°	326	328	330	329	328	322
125°	475	480	480	479	478	426
135°	618	622	623	623	620	476
145°	748	751	754	754	751	468
155°	856	856	857	860	856	394
165°	931	930	930	934	929	263
175°	968	965	965	970	964	92
180°	970	970	970	970	970	

TEST NUMBER: P1035955

CATALOG NUMBER: S125RDIW-B375D770UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	595.5	595.5	595.5	595.5	595.5
2.5°	596.9	595.5	591.0	595.5	595.1
5°	594.6	592.8	587.9	592.4	591.5
7.5°	590.1	588.3	582.5	586.1	585.2
10°	583.4	582.0	575.7	577.1	575.7
12.5°	575.7	573.9	564.9	565.8	563.6
15°	565.4	562.7	553.2	552.8	548.7
17.5°	554.6	550.5	539.3	537.0	533.9
20°	541.5	537.0	522.7	520.4	516.4
22.5°	527.2	522.7	507.4	502.4	499.3
25°	512.8	506.0	489.4	483.5	478.6
27.5°	496.6	488.5	470.9	463.3	458.3
30°	478.6	470.0	451.1	440.8	436.7
32.5°	461.0	450.7	431.3	419.7	414.3
35°	441.7	430.9	410.7	397.6	391.3
37.5°	423.3	410.2	389.5	374.2	367.9
40°	403.5	390.0	368.4	351.3	345.9
42.5°	382.8	368.8	346.3	330.1	321.6
45°	361.6	348.6	323.8	305.9	299.1
47.5°	339.6	326.1	301.4	282.9	275.3
50°	318.9	304.1	278.4	259.5	252.8
52.5°	296.4	281.1	257.3	236.6	229.8
55°	274.4	260.0	234.8	214.5	207.4
57.5°	251.9	236.6	212.3	192.5	186.2
60°	230.3	214.5	190.3	170.5	163.7
62.5°	207.4	192.5	167.8	149.8	143.0
65°	185.8	170.5	146.6	128.6	121.9
67.5°	164.2	148.9	125.9	108.8	103.5
70°	142.1	126.8	104.4	90.4	85.0
72.5°	120.5	105.7	85.0	72.4	69.3
75°	99.0	85.5	66.6	56.7	53.5
77.5°	76.9	66.1	50.4	42.7	40.0
80°	58.5	47.7	35.1	31.0	30.1
82.5°	40.5	31.0	23.4	22.0	21.6
85°	24.7	16.6	14.4	13.9	13.5
87.5°	10.3	7.2	6.7	6.7	6.3
90°	0.8	6.8	12.1	15.9	18.1
92.5°	22.7	26.4	33.2	38.5	40.0
95°	49.1	50.6	58.2	63.4	64.9
97.5°	75.5	76.3	86.9	91.4	92.1
100°	105.7	105.7	115.5	122.3	123.9
102.5°	138.2	142.0	145.8	153.3	155.6
105°	172.2	176.0	180.5	185.0	187.3
107.5°	209.2	213.0	216.7	219.0	219.0
110°	247.7	251.5	253.8	256.0	255.3

TEST NUMBER: P1035955

CATALOG NUMBER: S125RDIW-B375D770UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.0	288.5	291.5	292.3	290.8
115°	325.5	328.5	330.0	329.3	328.5
117.5°	364.8	365.5	367.0	367.8	364.8
120°	401.0	404.8	405.6	405.6	402.5
122.5°	440.3	441.1	443.3	442.6	440.3
125°	475.0	479.6	480.3	478.8	478.1
127.5°	513.6	515.8	516.6	515.8	514.3
130°	547.5	551.3	552.8	552.1	550.6
132.5°	581.5	588.3	587.6	586.8	584.5
135°	617.8	622.3	623.1	623.1	620.0
137.5°	651.8	656.3	657.8	658.6	654.8
140°	684.2	688.0	690.3	691.8	688.0
142.5°	716.7	719.7	722.8	723.5	719.7
145°	748.4	751.4	753.7	753.7	751.4
147.5°	777.9	780.1	781.7	783.9	777.9
150°	807.3	806.6	809.6	809.6	808.1
152.5°	831.5	833.0	833.8	836.0	833.0
155°	856.4	856.4	857.2	860.2	856.4
157.5°	879.1	877.6	878.3	881.3	876.1
160°	898.7	896.5	897.2	900.2	896.5
162.5°	916.1	914.6	914.6	918.4	913.8
165°	931.2	929.7	930.4	933.5	928.9
167.5°	944.8	941.8	941.8	946.3	941.8
170°	955.4	952.3	952.3	956.9	951.6
172.5°	962.9	959.9	959.9	964.4	959.9
175°	968.2	965.2	965.2	969.7	964.4
177.5°	972.0	969.0	968.2	972.7	967.4
180°	970.5	970.5	970.5	970.5	970.5

(END OF REPORT)