

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224177

Luminaire Tested: **LSSQWM2B10SP158030D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10SP158030D010 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 543.0 lumens
Efficiency: N/A
Efficacy: 52.7 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224177

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224177

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96		
3	110	106	103	101	108	105	102	100	102	100	98	100	99	97	98	97	96	94		
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93		
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91		
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90		
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88		
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87		
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86		
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2609240
5°	1886232
10°	549116
15°	192685
20°	82482
25°	37097
30°	14357
35°	7140
40°	4753
45°	3122
50°	1687
55°	1283
60°	697
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224177

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.3	63.2
10°-20°	139.6	25.7
20°-30°	42.9	7.9
30°-40°	10.6	1.9
40°-50°	4.4	0.8
50°-60°	1.9	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.8	96.8
0°-40°	536.4	98.8
0°-60°	542.7	99.9
0°-90°	543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	543.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6736	
5°	4851	343
15°	480	140
25°	87	43
35°	15	11
45°	6	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224177

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6736.2
1°	6633.3
2°	6382.2
3°	5981.9
4°	5459.0
5°	4851.1
6°	4165.7
7°	3421.9
8°	2667.7
9°	1962.5
10°	1396.1
11°	1000.6
12°	752.3
13°	612.6
14°	536.2
15°	480.5
17.5°	296.4
20°	200.1
22.5°	134.0
25°	86.8
27.5°	52.9
30°	32.1
32.5°	20.8
35°	15.1
37.5°	12.3
40°	9.4
42.5°	7.6
45°	5.7
47.5°	3.8
50°	2.8
52.5°	2.8
55°	1.9
57.5°	1.9
60°	0.9
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224177

CATALOG NUMBER: LSSQWM2B10SP158030D010 2LBDL*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)