

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035990

Luminaire Tested: S125RDIW-B610D1340UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035990
REPORT IS A COMBINATION OF REPORTS P1006626 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1340UB27-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7671.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035990

CATALOG NUMBER: S125RDIW-B610D1340UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035990

CATALOG NUMBER: S125RDIW-B610D1340UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	103	103	103	103		92	92	92	92		73	73	73		55	55	55		38	38	38
1	94	89	86	82		84	80	77	75		64	62	60		48	47	46		34	33	33
2	85	78	72	67		76	70	66	61		56	53	50		43	40	38		30	29	28
3	78	69	62	56		70	62	56	51		49	45	42		38	35	33		27	25	24
4	71	61	53	48		64	55	48	43		44	39	36		34	30	28		24	22	20
5	65	54	46	41		58	49	42	37		39	34	31		30	27	24		22	20	18
6	60	48	41	35		54	44	37	32		35	30	27		27	24	21		20	17	16
7	55	44	36	31		50	40	33	28		32	27	23		25	21	19		18	16	14
8	51	40	32	27		46	36	29	25		29	24	21		23	19	17		16	14	13
9	48	36	29	24		43	33	26	22		27	22	18		21	17	15		15	13	11
10	45	33	26	21		40	30	24	20		24	20	17		19	16	13		14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6365	6365	6365
5°	6366	6206	6216
10°	6303	6050	5997
15°	6214	5831	5707
20°	6103	5567	5404
25°	5977	5310	5080
30°	5822	5027	4738
35°	5664	4740	4376
40°	5513	4446	4022
45°	5332	4127	3651
50°	5149	3789	3274
55°	4936	3456	2883
60°	4718	3076	2478
65°	4459	2651	2040
70°	4156	2158	1606
75°	3738	1622	1171
80°	3151	1050	790
85°	2361	564	444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5332 cd/sqm

TEST NUMBER: P1035990

CATALOG NUMBER: S125RDIW-B610D1340UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	1.2
10°-20°	261.3	3.4
20°-30°	378.8	4.9
30°-40°	431.6	5.6
40°-50°	420.7	5.5
50°-60°	354.1	4.6
60°-70°	248.1	3.2
70°-80°	127.2	1.7
80°-90°	34.3	0.4
90°-100°	58.8	0.8
100°-110°	391.0	5.1
110°-120°	704.1	9.2
120°-130°	903.7	11.8
130°-140°	972.0	12.7
140°-150°	912.2	11.9
150°-160°	737.9	9.6
160°-170°	477.2	6.2
170°-180°	164.6	2.1
0°-30°	733.6	9.6
0°-40°	1165.2	15.2
0°-60°	1940.0	25.3
0°-90°	2349.6	30.6
90°-120°	1153.8	15.0
90°-150°	3941.7	51.4
90°-180°	5321.0	69.4
0°-180°	7671.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	992	989	981	988	987	94
15°	943	939	923	922	915	266
25°	855	844	816	807	798	394
35°	737	719	685	663	653	461
45°	603	582	540	510	499	465
55°	458	434	392	358	346	409
65°	310	284	245	215	203	307
75°	165	143	111	94	89	174
85°	41	28	24	23	22	45
90°	1	12	20	27	31	6
95°	73	69	20	27	27	90
105°	378	383	383	383	381	400
115°	709	715	717	711	704	703
125°	1008	1017	1017	1012	1008	900
135°	1257	1265	1262	1260	1252	969
145°	1458	1460	1460	1461	1454	912
155°	1605	1598	1600	1604	1594	740
165°	1694	1686	1687	1695	1685	478
175°	1732	1725	1726	1736	1725	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P1035990

CATALOG NUMBER: S125RDIW-B610D1340UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.4	993.4	993.4	993.4	993.4
2.5°	995.6	993.4	985.9	993.4	992.6
5°	991.9	988.9	980.6	988.1	986.6
7.5°	984.4	981.4	971.6	977.6	976.1
10°	973.1	970.9	960.4	962.6	960.4
12.5°	960.4	957.4	942.4	943.9	940.1
15°	943.1	938.6	922.9	922.1	915.3
17.5°	925.1	918.3	899.6	895.8	890.6
20°	903.3	895.8	871.8	868.1	861.3
22.5°	879.3	871.8	846.3	838.1	832.8
25°	855.3	844.1	816.3	806.6	798.3
27.5°	828.3	814.8	785.5	772.8	764.5
30°	798.3	784.0	752.5	735.3	728.5
32.5°	769.0	751.8	719.5	700.0	691.0
35°	736.8	718.8	685.0	663.3	652.7
37.5°	706.0	684.3	649.7	624.2	613.7
40°	673.0	650.5	614.5	586.0	577.0
42.5°	638.5	615.2	577.7	550.7	536.5
45°	603.2	581.5	540.2	510.2	498.9
47.5°	566.5	544.0	502.7	471.9	459.2
50°	532.0	507.2	464.4	432.9	421.7
52.5°	494.4	468.9	429.2	394.7	383.4
55°	457.7	433.7	391.6	357.9	345.9
57.5°	420.2	394.7	354.1	321.1	310.6
60°	384.1	357.9	317.4	284.4	273.1
62.5°	345.9	321.1	279.9	249.8	238.6
65°	309.9	284.4	244.6	214.6	203.3
67.5°	273.9	248.3	210.1	181.6	172.6
70°	237.1	211.6	174.1	150.8	141.8
72.5°	201.1	176.3	141.8	120.8	115.5
75°	165.1	142.6	111.0	94.5	89.3
77.5°	128.3	110.3	84.0	71.3	66.8
80°	97.5	79.5	58.5	51.8	50.3
82.5°	67.5	51.8	39.0	36.8	36.0
85°	41.3	27.8	24.0	23.3	22.5
87.5°	17.3	12.0	11.3	11.3	10.5
90°	1.3	11.6	20.5	27.0	30.8
92.5°	24.4	12.8	20.5	27.0	28.3
95°	73.2	69.3	20.5	27.0	27.0
97.5°	137.4	145.1	23.1	25.7	27.0
100°	214.5	218.3	223.4	32.1	27.0
102.5°	292.8	297.9	300.5	303.1	195.2
105°	377.5	382.7	382.7	382.7	381.4
107.5°	464.9	464.9	467.4	468.7	463.6
110°	549.6	549.6	552.2	548.3	549.6

TEST NUMBER: P1035990

CATALOG NUMBER: S125RDIW-B610D1340UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	629.2	633.1	634.4	629.2	626.7
115°	708.9	715.3	716.6	711.4	703.7
117.5°	792.3	792.3	797.5	789.8	787.2
120°	869.4	868.1	872.0	869.4	863.0
122.5°	937.4	943.9	945.2	942.6	934.9
125°	1008.1	1017.1	1017.1	1011.9	1008.1
127.5°	1076.1	1082.6	1081.3	1078.7	1068.4
130°	1137.8	1144.2	1145.5	1141.6	1135.2
132.5°	1199.4	1207.1	1203.3	1203.3	1196.9
135°	1257.2	1264.9	1262.3	1259.8	1252.1
137.5°	1311.1	1318.9	1316.3	1316.3	1309.9
140°	1363.8	1366.4	1365.1	1367.6	1359.9
142.5°	1411.3	1412.6	1415.2	1415.2	1407.5
145°	1457.5	1460.1	1460.1	1461.4	1453.7
147.5°	1498.6	1498.6	1499.9	1501.2	1492.2
150°	1537.2	1534.6	1537.2	1539.7	1529.5
152.5°	1574.4	1568.0	1570.5	1573.1	1564.1
155°	1605.2	1597.5	1600.1	1603.9	1593.7
157.5°	1629.6	1625.8	1625.8	1629.6	1619.3
160°	1655.3	1647.6	1648.9	1654.0	1643.7
162.5°	1675.9	1668.1	1669.4	1677.1	1665.6
165°	1693.8	1686.1	1687.4	1695.1	1684.8
167.5°	1708.0	1700.3	1701.5	1710.5	1699.0
170°	1719.5	1710.5	1711.8	1722.1	1710.5
172.5°	1727.2	1718.2	1720.8	1729.8	1718.2
175°	1732.4	1724.7	1725.9	1736.2	1724.7
177.5°	1736.2	1728.5	1729.8	1738.8	1728.5
180°	1732.4	1732.4	1732.4	1732.4	1732.4

(END OF REPORT)