

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036002

Luminaire Tested: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036002
REPORT IS A COMBINATION OF REPORTS P1006661 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1340UB50-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7460.0 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	31	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	26	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	23	21
5	66	54	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	15	13	12
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5678	5678	5678	5678
5°	5673	6399	5673	4919
10°	5641	7192	5622	4252
15°	5580	7608	5542	3702
20°	5506	8213	5457	3346
25°	5410	9296	5349	3037
30°	5311	9881	5232	2816
35°	5185	8127	5112	2610
40°	4959	5518	4918	2425
45°	4663	3967	4657	2242
50°	4360	3051	4381	2073
55°	4018	2481	4010	1911
60°	3699	2033	3682	1697
65°	3330	1694	3350	1366
70°	3022	1360	3010	1137
75°	2554	1030	2554	935
80°	2068	628	2046	628
85°	1458	330	1412	373

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8082 cd/sqm

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	1.1
10°-20°	249.2	3.3
20°-30°	395.1	5.3
30°-40°	477.4	6.4
40°-50°	425.0	5.7
50°-60°	325.9	4.4
60°-70°	211.7	2.8
70°-80°	102.7	1.4
80°-90°	26.7	0.4
90°-100°	57.0	0.8
100°-110°	379.2	5.1
110°-120°	682.9	9.2
120°-130°	876.6	11.8
130°-140°	942.8	12.6
140°-150°	884.8	11.9
150°-160°	715.7	9.6
160°-170°	462.9	6.2
170°-180°	159.6	2.1
0°-30°	729.2	9.8
0°-40°	1206.5	16.2
0°-60°	1957.5	26.2
0°-90°	2298.5	30.8
90°-120°	1119.2	15.0
90°-150°	3823.3	51.3
90°-180°	5162.0	69.2
0°-180°	7460.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	886	886	886	886	886	
5°	884	1016	884	781	884	84
15°	847	1220	841	594	847	239
25°	774	1461	765	477	774	357
35°	674	1212	665	389	674	420
45°	528	542	527	306	528	407
55°	372	298	372	229	372	334
65°	231	169	233	136	231	231
75°	113	79	113	71	113	121
85°	26	17	25	19	26	29
90°	1	30	1	30	1	5
95°	71	26	71	26	71	87
105°	366	370	366	370	366	388
115°	688	683	688	683	688	682
125°	978	978	978	978	978	873
135°	1219	1214	1219	1214	1219	940
145°	1414	1410	1414	1410	1414	884
155°	1557	1546	1557	1546	1557	717
165°	1643	1634	1643	1634	1643	464
175°	1680	1673	1680	1673	1680	160
180°	1680	1680	1680	1680	1680	

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2
2.5°	886.9	894.2	896.4	902.2	908.8	910.2	913.9	919.0	921.9	921.1	921.1
5°	884.0	896.4	905.1	915.3	927.7	932.8	937.1	948.1	956.8	961.9	970.6
7.5°	878.9	897.1	911.7	927.0	945.9	954.6	964.1	979.3	995.4	1005.5	1015.0
10°	870.9	894.2	914.6	937.1	962.6	975.7	987.4	1010.6	1030.3	1043.4	1065.2
12.5°	859.3	888.4	916.8	946.6	978.6	992.4	1008.5	1033.9	1061.6	1080.5	1098.7
15°	846.9	881.8	912.4	948.1	986.6	1007.7	1028.1	1055.0	1079.8	1100.9	1122.0
17.5°	832.4	869.5	907.3	948.1	991.7	1012.8	1030.3	1062.3	1088.5	1109.6	1128.5
20°	814.9	856.4	899.3	944.4	988.8	1008.5	1025.2	1060.1	1083.4	1105.9	1132.9
22.5°	796.0	841.1	886.9	931.3	975.0	996.1	1015.7	1046.3	1071.8	1102.3	1137.2
25°	774.2	823.6	870.2	914.6	956.1	975.7	993.2	1026.6	1062.3	1100.9	1140.1
27.5°	752.3	800.4	845.5	886.2	931.3	949.5	967.0	1009.2	1051.4	1092.1	1146.0
30°	728.3	777.1	816.4	854.2	897.9	916.8	938.6	986.6	1034.6	1089.9	1155.4
32.5°	701.4	745.8	782.2	821.5	860.7	884.0	911.7	964.1	1019.4	1085.6	1169.3
35°	674.5	710.1	743.6	780.7	828.0	852.7	879.7	935.0	1004.1	1083.4	1180.9
37.5°	640.3	674.5	700.7	738.5	787.3	816.4	843.3	907.3	985.9	1078.3	1180.2
40°	605.4	634.5	659.2	698.5	751.6	778.5	807.6	877.5	967.0	1063.7	1162.7
42.5°	567.5	592.3	619.2	657.0	708.7	734.9	768.3	849.8	940.8	1043.4	1117.6
45°	527.5	551.5	574.1	613.4	665.0	693.4	729.8	813.5	908.8	1000.4	1044.8
47.5°	488.2	509.3	533.3	567.5	619.9	651.2	688.3	777.8	865.8	943.0	946.6
50°	450.4	467.1	487.5	522.4	577.0	606.8	645.4	729.1	814.9	868.0	832.4
52.5°	411.1	426.4	447.5	478.0	529.0	563.9	597.4	681.0	753.1	788.7	723.2
55°	372.5	385.6	407.5	441.7	486.0	513.0	547.2	625.0	688.3	689.0	617.7
57.5°	334.7	346.3	364.5	395.1	436.6	467.8	499.1	566.8	609.7	597.4	518.1
60°	301.2	308.5	325.2	355.1	393.6	416.2	449.7	506.4	534.8	512.2	427.1
62.5°	266.3	273.6	286.7	310.7	347.1	371.1	392.2	438.7	458.4	424.2	354.3
65°	231.4	240.1	249.6	268.5	302.7	318.7	337.6	371.8	390.7	350.7	290.3
67.5°	200.8	205.2	214.6	234.3	258.3	272.8	285.9	309.2	312.9	280.9	231.4
70°	172.4	173.9	182.6	194.3	212.5	221.2	232.1	245.9	245.9	219.7	180.4
72.5°	140.4	142.6	149.2	161.5	172.4	176.8	180.4	189.2	187.7	163.7	136.8
75°	112.8	114.2	119.3	125.1	129.5	137.5	140.4	139.0	138.2	117.9	102.6
77.5°	87.3	88.0	91.7	96.8	97.5	100.4	98.2	98.2	91.7	80.0	72.0
80°	64.0	64.8	66.2	67.7	67.7	67.7	67.7	64.0	59.7	52.4	50.2
82.5°	42.9	42.9	43.7	45.1	44.4	42.9	41.5	37.8	34.9	32.7	31.3
85°	25.5	25.5	26.2	25.5	22.6	21.8	20.4	19.6	18.9	18.2	18.2
87.5°	12.4	11.6	10.2	8.7	8.7	8.7	8.7	8.7	8.7	8.0	8.0
90°	1.2	3.4	5.6	7.9	10.1	11.2	12.2	14.1	16.0	18.0	19.9
92.5°	23.7	21.2	18.7	16.2	13.7	12.5	13.3	15.0	16.6	18.3	19.9
95°	71.0	70.2	69.4	68.5	67.7	67.3	62.0	51.5	41.0	30.4	19.9
97.5°	133.3	135.0	136.6	138.3	140.0	140.8	127.6	101.3	75.0	48.7	22.4
100°	208.0	208.8	209.6	210.5	211.3	211.7	212.3	213.4	214.5	215.6	216.7
102.5°	284.0	285.1	286.2	287.3	288.4	289.0	289.3	289.8	290.4	290.9	291.5
105°	366.2	367.3	368.4	369.5	370.6	371.2	371.2	371.2	371.2	371.2	371.2
107.5°	450.9	450.9	450.9	450.9	450.9	450.9	451.2	451.7	452.3	452.8	453.4
110°	533.1	533.1	533.1	533.1	533.1	533.1	533.4	533.9	534.5	535.0	535.6

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	610.3	611.1	612.0	612.8	613.7	614.1	614.2	614.5	614.8	615.0	615.3
115°	687.6	689.0	690.4	691.7	693.1	693.8	693.9	694.2	694.5	694.7	695.0
117.5°	768.5	768.5	768.5	768.5	768.5	768.5	769.1	770.2	771.3	772.4	773.5
120°	843.3	843.0	842.7	842.4	842.1	842.0	842.4	843.3	844.1	845.0	845.8
122.5°	909.3	910.7	912.1	913.4	914.8	915.5	915.6	915.9	916.2	916.5	916.8
125°	977.8	979.7	981.7	983.6	985.5	986.5	986.5	986.5	986.5	986.5	986.5
127.5°	1043.8	1045.2	1046.6	1047.9	1049.3	1050.0	1049.9	1049.6	1049.3	1049.1	1048.8
130°	1103.6	1105.0	1106.4	1107.7	1109.1	1109.8	1109.9	1110.2	1110.5	1110.8	1111.1
132.5°	1163.4	1165.0	1166.7	1168.3	1170.0	1170.8	1170.4	1169.6	1168.7	1167.9	1167.1
135°	1219.4	1221.1	1222.7	1224.4	1226.1	1226.9	1226.6	1226.1	1225.5	1225.0	1224.4
137.5°	1271.7	1273.4	1275.0	1276.7	1278.4	1279.2	1278.9	1278.4	1277.8	1277.3	1276.7
140°	1322.8	1323.4	1323.9	1324.5	1325.0	1325.3	1325.2	1324.9	1324.6	1324.4	1324.1
142.5°	1368.9	1369.2	1369.4	1369.7	1370.0	1370.1	1370.4	1370.9	1371.5	1372.0	1372.6
145°	1413.7	1414.3	1414.8	1415.4	1415.9	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2
147.5°	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.7	1454.0	1454.3	1454.5	1454.8
150°	1491.0	1490.4	1489.9	1489.3	1488.8	1488.5	1488.8	1489.3	1489.9	1490.4	1491.0
152.5°	1527.1	1525.7	1524.3	1523.0	1521.6	1520.9	1521.2	1521.7	1522.3	1522.8	1523.4
155°	1557.0	1555.3	1553.7	1552.0	1550.3	1549.5	1549.8	1550.3	1550.9	1551.4	1552.0
157.5°	1580.6	1579.8	1579.0	1578.1	1577.3	1576.9	1576.9	1576.9	1576.9	1576.9	1576.9
160°	1605.6	1603.9	1602.3	1600.6	1598.9	1598.1	1598.2	1598.5	1598.8	1599.0	1599.3
162.5°	1625.5	1623.8	1622.2	1620.5	1618.8	1618.0	1618.1	1618.4	1618.7	1619.0	1619.3
165°	1642.9	1641.3	1639.6	1638.0	1636.3	1635.5	1635.6	1635.9	1636.2	1636.4	1636.7
167.5°	1656.6	1655.0	1653.3	1651.7	1650.0	1649.2	1649.3	1649.6	1649.9	1650.1	1650.4
170°	1667.8	1665.9	1663.9	1662.0	1660.1	1659.1	1659.2	1659.5	1659.8	1660.1	1660.4
172.5°	1675.3	1673.4	1671.4	1669.5	1667.6	1666.6	1666.9	1667.4	1668.0	1668.5	1669.1
175°	1680.3	1678.6	1677.0	1675.3	1673.6	1672.8	1672.9	1673.2	1673.5	1673.8	1674.1
177.5°	1684.0	1682.4	1680.7	1679.1	1677.4	1676.6	1676.7	1677.0	1677.3	1677.5	1677.8
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2
2.5°	924.8	929.9	934.2	932.1	940.8	940.1	941.5	944.4	945.2	943.7	940.8
5°	975.0	982.3	994.6	1001.2	999.7	1005.5	1008.5	1012.8	1017.2	1015.7	1015.7
7.5°	1031.0	1041.2	1053.6	1070.3	1072.5	1077.6	1086.3	1086.3	1091.4	1089.2	1088.5
10°	1079.8	1092.1	1111.8	1124.9	1130.7	1133.6	1142.3	1145.2	1151.1	1151.8	1151.8
12.5°	1119.8	1141.6	1154.7	1167.8	1170.7	1175.1	1181.6	1186.0	1188.2	1188.2	1186.0
15°	1140.9	1158.3	1173.6	1187.4	1195.4	1199.1	1205.6	1210.7	1213.6	1220.2	1221.6
17.5°	1149.6	1170.7	1195.4	1215.1	1228.9	1232.6	1245.6	1250.0	1255.8	1258.7	1262.4
20°	1162.0	1192.5	1222.4	1246.4	1259.5	1268.9	1282.8	1303.1	1308.9	1308.9	1306.8
22.5°	1172.9	1212.2	1252.9	1291.5	1302.4	1321.3	1346.8	1368.6	1377.3	1381.0	1378.1
25°	1186.0	1239.8	1292.9	1341.0	1370.8	1384.6	1418.8	1445.0	1455.2	1461.0	1462.5
27.5°	1208.5	1276.2	1343.9	1405.0	1435.6	1451.6	1487.2	1509.8	1522.1	1527.2	1523.6
30°	1234.0	1317.0	1395.5	1450.1	1470.5	1490.1	1513.4	1522.1	1519.2	1519.2	1530.1
32.5°	1260.2	1346.1	1415.9	1451.6	1458.8	1455.9	1446.5	1420.3	1405.0	1405.0	1414.5
35°	1274.8	1349.0	1384.6	1373.0	1344.6	1327.9	1276.2	1247.1	1214.4	1212.2	1223.1
37.5°	1266.7	1298.8	1284.2	1207.8	1169.3	1137.2	1056.5	1024.5	1000.4	967.0	1018.6
40°	1210.7	1199.8	1124.1	1014.3	971.3	926.2	862.2	830.2	796.7	791.6	804.0
42.5°	1116.1	1051.4	940.8	834.6	790.9	758.9	710.1	678.8	657.7	649.0	663.6
45°	998.3	896.4	785.8	701.4	653.4	636.6	592.3	564.6	548.6	542.1	552.2
47.5°	854.2	751.6	646.8	575.5	547.2	530.4	500.6	476.6	462.8	458.4	462.8
50°	725.4	619.9	531.9	486.0	460.6	446.7	422.0	406.7	395.8	392.9	400.2
52.5°	614.1	518.1	451.1	410.4	393.6	382.0	364.5	351.4	344.9	342.0	347.1
55°	514.4	436.6	382.7	347.8	335.4	328.1	312.9	305.6	298.3	297.6	302.7
57.5°	426.4	372.5	323.1	298.3	294.7	283.8	270.7	264.1	260.5	259.8	261.9
60°	355.1	307.0	277.2	255.4	250.3	241.6	234.3	229.9	225.6	224.1	225.6
62.5°	295.4	257.6	233.6	219.0	211.7	209.5	201.5	196.5	195.7	195.7	197.2
65°	243.7	211.7	196.5	184.8	179.7	177.5	171.7	168.1	168.8	168.8	169.5
67.5°	198.6	175.4	161.5	155.7	151.3	150.6	144.8	143.3	141.9	141.9	143.3
70°	157.9	143.3	133.2	130.2	129.5	124.4	122.2	121.5	119.3	120.1	120.1
72.5°	123.7	114.2	108.4	104.0	104.8	101.9	99.0	99.0	97.5	99.7	99.7
75°	91.7	87.3	82.9	81.5	82.9	81.5	79.3	78.6	79.3	78.6	78.6
77.5°	67.7	65.5	64.0	63.3	63.3	60.4	58.9	60.4	57.5	58.9	58.9
80°	47.3	44.4	43.7	42.2	42.9	40.7	41.5	40.0	40.0	40.0	40.0
82.5°	29.8	29.1	29.1	29.1	28.4	28.4	28.4	28.4	28.4	28.4	27.6
85°	18.2	17.5	17.5	17.5	16.7	16.7	16.7	16.7	16.7	16.7	16.7
87.5°	7.3	8.0	8.0	8.7	8.0	7.3	7.3	7.3	8.0	8.0	7.3
90°	21.3	22.7	24.1	25.5	26.2	26.6	27.4	28.3	29.1	29.9	29.1
92.5°	21.3	22.7	24.1	25.5	26.2	26.3	26.6	26.9	27.1	27.4	27.1
95°	21.3	22.7	24.1	25.5	26.2	26.2	26.2	26.2	26.2	26.2	26.2
97.5°	23.0	23.5	24.1	24.6	24.9	25.0	25.3	25.6	25.9	26.2	25.9
100°	175.5	134.2	93.0	51.7	31.1	30.6	29.5	28.4	27.3	26.2	27.3
102.5°	292.1	292.6	293.2	293.7	294.0	282.4	259.1	235.8	212.6	189.3	212.6
105°	371.2	371.2	371.2	371.2	371.2	371.1	370.8	370.5	370.2	369.9	370.2
107.5°	453.7	453.9	454.2	454.5	454.6	454.1	453.0	451.9	450.8	449.7	450.8
110°	534.8	534.0	533.1	532.3	531.9	532.0	532.3	532.6	532.8	533.1	532.8

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	614.2	613.1	612.0	610.9	610.3	610.0	609.5	608.9	608.4	607.8	608.4
115°	693.9	692.8	691.7	690.6	690.1	689.3	687.6	685.9	684.3	682.6	684.3
117.5°	771.8	770.2	768.5	766.8	766.0	765.7	765.2	764.6	764.1	763.5	764.1
120°	845.2	844.7	844.1	843.6	843.3	842.6	841.2	839.8	838.4	837.0	838.4
122.5°	916.2	915.7	915.1	914.6	914.3	913.5	911.8	910.1	908.5	906.8	908.5
125°	985.4	984.3	983.2	982.1	981.5	981.1	980.3	979.4	978.6	977.8	978.6
127.5°	1048.2	1047.7	1047.1	1046.6	1046.3	1045.2	1043.0	1040.7	1038.5	1036.3	1038.5
130°	1110.3	1109.4	1108.6	1107.7	1107.3	1106.6	1105.2	1103.9	1102.5	1101.1	1102.5
132.5°	1167.1	1167.1	1167.1	1167.1	1167.1	1166.4	1165.0	1163.7	1162.3	1160.9	1162.3
135°	1223.8	1223.3	1222.7	1222.2	1221.9	1221.1	1219.4	1217.7	1216.1	1214.4	1216.1
137.5°	1276.7	1276.7	1276.7	1276.7	1276.7	1276.0	1274.6	1273.3	1271.9	1270.5	1271.9
140°	1324.6	1325.2	1325.7	1326.2	1326.5	1325.7	1324.0	1322.4	1320.7	1319.1	1320.7
142.5°	1372.6	1372.6	1372.6	1372.6	1372.6	1371.8	1370.1	1368.5	1366.8	1365.2	1366.8
145°	1416.5	1416.8	1417.1	1417.4	1417.5	1416.7	1415.0	1413.3	1411.7	1410.0	1411.7
147.5°	1455.1	1455.4	1455.7	1456.0	1456.1	1455.1	1453.2	1451.3	1449.3	1447.4	1449.3
150°	1491.6	1492.1	1492.7	1493.2	1493.5	1492.4	1490.2	1487.9	1485.7	1483.5	1485.7
152.5°	1523.9	1524.5	1525.0	1525.5	1525.8	1524.8	1522.9	1521.0	1519.0	1517.1	1519.0
155°	1552.8	1553.6	1554.5	1555.3	1555.7	1554.6	1552.4	1550.2	1548.0	1545.8	1548.0
157.5°	1577.7	1578.5	1579.4	1580.2	1580.6	1579.5	1577.3	1575.1	1572.9	1570.7	1572.9
160°	1600.4	1601.5	1602.6	1603.7	1604.3	1603.2	1601.0	1598.7	1596.5	1594.3	1596.5
162.5°	1620.9	1622.6	1624.2	1625.9	1626.7	1625.5	1623.0	1620.5	1618.0	1615.5	1618.0
165°	1638.4	1640.0	1641.7	1643.4	1644.2	1643.1	1640.9	1638.6	1636.4	1634.2	1636.4
167.5°	1652.3	1654.3	1656.2	1658.1	1659.1	1657.9	1655.4	1652.9	1650.4	1647.9	1650.4
170°	1662.6	1664.8	1667.0	1669.2	1670.3	1669.1	1666.6	1664.1	1661.6	1659.1	1661.6
172.5°	1671.0	1673.0	1674.9	1676.8	1677.8	1676.6	1674.1	1671.6	1669.1	1666.6	1669.1
175°	1676.3	1678.5	1680.7	1682.9	1684.0	1682.8	1680.3	1677.8	1675.3	1672.8	1675.3
177.5°	1679.7	1681.7	1683.6	1685.5	1686.5	1685.4	1683.2	1681.0	1678.8	1676.6	1678.8
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2
2.5°	944.4	939.3	941.5	939.3	937.1	935.0	929.9	922.6	916.8	912.4	911.7
5°	1017.2	1010.6	1006.3	1004.1	999.7	993.9	984.4	973.5	960.4	955.3	945.2
7.5°	1084.1	1081.9	1071.8	1070.3	1067.4	1056.5	1040.5	1025.9	1009.2	995.4	982.3
10°	1147.4	1142.3	1135.1	1124.9	1123.4	1109.6	1094.3	1073.9	1052.1	1039.0	1015.7
12.5°	1186.7	1180.9	1172.9	1166.3	1162.7	1154.0	1132.9	1112.5	1092.9	1068.8	1048.5
15°	1215.1	1207.8	1193.3	1188.2	1183.8	1172.2	1156.9	1135.8	1109.6	1092.9	1063.7
17.5°	1253.7	1244.9	1230.4	1220.9	1212.9	1194.7	1172.9	1144.5	1119.8	1100.9	1074.7
20°	1298.0	1284.9	1266.0	1253.7	1242.0	1220.9	1190.4	1156.9	1121.2	1097.9	1071.0
22.5°	1371.5	1346.8	1317.0	1299.5	1283.5	1247.1	1210.7	1169.3	1129.2	1094.3	1061.6
25°	1442.8	1418.1	1381.0	1357.0	1332.2	1290.0	1242.0	1184.5	1133.6	1092.9	1049.9
27.5°	1509.0	1483.6	1449.4	1420.3	1396.3	1333.0	1269.7	1204.9	1140.1	1084.1	1040.5
30°	1524.3	1513.4	1487.2	1461.7	1439.9	1381.7	1308.2	1226.0	1148.2	1076.1	1027.4
32.5°	1431.9	1458.8	1465.4	1461.7	1447.9	1406.4	1338.8	1252.2	1159.8	1072.5	1005.5
35°	1239.8	1288.6	1338.8	1365.7	1378.8	1384.6	1344.6	1265.3	1167.8	1066.7	991.0
37.5°	1028.1	1075.4	1154.7	1194.7	1239.1	1297.3	1313.3	1262.4	1164.2	1062.3	967.7
40°	844.7	905.1	970.6	1007.0	1045.6	1150.3	1229.6	1223.8	1152.5	1046.3	949.5
42.5°	687.6	725.4	782.9	822.9	870.2	987.4	1093.6	1146.0	1117.6	1026.6	926.2
45°	573.3	602.5	643.2	683.9	713.0	819.3	945.2	1031.0	1057.9	991.7	890.6
47.5°	483.1	505.0	540.6	566.1	597.4	681.0	790.2	911.0	967.7	942.2	852.7
50°	414.0	431.5	459.8	475.8	503.5	575.5	658.5	785.1	870.9	873.8	802.5
52.5°	353.6	371.1	395.1	408.9	425.6	474.4	558.1	665.0	764.0	800.4	745.1
55°	307.8	318.0	337.6	348.5	363.8	411.1	464.2	555.2	658.5	718.1	683.2
57.5°	265.6	276.5	288.9	297.6	308.5	346.3	394.4	462.8	565.3	630.1	618.5
60°	231.4	237.9	249.6	256.1	266.3	291.0	324.5	392.9	474.4	535.5	542.1
62.5°	199.4	205.2	213.2	219.0	225.6	245.2	269.9	318.7	390.0	456.2	464.9
65°	171.7	176.8	181.2	186.3	191.4	203.7	224.8	262.7	318.0	379.8	398.7
67.5°	147.0	148.4	155.0	155.7	158.6	168.1	183.4	213.9	253.9	303.4	328.1
70°	123.0	125.9	127.3	129.5	132.4	139.0	151.3	167.3	197.2	237.2	260.5
72.5°	99.7	100.4	102.6	104.0	107.0	112.1	117.9	130.2	149.2	178.3	199.4
75°	79.3	80.0	81.5	82.2	84.4	85.9	88.8	97.5	110.6	128.1	143.3
77.5°	59.7	61.1	62.6	62.6	63.3	64.8	66.2	69.1	75.7	87.3	100.4
80°	40.7	41.5	41.5	42.2	41.5	43.7	45.8	49.5	52.4	56.0	62.6
82.5°	28.4	28.4	28.4	29.1	29.1	29.8	29.8	30.6	31.3	33.5	36.4
85°	17.5	17.5	18.2	16.7	17.5	18.2	18.2	17.5	18.2	18.9	19.6
87.5°	7.3	7.3	8.0	8.0	8.0	8.0	7.3	8.0	7.3	8.0	8.0
90°	28.3	27.4	26.6	26.2	25.5	24.1	22.7	21.3	19.9	18.0	16.0
92.5°	26.9	26.6	26.3	26.2	25.5	24.1	22.7	21.3	19.9	18.3	16.6
95°	26.2	26.2	26.2	26.2	25.5	24.1	22.7	21.3	19.9	30.4	41.0
97.5°	25.6	25.3	25.0	24.9	24.6	24.1	23.5	23.0	22.4	48.7	75.0
100°	28.4	29.5	30.6	31.1	51.7	93.0	134.2	175.5	216.7	215.6	214.5
102.5°	235.8	259.1	282.4	294.0	293.7	293.2	292.6	292.1	291.5	290.9	290.4
105°	370.5	370.8	371.1	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2
107.5°	451.9	453.0	454.1	454.6	454.5	454.2	453.9	453.7	453.4	452.8	452.3
110°	532.6	532.3	532.0	531.9	532.3	533.1	534.0	534.8	535.6	535.0	534.5

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	608.9	609.5	610.0	610.3	610.9	612.0	613.1	614.2	615.3	615.0	614.8
115°	685.9	687.6	689.3	690.1	690.6	691.7	692.8	693.9	695.0	694.7	694.5
117.5°	764.6	765.2	765.7	766.0	766.8	768.5	770.2	771.8	773.5	772.4	771.3
120°	839.8	841.2	842.6	843.3	843.6	844.1	844.7	845.2	845.8	845.0	844.1
122.5°	910.1	911.8	913.5	914.3	914.6	915.1	915.7	916.2	916.8	916.5	916.2
125°	979.4	980.3	981.1	981.5	982.1	983.2	984.3	985.4	986.5	986.5	986.5
127.5°	1040.7	1043.0	1045.2	1046.3	1046.6	1047.1	1047.7	1048.2	1048.8	1049.1	1049.3
130°	1103.9	1105.2	1106.6	1107.3	1107.7	1108.6	1109.4	1110.3	1111.1	1110.8	1110.5
132.5°	1163.7	1165.0	1166.4	1167.1	1167.1	1167.1	1167.1	1167.1	1167.1	1167.9	1168.7
135°	1217.7	1219.4	1221.1	1221.9	1222.2	1222.7	1223.3	1223.8	1224.4	1225.0	1225.5
137.5°	1273.3	1274.6	1276.0	1276.7	1276.7	1276.7	1276.7	1276.7	1276.7	1277.3	1277.8
140°	1322.4	1324.0	1325.7	1326.5	1326.2	1325.7	1325.2	1324.6	1324.1	1324.4	1324.6
142.5°	1368.5	1370.1	1371.8	1372.6	1372.6	1372.6	1372.6	1372.6	1372.6	1372.0	1371.5
145°	1413.3	1415.0	1416.7	1417.5	1417.4	1417.1	1416.8	1416.5	1416.2	1416.2	1416.2
147.5°	1451.3	1453.2	1455.1	1456.1	1456.0	1455.7	1455.4	1455.1	1454.8	1454.5	1454.3
150°	1487.9	1490.2	1492.4	1493.5	1493.2	1492.7	1492.1	1491.6	1491.0	1490.4	1489.9
152.5°	1521.0	1522.9	1524.8	1525.8	1525.5	1525.0	1524.5	1523.9	1523.4	1522.8	1522.3
155°	1550.2	1552.4	1554.6	1555.7	1555.3	1554.5	1553.6	1552.8	1552.0	1551.4	1550.9
157.5°	1575.1	1577.3	1579.5	1580.6	1580.2	1579.4	1578.5	1577.7	1576.9	1576.9	1576.9
160°	1598.7	1601.0	1603.2	1604.3	1603.7	1602.6	1601.5	1600.4	1599.3	1599.0	1598.8
162.5°	1620.5	1623.0	1625.5	1626.7	1625.9	1624.2	1622.6	1620.9	1619.3	1619.0	1618.7
165°	1638.6	1640.9	1643.1	1644.2	1643.4	1641.7	1640.0	1638.4	1636.7	1636.4	1636.2
167.5°	1652.9	1655.4	1657.9	1659.1	1658.1	1656.2	1654.3	1652.3	1650.4	1650.1	1649.9
170°	1664.1	1666.6	1669.1	1670.3	1669.2	1667.0	1664.8	1662.6	1660.4	1660.1	1659.8
172.5°	1671.6	1674.1	1676.6	1677.8	1676.8	1674.9	1673.0	1671.0	1669.1	1668.5	1668.0
175°	1677.8	1680.3	1682.8	1684.0	1682.9	1680.7	1678.5	1676.3	1674.1	1673.8	1673.5
177.5°	1681.0	1683.2	1685.4	1686.5	1685.5	1683.6	1681.7	1679.7	1677.8	1677.5	1677.3
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2
2.5°	909.5	905.1	902.2	901.5	897.1	893.5	889.1	888.4	886.2	880.4	876.8
5°	937.9	927.7	925.5	919.0	908.0	900.0	889.9	884.0	877.5	866.6	857.8
7.5°	967.0	953.2	943.0	933.5	918.2	903.7	889.1	877.5	865.8	849.8	836.7
10°	995.4	974.3	961.9	948.1	927.0	905.1	884.8	868.0	849.1	830.2	811.3
12.5°	1021.5	994.6	976.4	956.8	930.6	903.7	877.5	854.2	834.6	809.1	788.0
15°	1037.6	1007.7	989.5	970.6	931.3	901.5	870.9	841.1	814.9	788.0	768.3
17.5°	1047.0	1013.5	993.2	975.7	935.7	894.9	855.7	823.6	795.3	763.3	737.1
20°	1042.6	1009.9	991.0	974.3	927.7	886.9	844.7	807.6	772.0	739.2	711.6
22.5°	1033.2	999.0	977.9	962.6	921.1	873.1	826.6	786.5	749.4	716.7	685.4
25°	1012.8	979.3	961.2	942.2	901.5	855.7	808.4	765.4	726.1	691.2	656.3
27.5°	994.6	953.9	935.0	918.2	875.3	834.6	788.0	740.7	700.7	664.3	629.4
30°	973.5	927.7	907.3	884.8	846.2	807.6	761.1	717.4	675.9	637.4	603.9
32.5°	951.0	897.9	874.6	849.1	809.8	773.4	734.1	691.2	649.7	611.9	577.0
35°	921.9	865.1	838.2	814.2	773.4	737.1	700.7	665.0	623.6	583.5	550.1
37.5°	894.2	831.6	803.3	775.6	732.7	697.8	667.9	634.5	594.4	555.9	523.9
40°	862.9	790.9	761.8	736.3	691.9	653.4	626.5	600.3	565.3	528.2	493.3
42.5°	834.6	753.1	722.5	696.3	649.7	613.4	587.9	566.1	535.5	501.3	465.7
45°	795.3	712.3	681.0	653.4	606.1	571.9	545.7	526.8	502.8	470.8	438.7
47.5°	758.9	673.0	638.8	605.4	562.4	527.5	503.5	488.9	472.9	444.6	411.8
50°	714.5	627.9	593.0	565.3	516.6	486.8	462.8	452.6	438.0	411.1	384.9
52.5°	666.5	584.3	551.5	518.1	472.9	443.8	422.7	411.1	399.5	379.8	355.1
55°	610.5	535.5	505.0	475.1	430.0	403.1	384.2	371.8	365.3	347.1	328.9
57.5°	556.6	486.0	457.7	430.0	390.7	360.2	347.8	336.9	327.4	314.3	299.0
60°	502.0	438.0	407.5	382.7	348.5	320.9	310.7	299.8	292.5	282.3	271.4
62.5°	439.5	384.9	361.6	338.3	309.2	287.4	275.8	267.0	257.6	251.0	241.6
65°	373.3	334.7	312.1	294.7	267.0	247.4	238.7	232.8	224.8	218.3	211.0
67.5°	311.4	280.9	271.4	252.5	231.4	213.9	207.4	200.1	193.5	189.9	183.4
70°	251.7	229.9	220.5	215.4	192.1	180.4	174.6	171.7	163.7	160.1	155.7
72.5°	195.0	187.0	180.4	173.9	158.6	151.3	144.8	141.9	136.1	133.2	131.7
75°	144.1	139.0	135.3	134.6	128.1	120.8	114.2	112.8	108.4	105.5	104.0
77.5°	101.1	99.7	99.0	99.7	95.3	90.9	89.5	88.0	82.9	82.2	82.2
80°	66.2	69.8	69.8	69.1	67.7	66.9	64.8	63.3	60.4	59.7	60.4
82.5°	40.7	42.9	43.7	45.1	44.4	43.7	42.2	41.5	42.2	40.7	41.5
85°	20.4	21.8	24.7	24.7	25.5	25.5	25.5	24.7	23.3	24.0	23.3
87.5°	8.0	8.7	8.7	8.7	8.0	10.2	10.9	10.9	10.9	9.5	9.5
90°	14.1	12.2	11.2	10.1	7.9	5.6	3.4	1.2	3.4	5.6	7.9
92.5°	15.0	13.3	12.5	13.7	16.2	18.7	21.2	23.7	21.2	18.7	16.2
95°	51.5	62.0	67.3	67.7	68.5	69.4	70.2	71.0	70.2	69.4	68.5
97.5°	101.3	127.6	140.8	140.0	138.3	136.6	135.0	133.3	135.0	136.6	138.3
100°	213.4	212.3	211.7	211.3	210.5	209.6	208.8	208.0	208.8	209.6	210.5
102.5°	289.8	289.3	289.0	288.4	287.3	286.2	285.1	284.0	285.1	286.2	287.3
105°	371.2	371.2	371.2	370.6	369.5	368.4	367.3	366.2	367.3	368.4	369.5
107.5°	451.7	451.2	450.9	450.9	450.9	450.9	450.9	450.9	450.9	450.9	450.9
110°	533.9	533.4	533.1	533.1	533.1	533.1	533.1	533.1	533.1	533.1	533.1

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	614.5	614.2	614.1	613.7	612.8	612.0	611.1	610.3	611.1	612.0	612.8
115°	694.2	693.9	693.8	693.1	691.7	690.4	689.0	687.6	689.0	690.4	691.7
117.5°	770.2	769.1	768.5	768.5	768.5	768.5	768.5	768.5	768.5	768.5	768.5
120°	843.3	842.4	842.0	842.1	842.4	842.7	843.0	843.3	843.0	842.7	842.4
122.5°	915.9	915.6	915.5	914.8	913.4	912.1	910.7	909.3	910.7	912.1	913.4
125°	986.5	986.5	986.5	985.5	983.6	981.7	979.7	977.8	979.7	981.7	983.6
127.5°	1049.6	1049.9	1050.0	1049.3	1047.9	1046.6	1045.2	1043.8	1045.2	1046.6	1047.9
130°	1110.2	1109.9	1109.8	1109.1	1107.7	1106.4	1105.0	1103.6	1105.0	1106.4	1107.7
132.5°	1169.6	1170.4	1170.8	1170.0	1168.3	1166.7	1165.0	1163.4	1165.0	1166.7	1168.3
135°	1226.1	1226.6	1226.9	1226.1	1224.4	1222.7	1221.1	1219.4	1221.1	1222.7	1224.4
137.5°	1278.4	1278.9	1279.2	1278.4	1276.7	1275.0	1273.4	1271.7	1273.4	1275.0	1276.7
140°	1324.9	1325.2	1325.3	1325.0	1324.5	1323.9	1323.4	1322.8	1323.4	1323.9	1324.5
142.5°	1370.9	1370.4	1370.1	1370.0	1369.7	1369.4	1369.2	1368.9	1369.2	1369.4	1369.7
145°	1416.2	1416.2	1416.2	1415.9	1415.4	1414.8	1414.3	1413.7	1414.3	1414.8	1415.4
147.5°	1454.0	1453.7	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6	1453.6
150°	1489.3	1488.8	1488.5	1488.8	1489.3	1489.9	1490.4	1491.0	1490.4	1489.9	1489.3
152.5°	1521.7	1521.2	1520.9	1521.6	1523.0	1524.3	1525.7	1527.1	1525.7	1524.3	1523.0
155°	1550.3	1549.8	1549.5	1550.3	1552.0	1553.7	1555.3	1557.0	1555.3	1553.7	1552.0
157.5°	1576.9	1576.9	1576.9	1577.3	1578.1	1579.0	1579.8	1580.6	1579.8	1579.0	1578.1
160°	1598.5	1598.2	1598.1	1598.9	1600.6	1602.3	1603.9	1605.6	1603.9	1602.3	1600.6
162.5°	1618.4	1618.1	1618.0	1618.8	1620.5	1622.2	1623.8	1625.5	1623.8	1622.2	1620.5
165°	1635.9	1635.6	1635.5	1636.3	1638.0	1639.6	1641.3	1642.9	1641.3	1639.6	1638.0
167.5°	1649.6	1649.3	1649.2	1650.0	1651.7	1653.3	1655.0	1656.6	1655.0	1653.3	1651.7
170°	1659.5	1659.2	1659.1	1660.1	1662.0	1663.9	1665.9	1667.8	1665.9	1663.9	1662.0
172.5°	1667.4	1666.9	1666.6	1667.6	1669.5	1671.4	1673.4	1675.3	1673.4	1671.4	1669.5
175°	1673.2	1672.9	1672.8	1673.6	1675.3	1677.0	1678.6	1680.3	1678.6	1677.0	1675.3
177.5°	1677.0	1676.7	1676.6	1677.4	1679.1	1680.7	1682.4	1684.0	1682.4	1680.7	1679.1
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2
2.5°	874.6	871.7	869.5	867.3	857.8	847.7	846.2	844.0	839.6	844.7	842.6
5°	852.0	845.5	841.8	832.4	820.7	812.0	804.7	796.0	792.4	789.4	788.7
7.5°	824.4	818.5	812.0	802.5	788.0	773.4	762.5	753.8	746.5	742.9	742.9
10°	797.4	790.2	781.4	765.4	751.6	733.4	721.8	713.0	702.9	697.0	691.9
12.5°	769.8	761.8	753.8	733.4	717.4	698.5	681.8	670.8	665.8	659.2	650.5
15°	742.2	729.8	721.8	701.4	681.0	662.1	651.2	639.6	627.9	621.4	618.5
17.5°	713.0	704.3	691.2	669.4	646.8	630.1	614.1	603.2	589.4	582.8	576.3
20°	686.9	673.8	660.7	638.8	617.0	594.4	578.4	565.3	556.6	551.5	545.7
22.5°	655.6	643.2	632.3	609.0	585.0	563.9	546.4	538.4	529.7	521.7	515.9
25°	628.6	616.3	605.4	579.9	553.7	534.1	521.0	510.8	501.3	497.7	491.9
27.5°	600.3	588.6	574.1	548.6	525.3	508.6	494.8	485.3	478.0	470.8	466.4
30°	573.3	560.3	547.2	519.5	500.6	483.9	470.8	459.1	453.3	449.7	442.4
32.5°	547.2	530.4	519.5	494.0	475.8	459.8	448.9	438.7	431.5	424.9	419.1
35°	518.8	500.6	489.7	468.6	449.7	433.6	424.2	416.9	408.2	402.4	399.5
37.5°	491.9	476.6	465.7	443.8	424.9	411.8	401.6	392.2	388.5	380.5	379.1
40°	462.8	449.7	439.5	418.4	400.9	390.7	379.8	371.1	364.5	360.9	355.8
42.5°	436.6	425.6	414.7	395.1	378.4	366.0	358.0	350.0	344.2	338.3	334.7
45°	412.5	400.9	390.7	371.8	355.1	344.2	336.2	326.7	325.2	317.2	313.6
47.5°	387.1	376.9	368.2	348.5	333.2	322.3	312.9	306.3	299.8	296.9	291.8
50°	362.3	352.2	342.0	324.5	310.7	299.8	290.3	283.0	279.4	275.0	270.7
52.5°	335.4	327.4	319.4	301.2	287.4	277.9	269.9	260.5	256.8	253.2	250.3
55°	312.9	301.2	292.5	277.2	264.8	254.7	245.9	238.7	235.0	232.1	228.5
57.5°	282.3	275.0	267.8	253.9	242.3	232.1	223.4	217.6	213.2	211.0	211.7
60°	256.1	248.1	243.7	229.2	217.6	209.5	201.5	195.7	191.4	189.2	188.4
62.5°	228.5	222.6	214.6	204.5	192.8	185.5	179.7	175.4	168.1	167.3	165.2
65°	201.5	197.2	189.9	180.4	171.0	164.4	157.9	152.1	149.2	145.5	143.3
67.5°	175.4	171.0	164.4	156.4	149.9	143.3	137.5	131.7	126.6	123.7	122.2
70°	149.9	146.2	141.9	132.4	124.4	119.3	115.0	111.3	106.2	104.8	104.0
72.5°	125.1	121.5	119.3	111.3	104.0	99.7	95.3	91.7	89.5	88.8	86.6
75°	102.6	99.0	96.0	88.8	84.4	81.5	77.1	75.7	73.5	72.8	72.0
77.5°	80.0	76.4	75.7	70.6	65.5	64.0	62.6	59.7	59.7	59.7	58.2
80°	57.5	56.8	56.0	50.9	48.7	47.3	46.6	44.4	42.9	41.5	40.7
82.5°	38.6	37.8	37.1	34.9	32.7	32.0	31.3	29.8	29.8	30.6	29.1
85°	23.3	21.8	21.1	20.4	18.9	18.9	19.6	18.9	18.9	18.9	18.2
87.5°	8.7	8.7	8.7	8.7	9.5	8.0	8.7	8.7	8.0	8.0	7.3
90°	10.1	11.2	12.2	14.1	16.0	18.0	19.9	21.3	22.7	24.1	25.5
92.5°	13.7	12.5	13.3	15.0	16.6	18.3	19.9	21.3	22.7	24.1	25.5
95°	67.7	67.3	62.0	51.5	41.0	30.4	19.9	21.3	22.7	24.1	25.5
97.5°	140.0	140.8	127.6	101.3	75.0	48.7	22.4	23.0	23.5	24.1	24.6
100°	211.3	211.7	212.3	213.4	214.5	215.6	216.7	175.5	134.2	93.0	51.7
102.5°	288.4	289.0	289.3	289.8	290.4	290.9	291.5	292.1	292.6	293.2	293.7
105°	370.6	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2
107.5°	450.9	450.9	451.2	451.7	452.3	452.8	453.4	453.7	453.9	454.2	454.5
110°	533.1	533.1	533.4	533.9	534.5	535.0	535.6	534.8	534.0	533.1	532.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	613.7	614.1	614.2	614.5	614.8	615.0	615.3	614.2	613.1	612.0	610.9
115°	693.1	693.8	693.9	694.2	694.5	694.7	695.0	693.9	692.8	691.7	690.6
117.5°	768.5	768.5	769.1	770.2	771.3	772.4	773.5	771.8	770.2	768.5	766.8
120°	842.1	842.0	842.4	843.3	844.1	845.0	845.8	845.2	844.7	844.1	843.6
122.5°	914.8	915.5	915.6	915.9	916.2	916.5	916.8	916.2	915.7	915.1	914.6
125°	985.5	986.5	986.5	986.5	986.5	986.5	986.5	985.4	984.3	983.2	982.1
127.5°	1049.3	1050.0	1049.9	1049.6	1049.3	1049.1	1048.8	1048.2	1047.7	1047.1	1046.6
130°	1109.1	1109.8	1109.9	1110.2	1110.5	1110.8	1111.1	1110.3	1109.4	1108.6	1107.7
132.5°	1170.0	1170.8	1170.4	1169.6	1168.7	1167.9	1167.1	1167.1	1167.1	1167.1	1167.1
135°	1226.1	1226.9	1226.6	1226.1	1225.5	1225.0	1224.4	1223.8	1223.3	1222.7	1222.2
137.5°	1278.4	1279.2	1278.9	1278.4	1277.8	1277.3	1276.7	1276.7	1276.7	1276.7	1276.7
140°	1325.0	1325.3	1325.2	1324.9	1324.6	1324.4	1324.1	1324.6	1325.2	1325.7	1326.2
142.5°	1370.0	1370.1	1370.4	1370.9	1371.5	1372.0	1372.6	1372.6	1372.6	1372.6	1372.6
145°	1415.9	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1416.5	1416.8	1417.1	1417.4
147.5°	1453.6	1453.6	1453.7	1454.0	1454.3	1454.5	1454.8	1455.1	1455.4	1455.7	1456.0
150°	1488.8	1488.5	1488.8	1489.3	1489.9	1490.4	1491.0	1491.6	1492.1	1492.7	1493.2
152.5°	1521.6	1520.9	1521.2	1521.7	1522.3	1522.8	1523.4	1523.9	1524.5	1525.0	1525.5
155°	1550.3	1549.5	1549.8	1550.3	1550.9	1551.4	1552.0	1552.8	1553.6	1554.5	1555.3
157.5°	1577.3	1576.9	1576.9	1576.9	1576.9	1576.9	1576.9	1577.7	1578.5	1579.4	1580.2
160°	1598.9	1598.1	1598.2	1598.5	1598.8	1599.0	1599.3	1600.4	1601.5	1602.6	1603.7
162.5°	1618.8	1618.0	1618.1	1618.4	1618.7	1619.0	1619.3	1620.9	1622.6	1624.2	1625.9
165°	1636.3	1635.5	1635.6	1635.9	1636.2	1636.4	1636.7	1638.4	1640.0	1641.7	1643.4
167.5°	1650.0	1649.2	1649.3	1649.6	1649.9	1650.1	1650.4	1652.3	1654.3	1656.2	1658.1
170°	1660.1	1659.1	1659.2	1659.5	1659.8	1660.1	1660.4	1662.6	1664.8	1667.0	1669.2
172.5°	1667.6	1666.6	1666.9	1667.4	1668.0	1668.5	1669.1	1671.0	1673.0	1674.9	1676.8
175°	1673.6	1672.8	1672.9	1673.2	1673.5	1673.8	1674.1	1676.3	1678.5	1680.7	1682.9
177.5°	1677.4	1676.6	1676.7	1677.0	1677.3	1677.5	1677.8	1679.7	1681.7	1683.6	1685.5
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2
2.5°	838.9	840.4	836.7	835.3	832.4	836.0	836.7	836.0	842.6	839.6	841.1
5°	790.2	787.3	785.1	780.0	780.0	780.7	782.9	779.3	781.4	786.5	785.8
7.5°	736.3	734.9	735.6	729.8	725.4	726.9	725.4	732.0	735.6	734.1	737.1
10°	687.6	690.5	683.9	681.0	678.1	681.0	680.3	681.8	686.1	689.0	694.1
12.5°	648.3	647.6	643.9	641.0	635.9	637.4	641.7	640.3	641.0	647.6	646.8
15°	611.2	606.8	603.9	597.4	598.8	593.7	598.1	603.2	605.4	611.2	614.8
17.5°	574.1	573.3	569.7	569.0	561.0	558.8	563.2	564.6	566.8	569.7	574.8
20°	542.8	542.1	537.0	535.5	529.0	533.3	531.9	534.8	536.2	542.1	544.2
22.5°	514.4	510.8	509.3	507.1	505.0	504.2	507.1	506.4	511.5	513.7	514.4
25°	488.2	485.3	484.6	480.9	479.5	477.3	479.5	481.7	487.5	489.7	492.6
27.5°	464.2	462.0	460.6	457.7	455.5	455.5	456.9	459.8	462.0	463.5	464.9
30°	442.4	440.9	436.6	435.1	432.9	432.9	432.9	434.4	438.0	442.4	444.6
32.5°	419.8	416.9	414.0	414.0	411.8	411.8	412.5	414.0	417.6	418.4	422.0
35°	398.0	395.1	392.9	391.4	392.2	389.3	390.7	392.9	397.3	398.7	400.9
37.5°	376.9	376.2	371.8	369.6	371.1	371.1	370.3	371.8	374.7	377.6	379.1
40°	353.6	352.2	352.2	350.0	350.7	347.8	350.0	351.4	352.9	355.8	358.0
42.5°	333.2	331.8	328.9	329.6	327.4	327.4	328.9	329.6	331.8	335.4	336.9
45°	311.4	311.4	310.0	307.8	308.5	306.3	307.8	308.5	311.4	315.1	313.6
47.5°	290.3	289.6	289.6	286.7	288.1	285.9	288.1	288.9	290.3	292.5	291.8
50°	269.9	267.8	268.5	267.8	267.0	267.0	268.5	268.5	269.9	269.9	272.1
52.5°	248.8	248.8	247.4	248.1	249.6	248.1	250.3	248.1	249.6	250.3	251.7
55°	229.9	228.5	229.2	228.5	231.4	229.2	231.4	229.9	231.4	230.6	232.1
57.5°	209.5	207.4	208.1	207.4	209.5	208.8	211.0	208.8	209.5	210.3	212.5
60°	186.3	186.3	186.3	184.8	187.0	187.0	186.3	186.3	189.2	190.6	189.9
62.5°	164.4	163.7	161.5	160.8	161.5	160.1	163.0	162.3	163.7	165.2	166.6
65°	140.4	139.0	138.2	136.8	136.8	136.1	136.8	139.7	140.4	141.2	144.8
67.5°	120.8	120.1	119.3	117.1	117.1	118.6	118.6	118.6	123.0	120.8	123.7
70°	103.3	101.9	100.4	99.7	99.7	100.4	101.1	101.9	101.1	104.0	104.8
72.5°	86.6	87.3	85.9	85.9	85.9	85.1	85.1	86.6	87.3	86.6	87.3
75°	72.0	72.0	71.3	72.0	72.0	71.3	71.3	72.8	72.8	72.0	74.2
77.5°	58.2	57.5	56.0	54.6	55.3	54.6	55.3	54.6	56.8	58.9	57.5
80°	40.7	40.0	40.0	40.0	40.7	40.0	41.5	40.0	40.7	40.7	41.5
82.5°	29.1	29.8	29.8	29.1	29.8	29.1	29.8	29.8	29.8	29.1	29.8
85°	18.9	18.9	18.9	18.9	18.2	18.9	18.9	18.9	19.6	18.9	19.6
87.5°	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.0	8.7	8.0	8.7
90°	26.2	26.6	27.4	28.3	29.1	29.9	29.1	28.3	27.4	26.6	26.2
92.5°	26.2	26.3	26.6	26.9	27.1	27.4	27.1	26.9	26.6	26.3	26.2
95°	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2	26.2
97.5°	24.9	25.0	25.3	25.6	25.9	26.2	25.9	25.6	25.3	25.0	24.9
100°	31.1	30.6	29.5	28.4	27.3	26.2	27.3	28.4	29.5	30.6	31.1
102.5°	294.0	282.4	259.1	235.8	212.6	189.3	212.6	235.8	259.1	282.4	294.0
105°	371.2	371.1	370.8	370.5	370.2	369.9	370.2	370.5	370.8	371.1	371.2
107.5°	454.6	454.1	453.0	451.9	450.8	449.7	450.8	451.9	453.0	454.1	454.6
110°	531.9	532.0	532.3	532.6	532.8	533.1	532.8	532.6	532.3	532.0	531.9

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	610.3	610.0	609.5	608.9	608.4	607.8	608.4	608.9	609.5	610.0	610.3
115°	690.1	689.3	687.6	685.9	684.3	682.6	684.3	685.9	687.6	689.3	690.1
117.5°	766.0	765.7	765.2	764.6	764.1	763.5	764.1	764.6	765.2	765.7	766.0
120°	843.3	842.6	841.2	839.8	838.4	837.0	838.4	839.8	841.2	842.6	843.3
122.5°	914.3	913.5	911.8	910.1	908.5	906.8	908.5	910.1	911.8	913.5	914.3
125°	981.5	981.1	980.3	979.4	978.6	977.8	978.6	979.4	980.3	981.1	981.5
127.5°	1046.3	1045.2	1043.0	1040.7	1038.5	1036.3	1038.5	1040.7	1043.0	1045.2	1046.3
130°	1107.3	1106.6	1105.2	1103.9	1102.5	1101.1	1102.5	1103.9	1105.2	1106.6	1107.3
132.5°	1167.1	1166.4	1165.0	1163.7	1162.3	1160.9	1162.3	1163.7	1165.0	1166.4	1167.1
135°	1221.9	1221.1	1219.4	1217.7	1216.1	1214.4	1216.1	1217.7	1219.4	1221.1	1221.9
137.5°	1276.7	1276.0	1274.6	1273.3	1271.9	1270.5	1271.9	1273.3	1274.6	1276.0	1276.7
140°	1326.5	1325.7	1324.0	1322.4	1320.7	1319.1	1320.7	1322.4	1324.0	1325.7	1326.5
142.5°	1372.6	1371.8	1370.1	1368.5	1366.8	1365.2	1366.8	1368.5	1370.1	1371.8	1372.6
145°	1417.5	1416.7	1415.0	1413.3	1411.7	1410.0	1411.7	1413.3	1415.0	1416.7	1417.5
147.5°	1456.1	1455.1	1453.2	1451.3	1449.3	1447.4	1449.3	1451.3	1453.2	1455.1	1456.1
150°	1493.5	1492.4	1490.2	1487.9	1485.7	1483.5	1485.7	1487.9	1490.2	1492.4	1493.5
152.5°	1525.8	1524.8	1522.9	1521.0	1519.0	1517.1	1519.0	1521.0	1522.9	1524.8	1525.8
155°	1555.7	1554.6	1552.4	1550.2	1548.0	1545.8	1548.0	1550.2	1552.4	1554.6	1555.7
157.5°	1580.6	1579.5	1577.3	1575.1	1572.9	1570.7	1572.9	1575.1	1577.3	1579.5	1580.6
160°	1604.3	1603.2	1601.0	1598.7	1596.5	1594.3	1596.5	1598.7	1601.0	1603.2	1604.3
162.5°	1626.7	1625.5	1623.0	1620.5	1618.0	1615.5	1618.0	1620.5	1623.0	1625.5	1626.7
165°	1644.2	1643.1	1640.9	1638.6	1636.4	1634.2	1636.4	1638.6	1640.9	1643.1	1644.2
167.5°	1659.1	1657.9	1655.4	1652.9	1650.4	1647.9	1650.4	1652.9	1655.4	1657.9	1659.1
170°	1670.3	1669.1	1666.6	1664.1	1661.6	1659.1	1661.6	1664.1	1666.6	1669.1	1670.3
172.5°	1677.8	1676.6	1674.1	1671.6	1669.1	1666.6	1669.1	1671.6	1674.1	1676.6	1677.8
175°	1684.0	1682.8	1680.3	1677.8	1675.3	1672.8	1675.3	1677.8	1680.3	1682.8	1684.0
177.5°	1686.5	1685.4	1683.2	1681.0	1678.8	1676.6	1678.8	1681.0	1683.2	1685.4	1686.5
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2	886.2
2.5°	838.2	841.8	838.9	836.7	842.6	845.5	845.5	850.6	855.7	860.0	860.7
5°	786.5	792.4	793.8	793.1	801.8	806.2	815.6	820.7	828.0	833.1	838.9
7.5°	739.2	747.2	748.0	749.4	762.5	769.8	777.8	790.9	801.1	808.4	814.9
10°	691.9	697.0	702.1	708.7	721.8	734.1	745.8	759.6	772.7	780.0	789.4
12.5°	656.3	659.9	665.8	670.1	683.9	694.9	710.1	729.1	748.0	753.8	765.4
15°	619.2	621.4	633.0	637.4	649.0	667.2	676.7	694.9	715.2	726.1	739.2
17.5°	576.3	589.4	596.6	601.7	616.3	630.8	646.1	665.0	691.2	701.4	710.9
20°	545.7	555.2	563.2	569.7	582.8	604.6	618.5	633.7	658.5	670.1	683.9
22.5°	518.8	526.8	534.1	541.3	550.1	569.7	585.7	606.8	631.6	642.5	658.5
25°	493.3	501.3	505.7	514.4	526.1	539.9	558.8	577.7	602.5	614.8	630.1
27.5°	468.6	476.6	484.6	491.9	499.9	513.0	526.1	550.1	575.5	590.1	603.2
30°	447.5	451.1	458.4	466.4	474.4	486.8	502.0	518.8	547.9	561.0	577.0
32.5°	424.2	430.7	435.8	441.7	451.8	462.0	475.8	496.9	520.2	532.6	550.1
35°	402.4	408.2	411.8	422.0	428.6	439.5	453.3	472.2	491.9	505.7	521.0
37.5°	381.3	387.1	391.4	397.3	406.0	415.5	430.0	443.8	467.1	478.8	496.2
40°	359.4	364.5	369.6	376.2	384.2	395.8	404.5	422.0	440.9	454.0	467.1
42.5°	338.3	341.2	347.1	354.3	362.3	372.5	384.9	398.7	417.6	429.3	440.9
45°	315.8	320.9	327.4	332.5	339.8	350.0	360.9	373.3	392.2	403.8	416.2
47.5°	294.7	298.3	302.7	310.7	320.1	327.4	339.1	350.7	368.2	379.1	390.7
50°	272.8	276.5	283.0	288.1	295.4	304.9	315.8	328.1	344.9	352.2	363.8
52.5°	252.5	253.9	260.5	265.6	272.8	283.8	292.5	303.4	319.4	327.4	339.1
55°	232.1	233.6	237.2	242.3	250.3	259.0	268.5	280.9	294.7	302.0	312.9
57.5°	211.0	212.5	216.1	219.7	227.7	235.7	246.7	256.8	270.7	277.2	287.4
60°	189.9	189.9	193.5	198.6	204.5	211.7	221.2	233.6	243.7	251.7	259.0
62.5°	167.3	169.5	171.7	175.4	181.9	190.6	198.6	207.4	219.7	225.6	232.1
65°	144.8	147.0	151.3	155.0	160.1	165.9	176.1	183.4	192.8	199.4	205.2
67.5°	125.1	127.3	130.2	134.6	138.2	144.8	152.1	159.3	169.5	173.9	178.3
70°	104.8	107.0	109.1	115.0	118.6	123.7	128.8	136.1	144.8	147.7	151.3
72.5°	88.8	89.5	92.4	93.9	99.0	103.3	109.1	113.5	120.1	123.7	126.6
75°	74.9	74.9	75.7	77.1	80.0	82.9	87.3	91.7	97.5	99.7	103.3
77.5°	58.9	61.1	60.4	61.8	63.3	64.8	68.4	71.3	77.1	78.6	80.0
80°	42.2	42.9	45.1	47.3	47.3	49.5	51.7	52.4	56.0	58.2	58.2
82.5°	30.6	31.3	30.6	31.3	32.0	32.7	34.9	37.8	37.8	38.6	40.0
85°	18.9	18.9	19.6	20.4	20.4	19.6	21.1	20.4	21.1	22.6	22.6
87.5°	9.5	8.7	8.7	8.7	8.7	8.7	9.5	8.7	9.5	9.5	9.5
90°	25.5	24.1	22.7	21.3	19.9	18.0	16.0	14.1	12.2	11.2	10.1
92.5°	25.5	24.1	22.7	21.3	19.9	18.3	16.6	15.0	13.3	12.5	13.7
95°	25.5	24.1	22.7	21.3	19.9	30.4	41.0	51.5	62.0	67.3	67.7
97.5°	24.6	24.1	23.5	23.0	22.4	48.7	75.0	101.3	127.6	140.8	140.0
100°	51.7	93.0	134.2	175.5	216.7	215.6	214.5	213.4	212.3	211.7	211.3
102.5°	293.7	293.2	292.6	292.1	291.5	290.9	290.4	289.8	289.3	289.0	288.4
105°	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	371.2	370.6
107.5°	454.5	454.2	453.9	453.7	453.4	452.8	452.3	451.7	451.2	450.9	450.9
110°	532.3	533.1	534.0	534.8	535.6	535.0	534.5	533.9	533.4	533.1	533.1

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	610.9	612.0	613.1	614.2	615.3	615.0	614.8	614.5	614.2	614.1	613.7
115°	690.6	691.7	692.8	693.9	695.0	694.7	694.5	694.2	693.9	693.8	693.1
117.5°	766.8	768.5	770.2	771.8	773.5	772.4	771.3	770.2	769.1	768.5	768.5
120°	843.6	844.1	844.7	845.2	845.8	845.0	844.1	843.3	842.4	842.0	842.1
122.5°	914.6	915.1	915.7	916.2	916.8	916.5	916.2	915.9	915.6	915.5	914.8
125°	982.1	983.2	984.3	985.4	986.5	986.5	986.5	986.5	986.5	986.5	985.5
127.5°	1046.6	1047.1	1047.7	1048.2	1048.8	1049.1	1049.3	1049.6	1049.9	1050.0	1049.3
130°	1107.7	1108.6	1109.4	1110.3	1111.1	1110.8	1110.5	1110.2	1109.9	1109.8	1109.1
132.5°	1167.1	1167.1	1167.1	1167.1	1167.1	1167.9	1168.7	1169.6	1170.4	1170.8	1170.0
135°	1222.2	1222.7	1223.3	1223.8	1224.4	1225.0	1225.5	1226.1	1226.6	1226.9	1226.1
137.5°	1276.7	1276.7	1276.7	1276.7	1276.7	1277.3	1277.8	1278.4	1278.9	1279.2	1278.4
140°	1326.2	1325.7	1325.2	1324.6	1324.1	1324.4	1324.6	1324.9	1325.2	1325.3	1325.0
142.5°	1372.6	1372.6	1372.6	1372.6	1372.6	1372.0	1371.5	1370.9	1370.4	1370.1	1370.0
145°	1417.4	1417.1	1416.8	1416.5	1416.2	1416.2	1416.2	1416.2	1416.2	1416.2	1415.9
147.5°	1456.0	1455.7	1455.4	1455.1	1454.8	1454.5	1454.3	1454.0	1453.7	1453.6	1453.6
150°	1493.2	1492.7	1492.1	1491.6	1491.0	1490.4	1489.9	1489.3	1488.8	1488.5	1488.8
152.5°	1525.5	1525.0	1524.5	1523.9	1523.4	1522.8	1522.3	1521.7	1521.2	1520.9	1521.6
155°	1555.3	1554.5	1553.6	1552.8	1552.0	1551.4	1550.9	1550.3	1549.8	1549.5	1550.3
157.5°	1580.2	1579.4	1578.5	1577.7	1576.9	1576.9	1576.9	1576.9	1576.9	1576.9	1577.3
160°	1603.7	1602.6	1601.5	1600.4	1599.3	1599.0	1598.8	1598.5	1598.2	1598.1	1598.9
162.5°	1625.9	1624.2	1622.6	1620.9	1619.3	1619.0	1618.7	1618.4	1618.1	1618.0	1618.8
165°	1643.4	1641.7	1640.0	1638.4	1636.7	1636.4	1636.2	1635.9	1635.6	1635.5	1636.3
167.5°	1658.1	1656.2	1654.3	1652.3	1650.4	1650.1	1649.9	1649.6	1649.3	1649.2	1650.0
170°	1669.2	1667.0	1664.8	1662.6	1660.4	1660.1	1659.8	1659.5	1659.2	1659.1	1660.1
172.5°	1676.8	1674.9	1673.0	1671.0	1669.1	1668.5	1668.0	1667.4	1666.9	1666.6	1667.6
175°	1682.9	1680.7	1678.5	1676.3	1674.1	1673.8	1673.5	1673.2	1672.9	1672.8	1673.6
177.5°	1685.5	1683.6	1681.7	1679.7	1677.8	1677.5	1677.3	1677.0	1676.7	1676.6	1677.4
180°	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3	1680.3

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	886.2	886.2	886.2	886.2
2.5°	865.8	872.4	878.9	886.9
5°	848.4	860.0	872.4	884.0
7.5°	829.5	846.2	862.2	878.9
10°	808.4	829.5	847.7	870.9
12.5°	785.1	807.6	833.1	859.3
15°	761.8	790.2	817.1	846.9
17.5°	740.0	766.9	796.7	832.4
20°	713.8	743.6	777.1	814.9
22.5°	686.1	718.9	755.2	796.0
25°	662.8	696.3	731.2	774.2
27.5°	637.4	672.3	706.5	752.3
30°	608.3	646.1	681.0	728.3
32.5°	580.6	618.5	657.0	701.4
35°	553.7	590.8	629.4	674.5
37.5°	528.2	561.7	599.5	640.3
40°	504.2	534.8	568.3	605.4
42.5°	473.7	509.3	540.6	567.5
45°	447.5	476.6	505.7	527.5
47.5°	416.9	446.0	470.8	488.2
50°	391.4	414.7	435.1	450.4
52.5°	360.9	382.7	399.5	411.1
55°	331.1	350.0	364.5	372.5
57.5°	304.1	316.5	327.4	334.7
60°	274.3	283.8	293.2	301.2
62.5°	242.3	252.5	257.6	266.3
65°	213.9	220.5	228.5	231.4
67.5°	186.3	189.9	195.0	200.8
70°	157.2	159.3	164.4	172.4
72.5°	131.7	133.9	137.5	140.4
75°	104.8	107.0	109.9	112.8
77.5°	82.2	82.9	84.4	87.3
80°	59.7	61.8	63.3	64.0
82.5°	41.5	42.2	42.2	42.9
85°	26.2	24.7	24.7	25.5
87.5°	9.5	10.9	10.9	12.4
90°	7.9	5.6	3.4	1.2
92.5°	16.2	18.7	21.2	23.7
95°	68.5	69.4	70.2	71.0
97.5°	138.3	136.6	135.0	133.3
100°	210.5	209.6	208.8	208.0
102.5°	287.3	286.2	285.1	284.0
105°	369.5	368.4	367.3	366.2
107.5°	450.9	450.9	450.9	450.9
110°	533.1	533.1	533.1	533.1

TEST NUMBER: P1036002

CATALOG NUMBER: S125RDIW-B610D1340UB50-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	612.8	612.0	611.1	610.3
115°	691.7	690.4	689.0	687.6
117.5°	768.5	768.5	768.5	768.5
120°	842.4	842.7	843.0	843.3
122.5°	913.4	912.1	910.7	909.3
125°	983.6	981.7	979.7	977.8
127.5°	1047.9	1046.6	1045.2	1043.8
130°	1107.7	1106.4	1105.0	1103.6
132.5°	1168.3	1166.7	1165.0	1163.4
135°	1224.4	1222.7	1221.1	1219.4
137.5°	1276.7	1275.0	1273.4	1271.7
140°	1324.5	1323.9	1323.4	1322.8
142.5°	1369.7	1369.4	1369.2	1368.9
145°	1415.4	1414.8	1414.3	1413.7
147.5°	1453.6	1453.6	1453.6	1453.6
150°	1489.3	1489.9	1490.4	1491.0
152.5°	1523.0	1524.3	1525.7	1527.1
155°	1552.0	1553.7	1555.3	1557.0
157.5°	1578.1	1579.0	1579.8	1580.6
160°	1600.6	1602.3	1603.9	1605.6
162.5°	1620.5	1622.2	1623.8	1625.5
165°	1638.0	1639.6	1641.3	1642.9
167.5°	1651.7	1653.3	1655.0	1656.6
170°	1662.0	1663.9	1665.9	1667.8
172.5°	1669.5	1671.4	1673.4	1675.3
175°	1675.3	1677.0	1678.6	1680.3
177.5°	1679.1	1680.7	1682.4	1684.0
180°	1680.3	1680.3	1680.3	1680.3

(END OF REPORT)