

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223822

Luminaire Tested: **LSR2B10SP159030D010 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR2B10SP159030D010 2LBDL*WMH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 439.0 lumens
Efficiency: N/A
Efficacy: 42.6 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223822

CATALOG NUMBER: LSR2B10SP159030D010 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P223822

CATALOG NUMBER: LSR2B10SP159030D010 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96		
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94		
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93		
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91		
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90		
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88		
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87		
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86		
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2109486
5°	1524935
10°	443942
15°	155792
20°	66695
25°	30003
30°	11584
35°	5769
40°	3843
45°	2520
50°	1386
55°	1013
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223822

CATALOG NUMBER: LSR2B10SP159030D010 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.5	63.2
10°-20°	112.9	25.7
20°-30°	34.6	7.9
30°-40°	8.5	1.9
40°-50°	3.6	0.8
50°-60°	1.5	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.1	96.8
0°-40°	433.6	98.8
0°-60°	438.7	99.9
0°-90°	439.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	439.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5446	
5°	3922	278
15°	388	113
25°	70	35
35°	12	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223822

CATALOG NUMBER: LSR2B10SP159030D010 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5446.0
1°	5362.8
2°	5159.8
3°	4836.2
4°	4413.4
5°	3921.9
6°	3367.9
7°	2766.5
8°	2156.7
9°	1586.6
10°	1128.7
11°	809.0
12°	608.2
13°	495.3
14°	433.5
15°	388.5
17.5°	239.6
20°	161.8
22.5°	108.4
25°	70.2
27.5°	42.7
30°	25.9
32.5°	16.8
35°	12.2
37.5°	9.9
40°	7.6
42.5°	6.1
45°	4.6
47.5°	3.1
50°	2.3
52.5°	2.3
55°	1.5
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223822

CATALOG NUMBER: LSR2B10SP159030D010 2LBDL*WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)