

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224765

Luminaire Tested: **LSRWM2B10FL409030D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409030D010 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 772.6 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224765

CATALOG NUMBER: LSRWM2B10FL409030D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224765

CATALOG NUMBER: LSRWM2B10FL409030D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	99	108	104	101	98		101	98	96			98	96	94			91
3	105	100	96	93	104	99	95	92		96	93	90			94	91	89			86
4	101	95	90	87	100	94	90	86		92	88	85			90	87	85			82
5	98	91	86	82	96	90	85	82		88	84	81			86	83	80			79
6	94	86	82	78	93	86	81	78		84	80	77			83	79	77			75
7	90	83	78	74	89	82	77	74		81	77	74			80	76	73			72
8	87	79	74	71	86	79	74	71		78	74	71			77	73	70			69
9	84	76	71	68	83	76	71	68		75	71	68			74	70	67			66
10	81	73	68	65	80	73	68	65		72	68	65			71	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	699353
5°	686627
10°	610356
15°	480049
20°	319418
25°	183393
30°	92629
35°	43598
40°	17546
45°	8710
50°	4761
55°	3377
60°	3099
65°	1833
70°	2265
75°	1497
80°	2231
85°	0



TEST NUMBER: P224765

CATALOG NUMBER: LSRWM2B10FL409030D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.7	20.9
10°-20°	324.3	42.0
20°-30°	201.7	26.1
30°-40°	62.0	8.0
40°-50°	13.6	1.8
50°-60°	4.9	0.6
60°-70°	2.5	0.3
70°-80°	1.4	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.7	89.0
0°-40°	749.7	97.0
0°-60°	768.2	99.4
0°-90°	772.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	772.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1806	
5°	1766	162
15°	1197	324
25°	429	202
35°	92	62
45°	16	14
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224765

CATALOG NUMBER: LSRWM2B10FL409030D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1805.5
2.5°	1797.6
5°	1765.9
7.5°	1685.6
10°	1551.8
12.5°	1391.3
15°	1197.1
17.5°	985.0
20°	774.9
22.5°	587.6
25°	429.1
27.5°	302.2
30°	207.1
32.5°	139.7
35°	92.2
37.5°	55.5
40°	34.7
42.5°	23.8
45°	15.9
47.5°	10.9
50°	7.9
52.5°	6.9
55°	5.0
57.5°	4.0
60°	4.0
62.5°	3.0
65°	2.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)