

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B10WFL559030D010 2LBDL\*WMH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14805)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSSQWM2B10WFL559030D010 2LBDL\*WMH  
Description: 1000 Lumen, 2inch Portfolio LED Cylinder  
WIDE FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 716.5 lumens  
Efficiency: N/A  
Efficacy: 69.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDL\*WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDL\*WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 83  | 78  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 72  | 80  | 75  | 72  |  | 79  | 74  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 67  |  | 74  | 70  | 66  |  | 73  |
| 7   | 82  | 73  | 67  | 63  | 81  | 72  | 67  | 62  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 73  | 64  | 59  | 55  | 63  | 58  | 54  |  | 62  | 58  | 54  |  | 62  |
| 10  | 71  | 61  | 55  | 51  | 70  | 61  | 55  | 51  | 60  | 55  | 51  |  | 59  | 54  | 51  |  | 58  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 341213 |
| 5°  | 337190 |
| 10° | 311629 |
| 15° | 273128 |
| 20° | 235740 |
| 25° | 200659 |
| 30° | 158915 |
| 35° | 110319 |
| 40° | 71650  |
| 45° | 43111  |
| 50° | 24888  |
| 55° | 13979  |
| 60° | 6120   |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDL\*WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 80.4   | 11.2      |
| 10°-20°   | 189.8  | 26.5      |
| 20°-30°   | 213.6  | 29.8      |
| 30°-40°   | 147.5  | 20.6      |
| 40°-50°   | 63.9   | 8.9       |
| 50°-60°   | 19.8   | 2.8       |
| 60°-70°   | 1.4    | 0.2       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 483.8  | 67.5      |
| 0°-40°    | 631.3  | 88.1      |
| 0°-60°    | 715.1  | 99.8      |
| 0°-90°    | 716.5  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 716.5  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 881 |      |
| 5°  | 867 | 80   |
| 15° | 681 | 190  |
| 25° | 470 | 214  |
| 35° | 233 | 148  |
| 45° | 79  | 64   |
| 55° | 21  | 20   |
| 65° | 0   | 1    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDL\*WMH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 880.9 |
| 2.5°  | 879.0 |
| 5°    | 867.2 |
| 7.5°  | 839.6 |
| 10°   | 792.3 |
| 12.5° | 738.2 |
| 15°   | 681.1 |
| 17.5° | 622.1 |
| 20°   | 571.9 |
| 22.5° | 521.7 |
| 25°   | 469.5 |
| 27.5° | 416.4 |
| 30°   | 355.3 |
| 32.5° | 291.3 |
| 35°   | 233.3 |
| 37.5° | 183.1 |
| 40°   | 141.7 |
| 42.5° | 107.3 |
| 45°   | 78.7  |
| 47.5° | 58.1  |
| 50°   | 41.3  |
| 52.5° | 29.5  |
| 55°   | 20.7  |
| 57.5° | 14.8  |
| 60°   | 7.9   |
| 62.5° | 2.0   |
| 65°   | 0.0   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)