

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036028

Luminaire Tested: S125RDIW-B610D470UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036028
REPORT IS A COMBINATION OF REPORTS P1006714 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D470UB27-4F0-XX-W2A-F
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4227.0 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036028

CATALOG NUMBER: S125RDIW-B610D470UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1036028

CATALOG NUMBER: S125RDIW-B610D470UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	55	53	52
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44
3	83	73	66	60	77	69	62	57	59	54	50	51	47	44	43	40	38
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	39	35	33
5	70	58	50	44	65	54	47	42	47	42	37	41	36	33	35	31	29
6	64	52	44	38	60	49	42	36	43	37	33	37	33	29	32	28	25
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	33	29	36	30	26	31	26	23	27	23	20
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6365	6365	6365
5°	6366	6206	6216
10°	6303	6050	5997
15°	6214	5831	5707
20°	6103	5567	5404
25°	5977	5310	5080
30°	5822	5027	4738
35°	5664	4740	4376
40°	5513	4446	4022
45°	5332	4127	3651
50°	5149	3789	3274
55°	4936	3456	2883
60°	4718	3076	2478
65°	4459	2651	2040
70°	4156	2158	1606
75°	3738	1622	1171
80°	3151	1050	790
85°	2361	564	444

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5332 cd/sqm

TEST NUMBER: P1036028

CATALOG NUMBER: S125RDIW-B610D470UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.5	2.2
10°-20°	261.3	6.2
20°-30°	378.8	9.0
30°-40°	431.6	10.2
40°-50°	420.7	10.0
50°-60°	354.1	8.4
60°-70°	248.1	5.9
70°-80°	127.2	3.0
80°-90°	32.6	0.8
90°-100°	20.8	0.5
100°-110°	138.1	3.3
110°-120°	248.6	5.9
120°-130°	319.1	7.5
130°-140°	343.2	8.1
140°-150°	322.1	7.6
150°-160°	260.6	6.2
160°-170°	168.5	4.0
170°-180°	58.1	1.4
0°-30°	733.6	17.4
0°-40°	1165.2	27.6
0°-60°	1940.0	45.9
0°-90°	2347.9	55.5
90°-120°	407.4	9.6
90°-150°	1391.9	32.9
90°-180°	1879.0	44.5
0°-180°	4227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	992	989	981	988	987	94
15°	943	939	923	922	915	266
25°	855	844	816	807	798	394
35°	737	719	685	663	653	461
45°	603	582	540	510	499	465
55°	458	434	392	358	346	409
65°	310	284	245	215	203	307
75°	165	143	111	94	89	174
85°	41	28	24	23	22	45
90°	0	4	7	10	11	4
95°	26	24	7	10	10	32
105°	133	135	135	135	135	141
115°	250	253	253	251	248	248
125°	356	359	359	357	356	318
135°	444	447	446	445	442	342
145°	515	516	516	516	513	322
155°	567	564	565	566	563	261
165°	598	595	596	599	595	169
175°	612	609	610	613	609	58
180°	612	612	612	612	612	

TEST NUMBER: P1036028

CATALOG NUMBER: S125RDIW-B610D470UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.4	993.4	993.4	993.4	993.4
2.5°	995.6	993.4	985.9	993.4	992.6
5°	991.9	988.9	980.6	988.1	986.6
7.5°	984.4	981.4	971.6	977.6	976.1
10°	973.1	970.9	960.4	962.6	960.4
12.5°	960.4	957.4	942.4	943.9	940.1
15°	943.1	938.6	922.9	922.1	915.3
17.5°	925.1	918.3	899.6	895.8	890.6
20°	903.3	895.8	871.8	868.1	861.3
22.5°	879.3	871.8	846.3	838.1	832.8
25°	855.3	844.1	816.3	806.6	798.3
27.5°	828.3	814.8	785.5	772.8	764.5
30°	798.3	784.0	752.5	735.3	728.5
32.5°	769.0	751.8	719.5	700.0	691.0
35°	736.8	718.8	685.0	663.3	652.7
37.5°	706.0	684.3	649.7	624.2	613.7
40°	673.0	650.5	614.5	586.0	577.0
42.5°	638.5	615.2	577.7	550.7	536.5
45°	603.2	581.5	540.2	510.2	498.9
47.5°	566.5	544.0	502.7	471.9	459.2
50°	532.0	507.2	464.4	432.9	421.7
52.5°	494.4	468.9	429.2	394.7	383.4
55°	457.7	433.7	391.6	357.9	345.9
57.5°	420.2	394.7	354.1	321.1	310.6
60°	384.1	357.9	317.4	284.4	273.1
62.5°	345.9	321.1	279.9	249.8	238.6
65°	309.9	284.4	244.6	214.6	203.3
67.5°	273.9	248.3	210.1	181.6	172.6
70°	237.1	211.6	174.1	150.8	141.8
72.5°	201.1	176.3	141.8	120.8	115.5
75°	165.1	142.6	111.0	94.5	89.3
77.5°	128.3	110.3	84.0	71.3	66.8
80°	97.5	79.5	58.5	51.8	50.3
82.5°	67.5	51.8	39.0	36.8	36.0
85°	41.3	27.8	24.0	23.3	22.5
87.5°	17.3	12.0	11.3	11.3	10.5
90°	0.5	4.1	7.3	9.5	10.9
92.5°	8.6	4.5	7.3	9.5	10.0
95°	25.8	24.5	7.3	9.5	9.5
97.5°	48.5	51.2	8.2	9.1	9.5
100°	75.7	77.1	78.9	11.3	9.5
102.5°	103.4	105.2	106.1	107.0	68.9
105°	133.3	135.1	135.1	135.1	134.7
107.5°	164.2	164.2	165.1	165.5	163.7
110°	194.1	194.1	195.0	193.6	194.1



TEST NUMBER: P1036028

CATALOG NUMBER: S125RDIW-B610D470UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.2	223.6	224.0	222.2	221.3
115°	250.3	252.6	253.0	251.2	248.5
117.5°	279.8	279.8	281.6	278.9	278.0
120°	307.0	306.5	307.9	307.0	304.7
122.5°	331.0	333.3	333.8	332.8	330.1
125°	356.0	359.1	359.1	357.3	356.0
127.5°	380.0	382.3	381.8	380.9	377.3
130°	401.8	404.0	404.5	403.1	400.9
132.5°	423.5	426.3	424.9	424.9	422.6
135°	443.9	446.7	445.8	444.9	442.1
137.5°	463.0	465.7	464.8	464.8	462.5
140°	481.6	482.5	482.0	482.9	480.2
142.5°	498.4	498.8	499.7	499.7	497.0
145°	514.7	515.6	515.6	516.0	513.3
147.5°	529.2	529.2	529.6	530.1	526.9
150°	542.8	541.9	542.8	543.7	540.1
152.5°	555.9	553.7	554.6	555.5	552.3
155°	566.8	564.1	565.0	566.4	562.8
157.5°	575.4	574.1	574.1	575.4	571.8
160°	584.5	581.8	582.3	584.1	580.4
162.5°	591.8	589.1	589.5	592.2	588.1
165°	598.1	595.4	595.9	598.6	594.9
167.5°	603.1	600.4	600.8	604.0	599.9
170°	607.2	604.0	604.5	608.1	604.0
172.5°	609.9	606.7	607.6	610.8	606.7
175°	611.7	609.0	609.5	613.1	609.0
177.5°	613.1	610.4	610.8	614.0	610.4
180°	611.7	611.7	611.7	611.7	611.7

(END OF REPORT)