

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B10WFL559030D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10WFL559030D010 2LBDLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 704.5 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		101	99	98		97	96	95
2	108	102	98	95		105	101	97	94		98	94	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	85		91	87	84		89	85	83		87	84	81
4	97	89	83	79		95	88	82	78		85	81	77		83	80	76		82	78	76
5	91	83	77	72		90	82	76	72		80	75	71		78	74	71		77	73	70
6	87	78	71	67		85	77	71	67		75	70	66		74	69	66		73	69	65
7	82	73	67	62		81	72	66	62		71	66	62		70	65	62		69	64	61
8	78	69	62	58		77	68	62	58		67	62	58		66	61	58		65	61	57
9	74	65	59	55		73	64	58	54		63	58	54		62	57	54		61	57	54
10	71	61	55	51		70	61	55	51		60	55	51		59	54	51		58	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	330484
5°	328363
10°	305257
15°	267995
20°	231000
25°	197539
30°	156768
35°	109278
40°	69122
45°	42180
50°	24948
55°	13641
60°	3021
65°	2658
70°	2152
75°	2844
80°	2231
85°	4444



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.4	11.1
10°-20°	186.1	26.4
20°-30°	210.0	29.8
30°-40°	145.3	20.6
40°-50°	61.9	8.8
50°-60°	17.9	2.5
60°-70°	2.6	0.4
70°-80°	1.6	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	474.5	67.3
0°-40°	619.7	88.0
0°-60°	699.6	99.3
0°-90°	704.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	844	78
15°	668	186
25°	462	210
35°	231	145
45°	77	62
55°	20	18
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559030D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	853.2
2.5°	852.2
5°	844.5
7.5°	818.5
10°	776.1
12.5°	724.1
15°	668.3
17.5°	610.5
20°	560.4
22.5°	513.3
25°	462.2
27.5°	408.3
30°	350.5
32.5°	287.9
35°	231.1
37.5°	179.1
40°	136.7
42.5°	103.0
45°	77.0
47.5°	55.9
50°	41.4
52.5°	29.9
55°	20.2
57.5°	8.7
60°	3.9
62.5°	2.9
65°	2.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)