

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225487

Luminaire Tested: **LSRWM2B10FL409730D010 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409730D010 2LBDL*H
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 709.8 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225487

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P225487

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		108	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	86		99	94	89	86		91	88	85		90	86	84		88	85	83
5	97	90	85	81		96	89	84	81		87	83	80		86	82	80		84	81	79
6	93	86	81	77		92	85	80	77		84	79	76		82	79	76		81	78	75
7	90	82	77	73		88	81	76	73		80	76	73		79	75	72		78	75	72
8	86	78	73	70		85	78	73	70		77	72	69		76	72	69		75	71	69
9	83	75	70	67		82	75	70	67		74	69	66		73	69	66		72	69	66
10	80	72	67	64		79	72	67	64		71	67	64		70	66	64		70	66	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	623937
5°	603185
10°	532203
15°	419296
20°	288131
25°	173990
30°	94329
35°	48468
40°	23715
45°	11230
50°	5906
55°	3984
60°	2247
65°	917
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225487

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.7	20.0
10°-20°	284.6	40.1
20°-30°	190.2	26.8
30°-40°	68.9	9.7
40°-50°	17.8	2.5
50°-60°	5.3	0.7
60°-70°	1.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	616.5	86.9
0°-40°	685.4	96.6
0°-60°	708.5	99.8
0°-90°	709.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1611	
5°	1551	142
15°	1046	285
25°	407	190
35°	102	69
45°	20	18
55°	6	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225487

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1610.8
2.5°	1596.2
5°	1551.3
7.5°	1469.3
10°	1353.1
12.5°	1210.6
15°	1045.6
17.5°	869.8
20°	699.0
22.5°	541.8
25°	407.1
27.5°	296.8
30°	210.9
32.5°	148.4
35°	102.5
37.5°	71.3
40°	46.9
42.5°	30.3
45°	20.5
47.5°	14.6
50°	9.8
52.5°	7.8
55°	5.9
57.5°	3.9
60°	2.9
62.5°	2.0
65°	1.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)