

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224602

Luminaire Tested: **LSRWM2B10FL409730D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409730D010 2LBDLC*MMS
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 701.8 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224602

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224602

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	110	106	102	100		108	104	101	99		101	99	96			98	96	94			91
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			87
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83		96	90	86	82		88	85	82			87	83	81			79
6	94	87	82	78		93	86	82	78		85	81	78			83	80	77			76
7	91	83	78	75		89	82	78	75		81	77	74			80	77	74			72
8	87	80	75	71		86	79	75	71		78	74	71			77	73	71			69
9	84	76	72	68		83	76	71	68		75	71	68			74	71	68			67
10	81	74	69	66		81	73	69	66		72	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	638811
5°	626554
10°	556550
15°	439226
20°	292954
25°	168605
30°	85428
35°	40051
40°	16383
45°	7395
50°	3796
55°	2431
60°	1394
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224602

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.5	21.0
10°-20°	296.0	42.2
20°-30°	185.4	26.4
30°-40°	57.4	8.2
40°-50°	11.8	1.7
50°-60°	3.3	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.8	89.6
0°-40°	686.2	97.8
0°-60°	701.3	99.9
0°-90°	701.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	701.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1649	
5°	1611	147
15°	1095	296
25°	394	185
35°	85	57
45°	14	12
55°	4	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224602

CATALOG NUMBER: LSRWM2B10FL409730D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1649.2
2.5°	1641.1
5°	1611.4
7.5°	1535.7
10°	1415.0
12.5°	1266.4
15°	1095.3
17.5°	898.0
20°	710.7
22.5°	540.4
25°	394.5
27.5°	277.4
30°	191.0
32.5°	127.9
35°	84.7
37.5°	53.1
40°	32.4
42.5°	20.7
45°	13.5
47.5°	9.0
50°	6.3
52.5°	4.5
55°	3.6
57.5°	2.7
60°	1.8
62.5°	0.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)