

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B10WFL559730D010 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14806)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10WFL559730D010 2LBDL*GPH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 647.1 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	86		91	88	84		89	86	83		87	84	82
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	83	77	73		90	82	77	72		80	75	72		79	74	71		77	73	70
6	87	78	72	67		85	77	71	67		75	70	67		74	70	66		73	69	66
7	83	73	67	63		81	72	67	62		71	66	62		70	65	62		69	65	61
8	78	69	63	58		77	68	62	58		67	62	58		66	61	58		65	61	58
9	75	65	59	55		73	64	59	55		63	58	54		62	58	54		62	57	54
10	71	61	55	51		70	61	55	51		60	55	51		59	54	51		58	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	308327
5°	304956
10°	281854
15°	246822
20°	212780
25°	181683
30°	143707
35°	99443
40°	64369
45°	39057
50°	22839
55°	12831
60°	4881
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.7	11.2
10°-20°	171.6	26.5
20°-30°	193.1	29.8
30°-40°	133.2	20.6
40°-50°	57.5	8.9
50°-60°	17.9	2.8
60°-70°	1.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	437.4	67.6
0°-40°	570.5	88.2
0°-60°	645.9	99.8
0°-90°	647.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	647.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	796	
5°	784	73
15°	616	172
25°	425	193
35°	210	133
45°	71	58
55°	19	18
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	796.0
2.5°	794.2
5°	784.3
7.5°	758.1
10°	716.6
12.5°	667.8
15°	615.5
17.5°	563.1
20°	516.2
22.5°	471.1
25°	425.1
27.5°	376.3
30°	321.3
32.5°	263.5
35°	210.3
37.5°	165.2
40°	127.3
42.5°	95.7
45°	71.3
47.5°	52.3
50°	37.9
52.5°	27.1
55°	19.0
57.5°	12.6
60°	6.3
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)