

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B10WFL559730D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10WFL559730D010 2LBDLC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 647.2 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		101	99	98		97	96	95
2	108	102	98	95		105	101	97	94		98	94	92		95	92	90		92	90	88
3	102	95	90	86		100	94	89	85		91	87	84		89	85	83		87	84	81
4	97	89	83	79		95	88	82	78		85	81	77		83	80	76		82	78	76
5	91	83	77	72		90	82	76	72		80	75	71		78	74	71		77	73	70
6	87	78	71	67		85	77	71	67		75	70	66		74	69	66		73	69	65
7	82	73	67	62		81	72	66	62		71	66	62		70	65	62		69	64	61
8	78	69	62	58		77	68	62	58		67	62	58		66	61	58		65	61	57
9	74	65	59	55		73	64	58	54		63	58	54		62	57	54		61	57	54
10	71	61	55	51		70	61	55	51		60	55	51		59	54	51		58	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	303563
5°	301612
10°	280399
15°	246140
20°	212203
25°	181469
30°	144020
35°	100389
40°	63509
45°	38784
50°	22899
55°	12561
60°	2711
65°	2475
70°	2039
75°	2694
80°	2008
85°	4000



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.0	11.1
10°-20°	171.0	26.4
20°-30°	192.9	29.8
30°-40°	133.4	20.6
40°-50°	56.9	8.8
50°-60°	16.5	2.5
60°-70°	2.4	0.4
70°-80°	1.5	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.8	67.3
0°-40°	569.3	88.0
0°-60°	642.6	99.3
0°-90°	647.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	647.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	784	
5°	776	72
15°	614	171
25°	425	193
35°	212	133
45°	71	57
55°	19	16
65°	3	2
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B10WFL559730D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	783.7
2.5°	782.8
5°	775.7
7.5°	751.8
10°	712.9
12.5°	665.1
15°	613.8
17.5°	560.8
20°	514.8
22.5°	471.4
25°	424.6
27.5°	375.0
30°	322.0
32.5°	264.5
35°	212.3
37.5°	164.5
40°	125.6
42.5°	94.6
45°	70.8
47.5°	51.3
50°	38.0
52.5°	27.4
55°	18.6
57.5°	8.0
60°	3.5
62.5°	2.7
65°	2.7
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)