

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224719

Luminaire Tested: **LSSQ2B10FL408040D010 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL408040D010 2LBD*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1074.1 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224719

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224719

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	99	108	104	101	98		101	98	96			98	96	94			95
3	105	100	96	93	104	99	95	92		96	93	90			94	91	89			92
4	101	95	90	87	100	94	90	86		92	88	85			90	87	85			88
5	98	91	86	82	96	90	85	82		88	84	81			86	83	80			85
6	94	86	82	78	93	86	81	78		84	80	77			83	79	77			82
7	90	83	78	74	89	82	77	74		81	77	74			80	76	73			79
8	87	79	74	71	86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68	83	76	71	68		75	71	68			74	70	67			73
10	81	73	68	65	80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	972316
5°	954606
10°	848591
15°	667401
20°	444110
25°	254938
30°	128769
35°	60574
40°	24372
45°	12051
50°	6629
55°	4660
60°	4261
65°	2566
70°	3171
75°	2095
80°	3123
85°	0



TEST NUMBER: P224719

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.8	20.9
10°-20°	450.8	42.0
20°-30°	280.5	26.1
30°-40°	86.2	8.0
40°-50°	19.0	1.8
50°-60°	6.7	0.6
60°-70°	3.4	0.3
70°-80°	2.0	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	956.1	89.0
0°-40°	1042.4	97.0
0°-60°	1068.0	99.4
0°-90°	1074.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1074.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2510	
5°	2455	225
15°	1664	451
25°	596	280
35°	128	86
45°	22	19
55°	7	7
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P224719

CATALOG NUMBER: LSSQ2B10FL408040D010 2LBD*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2510.2
2.5°	2499.1
5°	2455.1
7.5°	2343.5
10°	2157.5
12.5°	1934.3
15°	1664.3
17.5°	1369.4
20°	1077.4
22.5°	817.0
25°	596.5
27.5°	420.2
30°	287.9
32.5°	194.3
35°	128.1
37.5°	77.2
40°	48.2
42.5°	33.1
45°	22.0
47.5°	15.2
50°	11.0
52.5°	9.6
55°	6.9
57.5°	5.5
60°	5.5
62.5°	4.1
65°	2.8
67.5°	2.8
70°	2.8
72.5°	2.8
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)