

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1036103

Luminaire Tested: S125RDIW-B850D1340UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1036103
REPORT IS A COMBINATION OF REPORTS P1006885 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B850D1340UB50-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7618.0 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1036103

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1036103

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41		
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35		
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30		
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	32	30	25		
4	73	63	55	49	66	57	51	46	48	43	39	39	35	32	30	28	26	22		
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	23	19		
6	62	50	42	36	56	46	39	34	38	33	29	31	27	25	25	22	20	17		
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15		
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16	13		
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14	12		
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8515	8515	8515
5°	8516	8303	8316
10°	8433	8094	8023
15°	8314	7801	7636
20°	8166	7448	7231
25°	7996	7104	6796
30°	7789	6726	6340
35°	7577	6342	5855
40°	7376	5948	5381
45°	7134	5521	4885
50°	6889	5069	4380
55°	6604	4625	3857
60°	6312	4115	3315
65°	5966	3546	2730
70°	5560	2887	2148
75°	4999	2171	1566
80°	4217	1406	1057
85°	3156	755	595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7134 cd/sqm

TEST NUMBER: P1036103

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.6
10°-20°	349.6	4.6
20°-30°	506.9	6.7
30°-40°	577.5	7.6
40°-50°	562.8	7.4
50°-60°	473.7	6.2
60°-70°	331.9	4.4
70°-80°	170.2	2.2
80°-90°	45.0	0.6
90°-100°	106.6	1.4
100°-110°	316.8	4.2
110°-120°	537.3	7.1
120°-130°	707.3	9.3
130°-140°	792.6	10.4
140°-150°	776.9	10.2
150°-160°	652.5	8.6
160°-170°	433.8	5.7
170°-180°	151.8	2.0
0°-30°	981.5	12.9
0°-40°	1559.0	20.5
0°-60°	2595.5	34.1
0°-90°	3142.5	41.3
90°-120°	960.7	12.6
90°-150°	3237.4	42.5
90°-180°	4475.0	58.7
0°-180°	7618.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1327	1323	1312	1322	1320	126
15°	1262	1256	1235	1234	1225	356
25°	1144	1129	1092	1079	1068	527
35°	986	962	916	887	873	617
45°	807	778	723	683	668	622
55°	612	580	524	479	463	548
65°	415	380	327	287	272	411
75°	221	191	149	126	120	233
85°	55	37	32	31	30	60
90°	1	11	20	26	30	9
95°	81	84	96	105	107	85
105°	284	291	298	306	310	303
115°	538	543	545	544	543	532
125°	785	792	794	791	790	703
135°	1021	1028	1030	1030	1025	787
145°	1237	1242	1245	1245	1242	773
155°	1415	1415	1416	1421	1415	652
165°	1539	1536	1538	1542	1535	434
175°	1600	1595	1595	1602	1594	152
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P1036103

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1329.0	1329.0	1329.0	1329.0	1329.0
2.5°	1332.0	1329.0	1319.0	1329.0	1328.0
5°	1327.0	1323.0	1312.0	1322.0	1320.0
7.5°	1317.0	1313.0	1299.9	1307.9	1305.9
10°	1301.9	1298.9	1284.9	1287.9	1284.9
12.5°	1284.9	1280.8	1260.8	1262.8	1257.8
15°	1261.8	1255.7	1234.7	1233.7	1224.6
17.5°	1237.7	1228.6	1203.5	1198.5	1191.5
20°	1208.6	1198.5	1166.4	1161.4	1152.4
22.5°	1176.4	1166.4	1132.3	1121.2	1114.2
25°	1144.3	1129.3	1092.1	1079.1	1068.0
27.5°	1108.2	1090.1	1051.0	1033.9	1022.9
30°	1068.0	1049.0	1006.8	983.7	974.7
32.5°	1028.9	1005.8	962.6	936.5	924.5
35°	985.7	961.6	916.5	887.4	873.3
37.5°	944.6	915.5	869.3	835.2	821.1
40°	900.4	870.3	822.1	784.0	771.9
42.5°	854.2	823.1	772.9	736.8	717.7
45°	807.0	777.9	722.7	682.6	667.5
47.5°	757.9	727.7	672.5	631.4	614.3
50°	711.7	678.6	621.3	579.2	564.1
52.5°	661.5	627.4	574.2	528.0	512.9
55°	612.3	580.2	524.0	478.8	462.7
57.5°	562.1	528.0	473.8	429.6	415.6
60°	513.9	478.8	424.6	380.4	365.4
62.5°	462.7	429.6	374.4	334.3	319.2
65°	414.6	380.4	327.2	287.1	272.0
67.5°	366.4	332.3	281.1	242.9	230.9
70°	317.2	283.1	232.9	201.8	189.7
72.5°	269.0	235.9	189.7	161.6	154.6
75°	220.8	190.7	148.6	126.5	119.5
77.5°	171.6	147.6	112.4	95.4	89.3
80°	130.5	106.4	78.3	69.3	67.3
82.5°	90.3	69.3	52.2	49.2	48.2
85°	55.2	37.1	32.1	31.1	30.1
87.5°	23.1	16.1	15.1	15.1	14.1
90°	1.2	11.2	20.0	26.2	30.0
92.5°	37.4	43.7	54.9	63.6	66.1
95°	81.1	83.6	96.1	104.8	107.3
97.5°	124.8	126.0	143.5	151.0	152.2
100°	174.7	174.7	190.9	202.2	204.7
102.5°	228.4	234.6	240.9	253.3	257.1
105°	284.5	290.8	298.3	305.7	309.5
107.5°	345.7	351.9	358.2	361.9	361.9
110°	409.3	415.6	419.3	423.0	421.8

TEST NUMBER: P1036103

CATALOG NUMBER: S125RDIW-B850D1340UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	474.2	476.7	481.7	483.0	480.5
115°	537.9	542.9	545.3	544.1	542.9
117.5°	602.8	604.0	606.5	607.7	602.8
120°	662.7	668.9	670.1	670.1	665.1
122.5°	727.5	728.8	732.5	731.3	727.5
125°	785.0	792.4	793.7	791.2	789.9
127.5°	848.6	852.3	853.6	852.3	849.8
130°	904.8	911.0	913.5	912.2	909.7
132.5°	960.9	972.1	970.9	969.6	965.9
135°	1020.8	1028.3	1029.5	1029.5	1024.6
137.5°	1077.0	1084.5	1087.0	1088.2	1082.0
140°	1130.6	1136.9	1140.6	1143.1	1136.9
142.5°	1184.3	1189.3	1194.3	1195.5	1189.3
145°	1236.7	1241.7	1245.4	1245.4	1241.7
147.5°	1285.4	1289.1	1291.6	1295.4	1285.4
150°	1334.0	1332.8	1337.8	1337.8	1335.3
152.5°	1374.0	1376.5	1377.7	1381.5	1376.5
155°	1415.2	1415.2	1416.4	1421.4	1415.2
157.5°	1452.6	1450.1	1451.3	1456.3	1447.6
160°	1485.0	1481.3	1482.5	1487.5	1481.3
162.5°	1513.7	1511.2	1511.2	1517.5	1510.0
165°	1538.7	1536.2	1537.5	1542.4	1535.0
167.5°	1561.2	1556.2	1556.2	1563.7	1556.2
170°	1578.6	1573.6	1573.6	1581.1	1572.4
172.5°	1591.1	1586.1	1586.1	1593.6	1586.1
175°	1599.9	1594.9	1594.9	1602.3	1593.6
177.5°	1606.1	1601.1	1599.9	1607.3	1598.6
180°	1603.6	1603.6	1603.6	1603.6	1603.6

(END OF REPORT)