

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224057

Luminaire Tested: **LSSQWM2B10SP158040D010 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10SP158040D010 2LBDL*WMH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
SPOT OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 572.4 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224057

CATALOG NUMBER: LSSQWM2B10SP158040D010 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P224057

CATALOG NUMBER: LSSQWM2B10SP158040D010 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	116	114	112	111	113	112	110	109		108	107	106			104	103	103			98
2	113	110	107	105	111	108	106	104		105	103	102			102	101	100			96
3	110	106	103	101	108	105	102	100		102	100	98			100	98	97			94
4	108	103	100	97	106	102	99	97		100	98	96			98	96	95			93
5	105	101	97	95	104	100	97	94		98	96	94			97	95	93			91
6	103	98	95	93	102	98	95	92		96	94	92			95	93	91			90
7	101	96	93	91	100	96	93	90		95	92	90			94	91	90			88
8	100	94	91	89	99	94	91	89		93	90	89			92	90	88			87
9	98	93	90	88	97	92	89	87		92	89	87			91	89	87			86
10	96	91	88	86	96	91	88	86		90	88	86			90	87	86			85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2750505
5°	1988337
10°	578851
15°	203112
20°	86975
25°	39106
30°	15118
35°	7519
40°	5056
45°	3287
50°	1808
55°	1351
60°	775
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224057

CATALOG NUMBER: LSSQWM2B10SP158040D010 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.9	63.2
10°-20°	147.2	25.7
20°-30°	45.2	7.9
30°-40°	11.1	1.9
40°-50°	4.7	0.8
50°-60°	2.0	0.3
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.3	96.8
0°-40°	565.4	98.8
0°-60°	572.1	99.9
0°-90°	572.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7101	
5°	5114	362
15°	506	147
25°	92	45
35°	16	11
45°	6	5
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224057

CATALOG NUMBER: LSSQWM2B10SP158040D010 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7100.9
1°	6992.4
2°	6727.7
3°	6305.8
4°	5754.5
5°	5113.7
6°	4391.3
7°	3607.2
8°	2812.1
9°	2068.8
10°	1471.7
11°	1054.8
12°	793.1
13°	645.8
14°	565.2
15°	506.5
17.5°	312.5
20°	211.0
22.5°	141.3
25°	91.5
27.5°	55.7
30°	33.8
32.5°	21.9
35°	15.9
37.5°	12.9
40°	10.0
42.5°	8.0
45°	6.0
47.5°	4.0
50°	3.0
52.5°	3.0
55°	2.0
57.5°	2.0
60°	1.0
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224057

CATALOG NUMBER: LSSQWM2B10SP158040D010 2LBDL*WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)