

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224767

Luminaire Tested: **LSSQWM2B10FL409040D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409040D010 2LBDL*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 819.3 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224767

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224767

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	97	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	741613
5°	728115
10°	647250
15°	509042
20°	338750
25°	194462
30°	98220
35°	46199
40°	18608
45°	9203
50°	5062
55°	3579
60°	3254
65°	1925
70°	2378
75°	1646
80°	2454
85°	0



TEST NUMBER: P224767

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	20.9
10°-20°	343.9	42.0
20°-30°	213.9	26.1
30°-40°	65.8	8.0
40°-50°	14.5	1.8
50°-60°	5.2	0.6
60°-70°	2.6	0.3
70°-80°	1.6	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.3	89.0
0°-40°	795.0	97.0
0°-60°	814.7	99.4
0°-90°	819.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	819.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1915	
5°	1873	172
15°	1269	344
25°	455	214
35°	98	66
45°	17	14
55°	5	5
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P224767

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1914.6
2.5°	1906.2
5°	1872.6
7.5°	1787.5
10°	1645.6
12.5°	1475.4
15°	1269.4
17.5°	1044.5
20°	821.8
22.5°	623.2
25°	455.0
27.5°	320.5
30°	219.6
32.5°	148.2
35°	97.7
37.5°	58.8
40°	36.8
42.5°	25.2
45°	16.8
47.5°	11.6
50°	8.4
52.5°	7.4
55°	5.3
57.5°	4.2
60°	4.2
62.5°	3.2
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)