

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224453

Luminaire Tested: **LSSQWM2B10FL409040D010 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409040D010 2LBDL*WH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 841.7 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224453

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224453

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87			
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75			
7	90	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	776590
5°	747245
10°	657712
15°	516621
20°	351240
25°	205104
30°	104482
35°	49414
40°	21591
45°	9367
50°	4520
55°	2904
60°	1627
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224453

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.5	20.9
10°-20°	350.3	41.6
20°-30°	224.9	26.7
30°-40°	71.4	8.5
40°-50°	15.3	1.8
50°-60°	3.9	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	750.7	89.2
0°-40°	822.0	97.7
0°-60°	841.2	99.9
0°-90°	841.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	841.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2005	
5°	1922	176
15°	1288	350
25°	480	225
35°	104	71
45°	17	15
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224453

CATALOG NUMBER: LSSQWM2B10FL409040D010 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2004.9
2.5°	1985.7
5°	1921.8
7.5°	1817.2
10°	1672.2
12.5°	1495.2
15°	1288.3
17.5°	1067.5
20°	852.1
22.5°	650.5
25°	479.9
27.5°	342.3
30°	233.6
32.5°	156.8
35°	104.5
37.5°	69.3
40°	42.7
42.5°	26.7
45°	17.1
47.5°	11.7
50°	7.5
52.5°	5.3
55°	4.3
57.5°	3.2
60°	2.1
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)