

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225353

Luminaire Tested: **LSRWM2B10FL409030D2WD010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B10FL409030D2WD010 2LBDC*MW
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 533.1 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225353

CATALOG NUMBER: LSRWM2B10FL409030D2WD010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P225353

CATALOG NUMBER: LSRWM2B10FL409030D2WD010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92
4	101	95	90	87	100	94	90	86	92	88	85		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		86	83	80		85
6	94	87	82	78	93	86	81	78	84	80	77		83	80	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	482633
5°	473862
10°	421247
15°	331274
20°	220447
25°	126550
30°	63959
35°	30074
40°	12085
45°	6026
50°	3314
55°	2296
60°	2092
65°	1192
70°	1472
75°	1048
80°	1561
85°	0



TEST NUMBER: P225353

CATALOG NUMBER: LSRWM2B10FL409030D2WD010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.6	20.9
10°-20°	223.8	42.0
20°-30°	139.2	26.1
30°-40°	42.8	8.0
40°-50°	9.4	1.8
50°-60°	3.3	0.6
60°-70°	1.7	0.3
70°-80°	1.0	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	474.6	89.0
0°-40°	517.4	97.1
0°-60°	530.2	99.5
0°-90°	533.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1246	
5°	1219	112
15°	826	224
25°	296	139
35°	64	43
45°	11	9
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225353

CATALOG NUMBER: LSRWM2B10FL409030D2WD010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1246.0
2.5°	1240.6
5°	1218.7
7.5°	1163.2
10°	1071.0
12.5°	960.1
15°	826.1
17.5°	679.8
20°	534.8
22.5°	405.6
25°	296.1
27.5°	208.6
30°	143.0
32.5°	96.4
35°	63.6
37.5°	38.3
40°	23.9
42.5°	16.4
45°	11.0
47.5°	7.5
50°	5.5
52.5°	4.8
55°	3.4
57.5°	2.7
60°	2.7
62.5°	2.1
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)