

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225043

Luminaire Tested: **LSSQ2B10FL409030D2WD010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B10FL409030D2WD010 2LBD*WMH
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 573.6 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225043

CATALOG NUMBER: LSSQ2B10FL409030D2WD010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P225043

CATALOG NUMBER: LSSQ2B10FL409030D2WD010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		88
5	98	91	86	82	96	90	85	82	88	84	81		87	83	81		85
6	94	87	82	78	93	86	81	78	85	81	77		83	80	77		82
7	91	83	78	75	89	82	78	74	81	77	74		80	76	74		79
8	87	79	75	71	86	79	74	71	78	74	71		77	73	71		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	520477
5°	509750
10°	451572
15°	354894
20°	238584
25°	138602
30°	69282
35°	32675
40°	15473
45°	6793
50°	3495
55°	1958
60°	1162
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225043

CATALOG NUMBER: LSSQ2B10FL409030D2WD010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.9	20.9
10°-20°	240.0	41.8
20°-30°	151.7	26.5
30°-40°	47.5	8.3
40°-50°	11.0	1.9
50°-60°	2.9	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.7	89.2
0°-40°	559.1	97.5
0°-60°	573.1	99.9
0°-90°	573.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	573.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1344	
5°	1311	120
15°	885	240
25°	324	152
35°	69	47
45°	12	11
55°	3	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225043

CATALOG NUMBER: LSSQ2B10FL409030D2WD010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1343.7
2.5°	1337.2
5°	1311.0
7.5°	1249.2
10°	1148.1
12.5°	1028.1
15°	885.0
17.5°	728.6
20°	578.8
22.5°	440.6
25°	324.3
27.5°	229.1
30°	154.9
32.5°	103.2
35°	69.1
37.5°	46.5
40°	30.6
42.5°	18.9
45°	12.4
47.5°	8.7
50°	5.8
52.5°	4.4
55°	2.9
57.5°	2.1
60°	1.5
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)