

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1004712

Luminaire Tested: S125DW-B1270DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1004712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-12)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DW-B1270DB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5096.0 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1004712

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1004712

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	86	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	72	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	62	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	46	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	41	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	36	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	33	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	30	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	27	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12544	12544	12544
5°	12572	12453	12533
10°	12497	12365	12436
15°	12360	12217	12268
20°	12167	12008	12030
25°	11958	11761	11750
30°	11700	11494	11437
35°	11425	11207	11050
40°	11142	10896	10740
45°	10835	10610	10400
50°	10499	10268	9959
55°	10174	9880	9603
60°	9786	9488	9151
65°	9322	9017	8713
70°	8879	8473	8183
75°	8090	7823	7555
80°	7202	7088	6914
85°	6263	6374	6035

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10835 cd/sqm

TEST NUMBER: P1004712

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.8	3.6
10°-20°	521.9	10.2
20°-30°	770.4	15.1
30°-40°	898.9	17.6
40°-50°	902.8	17.7
50°-60°	792.5	15.6
60°-70°	590.3	11.6
70°-80°	337.1	6.6
80°-90°	97.3	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1477.1	29.0
0°-40°	2376.0	46.6
0°-60°	4071.3	79.9
0°-90°	5096.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5096.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1958	1958	1958	1958	1958	
5°	1955	1952	1936	1950	1949	186
15°	1863	1859	1842	1850	1850	525
25°	1692	1684	1664	1667	1662	778
35°	1461	1454	1433	1425	1413	914
45°	1196	1190	1171	1152	1148	921
55°	911	906	884	870	860	813
65°	615	612	595	581	575	610
75°	327	324	316	311	305	348
85°	85	87	87	85	82	99
90°	0	0	0	0	0	



TEST NUMBER: P1004712

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1957.9	1957.9	1957.9	1957.9	1957.9
2.5°	1964.1	1959.5	1944.0	1959.5	1957.9
5°	1954.8	1951.7	1936.2	1950.2	1948.6
7.5°	1940.9	1937.8	1920.8	1934.7	1933.1
10°	1920.8	1917.7	1900.6	1913.0	1911.5
12.5°	1896.0	1889.8	1874.3	1883.6	1883.6
15°	1863.4	1858.8	1841.8	1849.5	1849.5
17.5°	1829.4	1821.6	1804.6	1813.9	1806.1
20°	1784.4	1781.3	1761.2	1772.0	1764.3
22.5°	1739.5	1733.3	1714.7	1720.9	1716.3
25°	1691.5	1683.8	1663.6	1666.7	1662.1
27.5°	1635.7	1631.1	1611.0	1612.5	1607.9
30°	1581.5	1576.9	1553.6	1550.5	1545.9
32.5°	1522.7	1514.9	1494.8	1488.6	1479.3
35°	1460.7	1454.5	1432.8	1425.1	1412.7
37.5°	1397.2	1389.4	1369.3	1358.5	1350.7
40°	1332.1	1324.4	1302.7	1288.8	1284.1
42.5°	1262.4	1256.2	1234.5	1222.2	1214.4
45°	1195.8	1189.6	1171.0	1152.5	1147.8
47.5°	1123.0	1124.6	1101.3	1082.7	1071.9
50°	1053.3	1048.7	1030.1	1009.9	999.1
52.5°	982.1	979.0	958.8	941.8	929.4
55°	910.8	906.2	884.5	870.5	859.7
57.5°	834.9	833.4	814.8	796.2	791.5
60°	763.7	757.5	740.4	724.9	714.1
62.5°	689.3	684.7	670.7	653.7	645.9
65°	614.9	611.9	594.8	580.9	574.7
67.5°	542.1	536.0	523.6	511.2	508.1
70°	474.0	466.2	452.3	443.0	436.8
72.5°	399.6	395.0	387.2	376.4	370.2
75°	326.8	323.7	316.0	311.3	305.2
77.5°	258.7	257.1	252.5	249.4	244.7
80°	195.2	195.2	192.1	190.5	187.4
82.5°	139.4	136.3	136.3	133.2	133.2
85°	85.2	86.7	86.7	85.2	82.1
87.5°	41.8	41.8	40.3	40.3	37.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)