

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224866

Luminaire Tested: **LSSQWM2B10FL409030D2WD010 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409030D2WD010 2LBD*B
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 601.2 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224866

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P224866

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108	112	110	108	106		106	104	103			102	101	100			95
2	110	106	103	100	108	104	101	99		101	99	96			98	96	94			91
3	106	100	96	93	104	99	95	92		97	93	91			94	92	89			87
4	102	95	91	87	100	94	90	87		92	89	86			90	87	85			83
5	98	91	86	83	96	90	86	82		88	85	82			87	84	81			79
6	94	87	82	79	93	86	82	78		85	81	78			84	80	77			76
7	91	83	78	75	90	83	78	75		81	77	74			80	77	74			72
8	87	80	75	72	86	79	75	71		78	74	71			77	74	71			69
9	84	77	72	69	83	76	72	68		75	71	68			74	71	68			67
10	82	74	69	66	81	73	69	66		73	68	65			72	68	65			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	543950
5°	534480
10°	476824
15°	376909
20°	251280
25°	145782
30°	72994
35°	34330
40°	13450
45°	6026
50°	2832
55°	1621
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224866

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBD*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	21.0
10°-20°	254.4	42.3
20°-30°	160.0	26.6
30°-40°	48.9	8.1
40°-50°	9.6	1.6
50°-60°	2.2	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	540.4	89.9
0°-40°	589.4	98.0
0°-60°	601.2	100.0
0°-90°	601.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1404	
5°	1375	126
15°	940	254
25°	341	160
35°	73	49
45°	11	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224866

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBD*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1404.3
2.5°	1401.2
5°	1374.6
7.5°	1312.2
10°	1212.3
12.5°	1087.4
15°	939.9
17.5°	775.9
20°	609.6
22.5°	467.6
25°	341.1
27.5°	240.4
30°	163.2
32.5°	110.1
35°	72.6
37.5°	44.5
40°	26.6
42.5°	17.2
45°	11.0
47.5°	7.0
50°	4.7
52.5°	3.1
55°	2.4
57.5°	1.6
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)