

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1004716

Luminaire Tested: S125DW-B1270DB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1004716
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-12)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DW-B1270DB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4943.0 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 61.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1004716

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1004716

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	109	104	100	96	106	102	98	95	98	94	92	94	91	89	90	88	86	86	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	72	72	70
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	62	62	59
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	51
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	57	51	46	46	46	44
6	71	57	49	42	69	56	48	42	55	47	42	53	46	41	51	46	41	41	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	36	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	33	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	30	30	30	28
10	54	40	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	27	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12168	12168	12168
5°	12195	12079	12156
10°	12121	11994	12063
15°	11989	11850	11900
20°	11802	11648	11668
25°	11599	11408	11397
30°	11349	11149	11094
35°	11082	10870	10718
40°	10807	10569	10418
45°	10510	10292	10088
50°	10184	9960	9660
55°	9869	9583	9315
60°	9491	9203	8875
65°	9043	8748	8450
70°	8613	8218	7937
75°	7847	7587	7328
80°	6985	6874	6708
85°	6072	6182	5852

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10510 cd/sqm

TEST NUMBER: P1004716

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.2	3.6
10°-20°	506.2	10.2
20°-30°	747.3	15.1
30°-40°	871.9	17.6
40°-50°	875.7	17.7
50°-60°	768.7	15.6
60°-70°	572.6	11.6
70°-80°	327.0	6.6
80°-90°	94.4	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1432.7	29.0
0°-40°	2304.6	46.6
0°-60°	3949.0	79.9
0°-90°	4943.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4943.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1899	1899	1899	1899	1899	
5°	1896	1893	1878	1892	1890	180
15°	1808	1803	1786	1794	1794	510
25°	1641	1633	1614	1617	1612	755
35°	1417	1411	1390	1382	1370	886
45°	1160	1154	1136	1118	1113	894
55°	884	879	858	844	834	789
65°	596	594	577	563	557	592
75°	317	314	306	302	296	337
85°	83	84	84	83	80	96
90°	0	0	0	0	0	



TEST NUMBER: P1004716

CATALOG NUMBER: S125DW-B1270DB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1899.1	1899.1	1899.1	1899.1	1899.1
2.5°	1905.2	1900.6	1885.6	1900.6	1899.1
5°	1896.1	1893.1	1878.1	1891.6	1890.1
7.5°	1882.6	1879.6	1863.1	1876.6	1875.1
10°	1863.1	1860.1	1843.6	1855.6	1854.1
12.5°	1839.0	1833.0	1818.0	1827.0	1827.0
15°	1807.5	1803.0	1786.5	1794.0	1794.0
17.5°	1774.4	1766.9	1750.4	1759.4	1751.9
20°	1730.9	1727.9	1708.3	1718.8	1711.3
22.5°	1687.3	1681.3	1663.3	1669.3	1664.8
25°	1640.7	1633.2	1613.7	1616.7	1612.2
27.5°	1586.6	1582.1	1562.6	1564.1	1559.6
30°	1534.0	1529.5	1507.0	1504.0	1499.5
32.5°	1476.9	1469.4	1449.9	1443.9	1434.9
35°	1416.8	1410.8	1389.8	1382.3	1370.3
37.5°	1355.2	1347.7	1328.2	1317.7	1310.2
40°	1292.1	1284.6	1263.6	1250.1	1245.6
42.5°	1224.5	1218.5	1197.5	1185.5	1177.9
45°	1159.9	1153.9	1135.9	1117.8	1113.3
47.5°	1089.3	1090.8	1068.3	1050.2	1039.7
50°	1021.7	1017.2	999.2	979.6	969.1
52.5°	952.6	949.6	930.0	913.5	901.5
55°	883.5	879.0	857.9	844.4	833.9
57.5°	809.8	808.3	790.3	772.3	767.8
60°	740.7	734.7	718.2	703.2	692.6
62.5°	668.6	664.1	650.6	634.0	626.5
65°	596.5	593.5	577.0	563.4	557.4
67.5°	525.9	519.9	507.8	495.8	492.8
70°	459.8	452.2	438.7	429.7	423.7
72.5°	387.6	383.1	375.6	365.1	359.1
75°	317.0	314.0	306.5	302.0	296.0
77.5°	250.9	249.4	244.9	241.9	237.4
80°	189.3	189.3	186.3	184.8	181.8
82.5°	135.2	132.2	132.2	129.2	129.2
85°	82.6	84.1	84.1	82.6	79.6
87.5°	40.6	40.6	39.1	39.1	36.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)