

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225451

Luminaire Tested: **LSSQWM2B10FL409030D2WD010 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B10FL409030D2WD010 2LBDLC*MB
Description: 1000 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 558.8 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225451

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225451

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	105	102	99		107	104	101	98		101	98	96			98	96	94			95
3	105	100	95	92		103	98	94	91		96	92	90			93	91	88			91
4	101	94	90	86		99	93	89	86		91	87	85			89	86	84			88
5	97	90	85	81		95	89	84	81		87	83	80			85	82	79			84
6	93	85	80	77		92	85	80	76		83	79	76			82	78	75			81
7	89	81	76	73		88	81	76	73		80	75	72			79	75	72			78
8	86	78	73	69		85	77	73	69		76	72	69			75	72	69			75
9	83	75	70	66		82	74	69	66		73	69	66			72	69	66			72
10	80	72	67	63		79	71	66	63		70	66	63			70	66	63			69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485926
5°	468496
10°	412044
15°	322933
20°	223704
25°	137833
30°	76662
35°	40903
40°	20276
45°	10353
50°	5725
55°	3714
60°	1859
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225451

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	19.7
10°-20°	220.0	39.4
20°-30°	150.3	26.9
30°-40°	57.3	10.2
40°-50°	15.9	2.8
50°-60°	5.0	0.9
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.2	85.9
0°-40°	537.4	96.2
0°-60°	558.3	99.9
0°-90°	558.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1254	
5°	1205	110
15°	805	220
25°	322	150
35°	86	57
45°	19	16
55°	6	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225451

CATALOG NUMBER: LSSQWM2B10FL409030D2WD010 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1254.5
2.5°	1241.1
5°	1204.9
7.5°	1137.3
10°	1047.6
12.5°	933.6
15°	805.3
17.5°	674.0
20°	542.7
22.5°	426.3
25°	322.5
27.5°	236.7
30°	171.4
32.5°	121.9
35°	86.5
37.5°	60.5
40°	40.1
42.5°	26.7
45°	18.9
47.5°	13.4
50°	9.5
52.5°	7.1
55°	5.5
57.5°	3.9
60°	2.4
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)