

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007289

Luminaire Tested: S125RDW-B610DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007289
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-27)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDW-B610DB2750-4F0-XX-W2A-F_4000K
Description: Define 5 Regressed Direct Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2353.0 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007289

CATALOG NUMBER: S125RDW-B610DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007289

CATALOG NUMBER: S125RDW-B610DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	105	101	97	107	103	99	96	99	96	93	95	92	90	91	89	87	85		
2	100	92	86	80	98	90	84	79	87	82	78	84	79	76	81	77	74	72		
3	92	82	74	68	89	80	73	67	77	71	66	74	69	65	72	67	64	61		
4	84	73	64	58	82	71	64	57	69	62	57	67	61	56	64	59	55	53		
5	78	65	57	50	76	64	56	50	62	55	49	60	54	49	58	53	48	46		
6	72	59	50	44	70	58	50	44	56	49	44	55	48	43	53	47	43	41		
7	67	54	45	39	65	53	45	39	51	44	39	50	43	39	49	43	38	36		
8	62	49	41	35	61	48	41	35	47	40	35	46	39	35	45	39	34	33		
9	58	45	37	32	57	45	37	32	44	37	32	42	36	31	41	36	31	29		
10	55	42	34	29	54	41	34	29	40	34	29	39	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6381	6381	6381
5°	6396	6323	6361
10°	6347	6264	6264
15°	6272	6137	6087
20°	6175	5960	5888
25°	6062	5786	5658
30°	5921	5582	5404
35°	5778	5372	5118
40°	5643	5153	4838
45°	5480	4907	4532
50°	5316	4641	4213
55°	5125	4387	3874
60°	4935	4077	3509
65°	4710	3717	3090
70°	4453	3269	2664
75°	4097	2755	2216
80°	3609	2166	1860
85°	3043	1772	1661

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5480 cd/sqm

TEST NUMBER: P1007289

CATALOG NUMBER: S125RDW-B610DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.7	4.0
10°-20°	261.9	11.1
20°-30°	379.8	16.1
30°-40°	432.7	18.4
40°-50°	421.8	17.9
50°-60°	355.0	15.1
60°-70°	248.7	10.6
70°-80°	127.5	5.4
80°-90°	31.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	735.5	31.3
0°-40°	1168.2	49.6
0°-60°	1944.9	82.7
0°-90°	2353.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2353.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	996	996	996	996	996	
5°	994	991	983	991	989	94
15°	946	941	925	924	918	267
25°	858	846	818	809	800	395
35°	739	721	687	665	654	463
45°	605	583	542	512	500	466
55°	459	435	393	359	347	410
65°	311	285	245	215	204	308
75°	166	143	111	95	90	175
85°	41	28	24	23	23	48
90°	0	0	0	0	0	

TEST NUMBER: P1007289

CATALOG NUMBER: S125RDW-B610DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	995.9	995.9	995.9	995.9	995.9
2.5°	998.2	995.9	988.4	995.9	995.2
5°	994.4	991.4	983.1	990.7	989.1
7.5°	986.9	983.9	974.1	980.1	978.6
10°	975.6	973.4	962.8	965.1	962.8
12.5°	962.8	959.8	944.8	946.3	942.5
15°	945.5	941.0	925.2	924.5	917.7
17.5°	927.5	920.7	901.9	898.1	892.9
20°	905.7	898.1	874.1	870.3	863.5
22.5°	881.6	874.1	848.5	840.2	834.9
25°	857.5	846.2	818.4	808.6	800.3
27.5°	830.4	816.9	787.6	774.8	766.5
30°	800.3	786.1	754.5	737.2	730.4
32.5°	771.0	753.7	721.4	701.8	692.8
35°	738.7	720.6	686.8	664.9	654.4
37.5°	707.8	686.0	651.4	625.8	615.3
40°	674.7	652.2	616.1	587.5	578.4
42.5°	640.1	616.8	579.2	552.1	537.8
45°	604.8	583.0	541.6	511.5	500.2
47.5°	567.9	545.3	504.0	473.1	460.3
50°	533.3	508.5	465.6	434.0	422.7
52.5°	495.7	470.1	430.3	395.7	384.4
55°	458.8	434.8	392.7	358.8	346.8
57.5°	421.2	395.7	355.0	321.9	311.4
60°	385.1	358.8	318.2	285.1	273.8
62.5°	346.8	321.9	280.6	250.5	239.2
65°	310.7	285.1	245.2	215.1	203.8
67.5°	274.6	249.0	210.6	182.0	173.0
70°	237.7	212.1	174.5	151.2	142.2
72.5°	201.6	176.8	142.2	121.1	115.8
75°	165.5	142.9	111.3	94.8	89.5
77.5°	128.6	110.6	84.2	71.5	66.9
80°	97.8	79.7	58.7	51.9	50.4
82.5°	67.7	51.9	39.1	36.9	36.1
85°	41.4	27.8	24.1	23.3	22.6
87.5°	17.3	12.0	11.3	11.3	10.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)