

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQ2B15WFL558035D010 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQ2B15WFL558035D010 2LBDC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1314.6 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL558035D010 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL558035D010 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	110	108	106		111	108	106	104		104	102	101			101	99	98			97
2	108	102	98	95		105	101	97	94		98	94	92			95	92	90			92
3	102	95	90	86		100	94	89	85		91	87	84			89	85	83			87
4	97	89	83	79		95	88	82	78		85	81	77			83	80	76			82
5	91	83	77	72		90	82	76	72		80	75	71			78	74	71			77
6	87	78	71	67		85	77	71	67		75	70	66			74	69	66			73
7	82	73	67	62		81	72	66	62		71	66	62			70	65	62			69
8	78	69	62	58		77	68	62	58		67	62	58			66	61	58			65
9	74	65	59	55		73	64	58	54		63	58	54			62	57	54			61
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	616655
5°	612750
10°	569647
15°	500060
20°	431084
25°	368623
30°	292558
35°	203898
40°	129040
45°	78717
50°	46581
55°	25459
60°	5578
65°	4949
70°	4077
75°	5388
80°	4015
85°	8000



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL558035D010 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.2	11.1
10°-20°	347.3	26.4
20°-30°	391.8	29.8
30°-40°	271.1	20.6
40°-50°	115.5	8.8
50°-60°	33.4	2.5
60°-70°	4.9	0.4
70°-80°	3.1	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	885.4	67.3
0°-40°	1156.5	88.0
0°-60°	1305.4	99.3
0°-90°	1314.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1314.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1592	
5°	1576	146
15°	1247	347
25°	862	392
35°	431	271
45°	144	116
55°	38	33
65°	5	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQ2B15WFL558035D010 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1592.0
2.5°	1590.2
5°	1575.9
7.5°	1527.3
10°	1448.3
12.5°	1351.2
15°	1247.0
17.5°	1139.2
20°	1045.8
22.5°	957.7
25°	862.5
27.5°	761.9
30°	654.1
32.5°	537.3
35°	431.2
37.5°	334.2
40°	255.2
42.5°	192.3
45°	143.7
47.5°	104.2
50°	77.3
52.5°	55.7
55°	37.7
57.5°	16.2
60°	7.2
62.5°	5.4
65°	5.4
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	1.8
80°	1.8
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)