

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983425

Luminaire Tested: S125IW-B1050UB2750-4F0-XX-W2A_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1050UB2750-4F0-XX-W2A_2700K
Description: Define 5 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4216.0 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983425

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P983425

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983425

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.0
90°-100°	46.6	1.1
100°-110°	309.6	7.3
110°-120°	557.5	13.2
120°-130°	715.6	17.0
130°-140°	769.7	18.3
140°-150°	722.4	17.1
150°-160°	584.3	13.9
160°-170°	377.9	9.0
170°-180°	130.3	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.0
90°-120°	913.7	21.7
90°-150°	3121.4	74.0
90°-180°	4214.0	100.0
0°-180°	4216.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	3
95°	58	55	16	21	21	71
105°	299	303	303	303	302	317
115°	561	566	567	563	557	556
125°	798	805	805	801	798	713
135°	996	1002	1000	998	992	768
145°	1154	1156	1156	1157	1151	722
155°	1271	1265	1267	1270	1262	586
165°	1341	1335	1336	1342	1334	379
175°	1372	1366	1367	1375	1366	131
180°	1372	1372	1372	1372	1372	

TEST NUMBER: P983425

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	9.2	16.3	21.4	24.4
92.5°	19.3	10.2	16.3	21.4	22.4
95°	58.0	54.9	16.3	21.4	21.4
97.5°	108.8	114.9	18.3	20.3	21.4
100°	169.8	172.9	176.9	25.4	21.4
102.5°	231.9	235.9	238.0	240.0	154.6
105°	299.0	303.0	303.0	303.0	302.0
107.5°	368.1	368.1	370.2	371.2	367.1
110°	435.2	435.2	437.3	434.2	435.2

TEST NUMBER: P983425

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	498.3	501.3	502.4	498.3	496.3
115°	561.3	566.4	567.4	563.4	557.3
117.5°	627.4	627.4	631.5	625.4	623.4
120°	688.5	687.4	690.5	688.5	683.4
122.5°	742.4	747.4	748.5	746.4	740.3
125°	798.3	805.4	805.4	801.3	798.3
127.5°	852.2	857.3	856.2	854.2	846.1
130°	901.0	906.1	907.1	904.0	899.0
132.5°	949.8	955.9	952.9	952.9	947.8
135°	995.6	1001.7	999.6	997.6	991.5
137.5°	1038.3	1044.4	1042.3	1042.3	1037.3
140°	1080.0	1082.0	1081.0	1083.0	1076.9
142.5°	1117.6	1118.6	1120.6	1120.6	1114.5
145°	1154.2	1156.2	1156.2	1157.3	1151.2
147.5°	1186.7	1186.7	1187.8	1188.8	1181.7
150°	1217.3	1215.2	1217.3	1219.3	1211.2
152.5°	1246.7	1241.7	1243.7	1245.7	1238.6
155°	1271.2	1265.1	1267.1	1270.1	1262.0
157.5°	1290.5	1287.4	1287.4	1290.5	1282.3
160°	1310.8	1304.7	1305.7	1309.8	1301.7
162.5°	1327.1	1321.0	1322.0	1328.1	1318.9
165°	1341.3	1335.2	1336.2	1342.3	1334.2
167.5°	1352.5	1346.4	1347.4	1354.5	1345.4
170°	1361.7	1354.5	1355.6	1363.7	1354.5
172.5°	1367.8	1360.6	1362.7	1369.8	1360.6
175°	1371.8	1365.7	1366.7	1374.9	1365.7
177.5°	1374.9	1368.8	1369.8	1376.9	1368.8
180°	1371.8	1371.8	1371.8	1371.8	1371.8

(END OF REPORT)