

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224771

Luminaire Tested: **LSSQWM2B15FL408035D010 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL408035D010 2LBDL*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1303.8 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224771

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224771

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	99		108	104	101	98		101	98	96			98	96	94			95
3	105	100	96	93		104	99	95	92		96	93	90			94	91	89			92
4	101	95	90	87		100	94	90	86		92	88	85			90	87	85			88
5	98	91	86	82		96	90	85	82		88	84	81			86	83	80			85
6	94	86	82	78		93	86	81	78		84	80	77			83	79	77			82
7	90	83	78	74		89	82	77	74		81	77	74			80	76	73			79
8	87	79	74	71		86	79	74	71		78	74	71			77	73	70			76
9	84	76	71	68		83	76	71	68		75	71	68			74	70	67			73
10	81	73	68	65		80	73	68	65		72	68	65			71	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1180359
5°	1158856
10°	1030148
15°	810201
20°	539123
25°	309515
30°	156320
35°	73530
40°	29580
45°	14681
50°	8075
55°	5673
60°	5190
65°	3025
70°	3737
75°	2544
80°	3792
85°	0



TEST NUMBER: P224771

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.0	20.9
10°-20°	547.3	42.0
20°-30°	340.5	26.1
30°-40°	104.7	8.0
40°-50°	23.0	1.8
50°-60°	8.2	0.6
60°-70°	4.1	0.3
70°-80°	2.4	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1160.7	89.0
0°-40°	1265.4	97.1
0°-60°	1296.6	99.4
0°-90°	1303.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1303.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3047	
5°	2980	273
15°	2020	547
25°	724	340
35°	156	105
45°	27	23
55°	8	8
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224771

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3047.3
2.5°	3033.9
5°	2980.4
7.5°	2844.9
10°	2619.1
12.5°	2348.2
15°	2020.4
17.5°	1662.4
20°	1307.9
22.5°	991.8
25°	724.2
27.5°	510.1
30°	349.5
32.5°	235.8
35°	155.5
37.5°	93.7
40°	58.5
42.5°	40.1
45°	26.8
47.5°	18.4
50°	13.4
52.5°	11.7
55°	8.4
57.5°	6.7
60°	6.7
62.5°	5.0
65°	3.3
67.5°	3.3
70°	3.3
72.5°	3.3
75°	1.7
77.5°	1.7
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)