

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224633

Luminaire Tested: **LSSQWM2B15FL408035D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15FL408035D010 2LBDLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1289.4 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224633

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224633

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100		108	104	101	99		101	99	96			98	96	94			95
3	106	100	96	93		104	99	95	92		97	93	91			94	92	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			89
5	98	91	86	83		96	90	86	82		88	85	82			87	83	81			85
6	94	87	82	78		93	86	82	78		85	81	78			83	80	77			82
7	91	83	78	75		89	82	78	75		81	77	74			80	77	74			79
8	87	80	75	71		86	79	75	71		78	74	71			77	73	71			76
9	84	76	72	68		83	76	71	68		75	71	68			74	71	68			74
10	81	74	69	66		81	73	69	66		72	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1173697
5°	1151157
10°	1022557
15°	806953
20°	538216
25°	309772
30°	156902
35°	73577
40°	30136
45°	13585
50°	6990
55°	4457
60°	2556
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224633

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.0	21.0
10°-20°	543.8	42.2
20°-30°	340.6	26.4
30°-40°	105.4	8.2
40°-50°	21.8	1.7
50°-60°	6.1	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.3	89.6
0°-40°	1260.7	97.8
0°-60°	1288.6	99.9
0°-90°	1289.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1289.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3030	
5°	2961	271
15°	2012	544
25°	725	341
35°	156	105
45°	25	22
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224633

CATALOG NUMBER: LSSQWM2B15FL408035D010 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3030.1
2.5°	3015.2
5°	2960.6
7.5°	2821.6
10°	2599.8
12.5°	2326.8
15°	2012.3
17.5°	1649.9
20°	1305.7
22.5°	992.9
25°	724.8
27.5°	509.7
30°	350.8
32.5°	235.0
35°	155.6
37.5°	97.6
40°	59.6
42.5°	38.1
45°	24.8
47.5°	16.5
50°	11.6
52.5°	8.3
55°	6.6
57.5°	5.0
60°	3.3
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)