

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983427

Luminaire Tested: S125IW-B1050UB2750-4F0-XX-W2A_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1050UB2750-4F0-XX-W2A_3500K
Description: Define 5 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4271.0 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983427

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P983427

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983427

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.0
90°-100°	47.2	1.1
100°-110°	313.6	7.3
110°-120°	564.8	13.2
120°-130°	725.0	17.0
130°-140°	779.7	18.3
140°-150°	731.8	17.1
150°-160°	592.0	13.9
160°-170°	382.8	9.0
170°-180°	132.0	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.0
90°-120°	925.6	21.7
90°-150°	3162.1	74.0
90°-180°	4269.0	100.0
0°-180°	4271.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	22	25	3
95°	59	56	16	22	22	72
105°	303	307	307	307	306	321
115°	569	574	575	571	564	564
125°	809	816	816	812	809	722
135°	1009	1015	1013	1011	1004	778
145°	1169	1171	1171	1172	1166	731
155°	1288	1282	1284	1287	1278	593
165°	1359	1353	1354	1360	1352	384
175°	1390	1384	1385	1393	1384	132
180°	1390	1390	1390	1390	1390	

TEST NUMBER: P983427

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	9.3	16.5	21.6	24.7
92.5°	19.6	10.3	16.5	21.6	22.7
95°	58.7	55.6	16.5	21.6	21.6
97.5°	110.2	116.4	18.5	20.6	21.6
100°	172.0	175.1	179.3	25.8	21.6
102.5°	234.9	239.0	241.1	243.1	156.6
105°	302.9	307.0	307.0	307.0	306.0
107.5°	372.9	372.9	375.0	376.0	371.9
110°	440.9	440.9	443.0	439.9	440.9

TEST NUMBER: P983427

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.8	507.9	508.9	504.8	502.7
115°	568.7	573.8	574.8	570.7	564.5
117.5°	635.6	635.6	639.7	633.6	631.5
120°	697.4	696.4	699.5	697.4	692.3
122.5°	752.0	757.2	758.2	756.2	750.0
125°	808.7	815.9	815.9	811.8	808.7
127.5°	863.3	868.4	867.4	865.4	857.1
130°	912.7	917.9	918.9	915.8	910.7
132.5°	962.2	968.4	965.3	965.3	960.1
135°	1008.6	1014.7	1012.7	1010.6	1004.4
137.5°	1051.8	1058.0	1055.9	1055.9	1050.8
140°	1094.1	1096.1	1095.1	1097.2	1091.0
142.5°	1132.2	1133.2	1135.3	1135.3	1129.1
145°	1169.3	1171.3	1171.3	1172.4	1166.2
147.5°	1202.2	1202.2	1203.3	1204.3	1197.1
150°	1233.1	1231.1	1233.1	1235.2	1227.0
152.5°	1263.0	1257.9	1259.9	1262.0	1254.8
155°	1287.7	1281.6	1283.6	1286.7	1278.5
157.5°	1307.3	1304.2	1304.2	1307.3	1299.1
160°	1327.9	1321.7	1322.8	1326.9	1318.6
162.5°	1344.4	1338.2	1339.2	1345.4	1336.2
165°	1358.8	1352.6	1353.7	1359.8	1351.6
167.5°	1370.2	1364.0	1365.0	1372.2	1362.9
170°	1379.4	1372.2	1373.2	1381.5	1372.2
172.5°	1385.6	1378.4	1380.5	1387.7	1378.4
175°	1389.7	1383.5	1384.6	1392.8	1383.5
177.5°	1392.8	1386.6	1387.7	1394.9	1386.6
180°	1389.7	1389.7	1389.7	1389.7	1389.7

(END OF REPORT)