

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983428

Luminaire Tested: S125IW-B1050UB2750-4F0-XX-W2A_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983428
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1050UB2750-4F0-XX-W2A_4000K
Description: Define 5 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4228.0 lumens
Efficiency: N/A
Efficacy: 134.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983428

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P983428

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983428

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.0
90°-100°	46.7	1.1
100°-110°	310.5	7.3
110°-120°	559.1	13.2
120°-130°	717.7	17.0
130°-140°	771.9	18.3
140°-150°	724.4	17.1
150°-160°	586.0	13.9
160°-170°	379.0	9.0
170°-180°	130.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.0
90°-120°	916.3	21.7
90°-150°	3130.3	74.0
90°-180°	4226.0	100.0
0°-180°	4228.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	3
95°	58	55	16	21	21	71
105°	300	304	304	304	303	318
115°	563	568	569	565	559	558
125°	801	808	808	804	801	715
135°	998	1004	1002	1000	994	770
145°	1158	1160	1160	1161	1154	724
155°	1275	1269	1271	1274	1266	587
165°	1345	1339	1340	1346	1338	380
175°	1376	1370	1371	1379	1370	131
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P983428

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	9.2	16.3	21.4	24.5
92.5°	19.4	10.2	16.3	21.4	22.4
95°	58.1	55.1	16.3	21.4	21.4
97.5°	109.1	115.2	18.4	20.4	21.4
100°	170.3	173.4	177.4	25.5	21.4
102.5°	232.5	236.6	238.6	240.7	155.0
105°	299.8	303.9	303.9	303.9	302.9
107.5°	369.2	369.2	371.2	372.2	368.2
110°	436.5	436.5	438.5	435.5	436.5

TEST NUMBER: P983428

CATALOG NUMBER: S125IW-B1050UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	499.7	502.8	503.8	499.7	497.7
115°	562.9	568.0	569.1	565.0	558.9
117.5°	629.2	629.2	633.3	627.2	625.1
120°	690.4	689.4	692.5	690.4	685.3
122.5°	744.5	749.6	750.6	748.5	742.4
125°	800.6	807.7	807.7	803.6	800.6
127.5°	854.6	859.7	858.7	856.6	848.5
130°	903.6	908.7	909.7	906.6	901.5
132.5°	952.5	958.6	955.6	955.6	950.5
135°	998.4	1004.5	1002.5	1000.4	994.3
137.5°	1041.2	1047.4	1045.3	1045.3	1040.2
140°	1083.0	1085.1	1084.1	1086.1	1080.0
142.5°	1120.8	1121.8	1123.8	1123.8	1117.7
145°	1157.5	1159.5	1159.5	1160.6	1154.4
147.5°	1190.1	1190.1	1191.1	1192.2	1185.0
150°	1220.7	1218.7	1220.7	1222.8	1214.6
152.5°	1250.3	1245.2	1247.2	1249.3	1242.1
155°	1274.8	1268.7	1270.7	1273.8	1265.6
157.5°	1294.1	1291.1	1291.1	1294.1	1286.0
160°	1314.5	1308.4	1309.4	1313.5	1305.4
162.5°	1330.9	1324.7	1325.8	1331.9	1322.7
165°	1345.1	1339.0	1340.0	1346.2	1338.0
167.5°	1356.4	1350.2	1351.3	1358.4	1349.2
170°	1365.5	1358.4	1359.4	1367.6	1358.4
172.5°	1371.7	1364.5	1366.6	1373.7	1364.5
175°	1375.7	1369.6	1370.6	1378.8	1369.6
177.5°	1378.8	1372.7	1373.7	1380.8	1372.7
180°	1375.7	1375.7	1375.7	1375.7	1375.7

(END OF REPORT)