

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B15WFL558035D010 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14804)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15WFL558035D010 2LBD*WH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1307.4 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.81
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBD*WH

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93						
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87						
3	102	96	90	86	100	94	90	86	92	88	84	89	86	83	87	84	82	80						
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74						
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69						
6	87	78	72	68	86	77	71	67	76	71	67	74	70	66	73	69	66	64						
7	83	73	67	63	81	73	67	63	71	66	62	70	65	62	69	65	62	60						
8	79	69	63	59	77	68	63	59	67	62	58	66	61	58	65	61	58	56						
9	75	65	59	55	74	64	59	55	64	58	55	63	58	54	62	57	54	53						
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	654460
5°	631842
10°	572047
15°	501142
20°	431496
25°	366828
30°	288309
35°	200352
40°	129849
45°	77677
50°	45436
55°	25459
60°	9761
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.6	11.4
10°-20°	347.9	26.6
20°-30°	389.8	29.8
30°-40°	267.9	20.5
40°-50°	115.1	8.8
50°-60°	35.1	2.7
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.3	67.9
0°-40°	1155.2	88.4
0°-60°	1305.4	99.9
0°-90°	1307.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1307.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1690	
5°	1625	150
15°	1250	348
25°	858	390
35°	424	268
45°	142	115
55°	38	35
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBD*WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1689.6
2.5°	1671.7
5°	1625.0
7.5°	1549.6
10°	1454.4
12.5°	1353.8
15°	1249.7
17.5°	1140.2
20°	1046.8
22.5°	953.4
25°	858.3
27.5°	757.7
30°	644.6
32.5°	529.7
35°	423.7
37.5°	332.2
40°	256.8
42.5°	192.1
45°	141.8
47.5°	104.1
50°	75.4
52.5°	52.1
55°	37.7
57.5°	25.1
60°	12.6
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)