

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983441

Luminaire Tested: S125IW-B1340UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1340UB2750-4F0-XX-W2A-1_3000K
Description: Define 5 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4657.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983441

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P983441

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983441

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	110.9	2.4
100°-110°	329.5	7.1
110°-120°	558.7	12.0
120°-130°	735.5	15.8
130°-140°	824.2	17.7
140°-150°	807.9	17.3
150°-160°	678.6	14.6
160°-170°	451.1	9.7
170°-180°	157.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	999.1	21.5
90°-150°	3366.8	72.3
90°-180°	4654.0	99.9
0°-180°	4657.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	12	21	27	31	6
95°	84	87	100	109	112	88
105°	296	302	310	318	322	316
115°	559	565	567	566	565	553
125°	816	824	825	823	822	731
135°	1062	1069	1071	1071	1066	818
145°	1286	1291	1295	1295	1291	804
155°	1472	1472	1473	1478	1472	678
165°	1600	1598	1599	1604	1596	452
175°	1664	1659	1659	1666	1657	158
180°	1668	1668	1668	1668	1668	

TEST NUMBER: P983441

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.3	11.7	20.8	27.3	31.1
92.5°	38.9	45.4	57.1	66.2	68.8
95°	84.4	87.0	99.9	109.0	111.6
97.5°	129.8	131.1	149.2	157.0	158.3
100°	181.7	181.7	198.6	210.2	212.8
102.5°	237.5	244.0	250.5	263.5	267.4
105°	295.9	302.4	310.2	318.0	321.9
107.5°	359.5	366.0	372.5	376.4	376.4
110°	425.7	432.2	436.1	440.0	438.7

TEST NUMBER: P983441

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	493.2	495.8	501.0	502.3	499.7
115°	559.4	564.6	567.1	565.8	564.6
117.5°	626.8	628.1	630.7	632.0	626.8
120°	689.1	695.6	696.9	696.9	691.7
122.5°	756.6	757.9	761.8	760.5	756.6
125°	816.3	824.1	825.4	822.8	821.5
127.5°	882.5	886.4	887.7	886.4	883.8
130°	940.9	947.4	950.0	948.7	946.1
132.5°	999.3	1011.0	1009.7	1008.4	1004.5
135°	1061.6	1069.4	1070.7	1070.7	1065.5
137.5°	1120.0	1127.8	1130.4	1131.7	1125.2
140°	1175.8	1182.3	1186.2	1188.8	1182.3
142.5°	1231.6	1236.8	1242.0	1243.3	1236.8
145°	1286.1	1291.3	1295.2	1295.2	1291.3
147.5°	1336.8	1340.6	1343.2	1347.1	1336.8
150°	1387.4	1386.1	1391.3	1391.3	1388.7
152.5°	1428.9	1431.5	1432.8	1436.7	1431.5
155°	1471.7	1471.7	1473.0	1478.2	1471.7
157.5°	1510.7	1508.1	1509.4	1514.6	1505.5
160°	1544.4	1540.5	1541.8	1547.0	1540.5
162.5°	1574.3	1571.7	1571.7	1578.1	1570.4
165°	1600.2	1597.6	1598.9	1604.1	1596.3
167.5°	1623.6	1618.4	1618.4	1626.2	1618.4
170°	1641.7	1636.5	1636.5	1644.3	1635.3
172.5°	1654.7	1649.5	1649.5	1657.3	1649.5
175°	1663.8	1658.6	1658.6	1666.4	1657.3
177.5°	1670.3	1665.1	1663.8	1671.6	1662.5
180°	1667.7	1667.7	1667.7	1667.7	1667.7

(END OF REPORT)