

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983442

Luminaire Tested: S125IW-B1340UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B1340UB2750-4F0-XX-W2A-1_3500K
Description: Define 5 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4677.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983442

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983442

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983442

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	111.4	2.4
100°-110°	330.9	7.1
110°-120°	561.1	12.0
120°-130°	738.7	15.8
130°-140°	827.8	17.7
140°-150°	811.4	17.3
150°-160°	681.5	14.6
160°-170°	453.0	9.7
170°-180°	158.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	1003.4	21.5
90°-150°	3381.3	72.3
90°-180°	4674.0	99.9
0°-180°	4677.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	12	21	27	31	6
95°	85	87	100	110	112	89
105°	297	304	312	319	323	317
115°	562	567	570	568	567	556
125°	820	828	829	826	825	735
135°	1066	1074	1075	1075	1070	822
145°	1292	1297	1301	1301	1297	808
155°	1478	1478	1479	1485	1478	681
165°	1607	1604	1606	1611	1603	453
175°	1671	1666	1666	1674	1664	159
180°	1675	1675	1675	1675	1675	

TEST NUMBER: P983442

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.3	11.7	20.9	27.4	31.3
92.5°	39.1	45.6	57.3	66.5	69.1
95°	84.7	87.3	100.4	109.5	112.1
97.5°	130.3	131.6	149.9	157.7	159.0
100°	182.5	182.5	199.4	211.1	213.8
102.5°	238.5	245.0	251.6	264.6	268.5
105°	297.2	303.7	311.5	319.3	323.2
107.5°	361.0	367.6	374.1	378.0	378.0
110°	427.5	434.0	437.9	441.8	440.5

TEST NUMBER: P983442

CATALOG NUMBER: S125IW-B1340UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	497.9	503.1	504.4	501.8
115°	561.8	567.0	569.6	568.3	567.0
117.5°	629.5	630.8	633.4	634.8	629.5
120°	692.1	698.6	699.9	699.9	694.7
122.5°	759.9	761.2	765.1	763.8	759.9
125°	819.8	827.7	829.0	826.4	825.0
127.5°	886.3	890.2	891.5	890.2	887.6
130°	945.0	951.5	954.1	952.8	950.2
132.5°	1003.6	1015.3	1014.0	1012.7	1008.8
135°	1066.2	1074.0	1075.3	1075.3	1070.1
137.5°	1124.8	1132.6	1135.3	1136.6	1130.0
140°	1180.9	1187.4	1191.3	1193.9	1187.4
142.5°	1236.9	1242.1	1247.3	1248.6	1242.1
145°	1291.7	1296.9	1300.8	1300.8	1296.9
147.5°	1342.5	1346.4	1349.0	1352.9	1342.5
150°	1393.3	1392.0	1397.2	1397.2	1394.6
152.5°	1435.0	1437.6	1438.9	1442.9	1437.6
155°	1478.0	1478.0	1479.3	1484.6	1478.0
157.5°	1517.1	1514.5	1515.8	1521.1	1511.9
160°	1551.0	1547.1	1548.4	1553.6	1547.1
162.5°	1581.0	1578.4	1578.4	1584.9	1577.1
165°	1607.1	1604.5	1605.8	1611.0	1603.2
167.5°	1630.5	1625.3	1625.3	1633.1	1625.3
170°	1648.8	1643.6	1643.6	1651.4	1642.3
172.5°	1661.8	1656.6	1656.6	1664.4	1656.6
175°	1670.9	1665.7	1665.7	1673.6	1664.4
177.5°	1677.5	1672.3	1670.9	1678.8	1669.6
180°	1674.9	1674.9	1674.9	1674.9	1674.9

(END OF REPORT)