

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LSSQWM2B15WFL558035D010 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14811)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSSQWM2B15WFL558035D010 2LBDC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
WIDE FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1309.2 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106		111	108	106	104		104	103	101			101	99	98			97
2	108	103	99	95		105	101	97	94		98	95	92			95	92	90			92
3	102	96	91	87		100	94	90	86		92	88	84			89	86	83			87
4	97	89	84	79		95	88	83	79		86	81	78			84	80	77			82
5	92	83	77	73		90	82	77	73		81	76	72			79	75	71			77
6	87	78	72	68		86	77	72	67		76	71	67			74	70	66			73
7	83	73	67	63		81	73	67	63		71	66	62			70	65	62			69
8	79	69	63	59		77	68	63	59		67	62	58			66	62	58			65
9	75	65	59	55		74	65	59	55		64	58	55			63	58	55			62
10	71	62	56	52		70	61	55	52		60	55	51			59	55	51			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	625021
5°	619010
10°	574603
15°	504390
20°	434052
25°	369392
30°	292558
35°	203094
40°	129040
45°	77786
50°	44412
55°	24244
60°	2789
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.7	11.3
10°-20°	350.1	26.7
20°-30°	393.0	30.0
30°-40°	270.8	20.7
40°-50°	114.5	8.7
50°-60°	32.2	2.5
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.8	68.0
0°-40°	1161.6	88.7
0°-60°	1308.4	99.9
0°-90°	1309.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1309.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1614	
5°	1592	148
15°	1258	350
25°	864	393
35°	430	271
45°	142	114
55°	36	32
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LSSQWM2B15WFL558035D010 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1613.6
2.5°	1608.2
5°	1592.0
7.5°	1541.7
10°	1460.9
12.5°	1362.0
15°	1257.8
17.5°	1148.2
20°	1053.0
22.5°	961.3
25°	864.3
27.5°	763.7
30°	654.1
32.5°	535.5
35°	429.5
37.5°	336.0
40°	255.2
42.5°	192.3
45°	142.0
47.5°	102.4
50°	73.7
52.5°	53.9
55°	35.9
57.5°	18.0
60°	3.6
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)