Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222687

Luminaire Tested: **LSR2B15NFL259035D010 2LBDLC*MMS**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



**Test Information**

| | |
|---|---|
| Test Method: | LM-41-14 |
| Report Number: | P222687 |
| | TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155) |
| Test Lab: | INNOVATION CENTER-P2 |
| Issue Date: | 3/3/2020 |
| Manufacturer: | COOPER LIGHTING SOLUTIONS (FORMERLY EATON) |
| Product Line: | io LED |
| Catalog Number: | LSR2B15NFL259035D010 2LBDLC*MMS |
| Description: | 1500 Lumen, 2inch Portfolio LED Cylinder |
| | NARROW FLOOD OPTIC |
| | LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER |
| Light Source: | - |
| Ballast/Driver: | - |

**Summary**

| | |
|---|---|
| Lumens per Lamp: | N/A |
| Luminaire Lumens: | 1073.9 lumens |
| Efficiency: | N/A |
| Efficacy: | 75.1 lumens/watt |
| Spacing Criteria (0/90/45): | 0.39 / 0.39 / 0.35 |
| Luminous Opening: | Rectangular (W 0.17' x L: 0.17' x H: 0') |
| CIE Type: | Direct |

| | |
|---|---|
| Input Watts (W): | 14.3 |
| Input Voltage (V): | NR |
| Input Current (Ain): | NR |
| Voltage Rise (V): | NR |
| Power Factor: | NR |
| Total Harmonic Distortion (THDi): | NR |
| Frequency (hertz): | 60 |
| Stabilization Time: | NR |
| Operation Time: | NR |
| Ambient Temperature (°C): | NR |
| Test Distance: | 25 FT |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P222687
CATALOG NUMBER: LSR2B15NFL259035D010 2LBDLC*MMS

## Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P222687
CATALOG NUMBER: LSR2B15NFL259035D010 2LBDLC*MMS

## COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| RF | 20 | | | | 20 | | | | 20 | | | 20 | | | 20 | | | 20 |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| RC | 80 | | | | 70 | | | | 50 | | | 30 | | | 10 | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 115 | 113 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99 | 97 |
| 2 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99 | 98 | 98 | 97 | 96 | 95 |
| 3 | 109 | 105 | 101 | 99 | 107 | 103 | 100 | 98 | 101 | 98 | 96 | 99 | 97 | 95 | 96 | 95 | 93 | 92 |
| 4 | 106 | 101 | 97 | 95 | 104 | 100 | 97 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 95 | 93 | 91 | 90 |
| 5 | 103 | 98 | 94 | 91 | 102 | 97 | 94 | 91 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 90 | 89 | 88 |
| 6 | 101 | 95 | 91 | 89 | 99 | 94 | 91 | 88 | 93 | 90 | 88 | 92 | 89 | 87 | 91 | 88 | 87 | 86 |
| 7 | 98 | 92 | 89 | 86 | 97 | 92 | 88 | 86 | 91 | 88 | 85 | 90 | 87 | 85 | 89 | 86 | 85 | 84 |
| 8 | 96 | 90 | 86 | 84 | 95 | 90 | 86 | 84 | 89 | 86 | 83 | 88 | 85 | 83 | 87 | 85 | 83 | 82 |
| 9 | 94 | 88 | 84 | 82 | 93 | 88 | 84 | 82 | 87 | 84 | 82 | 86 | 83 | 81 | 85 | 83 | 81 | 80 |
| 10 | 92 | 86 | 82 | 80 | 91 | 86 | 82 | 80 | 85 | 82 | 80 | 84 | 82 | 80 | 84 | 81 | 79 | 79 |

## AVERAGE LUMINANCE (cd/sqm):

| | 0° |
|---|---|
| 0° | 2467781 |
| 5° | 2278557 |
| 10° | 1542292 |
| 15° | 524722 |
| 20° | 192706 |
| 25° | 102189 |
| 30° | 52509 |
| 35° | 24494 |
| 40° | 8040 |
| 45° | 4054 |
| 50° | 1928 |
| 55° | 743 |
| 60° | 852 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P222687
CATALOG NUMBER: LSR2B15NFL259035D010 2LBDLC*MMS

**ZONAL LUMENS:**

| Zone | Lumens | % Fixture |
|---|---|---|
| 0°-10° | 498.5 | 46.4 |
| 10°-20° | 419.1 | 39.0 |
| 20°-30° | 115.0 | 10.7 |
| 30°-40° | 33.5 | 3.1 |
| 40°-50° | 6.2 | 0.6 |
| 50°-60° | 1.4 | 0.1 |
| 60°-70° | 0.1 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1032.6 | 96.2 |
| 0°-40° | 1066.2 | 99.3 |
| 0°-60° | 1073.8 | 100.0 |
| 0°-90° | 1073.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1073.9 | 100.0 |

**CANDELA DISTRIBUTION:**

| | 0° | Flux |
|---|---|---|
| 0° | 6371 | |
| 5° | 5860 | 498 |
| 15° | 1308 | 419 |
| 25° | 239 | 115 |
| 35° | 52 | 34 |
| 45° | 7 | 6 |
| 55° | 1 | 1 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P222687
CATALOG NUMBER: LSR2B15NFL259035D010 2LBDLC*MMS

**CANDELA DISTRIBUTION (FULL):**

| | 0° |
|---|---|
| 0° | 6371.0 |
| 1° | 6334.0 |
| 2° | 6268.4 |
| 3° | 6174.3 |
| 4° | 6045.2 |
| 5° | 5860.1 |
| 6° | 5607.3 |
| 7° | 5291.0 |
| 8° | 4905.0 |
| 9° | 4449.0 |
| 10° | 3921.2 |
| 11° | 3342.6 |
| 12° | 2740.7 |
| 13° | 2166.3 |
| 14° | 1676.6 |
| 15° | 1308.5 |
| 17.5° | 738.3 |
| 20° | 467.5 |
| 22.5° | 333.2 |
| 25° | 239.1 |
| 27.5° | 169.2 |
| 30° | 117.4 |
| 32.5° | 82.5 |
| 35° | 51.8 |
| 37.5° | 21.2 |
| 40° | 15.9 |
| 42.5° | 11.6 |
| 45° | 7.4 |
| 47.5° | 4.2 |
| 50° | 3.2 |
| 52.5° | 2.1 |
| 55° | 1.1 |
| 57.5° | 1.1 |
| 60° | 1.1 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |

TEST NUMBER: P222687
CATALOG NUMBER: LSR2B15NFL259035D010 2LBDLC*MMS

**CANDELA DISTRIBUTION (continued):**

| | 0° |
|---|---|
| 90° | *0.0* |

Report Generated By E9808895 / USPTCWHP6082093

0°-180°

| | |
|---|---|
| 85° | *0.0* |
| 87.5° | *0.0* |

(END OF REPORT)