

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225017

Luminaire Tested: **LSRWM2B15FL409035D010 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15FL409035D010 2LBD*WMH
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1082.9 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225017

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P225017

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	106	102	100		108	104	101	98		101	98	96			98	96	94			95
3	106	100	96	93		104	99	95	92		96	93	91			94	91	89			92
4	102	95	91	87		100	94	90	87		92	89	86			90	87	85			88
5	98	91	86	82		96	90	85	82		88	84	81			87	83	81			85
6	94	87	82	78		93	86	81	78		85	81	77			83	80	77			82
7	91	83	78	75		89	82	78	74		81	77	74			80	76	74			79
8	87	79	75	71		86	79	74	71		78	74	71			77	73	71			76
9	84	76	71	68		83	76	71	68		75	71	68			74	70	68			73
10	81	73	69	65		80	73	68	65		72	68	65			72	68	65			71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	982658
5°	962382
10°	852564
15°	669968
20°	450416
25°	261690
30°	130781
35°	61661
40°	29176
45°	12764
50°	6629
55°	3714
60°	2092
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225017

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.5	20.9
10°-20°	453.1	41.8
20°-30°	286.5	26.5
30°-40°	89.6	8.3
40°-50°	20.8	1.9
50°-60°	5.5	0.5
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	966.0	89.2
0°-40°	1055.6	97.5
0°-60°	1081.9	99.9
0°-90°	1082.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1082.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2537	
5°	2475	226
15°	1671	453
25°	612	286
35°	130	90
45°	23	21
55°	6	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225017

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2536.9
2.5°	2524.5
5°	2475.1
7.5°	2358.4
10°	2167.6
12.5°	1941.1
15°	1670.7
17.5°	1375.5
20°	1092.7
22.5°	831.9
25°	612.3
27.5°	432.4
30°	292.4
32.5°	194.9
35°	130.4
37.5°	87.9
40°	57.7
42.5°	35.7
45°	23.3
47.5°	16.5
50°	11.0
52.5°	8.2
55°	5.5
57.5°	4.1
60°	2.7
62.5°	2.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)