

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983480

Luminaire Tested: S125IW-B470UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IW-B470UB2750-4F0-XX-W2A-1_2700K
Description: Define 5 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1630.0 lumens
Efficiency: N/A
Efficacy: 123.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983480

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P983480

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983480

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.1
90°-100°	38.8	2.4
100°-110°	115.3	7.1
110°-120°	195.6	12.0
120°-130°	257.4	15.8
130°-140°	288.5	17.7
140°-150°	282.8	17.3
150°-160°	237.5	14.6
160°-170°	157.9	9.7
170°-180°	55.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.1
90°-120°	349.7	21.5
90°-150°	1178.4	72.3
90°-180°	1629.0	99.9
0°-180°	1630.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	7	10	11	2
95°	30	30	35	38	39	31
105°	104	106	109	111	113	110
115°	196	198	198	198	198	194
125°	286	288	289	288	288	256
135°	372	374	375	375	373	286
145°	450	452	453	453	452	281
155°	515	515	516	517	515	237
165°	560	559	560	562	559	158
175°	582	580	580	583	580	55
180°	584	584	584	584	584	

TEST NUMBER: P983480

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.5	4.1	7.3	9.5	10.9
92.5°	13.6	15.9	20.0	23.2	24.1
95°	29.5	30.4	35.0	38.2	39.1
97.5°	45.4	45.9	52.2	55.0	55.4
100°	63.6	63.6	69.5	73.6	74.5
102.5°	83.1	85.4	87.7	92.2	93.6
105°	103.6	105.8	108.6	111.3	112.7
107.5°	125.8	128.1	130.4	131.7	131.7
110°	149.0	151.3	152.6	154.0	153.5

TEST NUMBER: P983480

CATALOG NUMBER: S125IW-B470UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	172.6	173.5	175.3	175.8	174.9
115°	195.8	197.6	198.5	198.1	197.6
117.5°	219.4	219.9	220.8	221.2	219.4
120°	241.2	243.5	243.9	243.9	242.1
122.5°	264.8	265.3	266.6	266.2	264.8
125°	285.7	288.4	288.9	288.0	287.5
127.5°	308.9	310.3	310.7	310.3	309.3
130°	329.3	331.6	332.5	332.1	331.1
132.5°	349.8	353.9	353.4	353.0	351.6
135°	371.6	374.3	374.8	374.8	372.9
137.5°	392.0	394.7	395.7	396.1	393.8
140°	411.6	413.8	415.2	416.1	413.8
142.5°	431.1	432.9	434.7	435.2	432.9
145°	450.2	452.0	453.3	453.3	452.0
147.5°	467.9	469.2	470.1	471.5	467.9
150°	485.6	485.1	487.0	487.0	486.0
152.5°	500.1	501.0	501.5	502.9	501.0
155°	515.1	515.1	515.6	517.4	515.1
157.5°	528.7	527.8	528.3	530.1	526.9
160°	540.6	539.2	539.6	541.5	539.2
162.5°	551.0	550.1	550.1	552.4	549.6
165°	560.1	559.2	559.6	561.5	558.7
167.5°	568.3	566.4	566.4	569.2	566.4
170°	574.6	572.8	572.8	575.5	572.4
172.5°	579.2	577.4	577.4	580.1	577.4
175°	582.3	580.5	580.5	583.3	580.1
177.5°	584.6	582.8	582.3	585.1	581.9
180°	583.7	583.7	583.7	583.7	583.7

(END OF REPORT)