

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224837

Luminaire Tested: **LSRWM2B15FL409035D010 2LBDL*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224837
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15FL409035D010 2LBDL*B
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1066.7 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224837

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDL*B

Luminous Intensity Polar Plot





TEST NUMBER: P224837

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDL*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	96		98	96	94		95
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85
6	94	87	82	79	93	86	82	78	85	81	78		84	80	77		82
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79
8	87	80	75	72	86	79	75	71	78	74	71		77	74	71		76
9	84	77	72	69	83	76	72	68	75	71	68		74	71	68		74
10	82	74	69	66	81	73	69	66	73	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	965150
5°	948384
10°	846034
15°	668724
20°	445882
25°	258699
30°	129484
35°	60905
40°	23816
45°	10627
50°	5002
55°	2836
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224837

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDL*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.6	21.0
10°-20°	451.4	42.3
20°-30°	283.9	26.6
30°-40°	86.8	8.1
40°-50°	17.0	1.6
50°-60°	3.8	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	958.9	89.9
0°-40°	1045.7	98.0
0°-60°	1066.6	100.0
0°-90°	1066.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1066.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2492	
5°	2439	224
15°	1668	451
25°	605	284
35°	129	87
45°	19	17
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224837

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDL*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2491.7
2.5°	2486.1
5°	2439.1
7.5°	2328.2
10°	2151.0
12.5°	1929.4
15°	1667.6
17.5°	1376.7
20°	1081.7
22.5°	829.6
25°	605.3
27.5°	426.6
30°	289.5
32.5°	195.3
35°	128.8
37.5°	78.9
40°	47.1
42.5°	30.5
45°	19.4
47.5°	12.5
50°	8.3
52.5°	5.5
55°	4.2
57.5°	2.8
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)