

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224672

Luminaire Tested: **LSRWM2B15FL409035D010 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSRWM2B15FL409035D010 2LBDLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Cylinder
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1070.3 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224672

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224672

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	106	102	99		108	104	101	98		101	98	96		98	96	94		95	94	92
3	105	100	96	93		104	99	95	92		96	93	90		94	91	89		92	90	88
4	101	95	90	87		100	94	90	86		92	88	85		90	87	85		88	86	84
5	98	91	86	82		96	90	85	82		88	84	81		86	83	80		85	82	80
6	94	86	82	78		93	86	81	78		84	80	77		83	79	77		82	79	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	76	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	968946
5°	951301
10°	845641
15°	665075
20°	442543
25°	254083
30°	128321
35°	60384
40°	24321
45°	12051
50°	6629
55°	4660
60°	4261
65°	2475
70°	3058
75°	2095
80°	3123
85°	0



TEST NUMBER: P224672

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.1	20.9
10°-20°	449.3	42.0
20°-30°	279.5	26.1
30°-40°	85.9	8.0
40°-50°	18.9	1.8
50°-60°	6.7	0.6
60°-70°	3.4	0.3
70°-80°	2.0	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.8	89.0
0°-40°	1038.8	97.1
0°-60°	1064.4	99.4
0°-90°	1070.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1070.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2502	
5°	2447	224
15°	1658	449
25°	594	280
35°	128	86
45°	22	19
55°	7	7
65°	3	3
75°	1	2
85°	0	1
90°	0	



TEST NUMBER: P224672

CATALOG NUMBER: LSRWM2B15FL409035D010 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2501.5
2.5°	2490.5
5°	2446.6
7.5°	2335.4
10°	2150.0
12.5°	1927.6
15°	1658.5
17.5°	1364.7
20°	1073.6
22.5°	814.2
25°	594.5
27.5°	418.8
30°	286.9
32.5°	193.6
35°	127.7
37.5°	76.9
40°	48.1
42.5°	33.0
45°	22.0
47.5°	15.1
50°	11.0
52.5°	9.6
55°	6.9
57.5°	5.5
60°	5.5
62.5°	4.1
65°	2.7
67.5°	2.7
70°	2.7
72.5°	2.7
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)